

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030755

Luminaire Tested: S123DIW-B1165D1535UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030755
REPORT IS A COMBINATION OF REPORTS P991006 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1165D1535UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10902.0 lumens
Efficiency: N/A
Efficacy: 96.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030755

CATALOG NUMBER: S123DIW-B1165D1535UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1030755

CATALOG NUMBER: S123DIW-B1165D1535UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43		
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36		
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35	30		
3	80	70	63	57	73	65	58	53	54	49	45	44	40	38	34	32	30	26		
4	73	62	54	49	66	57	50	45	48	43	39	39	35	32	31	28	26	22		
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	23	19		
6	62	50	42	36	56	46	39	34	38	33	29	32	27	24	25	22	20	17		
7	57	45	37	31	52	41	34	29	35	29	25	29	25	21	23	20	18	15		
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13		
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12		
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19550	19550	19550
5°	19600	18876	18848
10°	19425	18237	18050
15°	19155	17572	17181
20°	18845	16834	16318
25°	18444	16057	15398
30°	18006	15251	14429
35°	17547	14428	13467
40°	17066	13565	12519
45°	16537	12723	11530
50°	15999	11785	10537
55°	15309	10807	9531
60°	14599	9730	8461
65°	13931	8563	7344
70°	12969	7269	6041
75°	11583	5755	4690
80°	10006	4046	3317
85°	7800	2175	1662

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16537 cd/sqm

TEST NUMBER: P1030755

CATALOG NUMBER: S123DIW-B1165D1535UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	1.6
10°-20°	483.5	4.4
20°-30°	714.1	6.5
30°-40°	834.0	7.6
40°-50°	838.4	7.7
50°-60°	736.5	6.8
60°-70°	548.5	5.0
70°-80°	312.1	2.9
80°-90°	92.8	0.9
90°-100°	71.4	0.7
100°-110°	345.1	3.2
110°-120°	845.7	7.8
120°-130°	1073.6	9.8
130°-140°	1146.9	10.5
140°-150°	1072.5	9.8
150°-160°	865.1	7.9
160°-170°	558.3	5.1
170°-180°	192.4	1.8
0°-30°	1368.8	12.6
0°-40°	2202.7	20.2
0°-60°	3777.6	34.7
0°-90°	4731.1	43.4
90°-120°	1262.2	11.6
90°-150°	4555.2	41.8
90°-180°	6171.0	56.6
0°-180°	10902.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1816	1816	1816	1816	1816	
5°	1818	1810	1793	1808	1805	172
15°	1730	1724	1704	1716	1707	488
25°	1571	1562	1541	1543	1538	724
35°	1359	1349	1329	1320	1312	850
45°	1114	1107	1087	1068	1060	860
55°	845	843	823	806	798	757
65°	576	568	553	540	536	569
75°	304	298	294	286	281	325
85°	81	78	78	75	75	87
90°	2	16	36	42	45	11
95°	92	30	47	57	57	110
105°	448	465	329	63	66	475
115°	841	850	863	878	884	830
125°	1185	1197	1203	1206	1209	1059
135°	1475	1484	1490	1495	1490	1136
145°	1702	1713	1716	1719	1719	1066
155°	1875	1872	1874	1881	1872	864
165°	1978	1973	1972	1984	1973	559
175°	2024	2017	2018	2029	2017	193
180°	2024	2024	2024	2024	2024	

TEST NUMBER: P1030755

CATALOG NUMBER: S123DIW-B1165D1535UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1816.3	1816.3	1816.3	1816.3	1816.3
2.5°	1824.1	1817.9	1800.7	1816.3	1814.7
5°	1817.9	1810.0	1792.9	1808.5	1805.4
7.5°	1803.8	1796.0	1778.8	1792.9	1791.3
10°	1785.1	1777.2	1756.9	1771.0	1767.9
12.5°	1760.1	1753.8	1735.1	1744.5	1742.9
15°	1730.4	1724.1	1703.8	1716.3	1707.0
17.5°	1697.6	1689.8	1669.5	1678.9	1675.7
20°	1660.1	1650.7	1630.4	1636.7	1632.0
22.5°	1618.0	1608.6	1588.3	1593.0	1586.7
25°	1571.1	1561.7	1541.4	1543.0	1538.3
27.5°	1522.7	1513.3	1491.5	1493.0	1488.3
30°	1469.6	1461.8	1439.9	1439.9	1429.0
32.5°	1416.5	1405.6	1389.9	1379.0	1374.3
35°	1358.7	1349.3	1329.0	1319.7	1311.9
37.5°	1300.9	1288.4	1268.1	1257.2	1252.5
40°	1240.0	1230.6	1208.8	1196.3	1190.0
42.5°	1179.1	1168.2	1146.3	1133.8	1127.6
45°	1113.5	1107.3	1087.0	1068.2	1060.4
47.5°	1049.5	1040.1	1021.4	1002.6	996.4
50°	983.9	976.1	955.8	938.6	929.2
52.5°	915.2	910.5	888.6	874.6	865.2
55°	844.9	843.3	823.0	805.9	798.0
57.5°	779.3	773.1	757.4	741.8	732.5
60°	707.5	705.9	687.2	673.1	665.3
62.5°	643.4	638.7	620.0	606.0	601.3
65°	576.3	568.5	552.9	540.4	535.7
67.5°	504.4	498.2	485.7	474.8	468.5
70°	440.4	431.0	421.7	410.7	402.9
72.5°	373.3	367.0	356.1	346.7	343.6
75°	304.5	298.3	293.6	285.8	281.1
77.5°	243.6	240.5	234.3	228.0	228.0
80°	184.3	179.6	176.5	174.9	174.9
82.5°	126.5	126.5	126.5	123.4	121.8
85°	81.2	78.1	78.1	75.0	75.0
87.5°	40.6	35.9	34.4	32.8	32.8
90°	1.5	16.5	36.1	42.1	45.1
92.5°	34.6	25.6	39.1	49.6	51.1
95°	91.7	30.1	46.6	57.1	57.1
97.5°	166.9	124.8	48.1	60.2	61.7
100°	254.2	284.2	49.6	61.7	63.2
102.5°	353.4	373.0	111.3	61.7	64.7
105°	448.2	464.7	329.3	63.2	66.2
107.5°	548.9	562.4	585.0	353.4	156.4
110°	649.7	661.7	678.2	628.6	413.6

TEST NUMBER: P1030755

CATALOG NUMBER: S123DIW-B1165D1535UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	745.9	756.4	773.0	786.5	783.5
115°	840.7	849.7	863.2	878.3	884.3
117.5°	933.9	944.4	951.9	964.0	965.5
120°	1019.6	1033.2	1037.7	1049.7	1049.7
122.5°	1106.8	1117.4	1123.4	1130.9	1132.4
125°	1185.0	1197.1	1203.1	1206.1	1209.1
127.5°	1263.2	1275.3	1282.8	1287.3	1284.3
130°	1335.4	1347.5	1353.5	1359.5	1356.5
132.5°	1404.6	1416.6	1421.2	1427.2	1422.7
135°	1475.3	1484.3	1490.3	1494.8	1490.3
137.5°	1535.4	1547.5	1550.5	1558.0	1555.0
140°	1595.6	1604.6	1609.1	1615.2	1612.1
142.5°	1651.2	1660.3	1664.8	1669.3	1664.8
145°	1702.4	1712.9	1715.9	1718.9	1718.9
147.5°	1752.0	1759.5	1762.5	1765.5	1758.0
150°	1797.1	1801.6	1804.6	1807.6	1803.1
152.5°	1837.7	1839.2	1840.7	1846.7	1839.2
155°	1875.3	1872.3	1873.8	1881.3	1872.3
157.5°	1905.4	1905.4	1903.9	1912.9	1900.9
160°	1932.5	1931.0	1929.5	1938.5	1928.0
162.5°	1958.0	1953.5	1952.0	1962.5	1953.5
165°	1977.6	1973.1	1971.6	1983.6	1973.1
167.5°	1994.1	1988.1	1988.1	2000.1	1988.1
170°	2007.7	2001.6	2001.6	2013.7	2001.6
172.5°	2016.7	2009.2	2010.7	2022.7	2009.2
175°	2024.2	2016.7	2018.2	2028.7	2016.7
177.5°	2027.2	2019.7	2021.2	2033.2	2018.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2

(END OF REPORT)