

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030793

Luminaire Tested: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030793
REPORT IS A COMBINATION OF REPORTS P991194 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K
Description: Define 3 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5380.0 lumens
Efficiency: N/A
Efficacy: 120.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	28
2	84	77	71	66	75	69	64	60	54	50	47	39	37	36	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21
4	70	60	53	47	62	54	47	42	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14
7	55	43	35	30	49	39	32	27	30	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	4843	4843	4843	4843
5°	4846	5580	4860	4164
10°	4815	6753	4821	3637
15°	4749	8009	4788	3273
20°	4692	9220	4702	3013
25°	4607	9453	4617	2876
30°	4546	7809	4546	2787
35°	4471	5223	4443	2708
40°	4381	3770	4326	2587
45°	4267	2987	4143	2437
50°	3992	2537	3849	2290
55°	3689	2229	3539	2125
60°	3382	1941	3202	1952
65°	3046	1662	2898	1722
70°	2698	1379	2518	1451
75°	2305	1039	2157	1119
80°	1824	694	1683	736
85°	1258	319	1009	290

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 7810 cd/sqm

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.3	0.8
10°-20°	142.1	2.6
20°-30°	239.1	4.4
30°-40°	270.3	5.0
40°-50°	242.1	4.5
50°-60°	195.4	3.6
60°-70°	136.2	2.5
70°-80°	71.5	1.3
80°-90°	19.8	0.4
90°-100°	46.5	0.9
100°-110°	224.8	4.2
110°-120°	550.8	10.2
120°-130°	699.3	13.0
130°-140°	747.0	13.9
140°-150°	698.6	13.0
150°-160°	563.5	10.5
160°-170°	363.6	6.8
170°-180°	125.3	2.3
0°-30°	425.5	7.9
0°-40°	695.8	12.9
0°-60°	1133.2	21.1
0°-90°	1360.6	25.3
90°-120°	822.1	15.3
90°-150°	2967.0	55.1
90°-180°	4019.0	74.7
0°-180°	5380.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	450	450	450	450	450	
5°	450	534	451	399	450	43
15°	429	796	432	325	429	121
25°	392	944	393	287	392	181
35°	346	509	344	264	346	217
45°	287	275	279	224	287	220
55°	204	187	195	178	204	182
65°	126	121	120	126	126	125
75°	61	62	57	67	61	65
85°	13	14	10	13	13	15
90°	1	29	1	29	1	4
95°	60	37	60	37	60	71
105°	292	43	292	43	292	309
115°	548	576	548	576	548	541
125°	772	788	772	788	772	690
135°	961	971	961	971	961	740
145°	1109	1120	1109	1120	1109	694
155°	1222	1220	1222	1220	1222	563
165°	1288	1285	1288	1285	1288	364
175°	1318	1314	1318	1314	1318	125
180°	1318	1318	1318	1318	1318	

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	451.3	454.7	456.5	459.1	461.7	465.6	466.9	469.1	468.3	470.0	470.9
5°	449.5	455.6	460.8	467.4	473.5	477.8	482.2	489.2	494.4	495.3	499.2
7.5°	446.5	455.2	464.3	473.5	485.3	492.2	500.1	509.7	517.5	530.2	535.0
10°	442.5	454.7	467.8	480.5	496.6	507.5	517.1	533.2	549.3	562.4	574.6
12.5°	436.4	451.7	468.7	487.4	508.4	521.0	534.1	555.5	579.9	599.9	613.0
15°	429.0	448.2	470.0	490.1	513.2	536.7	550.7	574.6	609.5	628.3	661.8
17.5°	422.9	442.5	464.3	495.7	527.1	550.7	560.7	604.7	628.7	660.1	698.0
20°	413.3	438.2	466.1	497.5	538.0	552.4	572.9	617.4	647.0	688.0	734.6
22.5°	403.3	429.9	463.5	496.2	541.5	556.8	584.7	620.0	667.1	707.6	759.1
25°	392.4	421.2	455.2	494.0	538.4	560.7	586.8	630.4	681.5	732.5	780.0
27.5°	381.5	412.9	448.2	487.0	530.2	556.3	582.5	627.8	693.2	748.6	809.2
30°	371.0	402.4	437.7	477.4	522.8	548.0	572.9	629.6	702.4	764.7	825.8
32.5°	359.7	392.0	429.0	462.2	507.9	535.0	562.9	629.6	708.0	774.3	830.1
35°	346.2	379.3	411.1	444.3	489.6	519.7	551.1	625.2	713.3	777.4	811.8
37.5°	333.1	362.3	389.8	422.0	469.6	501.8	538.0	620.0	710.7	764.3	773.9
40°	318.3	347.5	369.7	399.8	449.9	487.4	524.1	613.0	699.3	733.3	705.4
42.5°	303.9	327.0	346.2	375.4	429.9	466.5	506.2	600.4	677.1	684.1	621.3
45°	287.3	303.9	320.9	354.0	408.1	445.6	489.6	582.0	641.3	621.3	541.9
47.5°	266.0	280.8	299.5	330.0	385.0	423.8	465.6	558.5	589.5	547.6	460.8
50°	245.5	258.1	275.5	305.2	360.6	398.5	443.0	521.4	536.7	470.9	397.2
52.5°	225.0	234.6	251.6	281.2	336.6	373.2	413.8	483.5	474.8	404.2	338.8
55°	203.6	211.9	228.0	257.2	308.7	343.6	382.4	436.9	414.2	347.0	294.7
57.5°	182.7	191.4	208.0	232.4	280.8	314.8	345.7	388.5	354.5	300.8	254.6
60°	163.9	171.3	184.0	208.0	252.0	279.5	307.8	337.0	308.7	256.8	221.5
62.5°	144.3	151.3	163.1	184.9	222.8	247.2	269.9	293.9	262.5	224.5	193.1
65°	126.0	131.7	142.6	162.6	193.6	213.6	231.9	248.5	223.2	188.3	164.8
67.5°	109.4	114.2	123.4	141.3	167.4	181.8	196.6	210.6	189.2	161.3	141.3
70°	91.6	95.5	103.8	116.8	137.8	152.6	163.5	174.0	154.8	132.5	119.0
72.5°	75.9	79.8	85.0	98.5	112.9	122.1	133.8	139.5	128.6	110.3	96.8
75°	60.6	63.7	68.5	77.2	90.7	96.8	104.2	108.6	98.5	86.3	78.0
77.5°	47.5	48.8	52.3	58.4	67.6	74.6	80.2	82.8	75.9	68.0	61.0
80°	33.6	35.3	37.9	43.2	50.1	52.3	55.8	58.9	54.5	47.5	43.2
82.5°	22.2	24.4	25.7	27.9	32.3	34.9	35.8	38.4	34.4	31.8	30.1
85°	13.1	14.0	14.4	15.7	17.9	19.2	20.5	20.9	20.1	19.6	17.9
87.5°	6.5	6.5	6.5	7.4	7.8	8.7	9.2	9.2	9.2	8.7	8.3
90°	1.0	3.2	5.4	7.5	9.7	10.8	12.2	15.0	17.9	20.7	23.5
92.5°	22.5	21.2	19.9	18.6	17.3	16.7	17.7	19.6	21.6	23.5	25.5
95°	59.8	50.9	41.9	33.0	24.1	19.6	20.8	23.2	25.6	28.0	30.4
97.5°	108.7	102.6	96.5	90.4	84.3	81.3	75.7	64.6	53.5	42.4	31.3
100°	165.5	169.9	174.2	178.6	182.9	185.1	168.1	134.2	100.2	66.3	32.3
102.5°	230.2	233.0	235.8	238.7	241.5	242.9	224.0	186.1	148.2	110.4	72.5
105°	291.9	294.3	296.7	299.1	301.5	302.7	292.9	273.3	253.7	234.1	214.5
107.5°	357.5	359.5	361.4	363.4	365.3	366.3	367.9	371.2	374.5	377.7	381.0
110°	423.2	424.9	426.7	428.4	430.1	431.0	432.2	434.6	437.0	439.4	441.8

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	485.8	487.3	488.9	490.4	491.9	492.7	493.9	496.3	498.7	501.1	503.5
115°	547.6	548.9	550.2	551.5	552.8	553.4	554.4	556.3	558.3	560.2	562.2
117.5°	608.3	609.8	611.3	612.8	614.3	615.1	615.6	616.7	617.8	618.9	620.0
120°	664.1	666.1	668.0	670.0	671.9	672.9	673.2	673.9	674.6	675.2	675.9
122.5°	720.9	722.4	724.0	725.5	727.0	727.8	728.2	729.1	730.0	730.8	731.7
125°	771.9	773.6	775.4	777.1	778.8	779.7	780.1	781.0	781.9	782.7	783.6
127.5°	822.8	824.5	826.3	828.0	829.7	830.6	831.1	832.2	833.3	834.4	835.5
130°	869.8	871.6	873.3	875.1	876.8	877.7	878.1	879.0	879.9	880.7	881.6
132.5°	914.9	916.6	918.4	920.1	921.8	922.7	923.0	923.7	924.3	925.0	925.6
135°	960.9	962.2	963.5	964.8	966.1	966.8	967.2	968.1	969.0	969.8	970.7
137.5°	1000.1	1001.8	1003.6	1005.3	1007.0	1007.9	1008.1	1008.6	1009.0	1009.5	1009.9
140°	1039.3	1040.6	1041.9	1043.2	1044.5	1045.2	1045.5	1046.2	1046.8	1047.5	1048.1
142.5°	1075.5	1076.8	1078.1	1079.4	1080.7	1081.4	1081.7	1082.4	1083.0	1083.7	1084.3
145°	1108.8	1110.3	1111.9	1113.4	1114.9	1115.7	1115.9	1116.3	1116.8	1117.2	1117.6
147.5°	1141.1	1142.2	1143.3	1144.4	1145.5	1146.0	1146.2	1146.7	1147.1	1147.6	1148.0
150°	1170.5	1171.2	1171.8	1172.5	1173.2	1173.5	1173.7	1174.1	1174.6	1175.0	1175.4
152.5°	1197.0	1197.2	1197.4	1197.7	1197.9	1198.0	1198.1	1198.3	1198.5	1198.7	1198.9
155°	1221.5	1221.1	1220.6	1220.2	1219.7	1219.5	1219.6	1219.8	1220.1	1220.3	1220.5
157.5°	1241.1	1241.1	1241.1	1241.1	1241.1	1241.1	1241.0	1240.8	1240.5	1240.3	1240.1
160°	1258.7	1258.5	1258.3	1258.0	1257.8	1257.7	1257.6	1257.4	1257.1	1256.9	1256.7
162.5°	1275.3	1274.7	1274.0	1273.4	1272.7	1272.4	1272.3	1272.1	1271.8	1271.6	1271.4
165°	1288.1	1287.4	1286.8	1286.1	1285.4	1285.1	1285.0	1284.8	1284.6	1284.4	1284.2
167.5°	1298.8	1297.9	1297.1	1296.2	1295.3	1294.9	1294.9	1294.9	1294.9	1294.9	1294.9
170°	1307.7	1306.8	1305.9	1305.0	1304.1	1303.7	1303.7	1303.7	1303.7	1303.7	1303.7
172.5°	1313.5	1312.4	1311.3	1310.2	1309.1	1308.6	1308.7	1308.9	1309.2	1309.4	1309.6
175°	1318.4	1317.3	1316.2	1315.1	1314.0	1313.5	1313.6	1313.8	1314.1	1314.3	1314.5
177.5°	1320.4	1319.3	1318.2	1317.1	1316.0	1315.5	1315.6	1315.8	1316.1	1316.3	1316.5
180°	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	473.9	474.8	477.8	480.0	484.4	484.0	484.0	483.5	482.2	484.4	485.7
5°	507.1	514.5	515.3	524.9	525.4	529.3	531.9	529.7	535.0	534.5	530.6
7.5°	548.0	558.1	562.9	572.0	582.5	579.9	589.9	591.6	590.8	595.1	598.2
10°	592.9	610.4	622.6	639.6	644.0	646.6	653.1	658.8	670.1	661.4	667.1
12.5°	644.4	657.0	673.2	700.2	713.7	722.4	725.5	729.4	737.3	732.5	732.9
15°	687.6	704.6	732.0	765.6	769.5	780.4	777.8	801.4	812.7	795.7	805.3
17.5°	732.5	755.1	787.8	817.0	833.6	841.0	848.0	870.7	869.8	867.2	869.4
20°	761.2	798.3	838.8	877.7	882.4	888.1	906.9	916.5	914.7	922.1	926.9
22.5°	801.8	841.0	884.2	909.9	920.8	927.4	942.2	948.3	950.9	952.6	949.6
25°	835.8	877.7	909.5	932.1	938.7	942.2	947.0	948.7	947.4	944.4	947.0
27.5°	858.9	892.5	914.3	924.7	921.2	915.6	906.4	900.3	886.8	880.3	888.1
30°	868.5	883.3	889.9	872.4	855.0	841.0	823.6	791.3	766.0	773.4	763.4
32.5°	853.2	843.6	812.3	767.3	753.8	731.2	681.9	644.0	645.3	625.2	633.5
35°	808.3	764.7	705.4	637.4	619.5	607.3	553.3	545.0	527.5	508.8	514.0
37.5°	729.0	665.3	593.4	543.2	516.6	490.1	459.5	441.2	430.8	422.9	429.0
40°	632.2	554.6	495.3	450.4	427.7	410.7	389.8	371.5	359.7	358.4	360.6
42.5°	537.1	471.7	417.2	374.5	367.1	347.0	333.5	319.1	315.7	310.0	313.0
45°	454.7	401.5	356.6	321.8	313.0	307.8	291.2	282.1	278.2	274.7	279.9
47.5°	395.0	339.2	306.5	285.6	276.9	268.1	259.0	252.9	249.8	250.3	249.8
50°	337.5	296.5	267.7	251.6	246.3	240.2	232.8	228.9	227.6	223.7	226.7
52.5°	290.4	260.7	240.7	225.4	221.5	217.1	211.0	208.8	205.8	204.9	204.9
55°	252.4	229.3	213.2	203.2	198.4	194.9	191.4	188.8	186.6	186.6	186.6
57.5°	222.8	202.7	191.0	182.2	180.5	177.0	173.1	173.1	170.0	169.6	170.9
60°	197.5	179.6	170.5	163.1	160.4	159.6	155.6	155.6	154.8	152.6	154.3
62.5°	171.8	158.7	150.9	145.2	142.6	142.6	139.5	137.3	137.3	137.8	136.9
65°	148.2	138.6	131.7	127.3	126.0	124.3	123.8	122.1	120.8	121.2	120.8
67.5°	127.3	119.9	115.1	111.6	109.4	108.6	107.3	107.3	106.4	106.8	104.6
70°	108.6	101.1	97.2	93.7	92.9	92.9	91.1	91.6	90.7	92.0	91.1
72.5°	89.4	83.7	80.7	79.4	78.5	78.0	77.2	76.3	75.9	76.7	76.3
75°	72.4	67.6	65.4	64.5	63.7	63.7	63.2	62.8	62.3	62.3	62.3
77.5°	56.2	53.2	50.6	51.4	50.1	50.6	49.3	49.3	49.7	49.3	49.3
80°	41.4	39.2	39.2	38.4	36.6	37.5	37.5	36.2	35.8	36.6	35.3
82.5°	27.5	27.0	26.2	25.7	24.9	25.3	24.9	24.4	24.0	24.9	24.0
85°	16.1	16.1	15.7	14.8	15.7	15.3	14.8	14.8	14.4	14.4	14.4
87.5°	8.3	7.4	7.4	7.0	7.4	6.5	7.0	6.5	6.1	6.5	6.1
90°	24.4	25.2	26.1	27.0	27.4	27.6	28.1	28.5	29.0	29.4	29.0
92.5°	27.0	28.5	30.0	31.5	32.3	32.4	32.6	32.9	33.1	33.3	33.1
95°	31.9	33.4	34.9	36.4	37.2	37.2	37.2	37.2	37.2	37.2	37.2
97.5°	33.1	34.8	36.6	38.3	39.2	39.3	39.5	39.8	40.0	40.2	40.0
100°	34.1	35.8	37.6	39.3	40.2	40.3	40.5	40.7	40.9	41.1	40.9
102.5°	65.3	58.1	51.0	43.8	40.2	40.4	40.8	41.3	41.7	42.1	41.7
105°	176.0	137.4	98.9	60.4	41.1	41.3	41.8	42.2	42.7	43.1	42.7
107.5°	347.5	314.0	280.5	247.0	230.2	215.9	187.4	158.9	130.4	101.9	130.4
110°	434.6	427.4	420.2	413.0	409.4	393.8	362.7	331.6	300.5	269.4	300.5

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	505.5	507.4	509.4	511.3	512.3	512.1	511.6	511.2	510.7	510.3	510.7
115°	564.4	566.6	568.7	570.9	572.0	572.4	573.3	574.2	575.1	576.0	575.1
117.5°	621.8	623.5	625.3	627.0	627.9	628.0	628.2	628.5	628.7	628.9	628.7
120°	677.6	679.4	681.1	682.8	683.7	683.7	683.7	683.7	683.7	683.7	683.7
122.5°	732.8	733.9	735.0	736.1	736.6	736.7	736.9	737.2	737.4	737.6	737.4
125°	784.0	784.5	784.9	785.4	785.6	785.8	786.2	786.7	787.1	787.5	787.1
127.5°	836.2	836.8	837.5	838.2	838.5	838.3	837.8	837.4	836.9	836.5	836.9
130°	882.5	883.3	884.2	885.1	885.5	885.3	884.8	884.4	883.9	883.5	883.9
132.5°	926.5	927.4	928.3	929.2	929.6	929.3	928.6	927.9	927.3	926.6	927.3
135°	971.3	972.0	972.6	973.3	973.6	973.3	972.6	972.0	971.3	970.7	971.3
137.5°	1011.0	1012.1	1013.2	1014.3	1014.8	1014.6	1014.1	1013.7	1013.2	1012.8	1013.2
140°	1049.0	1049.8	1050.7	1051.6	1052.0	1051.8	1051.3	1050.9	1050.4	1050.0	1050.4
142.5°	1085.0	1085.6	1086.3	1087.0	1087.3	1087.0	1086.3	1085.6	1085.0	1084.3	1085.0
145°	1118.0	1118.5	1118.9	1119.4	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6
147.5°	1148.4	1148.9	1149.3	1149.8	1150.0	1149.5	1148.4	1147.3	1146.2	1145.1	1146.2
150°	1175.8	1176.3	1176.7	1177.2	1177.4	1177.1	1176.4	1175.7	1175.1	1174.4	1175.1
152.5°	1199.8	1200.7	1201.6	1202.5	1202.9	1202.4	1201.3	1200.2	1199.1	1198.0	1199.1
155°	1221.6	1222.7	1223.8	1224.9	1225.4	1224.7	1223.4	1222.1	1220.8	1219.5	1220.8
157.5°	1241.4	1242.7	1244.0	1245.3	1246.0	1245.1	1243.4	1241.6	1239.9	1238.1	1239.9
160°	1258.0	1259.3	1260.6	1261.9	1262.6	1261.8	1260.3	1258.8	1257.2	1255.7	1257.2
162.5°	1272.9	1274.5	1276.0	1277.5	1278.3	1277.6	1276.3	1275.0	1273.7	1272.4	1273.7
165°	1285.9	1287.7	1289.4	1291.1	1292.0	1291.2	1289.7	1288.2	1286.6	1285.1	1286.6
167.5°	1296.7	1298.4	1300.2	1301.9	1302.8	1301.9	1300.2	1298.4	1296.7	1294.9	1296.7
170°	1305.5	1307.2	1309.0	1310.7	1311.6	1310.7	1309.0	1307.2	1305.5	1303.7	1305.5
172.5°	1311.4	1313.1	1314.9	1316.6	1317.5	1316.5	1314.5	1312.6	1310.6	1308.6	1310.6
175°	1316.0	1317.6	1319.1	1320.6	1321.4	1320.5	1318.8	1317.0	1315.3	1313.5	1315.3
177.5°	1318.2	1320.0	1321.7	1323.4	1324.3	1323.2	1321.0	1318.9	1316.7	1314.5	1316.7
180°	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	482.2	483.5	480.0	479.2	479.2	480.9	479.6	467.8	470.0	467.4	466.5
5°	535.4	532.8	529.3	527.5	525.4	519.3	518.8	505.3	502.7	494.0	490.1
7.5°	593.8	591.6	581.2	579.9	579.0	573.3	558.9	544.6	534.1	524.1	514.5
10°	660.5	654.0	649.2	639.6	634.8	627.0	608.2	594.7	576.8	561.6	541.5
12.5°	740.7	733.3	717.2	710.2	704.1	682.3	663.6	648.3	613.4	603.0	578.1
15°	799.6	783.9	782.2	766.9	766.0	742.1	706.3	689.7	662.7	624.3	598.6
17.5°	863.3	849.3	838.4	820.1	817.5	794.8	768.7	728.1	698.5	661.8	629.1
20°	909.9	902.5	883.8	876.3	861.1	841.9	814.9	764.7	728.5	691.9	651.8
22.5°	947.0	939.6	924.7	914.7	906.0	881.1	848.9	806.1	756.4	708.5	667.1
25°	946.5	944.4	938.3	933.5	926.9	908.6	881.6	840.6	785.2	732.5	674.9
27.5°	892.9	899.0	909.5	914.7	913.4	910.8	895.5	861.1	811.4	748.6	684.1
30°	781.3	803.5	823.2	849.3	857.2	876.3	885.1	865.4	825.8	767.3	695.8
32.5°	647.9	680.1	722.9	737.3	762.1	799.2	840.6	848.0	823.2	778.2	703.3
35°	531.5	558.1	591.2	613.9	636.1	696.3	748.6	793.9	802.2	772.6	701.5
37.5°	439.9	458.7	487.9	507.1	527.5	579.0	652.2	711.1	752.5	753.4	696.7
40°	373.6	381.9	407.2	421.2	440.8	485.3	550.7	627.4	688.0	715.9	684.1
42.5°	316.5	327.4	348.4	358.8	371.5	410.3	453.4	526.2	601.2	661.0	660.5
45°	282.5	290.4	300.0	308.7	323.1	346.2	395.4	449.9	521.9	589.5	616.1
47.5°	252.4	259.9	269.4	272.1	281.7	303.4	333.5	381.1	448.2	515.3	565.5
50°	227.2	233.3	239.8	244.6	249.0	266.8	289.5	329.6	383.2	448.2	510.5
52.5°	207.5	211.9	217.6	220.2	224.1	237.2	254.6	284.3	328.3	387.6	448.2
55°	189.2	192.3	195.8	200.1	201.9	211.5	225.0	250.3	283.0	336.1	393.7
57.5°	172.2	173.5	175.7	178.3	180.5	188.8	200.6	217.6	246.3	287.3	341.8
60°	153.0	156.5	157.8	160.4	161.8	168.3	177.4	191.8	214.1	249.4	290.4
62.5°	136.9	139.1	141.3	142.6	145.6	147.8	155.2	168.3	186.6	212.8	249.8
65°	122.5	123.4	124.7	126.0	126.9	129.5	136.5	145.2	159.1	182.2	211.0
67.5°	105.9	106.8	108.6	109.0	109.9	113.4	117.3	124.7	136.5	153.9	177.4
70°	89.8	91.1	92.0	92.9	94.2	95.5	99.8	105.9	115.1	127.3	145.6
72.5°	75.9	77.2	77.2	78.0	77.6	79.4	83.7	88.1	94.2	104.2	120.3
75°	61.9	61.9	62.8	63.2	63.7	65.4	67.1	70.6	75.4	83.3	93.3
77.5°	48.8	48.4	49.3	49.3	49.3	50.6	52.3	54.1	57.1	62.8	70.6
80°	35.8	35.8	36.6	37.1	36.2	36.6	37.5	39.2	41.4	45.3	49.7
82.5°	23.5	25.3	24.9	25.3	24.9	25.7	26.2	26.6	27.5	29.2	32.3
85°	14.4	14.4	14.4	14.8	14.4	14.8	14.8	14.8	15.3	16.1	17.4
87.5°	6.1	6.1	6.1	6.5	6.1	6.1	6.5	6.1	6.5	6.5	7.0
90°	28.5	28.1	27.6	27.4	27.0	26.1	25.2	24.4	23.5	20.7	17.9
92.5°	32.9	32.6	32.4	32.3	31.5	30.0	28.5	27.0	25.5	23.5	21.6
95°	37.2	37.2	37.2	37.2	36.4	34.9	33.4	31.9	30.4	28.0	25.6
97.5°	39.8	39.5	39.3	39.2	38.3	36.6	34.8	33.1	31.3	42.4	53.5
100°	40.7	40.5	40.3	40.2	39.3	37.6	35.8	34.1	32.3	66.3	100.2
102.5°	41.3	40.8	40.4	40.2	43.8	51.0	58.1	65.3	72.5	110.4	148.2
105°	42.2	41.8	41.3	41.1	60.4	98.9	137.4	176.0	214.5	234.1	253.7
107.5°	158.9	187.4	215.9	230.2	247.0	280.5	314.0	347.5	381.0	377.7	374.5
110°	331.6	362.7	393.8	409.4	413.0	420.2	427.4	434.6	441.8	439.4	437.0

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	511.2	511.6	512.1	512.3	511.3	509.4	507.4	505.5	503.5	501.1	498.7
115°	574.2	573.3	572.4	572.0	570.9	568.7	566.6	564.4	562.2	560.2	558.3
117.5°	628.5	628.2	628.0	627.9	627.0	625.3	623.5	621.8	620.0	618.9	617.8
120°	683.7	683.7	683.7	683.7	682.8	681.1	679.4	677.6	675.9	675.2	674.6
122.5°	737.2	736.9	736.7	736.6	736.1	735.0	733.9	732.8	731.7	730.8	730.0
125°	786.7	786.2	785.8	785.6	785.4	784.9	784.5	784.0	783.6	782.7	781.9
127.5°	837.4	837.8	838.3	838.5	838.2	837.5	836.8	836.2	835.5	834.4	833.3
130°	884.4	884.8	885.3	885.5	885.1	884.2	883.3	882.5	881.6	880.7	879.9
132.5°	927.9	928.6	929.3	929.6	929.2	928.3	927.4	926.5	925.6	925.0	924.3
135°	972.0	972.6	973.3	973.6	973.3	972.6	972.0	971.3	970.7	969.8	969.0
137.5°	1013.7	1014.1	1014.6	1014.8	1014.3	1013.2	1012.1	1011.0	1009.9	1009.5	1009.0
140°	1050.9	1051.3	1051.8	1052.0	1051.6	1050.7	1049.8	1049.0	1048.1	1047.5	1046.8
142.5°	1085.6	1086.3	1087.0	1087.3	1087.0	1086.3	1085.6	1085.0	1084.3	1083.7	1083.0
145°	1119.6	1119.6	1119.6	1119.6	1119.4	1118.9	1118.5	1118.0	1117.6	1117.2	1116.8
147.5°	1147.3	1148.4	1149.5	1150.0	1149.8	1149.3	1148.9	1148.4	1148.0	1147.6	1147.1
150°	1175.7	1176.4	1177.1	1177.4	1177.2	1176.7	1176.3	1175.8	1175.4	1175.0	1174.6
152.5°	1200.2	1201.3	1202.4	1202.9	1202.5	1201.6	1200.7	1199.8	1198.9	1198.7	1198.5
155°	1222.1	1223.4	1224.7	1225.4	1224.9	1223.8	1222.7	1221.6	1220.5	1220.3	1220.1
157.5°	1241.6	1243.4	1245.1	1246.0	1245.3	1244.0	1242.7	1241.4	1240.1	1240.3	1240.5
160°	1258.8	1260.3	1261.8	1262.6	1261.9	1260.6	1259.3	1258.0	1256.7	1256.9	1257.1
162.5°	1275.0	1276.3	1277.6	1278.3	1277.5	1276.0	1274.5	1272.9	1271.4	1271.6	1271.8
165°	1288.2	1289.7	1291.2	1292.0	1291.1	1289.4	1287.7	1285.9	1284.2	1284.4	1284.6
167.5°	1298.4	1300.2	1301.9	1302.8	1301.9	1300.2	1298.4	1296.7	1294.9	1294.9	1294.9
170°	1307.2	1309.0	1310.7	1311.6	1310.7	1309.0	1307.2	1305.5	1303.7	1303.7	1303.7
172.5°	1312.6	1314.5	1316.5	1317.5	1316.6	1314.9	1313.1	1311.4	1309.6	1309.4	1309.2
175°	1317.0	1318.8	1320.5	1321.4	1320.6	1319.1	1317.6	1316.0	1314.5	1314.3	1314.1
177.5°	1318.9	1321.0	1323.2	1324.3	1323.4	1321.7	1320.0	1318.2	1316.5	1316.3	1316.1
180°	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	462.2	460.8	460.8	460.0	457.4	452.6	452.1	453.0	450.4	447.8	443.8
5°	484.8	476.5	473.9	471.3	466.1	457.4	453.9	450.8	446.0	440.4	434.2
7.5°	504.0	492.2	488.7	484.0	473.5	461.3	453.4	446.9	440.4	432.5	425.1
10°	528.0	511.0	502.7	495.7	481.3	464.3	452.6	443.0	432.5	422.9	413.3
12.5°	555.0	527.5	524.9	507.9	491.4	466.1	451.7	437.7	423.8	412.0	402.0
15°	577.7	547.6	536.7	525.4	493.5	462.2	448.2	432.5	416.4	403.7	388.9
17.5°	592.1	567.2	544.1	528.9	495.7	467.8	440.8	422.9	405.9	388.5	376.3
20°	609.5	573.3	553.3	532.8	500.1	463.5	436.4	414.2	393.3	377.6	362.7
22.5°	627.0	578.1	561.6	539.3	501.0	459.1	428.6	406.3	382.4	366.7	350.5
25°	625.2	585.1	557.6	538.9	492.2	455.2	419.4	393.3	371.0	351.0	334.8
27.5°	626.5	577.3	549.3	527.5	486.1	449.5	409.8	382.4	359.3	338.3	321.3
30°	627.0	565.5	541.1	514.9	474.8	436.0	398.9	371.0	346.6	323.9	308.7
32.5°	625.6	555.9	525.4	501.8	456.9	422.9	386.3	356.6	331.8	310.9	296.5
35°	622.6	544.6	509.2	479.6	438.6	404.2	374.5	344.0	317.4	298.2	281.7
37.5°	614.3	532.3	492.2	463.0	417.2	382.4	356.2	330.9	305.2	282.5	268.6
40°	608.2	515.8	475.2	443.4	394.1	360.1	338.3	314.3	289.1	268.6	255.1
42.5°	594.3	500.1	457.8	419.9	371.5	336.6	316.1	296.9	275.1	255.1	242.8
45°	571.6	483.1	436.4	398.1	346.6	313.5	294.7	279.0	259.9	240.7	228.5
47.5°	539.8	458.7	413.8	375.4	322.2	288.6	269.9	258.1	242.8	226.7	216.3
50°	505.3	432.1	390.6	352.7	298.7	266.0	247.6	236.7	226.7	211.9	201.9
52.5°	460.4	403.7	364.1	327.9	273.4	242.0	225.8	218.0	207.5	197.1	188.3
55°	416.8	367.1	334.4	300.0	248.5	219.3	203.6	195.3	189.2	180.5	173.5
57.5°	366.2	333.1	303.0	271.6	225.4	198.8	184.0	174.0	170.0	166.1	159.6
60°	319.6	294.3	269.9	243.7	201.4	177.4	163.1	155.2	151.3	148.7	144.3
62.5°	276.9	257.2	236.3	215.4	177.0	155.2	144.3	136.5	133.0	132.5	128.6
65°	235.9	221.9	204.9	184.4	154.3	135.2	124.7	119.9	116.0	116.0	112.9
67.5°	194.9	185.3	171.8	157.4	133.8	116.0	106.4	102.0	99.8	99.8	97.7
70°	162.2	155.6	143.4	130.8	110.3	96.8	89.4	85.5	84.1	84.6	82.8
72.5°	131.7	124.7	114.7	105.5	90.3	80.2	75.0	70.6	68.5	68.9	68.5
75°	102.0	98.5	89.8	82.8	70.6	63.7	58.9	56.7	54.9	55.4	54.5
77.5°	76.7	71.5	66.7	61.9	54.5	48.8	44.9	42.7	41.4	41.4	41.4
80°	52.3	51.4	47.5	44.9	38.8	34.4	31.4	31.0	29.6	29.6	29.6
82.5°	34.0	31.8	29.6	27.9	24.4	21.8	20.5	19.6	19.2	18.7	19.6
85°	18.7	17.4	16.6	14.8	13.5	12.2	10.9	10.5	10.0	10.5	10.0
87.5°	7.4	6.1	6.1	5.7	5.2	4.8	4.8	3.9	3.9	3.5	3.5
90°	15.0	12.2	10.8	9.7	7.5	5.4	3.2	1.0	3.2	5.4	7.5
92.5°	19.6	17.7	16.7	17.3	18.6	19.9	21.2	22.5	21.2	19.9	18.6
95°	23.2	20.8	19.6	24.1	33.0	41.9	50.9	59.8	50.9	41.9	33.0
97.5°	64.6	75.7	81.3	84.3	90.4	96.5	102.6	108.7	102.6	96.5	90.4
100°	134.2	168.1	185.1	182.9	178.6	174.2	169.9	165.5	169.9	174.2	178.6
102.5°	186.1	224.0	242.9	241.5	238.7	235.8	233.0	230.2	233.0	235.8	238.7
105°	273.3	292.9	302.7	301.5	299.1	296.7	294.3	291.9	294.3	296.7	299.1
107.5°	371.2	367.9	366.3	365.3	363.4	361.4	359.5	357.5	359.5	361.4	363.4
110°	434.6	432.2	431.0	430.1	428.4	426.7	424.9	423.2	424.9	426.7	428.4

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	496.3	493.9	492.7	491.9	490.4	488.9	487.3	485.8	487.3	488.9	490.4
115°	556.3	554.4	553.4	552.8	551.5	550.2	548.9	547.6	548.9	550.2	551.5
117.5°	616.7	615.6	615.1	614.3	612.8	611.3	609.8	608.3	609.8	611.3	612.8
120°	673.9	673.2	672.9	671.9	670.0	668.0	666.1	664.1	666.1	668.0	670.0
122.5°	729.1	728.2	727.8	727.0	725.5	724.0	722.4	720.9	722.4	724.0	725.5
125°	781.0	780.1	779.7	778.8	777.1	775.4	773.6	771.9	773.6	775.4	777.1
127.5°	832.2	831.1	830.6	829.7	828.0	826.3	824.5	822.8	824.5	826.3	828.0
130°	879.0	878.1	877.7	876.8	875.1	873.3	871.6	869.8	871.6	873.3	875.1
132.5°	923.7	923.0	922.7	921.8	920.1	918.4	916.6	914.9	916.6	918.4	920.1
135°	968.1	967.2	966.8	966.1	964.8	963.5	962.2	960.9	962.2	963.5	964.8
137.5°	1008.6	1008.1	1007.9	1007.0	1005.3	1003.6	1001.8	1000.1	1001.8	1003.6	1005.3
140°	1046.2	1045.5	1045.2	1044.5	1043.2	1041.9	1040.6	1039.3	1040.6	1041.9	1043.2
142.5°	1082.4	1081.7	1081.4	1080.7	1079.4	1078.1	1076.8	1075.5	1076.8	1078.1	1079.4
145°	1116.3	1115.9	1115.7	1114.9	1113.4	1111.9	1110.3	1108.8	1110.3	1111.9	1113.4
147.5°	1146.7	1146.2	1146.0	1145.5	1144.4	1143.3	1142.2	1141.1	1142.2	1143.3	1144.4
150°	1174.1	1173.7	1173.5	1173.2	1172.5	1171.8	1171.2	1170.5	1171.2	1171.8	1172.5
152.5°	1198.3	1198.1	1198.0	1197.9	1197.7	1197.4	1197.2	1197.0	1197.2	1197.4	1197.7
155°	1219.8	1219.6	1219.5	1219.7	1220.2	1220.6	1221.1	1221.5	1221.1	1220.6	1220.2
157.5°	1240.8	1241.0	1241.1	1241.1	1241.1	1241.1	1241.1	1241.1	1241.1	1241.1	1241.1
160°	1257.4	1257.6	1257.7	1257.8	1258.0	1258.3	1258.5	1258.7	1258.5	1258.3	1258.0
162.5°	1272.1	1272.3	1272.4	1272.7	1273.4	1274.0	1274.7	1275.3	1274.7	1274.0	1273.4
165°	1284.8	1285.0	1285.1	1285.4	1286.1	1286.8	1287.4	1288.1	1287.4	1286.8	1286.1
167.5°	1294.9	1294.9	1294.9	1295.3	1296.2	1297.1	1297.9	1298.8	1297.9	1297.1	1296.2
170°	1303.7	1303.7	1303.7	1304.1	1305.0	1305.9	1306.8	1307.7	1306.8	1305.9	1305.0
172.5°	1308.9	1308.7	1308.6	1309.1	1310.2	1311.3	1312.4	1313.5	1312.4	1311.3	1310.2
175°	1313.8	1313.6	1313.5	1314.0	1315.1	1316.2	1317.3	1318.4	1317.3	1316.2	1315.1
177.5°	1315.8	1315.6	1315.5	1316.0	1317.1	1318.2	1319.3	1320.4	1319.3	1318.2	1317.1
180°	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	443.0	442.5	443.4	440.8	436.4	434.2	428.1	426.8	426.4	426.8	427.3
5°	430.8	430.3	429.0	424.7	419.4	415.5	408.1	407.7	405.0	402.4	403.7
7.5°	419.0	417.2	414.6	409.0	402.0	397.6	391.5	387.2	383.7	381.5	379.7
10°	407.2	404.6	402.0	394.6	385.9	379.3	371.9	368.4	364.5	362.7	361.0
12.5°	392.0	389.3	384.5	375.8	370.6	362.3	354.9	351.4	349.2	345.7	343.6
15°	379.7	374.5	371.9	362.7	351.8	351.0	337.5	336.6	332.2	332.2	328.7
17.5°	365.8	361.9	357.1	347.9	340.1	332.2	325.2	322.6	318.7	317.8	316.1
20°	352.3	347.0	345.3	336.1	327.9	318.3	310.9	308.2	306.5	304.8	306.1
22.5°	338.3	334.0	329.6	321.3	315.2	305.6	301.3	298.7	296.0	295.2	295.6
25°	324.8	320.9	316.5	308.2	301.7	293.9	289.9	288.6	287.3	287.3	286.9
27.5°	311.7	307.8	303.9	296.5	289.9	284.3	281.2	279.9	278.6	279.5	280.3
30°	298.2	294.7	291.2	284.7	279.5	274.2	272.5	271.6	271.2	273.4	273.4
32.5°	286.0	283.0	280.3	274.2	269.0	264.6	263.3	263.8	264.2	265.5	266.4
35°	273.4	271.2	268.6	263.3	259.0	255.1	255.5	255.5	256.4	258.5	260.3
37.5°	262.0	259.0	256.8	252.4	249.0	245.5	246.8	248.1	249.0	251.6	252.4
40°	248.5	247.2	245.5	241.1	238.1	237.6	238.1	238.9	240.7	242.0	243.3
42.5°	237.6	235.9	233.7	230.2	227.6	228.0	228.5	229.3	230.2	232.4	233.7
45°	225.4	224.1	222.4	219.3	217.1	217.6	218.0	218.0	218.9	221.5	222.4
47.5°	211.9	212.3	210.1	207.1	205.8	205.8	205.8	206.7	208.8	209.7	210.1
50°	198.8	197.9	197.5	194.5	193.6	193.1	193.6	194.0	197.1	196.6	197.9
52.5°	184.9	184.9	184.4	182.7	181.4	181.4	180.5	182.7	183.6	184.4	185.7
55°	171.3	170.0	169.6	168.7	167.0	166.5	167.4	170.0	170.9	171.8	173.1
57.5°	156.5	156.5	155.6	154.3	154.3	154.3	154.3	156.1	157.4	158.3	160.9
60°	143.0	141.3	140.0	140.0	140.0	139.5	142.1	142.1	144.7	145.2	146.1
62.5°	126.9	126.0	125.1	125.6	125.1	126.0	126.9	128.6	129.1	130.4	131.7
65°	111.6	111.6	110.7	113.4	111.6	111.6	113.8	113.8	114.7	116.0	117.7
67.5°	96.8	97.2	96.4	96.4	97.2	97.7	98.1	99.8	100.3	102.0	104.2
70°	81.5	82.4	82.8	82.0	82.8	83.7	84.6	85.0	86.8	87.6	88.9
72.5°	68.0	68.9	67.6	68.0	68.5	69.3	69.8	70.6	71.5	74.1	75.0
75°	54.5	54.1	53.6	55.4	54.5	56.2	56.7	56.7	57.6	59.7	60.6
77.5°	41.9	41.9	42.3	41.4	42.7	42.3	42.7	44.0	45.3	45.3	48.8
80°	29.2	30.1	30.1	30.1	30.5	31.0	30.1	32.3	32.7	32.7	34.0
82.5°	18.7	19.2	18.7	19.6	19.6	20.5	20.1	20.5	21.4	22.2	22.7
85°	10.0	10.0	10.9	10.9	10.5	10.9	10.5	10.9	11.8	11.8	12.2
87.5°	3.5	3.5	3.5	3.5	3.9	3.5	3.9	3.9	3.5	3.5	4.8
90°	9.7	10.8	12.2	15.0	17.9	20.7	23.5	24.4	25.2	26.1	27.0
92.5°	17.3	16.7	17.7	19.6	21.6	23.5	25.5	27.0	28.5	30.0	31.5
95°	24.1	19.6	20.8	23.2	25.6	28.0	30.4	31.9	33.4	34.9	36.4
97.5°	84.3	81.3	75.7	64.6	53.5	42.4	31.3	33.1	34.8	36.6	38.3
100°	182.9	185.1	168.1	134.2	100.2	66.3	32.3	34.1	35.8	37.6	39.3
102.5°	241.5	242.9	224.0	186.1	148.2	110.4	72.5	65.3	58.1	51.0	43.8
105°	301.5	302.7	292.9	273.3	253.7	234.1	214.5	176.0	137.4	98.9	60.4
107.5°	365.3	366.3	367.9	371.2	374.5	377.7	381.0	347.5	314.0	280.5	247.0
110°	430.1	431.0	432.2	434.6	437.0	439.4	441.8	434.6	427.4	420.2	413.0

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	491.9	492.7	493.9	496.3	498.7	501.1	503.5	505.5	507.4	509.4	511.3
115°	552.8	553.4	554.4	556.3	558.3	560.2	562.2	564.4	566.6	568.7	570.9
117.5°	614.3	615.1	615.6	616.7	617.8	618.9	620.0	621.8	623.5	625.3	627.0
120°	671.9	672.9	673.2	673.9	674.6	675.2	675.9	677.6	679.4	681.1	682.8
122.5°	727.0	727.8	728.2	729.1	730.0	730.8	731.7	732.8	733.9	735.0	736.1
125°	778.8	779.7	780.1	781.0	781.9	782.7	783.6	784.0	784.5	784.9	785.4
127.5°	829.7	830.6	831.1	832.2	833.3	834.4	835.5	836.2	836.8	837.5	838.2
130°	876.8	877.7	878.1	879.0	879.9	880.7	881.6	882.5	883.3	884.2	885.1
132.5°	921.8	922.7	923.0	923.7	924.3	925.0	925.6	926.5	927.4	928.3	929.2
135°	966.1	966.8	967.2	968.1	969.0	969.8	970.7	971.3	972.0	972.6	973.3
137.5°	1007.0	1007.9	1008.1	1008.6	1009.0	1009.5	1009.9	1011.0	1012.1	1013.2	1014.3
140°	1044.5	1045.2	1045.5	1046.2	1046.8	1047.5	1048.1	1049.0	1049.8	1050.7	1051.6
142.5°	1080.7	1081.4	1081.7	1082.4	1083.0	1083.7	1084.3	1085.0	1085.6	1086.3	1087.0
145°	1114.9	1115.7	1115.9	1116.3	1116.8	1117.2	1117.6	1118.0	1118.5	1118.9	1119.4
147.5°	1145.5	1146.0	1146.2	1146.7	1147.1	1147.6	1148.0	1148.4	1148.9	1149.3	1149.8
150°	1173.2	1173.5	1173.7	1174.1	1174.6	1175.0	1175.4	1175.8	1176.3	1176.7	1177.2
152.5°	1197.9	1198.0	1198.1	1198.3	1198.5	1198.7	1198.9	1199.8	1200.7	1201.6	1202.5
155°	1219.7	1219.5	1219.6	1219.8	1220.1	1220.3	1220.5	1221.6	1222.7	1223.8	1224.9
157.5°	1241.1	1241.1	1241.0	1240.8	1240.5	1240.3	1240.1	1241.4	1242.7	1244.0	1245.3
160°	1257.8	1257.7	1257.6	1257.4	1257.1	1256.9	1256.7	1258.0	1259.3	1260.6	1261.9
162.5°	1272.7	1272.4	1272.3	1272.1	1271.8	1271.6	1271.4	1272.9	1274.5	1276.0	1277.5
165°	1285.4	1285.1	1285.0	1284.8	1284.6	1284.4	1284.2	1285.9	1287.7	1289.4	1291.1
167.5°	1295.3	1294.9	1294.9	1294.9	1294.9	1294.9	1294.9	1296.7	1298.4	1300.2	1301.9
170°	1304.1	1303.7	1303.7	1303.7	1303.7	1303.7	1303.7	1305.5	1307.2	1309.0	1310.7
172.5°	1309.1	1308.6	1308.7	1308.9	1309.2	1309.4	1309.6	1311.4	1313.1	1314.9	1316.6
175°	1314.0	1313.5	1313.6	1313.8	1314.1	1314.3	1314.5	1316.0	1317.6	1319.1	1320.6
177.5°	1316.0	1315.5	1315.6	1315.8	1316.1	1316.3	1316.5	1318.2	1320.0	1321.7	1323.4
180°	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	426.8	427.3	425.5	424.2	427.7	425.5	425.5	426.0	425.1	426.4	426.0
5°	402.9	403.3	400.2	401.1	399.4	398.9	398.5	401.1	400.7	400.2	401.1
7.5°	379.3	379.3	378.0	377.1	377.1	375.8	377.6	377.1	378.0	378.0	379.3
10°	359.7	360.6	358.4	356.2	355.8	356.2	356.2	356.6	357.1	360.1	359.7
12.5°	343.6	342.3	341.8	340.5	338.3	337.5	336.6	341.4	340.1	340.1	340.1
15°	325.7	328.7	328.3	324.4	323.5	325.2	324.4	324.4	328.7	328.3	327.9
17.5°	316.1	315.2	314.3	312.2	312.6	312.2	312.6	312.6	315.2	315.2	315.2
20°	305.2	303.4	303.4	302.6	302.6	301.3	303.0	303.4	305.2	305.2	305.6
22.5°	295.6	294.3	294.3	293.9	294.7	293.0	294.7	295.2	295.2	296.5	296.5
25°	287.3	286.4	286.4	287.3	287.3	287.3	287.3	289.1	287.8	288.2	287.8
27.5°	279.9	280.3	280.8	281.2	280.8	281.2	281.7	282.5	283.0	282.5	281.7
30°	272.9	274.2	274.7	274.7	275.5	276.0	276.4	276.4	276.9	275.5	276.4
32.5°	267.7	267.7	268.6	269.0	269.9	270.3	270.3	271.2	270.8	269.4	269.9
35°	260.3	260.3	262.0	262.9	264.2	263.8	264.2	264.2	264.6	263.8	262.5
37.5°	252.9	253.7	253.7	255.5	255.9	256.4	255.9	256.8	256.4	255.5	255.1
40°	244.2	243.7	244.2	245.5	245.9	245.9	245.9	246.8	246.8	246.8	246.3
42.5°	233.3	234.6	234.1	235.4	235.0	235.0	235.9	236.7	237.2	235.9	236.3
45°	222.8	222.8	223.7	223.7	224.1	224.1	225.8	225.0	225.8	225.0	225.4
47.5°	211.5	211.9	211.9	212.3	213.2	214.1	213.2	213.6	213.6	214.1	213.2
50°	198.8	198.8	199.7	201.0	202.7	201.9	201.4	203.2	201.9	201.9	201.0
52.5°	185.7	187.0	187.5	188.8	190.1	190.5	191.0	190.1	190.5	189.2	189.7
55°	173.1	173.5	175.3	176.6	177.9	177.9	177.4	177.9	178.3	176.6	176.6
57.5°	160.4	161.8	163.5	163.5	165.2	165.2	164.8	164.8	165.2	163.9	163.5
60°	146.9	148.2	150.4	150.4	153.0	153.5	152.6	151.7	151.7	150.4	150.9
62.5°	132.5	133.8	135.2	137.3	139.1	138.2	140.0	138.2	138.6	136.0	136.0
65°	119.9	120.3	122.5	124.7	124.7	125.6	124.7	125.1	123.8	123.8	122.1
67.5°	105.1	105.1	107.3	109.4	111.6	111.6	111.6	110.3	110.3	109.0	109.0
70°	92.0	91.6	93.7	95.0	96.4	96.8	95.9	95.5	94.6	93.3	92.9
72.5°	75.9	76.7	78.9	79.8	82.0	81.5	83.7	81.1	81.1	78.9	78.5
75°	61.5	62.3	64.5	65.8	67.1	67.1	68.5	67.1	65.4	64.5	64.1
77.5°	48.8	48.4	50.1	52.3	52.8	52.3	53.2	52.8	51.0	51.0	50.1
80°	34.9	36.2	37.9	37.5	39.2	38.8	38.8	37.9	37.9	36.6	37.5
82.5°	23.1	24.4	24.9	24.4	24.9	25.7	26.2	25.7	25.7	24.9	25.3
85°	12.2	12.2	13.1	13.5	13.1	13.1	13.5	14.8	14.0	13.1	14.0
87.5°	3.9	3.5	3.5	3.9	3.5	3.5	3.9	3.9	4.4	4.4	4.4
90°	27.4	27.6	28.1	28.5	29.0	29.4	29.0	28.5	28.1	27.6	27.4
92.5°	32.3	32.4	32.6	32.9	33.1	33.3	33.1	32.9	32.6	32.4	32.3
95°	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2	37.2
97.5°	39.2	39.3	39.5	39.8	40.0	40.2	40.0	39.8	39.5	39.3	39.2
100°	40.2	40.3	40.5	40.7	40.9	41.1	40.9	40.7	40.5	40.3	40.2
102.5°	40.2	40.4	40.8	41.3	41.7	42.1	41.7	41.3	40.8	40.4	40.2
105°	41.1	41.3	41.8	42.2	42.7	43.1	42.7	42.2	41.8	41.3	41.1
107.5°	230.2	215.9	187.4	158.9	130.4	101.9	130.4	158.9	187.4	215.9	230.2
110°	409.4	393.8	362.7	331.6	300.5	269.4	300.5	331.6	362.7	393.8	409.4

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	512.3	512.1	511.6	511.2	510.7	510.3	510.7	511.2	511.6	512.1	512.3
115°	572.0	572.4	573.3	574.2	575.1	576.0	575.1	574.2	573.3	572.4	572.0
117.5°	627.9	628.0	628.2	628.5	628.7	628.9	628.7	628.5	628.2	628.0	627.9
120°	683.7	683.7	683.7	683.7	683.7	683.7	683.7	683.7	683.7	683.7	683.7
122.5°	736.6	736.7	736.9	737.2	737.4	737.6	737.4	737.2	736.9	736.7	736.6
125°	785.6	785.8	786.2	786.7	787.1	787.5	787.1	786.7	786.2	785.8	785.6
127.5°	838.5	838.3	837.8	837.4	836.9	836.5	836.9	837.4	837.8	838.3	838.5
130°	885.5	885.3	884.8	884.4	883.9	883.5	883.9	884.4	884.8	885.3	885.5
132.5°	929.6	929.3	928.6	927.9	927.3	926.6	927.3	927.9	928.6	929.3	929.6
135°	973.6	973.3	972.6	972.0	971.3	970.7	971.3	972.0	972.6	973.3	973.6
137.5°	1014.8	1014.6	1014.1	1013.7	1013.2	1012.8	1013.2	1013.7	1014.1	1014.6	1014.8
140°	1052.0	1051.8	1051.3	1050.9	1050.4	1050.0	1050.4	1050.9	1051.3	1051.8	1052.0
142.5°	1087.3	1087.0	1086.3	1085.6	1085.0	1084.3	1085.0	1085.6	1086.3	1087.0	1087.3
145°	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6	1119.6
147.5°	1150.0	1149.5	1148.4	1147.3	1146.2	1145.1	1146.2	1147.3	1148.4	1149.5	1150.0
150°	1177.4	1177.1	1176.4	1175.7	1175.1	1174.4	1175.1	1175.7	1176.4	1177.1	1177.4
152.5°	1202.9	1202.4	1201.3	1200.2	1199.1	1198.0	1199.1	1200.2	1201.3	1202.4	1202.9
155°	1225.4	1224.7	1223.4	1222.1	1220.8	1219.5	1220.8	1222.1	1223.4	1224.7	1225.4
157.5°	1246.0	1245.1	1243.4	1241.6	1239.9	1238.1	1239.9	1241.6	1243.4	1245.1	1246.0
160°	1262.6	1261.8	1260.3	1258.8	1257.2	1255.7	1257.2	1258.8	1260.3	1261.8	1262.6
162.5°	1278.3	1277.6	1276.3	1275.0	1273.7	1272.4	1273.7	1275.0	1276.3	1277.6	1278.3
165°	1292.0	1291.2	1289.7	1288.2	1286.6	1285.1	1286.6	1288.2	1289.7	1291.2	1292.0
167.5°	1302.8	1301.9	1300.2	1298.4	1296.7	1294.9	1296.7	1298.4	1300.2	1301.9	1302.8
170°	1311.6	1310.7	1309.0	1307.2	1305.5	1303.7	1305.5	1307.2	1309.0	1310.7	1311.6
172.5°	1317.5	1316.5	1314.5	1312.6	1310.6	1308.6	1310.6	1312.6	1314.5	1316.5	1317.5
175°	1321.4	1320.5	1318.8	1317.0	1315.3	1313.5	1315.3	1317.0	1318.8	1320.5	1321.4
177.5°	1324.3	1323.2	1321.0	1318.9	1316.7	1314.5	1316.7	1318.9	1321.0	1323.2	1324.3
180°	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9	449.9
2.5°	427.3	428.1	428.6	426.8	425.5	427.7	430.8	432.9	434.7	436.9	438.2
5°	402.0	405.0	405.0	405.9	407.2	409.4	415.1	419.0	422.5	425.1	427.3
7.5°	380.6	382.8	384.1	386.3	388.5	391.5	398.1	403.7	409.0	412.0	415.5
10°	361.4	363.2	365.4	366.7	370.6	375.0	383.2	388.0	394.1	398.9	403.3
12.5°	343.1	349.2	350.5	350.1	353.6	358.4	366.7	374.1	380.6	385.4	390.2
15°	330.0	332.2	334.8	334.4	341.8	343.1	350.1	358.8	367.5	370.6	375.0
17.5°	315.7	319.1	321.8	323.1	325.2	330.0	336.6	343.1	354.5	354.9	366.2
20°	304.3	307.8	309.6	311.3	312.6	318.3	323.9	331.4	340.5	345.3	351.4
22.5°	296.9	298.7	300.0	301.3	303.0	306.1	313.0	321.3	327.4	332.7	336.6
25°	288.2	289.9	291.7	292.6	293.9	295.6	300.8	307.4	316.1	319.6	323.5
27.5°	282.1	282.1	283.0	283.0	284.7	286.4	290.4	296.5	303.4	307.8	313.0
30°	275.5	275.1	275.5	275.1	274.7	277.3	280.8	286.0	290.8	296.0	299.5
32.5°	269.0	268.6	268.6	269.0	267.3	268.6	270.3	275.1	280.3	283.0	286.9
35°	262.0	261.2	261.2	261.2	260.3	259.4	261.2	265.5	269.0	272.5	275.5
37.5°	255.1	253.7	253.7	252.9	252.0	250.7	250.7	254.2	259.0	260.3	264.2
40°	245.5	245.5	244.6	244.2	243.3	242.4	241.1	244.2	248.5	249.8	252.9
42.5°	235.9	234.6	234.1	234.1	234.1	232.8	231.9	234.1	236.7	238.9	240.7
45°	225.0	224.1	224.5	224.1	223.2	222.8	222.4	223.2	226.3	227.2	229.3
47.5°	213.2	212.8	212.8	212.3	211.9	212.3	210.6	212.8	213.6	214.5	216.3
50°	201.0	200.6	200.1	199.7	199.7	200.1	199.7	199.7	201.4	202.3	204.0
52.5°	188.8	187.5	187.5	187.0	187.0	186.2	187.0	187.5	188.3	189.2	190.1
55°	175.7	175.7	174.4	174.4	173.5	173.5	174.0	173.5	175.3	176.1	176.1
57.5°	163.1	161.3	161.8	160.9	160.0	159.6	159.6	160.4	161.3	161.3	162.2
60°	149.5	147.8	147.4	145.6	146.5	145.2	145.6	145.6	147.4	146.5	147.4
62.5°	136.0	133.8	132.5	131.7	131.7	132.1	131.2	130.8	131.7	132.5	134.3
65°	121.6	120.3	119.0	117.7	117.7	117.3	118.2	116.8	116.4	116.8	117.7
67.5°	106.8	105.5	104.2	102.9	103.3	102.0	101.1	102.5	101.6	102.0	102.9
70°	92.4	91.6	88.9	88.1	87.6	88.1	87.6	86.8	88.1	87.6	88.1
72.5°	78.0	77.2	75.9	73.7	73.7	73.2	72.8	72.8	72.4	72.4	72.4
75°	64.1	62.3	61.0	60.6	59.7	59.3	58.9	58.0	58.4	58.9	58.0
77.5°	49.7	47.5	47.1	47.1	45.8	45.8	46.2	45.8	45.3	45.3	45.3
80°	36.6	34.9	34.9	34.0	33.1	33.1	33.1	33.1	32.7	32.3	32.7
82.5°	23.5	23.1	22.7	22.7	23.5	21.8	22.7	22.2	21.8	21.8	21.4
85°	13.1	13.5	13.1	13.5	12.6	13.1	13.1	13.1	12.6	13.1	12.2
87.5°	4.8	4.8	4.8	5.2	5.2	5.2	5.2	5.2	5.7	5.2	5.2
90°	27.0	26.1	25.2	24.4	23.5	20.7	17.9	15.0	12.2	10.8	9.7
92.5°	31.5	30.0	28.5	27.0	25.5	23.5	21.6	19.6	17.7	16.7	17.3
95°	36.4	34.9	33.4	31.9	30.4	28.0	25.6	23.2	20.8	19.6	24.1
97.5°	38.3	36.6	34.8	33.1	31.3	42.4	53.5	64.6	75.7	81.3	84.3
100°	39.3	37.6	35.8	34.1	32.3	66.3	100.2	134.2	168.1	185.1	182.9
102.5°	43.8	51.0	58.1	65.3	72.5	110.4	148.2	186.1	224.0	242.9	241.5
105°	60.4	98.9	137.4	176.0	214.5	234.1	253.7	273.3	292.9	302.7	301.5
107.5°	247.0	280.5	314.0	347.5	381.0	377.7	374.5	371.2	367.9	366.3	365.3
110°	413.0	420.2	427.4	434.6	441.8	439.4	437.0	434.6	432.2	431.0	430.1

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	511.3	509.4	507.4	505.5	503.5	501.1	498.7	496.3	493.9	492.7	491.9
115°	570.9	568.7	566.6	564.4	562.2	560.2	558.3	556.3	554.4	553.4	552.8
117.5°	627.0	625.3	623.5	621.8	620.0	618.9	617.8	616.7	615.6	615.1	614.3
120°	682.8	681.1	679.4	677.6	675.9	675.2	674.6	673.9	673.2	672.9	671.9
122.5°	736.1	735.0	733.9	732.8	731.7	730.8	730.0	729.1	728.2	727.8	727.0
125°	785.4	784.9	784.5	784.0	783.6	782.7	781.9	781.0	780.1	779.7	778.8
127.5°	838.2	837.5	836.8	836.2	835.5	834.4	833.3	832.2	831.1	830.6	829.7
130°	885.1	884.2	883.3	882.5	881.6	880.7	879.9	879.0	878.1	877.7	876.8
132.5°	929.2	928.3	927.4	926.5	925.6	925.0	924.3	923.7	923.0	922.7	921.8
135°	973.3	972.6	972.0	971.3	970.7	969.8	969.0	968.1	967.2	966.8	966.1
137.5°	1014.3	1013.2	1012.1	1011.0	1009.9	1009.5	1009.0	1008.6	1008.1	1007.9	1007.0
140°	1051.6	1050.7	1049.8	1049.0	1048.1	1047.5	1046.8	1046.2	1045.5	1045.2	1044.5
142.5°	1087.0	1086.3	1085.6	1085.0	1084.3	1083.7	1083.0	1082.4	1081.7	1081.4	1080.7
145°	1119.4	1118.9	1118.5	1118.0	1117.6	1117.2	1116.8	1116.3	1115.9	1115.7	1114.9
147.5°	1149.8	1149.3	1148.9	1148.4	1148.0	1147.6	1147.1	1146.7	1146.2	1146.0	1145.5
150°	1177.2	1176.7	1176.3	1175.8	1175.4	1175.0	1174.6	1174.1	1173.7	1173.5	1173.2
152.5°	1202.5	1201.6	1200.7	1199.8	1198.9	1198.7	1198.5	1198.3	1198.1	1198.0	1197.9
155°	1224.9	1223.8	1222.7	1221.6	1220.5	1220.3	1220.1	1219.8	1219.6	1219.5	1219.7
157.5°	1245.3	1244.0	1242.7	1241.4	1240.1	1240.3	1240.5	1240.8	1241.0	1241.1	1241.1
160°	1261.9	1260.6	1259.3	1258.0	1256.7	1256.9	1257.1	1257.4	1257.6	1257.7	1257.8
162.5°	1277.5	1276.0	1274.5	1272.9	1271.4	1271.6	1271.8	1272.1	1272.3	1272.4	1272.7
165°	1291.1	1289.4	1287.7	1285.9	1284.2	1284.4	1284.6	1284.8	1285.0	1285.1	1285.4
167.5°	1301.9	1300.2	1298.4	1296.7	1294.9	1294.9	1294.9	1294.9	1294.9	1294.9	1295.3
170°	1310.7	1309.0	1307.2	1305.5	1303.7	1303.7	1303.7	1303.7	1303.7	1303.7	1304.1
172.5°	1316.6	1314.9	1313.1	1311.4	1309.6	1309.4	1309.2	1308.9	1308.7	1308.6	1309.1
175°	1320.6	1319.1	1317.6	1316.0	1314.5	1314.3	1314.1	1313.8	1313.6	1313.5	1314.0
177.5°	1323.4	1321.7	1320.0	1318.2	1316.5	1316.3	1316.1	1315.8	1315.6	1315.5	1316.0
180°	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4	1318.4

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	449.9	449.9	449.9	449.9
2.5°	440.4	441.7	446.0	451.3
5°	431.6	435.1	441.2	449.5
7.5°	422.0	427.3	436.0	446.5
10°	411.1	418.6	429.5	442.5
12.5°	399.4	409.0	422.9	436.4
15°	392.0	401.5	414.2	429.0
17.5°	377.6	388.9	402.0	422.9
20°	362.7	375.4	392.4	413.3
22.5°	351.4	364.9	381.1	403.3
25°	337.9	351.8	369.3	392.4
27.5°	323.5	337.5	357.1	381.5
30°	312.6	326.1	344.9	371.0
32.5°	299.5	312.6	332.2	359.7
35°	284.7	299.5	318.3	346.2
37.5°	273.4	286.9	306.5	333.1
40°	261.2	272.9	292.1	318.3
42.5°	248.1	261.2	277.7	303.9
45°	235.9	245.5	262.5	287.3
47.5°	222.8	233.7	246.8	266.0
50°	208.8	218.0	232.4	245.5
52.5°	195.3	202.7	214.9	225.0
55°	180.9	188.3	197.5	203.6
57.5°	167.4	172.7	178.8	182.7
60°	150.9	156.1	160.0	163.9
62.5°	136.0	140.0	142.1	144.3
65°	120.8	122.9	124.3	126.0
67.5°	104.2	106.4	106.8	109.4
70°	88.9	89.4	90.3	91.6
72.5°	74.6	75.4	75.0	75.9
75°	59.7	60.6	59.7	60.6
77.5°	45.3	46.2	46.2	47.5
80°	32.7	33.1	33.6	33.6
82.5°	21.4	22.7	21.8	22.2
85°	12.2	12.6	12.6	13.1
87.5°	5.7	6.1	5.7	6.5
90°	7.5	5.4	3.2	1.0
92.5°	18.6	19.9	21.2	22.5
95°	33.0	41.9	50.9	59.8
97.5°	90.4	96.5	102.6	108.7
100°	178.6	174.2	169.9	165.5
102.5°	238.7	235.8	233.0	230.2
105°	299.1	296.7	294.3	291.9
107.5°	363.4	361.4	359.5	357.5
110°	428.4	426.7	424.9	423.2

TEST NUMBER: P1030793

CATALOG NUMBER: S123DIW-B340D1030UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	490.4	488.9	487.3	485.8
115°	551.5	550.2	548.9	547.6
117.5°	612.8	611.3	609.8	608.3
120°	670.0	668.0	666.1	664.1
122.5°	725.5	724.0	722.4	720.9
125°	777.1	775.4	773.6	771.9
127.5°	828.0	826.3	824.5	822.8
130°	875.1	873.3	871.6	869.8
132.5°	920.1	918.4	916.6	914.9
135°	964.8	963.5	962.2	960.9
137.5°	1005.3	1003.6	1001.8	1000.1
140°	1043.2	1041.9	1040.6	1039.3
142.5°	1079.4	1078.1	1076.8	1075.5
145°	1113.4	1111.9	1110.3	1108.8
147.5°	1144.4	1143.3	1142.2	1141.1
150°	1172.5	1171.8	1171.2	1170.5
152.5°	1197.7	1197.4	1197.2	1197.0
155°	1220.2	1220.6	1221.1	1221.5
157.5°	1241.1	1241.1	1241.1	1241.1
160°	1258.0	1258.3	1258.5	1258.7
162.5°	1273.4	1274.0	1274.7	1275.3
165°	1286.1	1286.8	1287.4	1288.1
167.5°	1296.2	1297.1	1297.9	1298.8
170°	1305.0	1305.9	1306.8	1307.7
172.5°	1310.2	1311.3	1312.4	1313.5
175°	1315.1	1316.2	1317.3	1318.4
177.5°	1317.1	1318.2	1319.3	1320.4
180°	1318.4	1318.4	1318.4	1318.4

(END OF REPORT)