

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P987601

Luminaire Tested: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

Issue Date: 5/2/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P987601  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1802-639-19)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/2/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K  
Description: Define 2 Direct Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1258.0 lumens  
Efficiency: N/A  
Efficacy: 96.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.09 / 1.23  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 13  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|--|--|---|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |  |     |  |  |   |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |  |     |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |  |  |   |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |  |  |   |
| 1   | 110 | 106 | 102 | 98  |  | 107 | 103 | 100 | 97  |  | 99  | 96  | 94  |  | 95  | 93  | 91  |  | 92  | 90  | 88  |  | 86  |  |  |   |
| 2   | 101 | 94  | 87  | 82  |  | 98  | 92  | 86  | 81  |  | 88  | 83  | 79  |  | 85  | 81  | 78  |  | 82  | 79  | 76  |  | 74  |  |  |   |
| 3   | 93  | 83  | 76  | 70  |  | 90  | 82  | 75  | 69  |  | 79  | 73  | 68  |  | 76  | 71  | 67  |  | 74  | 69  | 66  |  | 64  |  |  |   |
| 4   | 86  | 75  | 66  | 60  |  | 83  | 73  | 66  | 60  |  | 71  | 64  | 59  |  | 69  | 63  | 58  |  | 66  | 62  | 58  |  | 55  |  |  |   |
| 5   | 79  | 67  | 59  | 53  |  | 77  | 66  | 58  | 52  |  | 64  | 57  | 52  |  | 62  | 56  | 51  |  | 60  | 55  | 51  |  | 49  |  |  |   |
| 6   | 74  | 61  | 53  | 47  |  | 72  | 60  | 52  | 46  |  | 58  | 51  | 46  |  | 57  | 51  | 46  |  | 55  | 50  | 45  |  | 43  |  |  |   |
| 7   | 69  | 56  | 48  | 42  |  | 67  | 55  | 47  | 42  |  | 54  | 46  | 41  |  | 52  | 46  | 41  |  | 51  | 45  | 41  |  | 39  |  |  |   |
| 8   | 64  | 51  | 43  | 38  |  | 63  | 51  | 43  | 38  |  | 49  | 42  | 37  |  | 48  | 42  | 37  |  | 47  | 41  | 37  |  | 35  |  |  |   |
| 9   | 60  | 47  | 39  | 34  |  | 59  | 47  | 39  | 34  |  | 46  | 39  | 34  |  | 45  | 38  | 34  |  | 44  | 38  | 34  |  | 32  |  |  |   |
| 10  | 56  | 44  | 36  | 31  |  | 55  | 43  | 36  | 31  |  | 42  | 36  | 31  |  | 41  | 35  | 31  |  | 41  | 35  | 31  |  | 29  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°   | 90°   | 180° | 270° |
|-----|------|-------|------|------|
| 0°  | 9026 | 9026  | 9026 | 9026 |
| 5°  | 9067 | 10119 | 9102 | 8050 |
| 10° | 8982 | 11595 | 9038 | 6966 |
| 15° | 8784 | 12827 | 8905 | 6155 |
| 20° | 8667 | 12632 | 8667 | 5611 |
| 25° | 8413 | 11389 | 8450 | 5266 |
| 30° | 7978 | 9413  | 8130 | 5016 |
| 35° | 7596 | 6860  | 7724 | 4835 |
| 40° | 7154 | 5480  | 7236 | 4736 |
| 45° | 6604 | 4788  | 6711 | 4600 |
| 50° | 6129 | 4502  | 6142 | 4511 |
| 55° | 5588 | 4148  | 5624 | 4391 |
| 60° | 5008 | 3802  | 5078 | 4204 |
| 65° | 4498 | 3465  | 4581 | 4023 |
| 70° | 3994 | 3143  | 4096 | 3753 |
| 75° | 3431 | 2789  | 3566 | 3321 |
| 80° | 2799 | 2397  | 2999 | 2680 |
| 85° | 2070 | 2143  | 2234 | 1598 |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle:  $155^\circ$

Vertical Angle:  $45^\circ$

Luminance: 11784 cd/sqm

TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 54.3   | 4.3       |
| 10°-20°   | 158.1  | 12.6      |
| 20°-30°   | 229.4  | 18.2      |
| 30°-40°   | 241.8  | 19.2      |
| 40°-50°   | 214.0  | 17.0      |
| 50°-60°   | 170.9  | 13.6      |
| 60°-70°   | 116.1  | 9.2       |
| 70°-80°   | 59.4   | 4.7       |
| 80°-90°   | 14.0   | 1.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 441.8  | 35.1      |
| 0°-40°    | 683.6  | 54.3      |
| 0°-60°    | 1068.5 | 84.9      |
| 0°-90°    | 1258.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1258.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | 90° | 180° | 270° | 360° | Flux |
|-----|-----|-----|------|------|------|------|
| 0°  | 570 | 570 | 570  | 570  | 570  |      |
| 5°  | 571 | 637 | 573  | 507  | 571  | 54   |
| 15° | 536 | 783 | 543  | 376  | 536  | 151  |
| 25° | 482 | 652 | 484  | 302  | 482  | 220  |
| 35° | 393 | 355 | 400  | 250  | 393  | 246  |
| 45° | 295 | 214 | 300  | 206  | 295  | 229  |
| 55° | 202 | 150 | 204  | 159  | 202  | 181  |
| 65° | 120 | 92  | 122  | 107  | 120  | 119  |
| 75° | 56  | 46  | 58   | 54   | 56   | 60   |
| 85° | 11  | 12  | 12   | 9    | 11   | 14   |
| 90° | 0   | 0   | 0    | 0    | 0    |      |

TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    | 5°    | 10°   | 15°   | 20°   | 22.5° | 25°   | 30°   | 35°   | 40°   | 45°   |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 |
| 2.5°  | 573.3 | 574.6 | 576.8 | 577.2 | 581.6 | 585.1 | 589.0 | 589.0 | 590.3 | 589.9 | 586.4 |
| 5°    | 570.6 | 574.6 | 580.3 | 585.1 | 593.0 | 596.5 | 601.7 | 605.7 | 609.2 | 611.8 | 611.4 |
| 7.5°  | 566.2 | 573.3 | 581.6 | 590.8 | 601.3 | 607.4 | 614.9 | 621.9 | 626.7 | 631.1 | 634.2 |
| 10°   | 558.8 | 570.6 | 582.0 | 594.3 | 607.9 | 616.2 | 625.0 | 634.2 | 641.6 | 649.9 | 657.8 |
| 12.5° | 548.7 | 565.8 | 579.8 | 596.0 | 612.7 | 621.9 | 635.9 | 642.9 | 657.4 | 678.4 | 684.1 |
| 15°   | 536.0 | 559.2 | 572.4 | 593.0 | 614.9 | 622.3 | 641.6 | 653.0 | 682.8 | 696.0 | 711.7 |
| 17.5° | 524.2 | 550.0 | 567.6 | 591.2 | 612.7 | 627.2 | 646.0 | 669.2 | 694.2 | 713.1 | 730.6 |
| 20°   | 514.5 | 539.5 | 560.5 | 586.8 | 614.0 | 632.4 | 652.1 | 680.2 | 707.4 | 726.6 | 740.2 |
| 22.5° | 492.6 | 524.6 | 549.1 | 578.5 | 611.4 | 636.8 | 655.6 | 686.3 | 715.7 | 727.5 | 739.4 |
| 25°   | 481.7 | 509.3 | 537.8 | 571.1 | 609.6 | 639.9 | 656.1 | 690.3 | 716.1 | 720.5 | 723.1 |
| 27.5° | 461.5 | 492.6 | 525.9 | 564.0 | 609.2 | 634.6 | 655.2 | 686.3 | 706.9 | 703.9 | 696.0 |
| 30°   | 436.5 | 474.6 | 511.5 | 552.7 | 603.1 | 630.7 | 649.9 | 678.4 | 689.0 | 673.2 | 659.2 |
| 32.5° | 418.1 | 454.0 | 494.8 | 542.6 | 596.0 | 622.3 | 641.2 | 663.5 | 665.7 | 637.2 | 613.6 |
| 35°   | 393.1 | 433.0 | 479.0 | 529.4 | 584.2 | 607.9 | 625.4 | 639.0 | 628.5 | 588.6 | 560.5 |
| 37.5° | 370.8 | 410.2 | 459.3 | 510.6 | 568.0 | 591.2 | 605.2 | 607.4 | 581.6 | 546.5 | 505.3 |
| 40°   | 346.2 | 387.0 | 438.3 | 492.2 | 550.0 | 570.2 | 578.9 | 572.4 | 535.1 | 494.4 | 446.6 |
| 42.5° | 321.7 | 362.0 | 417.2 | 472.5 | 527.2 | 544.3 | 547.8 | 529.9 | 484.3 | 436.5 | 381.3 |
| 45°   | 295.0 | 337.0 | 392.2 | 447.9 | 500.9 | 510.6 | 511.0 | 485.2 | 431.3 | 381.3 | 330.0 |
| 47.5° | 273.0 | 312.0 | 366.8 | 422.5 | 467.2 | 473.8 | 471.1 | 441.3 | 382.6 | 326.5 | 281.8 |
| 50°   | 248.9 | 286.2 | 340.5 | 395.3 | 433.4 | 435.2 | 428.6 | 386.1 | 328.7 | 277.4 | 241.9 |
| 52.5° | 223.1 | 260.8 | 310.7 | 363.3 | 397.5 | 394.9 | 382.2 | 336.6 | 282.7 | 240.2 | 213.0 |
| 55°   | 202.5 | 235.8 | 282.7 | 334.0 | 358.1 | 350.6 | 336.6 | 290.1 | 247.6 | 211.7 | 188.0 |
| 57.5° | 179.7 | 209.1 | 255.1 | 299.8 | 313.8 | 306.8 | 292.8 | 249.4 | 209.9 | 182.8 | 167.0 |
| 60°   | 158.2 | 184.9 | 225.3 | 262.5 | 273.5 | 266.0 | 249.8 | 210.8 | 182.3 | 159.5 | 147.7 |
| 62.5° | 138.5 | 161.7 | 195.5 | 229.7 | 234.0 | 226.6 | 212.6 | 181.0 | 156.5 | 138.5 | 129.7 |
| 65°   | 120.1 | 142.0 | 169.2 | 195.0 | 199.0 | 191.1 | 176.6 | 153.8 | 133.2 | 121.8 | 113.5 |
| 67.5° | 102.1 | 119.6 | 143.8 | 162.6 | 164.8 | 157.3 | 145.5 | 127.1 | 114.4 | 102.1 | 96.0  |
| 70°   | 86.3  | 99.5  | 118.3 | 133.7 | 134.5 | 127.5 | 121.4 | 104.7 | 95.1  | 86.3  | 81.5  |
| 72.5° | 71.0  | 80.2  | 94.7  | 106.1 | 106.5 | 102.1 | 96.4  | 85.9  | 77.6  | 71.4  | 66.6  |
| 75°   | 56.1  | 64.0  | 72.8  | 82.8  | 82.4  | 78.9  | 74.5  | 67.9  | 60.9  | 57.0  | 54.8  |
| 77.5° | 43.0  | 47.8  | 54.8  | 61.4  | 61.4  | 59.6  | 57.0  | 52.2  | 47.8  | 43.8  | 41.6  |
| 80°   | 30.7  | 33.7  | 39.4  | 41.6  | 42.5  | 42.1  | 39.9  | 36.4  | 34.6  | 31.6  | 30.7  |
| 82.5° | 19.7  | 21.9  | 24.5  | 26.7  | 28.0  | 27.2  | 26.7  | 25.0  | 22.4  | 21.5  | 20.6  |
| 85°   | 11.4  | 12.3  | 13.6  | 14.9  | 15.3  | 14.9  | 15.8  | 14.5  | 13.1  | 13.1  | 12.7  |
| 87.5° | 4.8   | 5.3   | 6.1   | 6.1   | 6.6   | 6.6   | 6.1   | 6.6   | 6.6   | 6.1   | 5.7   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 50°   | 55°   | 60°   | 65°   | 67.5° | 70°   | 75°   | 80°   | 85°   | 90°   | 95°   |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 |
| 2.5°  | 592.5 | 593.0 | 593.9 | 598.2 | 600.4 | 600.9 | 599.1 | 603.1 | 604.4 | 603.1 | 602.2 |
| 5°    | 620.6 | 623.2 | 628.5 | 634.2 | 633.7 | 634.2 | 636.8 | 639.4 | 640.3 | 636.8 | 638.1 |
| 7.5°  | 645.1 | 650.4 | 656.1 | 664.8 | 664.8 | 669.2 | 671.0 | 673.2 | 678.4 | 675.8 | 674.9 |
| 10°   | 673.2 | 680.2 | 690.7 | 704.7 | 705.2 | 709.6 | 713.9 | 720.9 | 723.1 | 721.4 | 722.3 |
| 12.5° | 708.2 | 721.8 | 722.7 | 738.0 | 745.1 | 745.9 | 752.9 | 751.6 | 756.0 | 756.0 | 763.5 |
| 15°   | 723.6 | 744.6 | 756.4 | 771.3 | 775.7 | 770.5 | 776.2 | 782.3 | 782.7 | 782.7 | 782.3 |
| 17.5° | 751.2 | 759.5 | 771.3 | 779.2 | 781.0 | 781.0 | 781.4 | 784.1 | 782.3 | 778.8 | 781.4 |
| 20°   | 756.9 | 760.4 | 764.8 | 763.9 | 764.8 | 760.4 | 756.0 | 751.6 | 752.1 | 749.9 | 756.4 |
| 22.5° | 746.4 | 745.5 | 735.4 | 728.8 | 728.8 | 720.1 | 711.7 | 707.8 | 703.9 | 705.2 | 707.4 |
| 25°   | 720.1 | 706.5 | 694.2 | 684.6 | 682.4 | 668.4 | 657.0 | 653.5 | 646.9 | 652.1 | 653.0 |
| 27.5° | 678.0 | 662.7 | 642.9 | 634.6 | 623.2 | 617.5 | 609.6 | 599.1 | 585.5 | 593.4 | 592.1 |
| 30°   | 632.9 | 610.1 | 593.9 | 573.7 | 555.7 | 554.4 | 539.5 | 522.0 | 515.0 | 515.0 | 518.9 |
| 32.5° | 582.5 | 552.2 | 528.5 | 500.1 | 482.5 | 475.1 | 457.1 | 439.6 | 443.5 | 430.4 | 435.2 |
| 35°   | 523.7 | 483.8 | 454.0 | 426.4 | 413.3 | 404.5 | 381.3 | 371.6 | 361.1 | 355.0 | 366.4 |
| 37.5° | 467.6 | 421.6 | 383.5 | 353.2 | 348.4 | 332.6 | 316.9 | 310.7 | 304.6 | 307.2 | 306.8 |
| 40°   | 399.3 | 358.5 | 324.3 | 300.7 | 292.3 | 284.9 | 274.4 | 266.9 | 263.0 | 265.2 | 265.6 |
| 42.5° | 337.5 | 303.3 | 277.9 | 261.2 | 254.2 | 248.9 | 243.7 | 237.5 | 236.2 | 236.2 | 238.0 |
| 45°   | 289.7 | 261.6 | 244.6 | 231.0 | 227.0 | 223.1 | 219.1 | 216.5 | 215.6 | 213.9 | 215.2 |
| 47.5° | 251.6 | 229.2 | 218.7 | 208.6 | 204.2 | 203.4 | 199.8 | 198.5 | 196.8 | 196.3 | 196.8 |
| 50°   | 219.6 | 205.5 | 195.9 | 190.2 | 187.1 | 185.8 | 184.1 | 181.4 | 180.6 | 182.8 | 181.9 |
| 52.5° | 197.2 | 184.1 | 178.8 | 173.1 | 171.4 | 169.6 | 167.0 | 167.4 | 167.0 | 166.1 | 166.1 |
| 55°   | 174.9 | 166.5 | 161.3 | 156.9 | 156.5 | 154.7 | 152.5 | 151.6 | 151.2 | 150.3 | 151.6 |
| 57.5° | 156.9 | 150.3 | 145.5 | 141.6 | 139.8 | 139.8 | 137.6 | 135.9 | 135.9 | 135.4 | 135.9 |
| 60°   | 138.9 | 132.4 | 129.3 | 125.3 | 124.0 | 123.6 | 122.3 | 121.4 | 120.1 | 120.1 | 120.1 |
| 62.5° | 122.3 | 117.0 | 113.5 | 110.0 | 110.4 | 108.3 | 106.5 | 105.6 | 105.6 | 106.1 | 106.1 |
| 65°   | 106.5 | 103.0 | 98.6  | 95.5  | 94.7  | 94.2  | 93.4  | 92.9  | 91.6  | 92.5  | 92.5  |
| 67.5° | 92.0  | 87.2  | 84.6  | 83.3  | 82.0  | 81.5  | 80.6  | 79.8  | 79.3  | 78.9  | 79.8  |
| 70°   | 77.6  | 73.6  | 71.4  | 70.6  | 69.2  | 68.8  | 68.4  | 67.1  | 67.5  | 67.9  | 68.4  |
| 72.5° | 64.4  | 60.9  | 60.5  | 57.9  | 57.9  | 57.9  | 56.1  | 57.0  | 56.5  | 55.7  | 56.5  |
| 75°   | 50.8  | 49.1  | 48.2  | 46.9  | 47.3  | 46.9  | 46.5  | 45.1  | 45.1  | 45.6  | 46.0  |
| 77.5° | 40.3  | 38.6  | 38.1  | 36.8  | 35.9  | 36.8  | 35.9  | 35.5  | 35.5  | 35.9  | 35.9  |
| 80°   | 29.8  | 28.9  | 27.6  | 27.6  | 27.6  | 27.2  | 27.2  | 27.2  | 26.7  | 26.3  | 26.7  |
| 82.5° | 19.7  | 19.7  | 19.3  | 18.8  | 19.3  | 18.4  | 18.8  | 18.8  | 18.8  | 18.8  | 18.8  |
| 85°   | 12.7  | 12.3  | 12.3  | 11.8  | 11.8  | 11.8  | 12.3  | 11.4  | 11.4  | 11.8  | 11.8  |
| 87.5° | 5.7   | 5.7   | 5.7   | 6.1   | 5.7   | 5.7   | 5.7   | 6.1   | 5.7   | 5.7   | 5.7   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 100°  | 105°  | 110°  | 112.5° | 115°  | 120°  | 125°  | 130°  | 135°  | 140°  | 145°  |
|-------|-------|-------|-------|--------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 570.2 | 570.2 | 570.2 | 570.2  | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 |
| 2.5°  | 604.4 | 601.3 | 598.7 | 599.1  | 601.3 | 599.5 | 595.2 | 589.5 | 587.3 | 584.6 | 587.3 |
| 5°    | 640.7 | 638.1 | 632.9 | 633.3  | 632.0 | 630.2 | 623.2 | 614.4 | 614.4 | 607.4 | 606.6 |
| 7.5°  | 676.7 | 672.7 | 669.2 | 668.4  | 663.5 | 660.0 | 653.9 | 641.6 | 636.8 | 628.5 | 623.7 |
| 10°   | 717.0 | 713.9 | 710.0 | 705.2  | 702.5 | 696.4 | 686.3 | 668.4 | 659.6 | 648.2 | 639.9 |
| 12.5° | 757.8 | 757.3 | 748.6 | 738.9  | 738.5 | 728.8 | 721.8 | 697.7 | 685.9 | 670.5 | 650.8 |
| 15°   | 783.6 | 781.4 | 776.6 | 771.8  | 773.1 | 762.6 | 746.8 | 718.3 | 710.4 | 692.0 | 671.0 |
| 17.5° | 783.2 | 783.2 | 781.9 | 781.0  | 779.7 | 776.6 | 767.8 | 749.0 | 736.3 | 713.1 | 693.3 |
| 20°   | 758.2 | 763.9 | 765.2 | 764.8  | 769.2 | 771.3 | 770.9 | 759.1 | 749.0 | 728.4 | 708.2 |
| 22.5° | 708.2 | 721.4 | 727.1 | 730.6  | 739.8 | 744.6 | 756.0 | 751.6 | 749.0 | 733.7 | 716.6 |
| 25°   | 661.8 | 666.2 | 683.3 | 684.1  | 696.8 | 708.7 | 720.1 | 727.5 | 737.2 | 731.5 | 717.0 |
| 27.5° | 601.7 | 611.8 | 624.1 | 633.3  | 635.9 | 660.0 | 678.9 | 692.9 | 714.8 | 716.6 | 711.7 |
| 30°   | 533.8 | 538.6 | 558.8 | 571.1  | 585.1 | 602.6 | 629.8 | 653.9 | 673.6 | 691.6 | 697.7 |
| 32.5° | 451.0 | 470.7 | 482.5 | 497.4  | 509.7 | 540.8 | 574.1 | 605.2 | 628.0 | 658.3 | 671.4 |
| 35°   | 375.2 | 390.5 | 410.7 | 416.8  | 439.1 | 465.4 | 508.8 | 548.7 | 583.3 | 614.0 | 640.7 |
| 37.5° | 312.5 | 324.8 | 346.2 | 355.9  | 369.0 | 402.8 | 439.1 | 488.7 | 530.3 | 568.0 | 601.3 |
| 40°   | 269.5 | 278.7 | 295.0 | 298.0  | 309.0 | 339.7 | 369.0 | 415.5 | 470.7 | 521.5 | 557.9 |
| 42.5° | 240.2 | 244.6 | 255.5 | 259.5  | 266.5 | 287.1 | 313.4 | 357.2 | 408.5 | 461.1 | 512.3 |
| 45°   | 219.1 | 222.2 | 228.8 | 232.3  | 241.0 | 250.2 | 271.7 | 306.8 | 347.1 | 400.1 | 455.4 |
| 47.5° | 200.3 | 204.2 | 206.9 | 209.1  | 213.9 | 224.0 | 238.0 | 263.8 | 302.4 | 351.1 | 404.5 |
| 50°   | 184.5 | 185.8 | 190.6 | 191.1  | 194.2 | 200.7 | 213.9 | 229.7 | 260.3 | 299.8 | 351.5 |
| 52.5° | 168.7 | 170.0 | 173.1 | 176.2  | 177.5 | 182.8 | 191.5 | 204.7 | 227.5 | 258.6 | 304.6 |
| 55°   | 153.0 | 154.7 | 157.8 | 160.0  | 161.3 | 165.7 | 170.9 | 183.6 | 201.6 | 223.5 | 261.2 |
| 57.5° | 137.2 | 141.1 | 142.0 | 143.3  | 145.5 | 150.3 | 155.1 | 162.6 | 176.6 | 196.8 | 224.4 |
| 60°   | 122.3 | 123.6 | 126.7 | 128.0  | 130.2 | 132.8 | 138.9 | 144.6 | 154.7 | 170.5 | 195.5 |
| 62.5° | 106.9 | 110.0 | 111.3 | 112.6  | 114.4 | 117.5 | 121.4 | 127.5 | 136.3 | 149.0 | 168.7 |
| 65°   | 93.8  | 94.2  | 96.9  | 98.6   | 100.4 | 102.6 | 106.5 | 112.2 | 117.5 | 129.3 | 143.8 |
| 67.5° | 81.1  | 82.0  | 82.8  | 84.6   | 86.8  | 89.0  | 92.5  | 95.5  | 102.1 | 110.0 | 121.4 |
| 70°   | 68.8  | 68.8  | 71.0  | 72.3   | 71.9  | 74.5  | 77.1  | 80.6  | 85.5  | 92.9  | 102.1 |
| 72.5° | 57.9  | 57.4  | 59.2  | 59.6   | 60.5  | 62.2  | 64.0  | 67.5  | 70.1  | 75.8  | 82.8  |
| 75°   | 46.0  | 46.9  | 47.8  | 47.8   | 49.1  | 50.4  | 52.2  | 53.9  | 57.0  | 60.5  | 65.7  |
| 77.5° | 36.4  | 36.4  | 37.3  | 37.7   | 39.0  | 38.6  | 40.3  | 42.1  | 44.3  | 47.3  | 51.3  |
| 80°   | 26.7  | 27.6  | 27.6  | 27.6   | 28.0  | 28.5  | 30.2  | 31.6  | 32.9  | 35.1  | 36.8  |
| 82.5° | 18.8  | 18.8  | 19.7  | 19.7   | 19.7  | 20.6  | 20.6  | 21.0  | 21.9  | 23.2  | 24.5  |
| 85°   | 11.8  | 11.8  | 11.8  | 12.3   | 11.8  | 12.3  | 13.1  | 12.7  | 13.1  | 14.0  | 14.0  |
| 87.5° | 5.7   | 5.7   | 5.7   | 5.7    | 5.7   | 6.1   | 5.7   | 6.1   | 6.6   | 6.6   | 6.6   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |



TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 150°  | 155°  | 157.5° | 160°  | 165°  | 170°  | 175°  | 180°  | 185°  | 190°  | 195°  |
|-------|-------|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 570.2 | 570.2 | 570.2  | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 |
| 2.5°  | 585.1 | 582.9 | 581.6  | 582.5 | 579.8 | 573.3 | 573.3 | 575.4 | 572.8 | 570.2 | 566.2 |
| 5°    | 601.3 | 596.9 | 594.3  | 593.9 | 587.7 | 577.2 | 575.0 | 572.8 | 567.1 | 561.0 | 554.4 |
| 7.5°  | 617.1 | 609.2 | 604.8  | 601.7 | 593.0 | 579.4 | 573.7 | 568.9 | 559.7 | 550.5 | 542.1 |
| 10°   | 630.2 | 618.8 | 613.6  | 608.8 | 597.4 | 580.3 | 571.1 | 562.3 | 550.5 | 538.6 | 528.1 |
| 12.5° | 640.7 | 627.6 | 621.0  | 614.0 | 600.0 | 577.6 | 566.2 | 552.2 | 540.4 | 524.6 | 514.1 |
| 15°   | 658.3 | 631.1 | 625.0  | 618.4 | 603.9 | 573.3 | 559.2 | 543.4 | 527.2 | 506.2 | 494.8 |
| 17.5° | 672.3 | 635.9 | 635.5  | 621.5 | 602.6 | 571.5 | 550.0 | 529.4 | 511.9 | 490.9 | 472.9 |
| 20°   | 680.6 | 643.4 | 636.4  | 621.9 | 598.2 | 559.7 | 537.3 | 514.5 | 495.7 | 470.3 | 452.3 |
| 22.5° | 687.6 | 653.9 | 635.5  | 618.0 | 589.0 | 555.7 | 522.9 | 501.4 | 475.5 | 447.9 | 430.8 |
| 25°   | 690.3 | 656.1 | 636.8  | 616.6 | 582.5 | 544.3 | 507.1 | 483.8 | 454.9 | 429.9 | 406.7 |
| 27.5° | 690.7 | 655.6 | 632.0  | 610.9 | 573.3 | 529.4 | 491.3 | 466.8 | 434.8 | 405.8 | 382.6 |
| 30°   | 686.3 | 650.8 | 629.4  | 606.6 | 564.5 | 515.8 | 472.0 | 444.8 | 410.7 | 381.7 | 357.6 |
| 32.5° | 673.2 | 641.2 | 623.7  | 598.7 | 553.1 | 497.0 | 453.6 | 423.4 | 387.4 | 358.9 | 335.7 |
| 35°   | 651.3 | 629.4 | 610.1  | 586.8 | 538.2 | 479.5 | 435.2 | 399.7 | 363.3 | 336.2 | 314.2 |
| 37.5° | 624.1 | 612.3 | 594.3  | 571.5 | 521.1 | 463.7 | 414.6 | 375.2 | 338.8 | 312.5 | 291.0 |
| 40°   | 587.3 | 590.3 | 572.8  | 552.2 | 500.9 | 442.2 | 387.9 | 350.2 | 316.0 | 291.4 | 270.4 |
| 42.5° | 547.4 | 560.1 | 550.0  | 530.3 | 478.6 | 418.5 | 368.1 | 326.5 | 293.2 | 267.8 | 250.2 |
| 45°   | 504.4 | 526.4 | 520.2  | 505.8 | 455.4 | 393.6 | 340.1 | 299.8 | 270.4 | 245.9 | 230.5 |
| 47.5° | 457.5 | 488.7 | 488.7  | 478.1 | 429.5 | 368.6 | 316.0 | 274.8 | 245.9 | 228.3 | 213.4 |
| 50°   | 409.8 | 444.8 | 450.5  | 443.5 | 400.6 | 340.1 | 286.6 | 249.4 | 224.4 | 207.3 | 196.3 |
| 52.5° | 359.8 | 400.6 | 411.1  | 407.6 | 369.9 | 312.9 | 262.5 | 226.1 | 203.4 | 188.5 | 178.8 |
| 55°   | 312.0 | 359.4 | 370.8  | 372.1 | 337.0 | 283.1 | 235.8 | 203.8 | 181.9 | 171.8 | 163.5 |
| 57.5° | 266.9 | 312.5 | 325.2  | 327.4 | 303.7 | 255.9 | 210.8 | 182.8 | 163.0 | 154.7 | 148.1 |
| 60°   | 228.3 | 266.5 | 283.1  | 287.9 | 267.3 | 224.4 | 187.6 | 160.4 | 145.5 | 137.6 | 131.5 |
| 62.5° | 196.8 | 227.5 | 245.0  | 246.3 | 237.1 | 196.8 | 163.5 | 140.7 | 128.0 | 121.0 | 117.9 |
| 65°   | 166.1 | 193.7 | 204.2  | 209.5 | 202.0 | 170.5 | 141.1 | 122.3 | 112.2 | 106.1 | 103.0 |
| 67.5° | 141.6 | 159.1 | 167.9  | 174.9 | 167.4 | 143.8 | 120.1 | 104.7 | 97.3  | 91.2  | 89.4  |
| 70°   | 116.1 | 130.6 | 137.2  | 144.2 | 137.6 | 119.6 | 102.6 | 88.5  | 82.0  | 77.1  | 74.9  |
| 72.5° | 92.9  | 104.3 | 110.4  | 114.8 | 110.9 | 96.0  | 82.0  | 72.3  | 67.5  | 64.0  | 62.7  |
| 75°   | 73.6  | 81.5  | 85.0   | 88.1  | 86.3  | 74.9  | 66.2  | 58.3  | 53.9  | 50.8  | 50.0  |
| 77.5° | 56.1  | 61.8  | 65.7   | 66.6  | 64.4  | 57.0  | 49.5  | 44.7  | 41.2  | 39.4  | 38.6  |
| 80°   | 39.9  | 43.4  | 45.6   | 46.9  | 44.7  | 41.6  | 36.4  | 32.9  | 29.8  | 27.6  | 27.2  |
| 82.5° | 26.7  | 28.5  | 30.2   | 29.8  | 28.9  | 26.3  | 23.2  | 21.5  | 20.2  | 18.4  | 18.4  |
| 85°   | 15.3  | 15.8  | 16.7   | 17.1  | 16.7  | 14.9  | 13.1  | 12.3  | 11.4  | 10.1  | 10.1  |
| 87.5° | 6.6   | 7.0   | 7.0    | 7.5   | 6.6   | 6.6   | 5.7   | 4.8   | 4.8   | 4.4   | 3.9   |
| 90°   | 0.0   | 0.0   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 200°  | 202.5° | 205°  | 210°  | 215°  | 220°  | 225°  | 230°  | 235°  | 240°  | 245°  |
|-------|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| 0°    | 570.2 | 570.2  | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 |
| 2.5°  | 564.0 | 566.2  | 565.8 | 561.4 | 556.6 | 552.7 | 545.2 | 546.1 | 543.4 | 543.9 | 546.5 |
| 5°    | 550.0 | 550.0  | 548.3 | 542.1 | 534.2 | 529.9 | 521.5 | 519.3 | 514.1 | 513.6 | 513.2 |
| 7.5°  | 535.1 | 532.9  | 530.7 | 522.0 | 512.3 | 505.3 | 493.9 | 491.3 | 486.0 | 482.5 | 480.8 |
| 10°   | 517.6 | 514.5  | 510.1 | 500.1 | 488.2 | 479.5 | 467.6 | 464.1 | 454.0 | 449.7 | 447.0 |
| 12.5° | 498.3 | 496.6  | 489.5 | 481.2 | 461.9 | 452.3 | 435.2 | 438.7 | 428.6 | 419.9 | 418.5 |
| 15°   | 479.0 | 472.5  | 468.5 | 454.9 | 431.7 | 427.3 | 413.7 | 406.7 | 397.5 | 390.5 | 390.5 |
| 17.5° | 460.2 | 450.1  | 441.3 | 426.9 | 409.8 | 397.5 | 387.4 | 383.9 | 372.5 | 365.5 | 364.2 |
| 20°   | 435.2 | 423.8  | 421.6 | 401.0 | 389.2 | 375.6 | 366.0 | 357.2 | 348.9 | 345.8 | 343.6 |
| 22.5° | 411.5 | 398.4  | 394.9 | 377.3 | 365.5 | 351.9 | 342.3 | 336.2 | 330.0 | 327.8 | 323.9 |
| 25°   | 386.1 | 378.2  | 373.0 | 354.1 | 341.0 | 328.3 | 321.7 | 317.3 | 311.6 | 311.2 | 308.5 |
| 27.5° | 361.6 | 354.1  | 348.9 | 330.9 | 321.2 | 309.4 | 304.2 | 299.3 | 296.3 | 295.0 | 293.6 |
| 30°   | 340.5 | 332.2  | 326.1 | 312.9 | 301.1 | 291.4 | 287.1 | 284.0 | 282.2 | 280.1 | 279.6 |
| 32.5° | 317.3 | 312.5  | 304.2 | 294.1 | 284.9 | 275.7 | 273.0 | 270.8 | 268.2 | 267.3 | 266.9 |
| 35°   | 297.6 | 291.0  | 285.7 | 274.4 | 270.4 | 262.5 | 259.5 | 257.7 | 254.2 | 253.3 | 252.4 |
| 37.5° | 278.3 | 272.2  | 266.5 | 259.5 | 252.0 | 247.6 | 245.9 | 243.2 | 241.5 | 241.9 | 241.0 |
| 40°   | 259.0 | 254.2  | 249.8 | 242.4 | 238.0 | 235.8 | 232.3 | 229.7 | 228.8 | 229.2 | 228.8 |
| 42.5° | 240.2 | 235.8  | 233.2 | 227.5 | 223.1 | 220.9 | 218.7 | 216.1 | 217.4 | 217.4 | 218.7 |
| 45°   | 223.1 | 219.1  | 217.4 | 213.0 | 210.4 | 206.9 | 204.7 | 204.2 | 206.0 | 205.5 | 205.5 |
| 47.5° | 205.5 | 204.2  | 202.0 | 198.1 | 194.6 | 192.4 | 192.0 | 192.0 | 193.7 | 194.6 | 194.2 |
| 50°   | 192.0 | 189.3  | 186.7 | 183.6 | 181.0 | 180.1 | 178.8 | 179.7 | 181.4 | 181.4 | 182.3 |
| 52.5° | 174.9 | 173.1  | 172.2 | 169.6 | 167.9 | 167.9 | 167.9 | 168.3 | 169.6 | 170.9 | 170.5 |
| 55°   | 160.0 | 158.7  | 157.8 | 156.5 | 154.3 | 154.7 | 154.3 | 155.1 | 156.5 | 157.8 | 158.7 |
| 57.5° | 144.2 | 143.8  | 142.9 | 140.7 | 140.7 | 140.2 | 141.6 | 142.0 | 144.2 | 145.1 | 146.4 |
| 60°   | 130.2 | 128.9  | 128.9 | 127.1 | 127.1 | 127.1 | 128.4 | 129.7 | 131.5 | 131.9 | 132.8 |
| 62.5° | 115.3 | 115.3  | 114.8 | 113.5 | 113.5 | 114.8 | 115.3 | 117.0 | 117.9 | 117.9 | 119.2 |
| 65°   | 101.2 | 100.8  | 100.4 | 100.8 | 101.2 | 101.2 | 102.6 | 103.4 | 104.3 | 104.7 | 105.2 |
| 67.5° | 87.2  | 86.8   | 87.7  | 87.2  | 88.1  | 89.8  | 89.4  | 90.7  | 92.0  | 92.0  | 92.5  |
| 70°   | 74.1  | 74.9   | 74.5  | 75.4  | 74.9  | 75.8  | 77.1  | 77.6  | 77.6  | 78.0  | 79.3  |
| 72.5° | 61.8  | 61.8   | 61.8  | 61.4  | 61.8  | 62.7  | 63.5  | 64.0  | 64.9  | 65.3  | 66.6  |
| 75°   | 50.0  | 50.0   | 49.1  | 50.0  | 50.0  | 50.8  | 51.7  | 51.7  | 51.7  | 52.6  | 53.9  |
| 77.5° | 37.7  | 38.1   | 37.7  | 38.6  | 38.6  | 39.0  | 39.9  | 39.4  | 40.3  | 40.8  | 41.2  |
| 80°   | 27.6  | 27.2   | 27.2  | 27.2  | 27.6  | 27.6  | 28.5  | 28.9  | 28.9  | 30.2  | 29.4  |
| 82.5° | 17.5  | 18.0   | 17.5  | 18.0  | 18.0  | 18.4  | 18.0  | 18.4  | 18.8  | 19.7  | 19.3  |
| 85°   | 10.1  | 9.6    | 9.6   | 10.1  | 9.6   | 9.6   | 10.1  | 9.6   | 10.1  | 9.6   | 10.1  |
| 87.5° | 3.9   | 3.5    | 3.5   | 3.5   | 3.5   | 3.1   | 3.1   | 2.6   | 2.6   | 2.6   | 2.2   |
| 90°   | 0.0   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |

TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 247.5° | 250°  | 255°  | 260°  | 265°  | 270°  | 275°  | 280°  | 285°  | 290°  | 292.5° |
|-------|--------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|
| 0°    | 570.2  | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2  |
| 2.5°  | 543.4  | 544.8 | 541.7 | 540.8 | 541.7 | 538.6 | 539.5 | 540.4 | 540.4 | 541.7 | 542.6  |
| 5°    | 511.9  | 510.1 | 507.1 | 506.2 | 505.3 | 506.6 | 505.8 | 507.1 | 507.5 | 510.6 | 511.0  |
| 7.5°  | 480.8  | 478.1 | 475.5 | 472.9 | 472.0 | 469.8 | 472.0 | 472.0 | 475.1 | 474.2 | 476.4  |
| 10°   | 444.0  | 443.5 | 440.0 | 438.7 | 437.0 | 433.4 | 438.3 | 437.0 | 439.1 | 443.1 | 444.0  |
| 12.5° | 416.8  | 412.0 | 414.2 | 408.0 | 410.2 | 406.7 | 407.1 | 407.1 | 410.7 | 411.1 | 410.2  |
| 15°   | 390.9  | 387.0 | 381.3 | 378.7 | 377.3 | 375.6 | 381.3 | 381.7 | 379.1 | 385.2 | 383.0  |
| 17.5° | 364.6  | 364.6 | 359.4 | 358.1 | 354.6 | 356.3 | 355.4 | 355.9 | 355.0 | 359.4 | 361.6  |
| 20°   | 341.8  | 339.7 | 337.9 | 338.3 | 334.0 | 333.1 | 332.2 | 333.1 | 336.2 | 339.2 | 340.1  |
| 22.5° | 323.4  | 322.1 | 317.7 | 318.6 | 315.1 | 316.4 | 315.6 | 317.7 | 318.2 | 318.2 | 321.2  |
| 25°   | 305.9  | 304.2 | 304.6 | 302.8 | 301.5 | 301.5 | 300.2 | 301.5 | 303.3 | 304.2 | 304.6  |
| 27.5° | 292.8  | 291.4 | 289.3 | 287.9 | 288.8 | 286.6 | 288.4 | 289.7 | 289.7 | 288.8 | 289.7  |
| 30°   | 277.0  | 277.9 | 277.9 | 273.5 | 275.2 | 274.4 | 275.7 | 276.5 | 276.5 | 277.0 | 276.1  |
| 32.5° | 266.5  | 263.8 | 263.4 | 263.0 | 263.0 | 261.2 | 261.2 | 262.5 | 263.0 | 263.4 | 264.7  |
| 35°   | 252.4  | 252.4 | 250.2 | 251.6 | 249.8 | 250.2 | 249.8 | 250.2 | 251.1 | 249.8 | 251.1  |
| 37.5° | 239.7  | 240.2 | 239.3 | 240.2 | 240.6 | 239.7 | 238.9 | 240.6 | 239.7 | 239.7 | 238.9  |
| 40°   | 228.8  | 228.3 | 228.8 | 228.8 | 228.8 | 229.2 | 228.3 | 228.3 | 228.3 | 227.5 | 226.6  |
| 42.5° | 219.6  | 216.9 | 217.8 | 218.3 | 216.9 | 216.9 | 217.4 | 216.9 | 218.3 | 215.6 | 215.6  |
| 45°   | 206.4  | 205.5 | 206.0 | 206.0 | 206.9 | 205.5 | 206.4 | 206.9 | 205.5 | 205.1 | 204.2  |
| 47.5° | 194.6  | 195.5 | 194.6 | 195.5 | 195.5 | 196.3 | 194.6 | 195.0 | 195.5 | 193.7 | 192.4  |
| 50°   | 182.8  | 182.8 | 184.1 | 183.6 | 184.1 | 183.2 | 183.2 | 182.8 | 183.2 | 182.3 | 181.0  |
| 52.5° | 171.8  | 170.5 | 172.7 | 172.2 | 171.8 | 171.4 | 170.9 | 171.4 | 170.5 | 169.6 | 169.6  |
| 55°   | 158.2  | 158.2 | 159.5 | 160.0 | 160.0 | 159.1 | 158.2 | 158.7 | 158.2 | 157.8 | 157.3  |
| 57.5° | 147.3  | 145.5 | 146.4 | 146.8 | 146.8 | 145.5 | 146.4 | 145.5 | 145.5 | 145.9 | 144.6  |
| 60°   | 133.2  | 133.2 | 132.4 | 133.7 | 133.7 | 132.8 | 132.8 | 133.2 | 132.4 | 131.9 | 131.5  |
| 62.5° | 118.3  | 118.8 | 120.1 | 120.5 | 121.0 | 120.1 | 119.2 | 119.6 | 119.6 | 118.3 | 118.8  |
| 65°   | 105.6  | 106.5 | 108.3 | 107.8 | 106.9 | 107.4 | 106.5 | 106.9 | 105.6 | 106.1 | 104.7  |
| 67.5° | 93.4   | 92.9  | 93.4  | 93.4  | 94.2  | 93.8  | 92.9  | 92.9  | 92.5  | 93.8  | 92.5   |
| 70°   | 80.2   | 80.2  | 80.2  | 80.2  | 80.6  | 81.1  | 80.2  | 79.3  | 79.8  | 78.9  | 78.4   |
| 72.5° | 66.6   | 67.1  | 66.6  | 67.5  | 66.2  | 67.1  | 67.1  | 66.6  | 66.2  | 66.2  | 66.2   |
| 75°   | 53.9   | 54.8  | 53.5  | 53.9  | 53.5  | 54.3  | 53.9  | 53.9  | 53.0  | 52.6  | 53.0   |
| 77.5° | 41.2   | 41.6  | 40.8  | 41.2  | 40.8  | 41.2  | 41.2  | 40.8  | 40.8  | 40.8  | 40.8   |
| 80°   | 29.4   | 29.8  | 29.4  | 28.9  | 28.5  | 29.4  | 28.5  | 28.9  | 29.4  | 28.9  | 29.8   |
| 82.5° | 18.8   | 18.8  | 18.4  | 18.8  | 18.0  | 18.0  | 18.4  | 18.4  | 18.0  | 18.8  | 18.0   |
| 85°   | 9.2    | 9.2   | 10.1  | 9.2   | 8.8   | 8.8   | 8.8   | 9.2   | 8.8   | 9.6   | 9.2    |
| 87.5° | 2.2    | 1.8   | 2.2   | 2.2   | 1.8   | 1.8   | 2.2   | 1.8   | 2.2   | 2.6   | 1.8    |
| 90°   | 0.0    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    |

TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 295°  | 300°  | 305°  | 310°  | 315°  | 320°  | 325°  | 330°  | 335°  | 337.5° | 340°  |
|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|--------|-------|
| 0°    | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2 | 570.2  | 570.2 |
| 2.5°  | 541.3 | 544.8 | 543.4 | 538.6 | 544.3 | 544.3 | 548.3 | 548.3 | 553.1 | 554.8  | 557.5 |
| 5°    | 510.6 | 513.2 | 515.4 | 513.2 | 517.2 | 523.3 | 526.8 | 529.9 | 536.4 | 539.1  | 543.0 |
| 7.5°  | 477.7 | 482.5 | 484.7 | 484.7 | 491.3 | 498.3 | 505.3 | 509.7 | 518.9 | 522.4  | 526.4 |
| 10°   | 445.7 | 451.4 | 455.8 | 455.4 | 466.3 | 470.7 | 479.5 | 489.5 | 498.7 | 504.0  | 509.7 |
| 12.5° | 412.0 | 415.0 | 421.2 | 429.9 | 432.6 | 440.5 | 450.5 | 463.2 | 479.9 | 484.7  | 493.0 |
| 15°   | 383.9 | 392.2 | 397.1 | 401.0 | 407.1 | 414.6 | 425.6 | 437.8 | 454.5 | 465.0  | 473.8 |
| 17.5° | 360.3 | 371.2 | 374.3 | 373.4 | 381.3 | 392.7 | 405.4 | 414.6 | 429.5 | 442.2  | 450.5 |
| 20°   | 341.0 | 345.4 | 350.6 | 352.8 | 358.9 | 371.2 | 383.5 | 394.0 | 406.3 | 416.4  | 426.0 |
| 22.5° | 321.7 | 325.2 | 329.6 | 333.5 | 338.3 | 345.4 | 357.2 | 370.3 | 382.2 | 391.8  | 402.8 |
| 25°   | 305.9 | 308.1 | 312.0 | 315.1 | 320.4 | 325.2 | 333.5 | 348.0 | 362.0 | 367.7  | 377.3 |
| 27.5° | 290.6 | 292.3 | 295.0 | 298.5 | 301.1 | 305.9 | 313.4 | 325.2 | 339.7 | 345.4  | 358.5 |
| 30°   | 277.0 | 278.3 | 280.9 | 282.7 | 284.0 | 289.7 | 295.4 | 304.6 | 315.6 | 323.4  | 333.1 |
| 32.5° | 264.3 | 265.6 | 268.2 | 268.7 | 270.4 | 273.5 | 278.7 | 287.1 | 296.7 | 303.3  | 311.6 |
| 35°   | 250.2 | 251.1 | 253.8 | 254.6 | 255.9 | 258.6 | 262.5 | 268.7 | 277.4 | 282.2  | 289.7 |
| 37.5° | 239.3 | 238.9 | 240.6 | 241.9 | 243.7 | 245.0 | 246.3 | 252.4 | 259.0 | 263.4  | 269.1 |
| 40°   | 227.5 | 226.6 | 227.0 | 228.8 | 229.7 | 231.4 | 231.4 | 237.5 | 241.9 | 245.4  | 249.8 |
| 42.5° | 215.6 | 215.2 | 214.3 | 215.2 | 216.1 | 216.5 | 216.9 | 221.3 | 225.7 | 228.8  | 233.6 |
| 45°   | 203.8 | 203.4 | 202.5 | 202.9 | 202.9 | 203.8 | 205.1 | 206.9 | 209.9 | 212.6  | 215.2 |
| 47.5° | 192.8 | 192.0 | 190.6 | 190.2 | 191.1 | 191.1 | 191.1 | 192.8 | 195.9 | 196.8  | 199.4 |
| 50°   | 181.4 | 180.1 | 178.4 | 177.5 | 177.5 | 177.1 | 177.9 | 178.4 | 181.0 | 181.9  | 184.1 |
| 52.5° | 169.2 | 168.3 | 166.5 | 164.8 | 165.2 | 164.3 | 164.8 | 165.2 | 166.1 | 167.4  | 168.7 |
| 55°   | 156.9 | 155.1 | 153.8 | 153.4 | 152.1 | 152.1 | 150.8 | 152.5 | 152.1 | 152.5  | 154.3 |
| 57.5° | 145.1 | 143.3 | 141.1 | 140.2 | 138.9 | 138.5 | 137.6 | 137.2 | 137.6 | 138.9  | 140.2 |
| 60°   | 131.0 | 130.2 | 128.9 | 127.5 | 126.7 | 125.3 | 124.5 | 124.5 | 124.0 | 124.0  | 124.5 |
| 62.5° | 117.5 | 117.0 | 115.3 | 114.8 | 113.9 | 113.1 | 111.8 | 110.9 | 110.9 | 111.8  | 112.2 |
| 65°   | 104.3 | 103.9 | 102.6 | 102.1 | 99.9  | 99.0  | 98.6  | 98.2  | 97.3  | 97.3   | 97.3  |
| 67.5° | 92.0  | 90.7  | 90.7  | 88.5  | 86.8  | 85.9  | 85.0  | 84.6  | 84.6  | 84.6   | 85.0  |
| 70°   | 78.4  | 78.4  | 77.1  | 75.8  | 74.1  | 74.5  | 73.2  | 71.9  | 71.9  | 71.0   | 71.4  |
| 72.5° | 65.3  | 64.9  | 63.5  | 63.1  | 61.8  | 60.5  | 59.6  | 60.5  | 59.2  | 58.7   | 59.2  |
| 75°   | 52.6  | 52.2  | 51.3  | 50.4  | 50.8  | 49.5  | 48.2  | 47.8  | 47.8  | 46.9   | 46.9  |
| 77.5° | 40.3  | 41.2  | 39.4  | 39.0  | 38.1  | 37.3  | 36.8  | 36.4  | 36.4  | 36.4   | 37.3  |
| 80°   | 28.0  | 28.5  | 28.5  | 27.6  | 28.0  | 26.7  | 26.7  | 26.7  | 25.4  | 25.9   | 26.3  |
| 82.5° | 18.0  | 18.0  | 17.5  | 18.0  | 17.5  | 17.5  | 17.1  | 17.1  | 16.7  | 16.7   | 17.1  |
| 85°   | 10.1  | 9.6   | 9.2   | 10.1  | 9.6   | 9.6   | 9.2   | 9.2   | 9.2   | 9.2    | 9.2   |
| 87.5° | 2.2   | 2.6   | 2.6   | 2.6   | 2.6   | 3.1   | 3.1   | 3.1   | 3.5   | 3.5    | 3.5   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0    | 0.0   |

TEST NUMBER: P987601

CATALOG NUMBER: S122DW-B290DB2750-4F0-XX-W2A-A\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 345°  | 350°  | 355°  | 360°  |
|-------|-------|-------|-------|-------|
| 0°    | 570.2 | 570.2 | 570.2 | 570.2 |
| 2.5°  | 559.7 | 559.7 | 566.2 | 573.3 |
| 5°    | 547.4 | 550.5 | 561.0 | 570.6 |
| 7.5°  | 535.6 | 540.8 | 554.0 | 566.2 |
| 10°   | 521.1 | 528.1 | 544.3 | 558.8 |
| 12.5° | 507.1 | 513.6 | 532.5 | 548.7 |
| 15°   | 487.4 | 495.7 | 515.8 | 536.0 |
| 17.5° | 467.6 | 476.0 | 500.5 | 524.2 |
| 20°   | 444.4 | 455.4 | 483.0 | 514.5 |
| 22.5° | 422.9 | 436.5 | 467.2 | 492.6 |
| 25°   | 399.3 | 420.3 | 448.8 | 481.7 |
| 27.5° | 378.2 | 399.3 | 428.2 | 461.5 |
| 30°   | 354.6 | 376.0 | 405.8 | 436.5 |
| 32.5° | 331.8 | 351.5 | 380.4 | 418.1 |
| 35°   | 308.1 | 326.9 | 355.0 | 393.1 |
| 37.5° | 286.6 | 305.0 | 335.7 | 370.8 |
| 40°   | 265.6 | 284.9 | 311.2 | 346.2 |
| 42.5° | 245.9 | 263.0 | 286.6 | 321.7 |
| 45°   | 227.9 | 240.2 | 262.1 | 295.0 |
| 47.5° | 209.1 | 220.0 | 240.2 | 273.0 |
| 50°   | 191.5 | 200.7 | 218.3 | 248.9 |
| 52.5° | 174.4 | 182.3 | 198.5 | 223.1 |
| 55°   | 159.1 | 166.5 | 178.4 | 202.5 |
| 57.5° | 143.3 | 149.0 | 160.4 | 179.7 |
| 60°   | 128.0 | 133.2 | 142.4 | 158.2 |
| 62.5° | 112.6 | 117.0 | 125.8 | 138.5 |
| 65°   | 99.0  | 102.6 | 109.1 | 120.1 |
| 67.5° | 85.9  | 88.1  | 93.4  | 102.1 |
| 70°   | 73.2  | 74.9  | 79.3  | 86.3  |
| 72.5° | 59.6  | 61.4  | 66.2  | 71.0  |
| 75°   | 48.2  | 48.6  | 52.2  | 56.1  |
| 77.5° | 37.7  | 37.3  | 39.9  | 43.0  |
| 80°   | 25.9  | 27.2  | 29.4  | 30.7  |
| 82.5° | 17.5  | 18.0  | 18.8  | 19.7  |
| 85°   | 9.6   | 10.1  | 10.1  | 11.4  |
| 87.5° | 3.9   | 4.4   | 4.4   | 4.8   |
| 90°   | 0.0   | 0.0   | 0.0   | 0.0   |

(END OF REPORT)