

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030830

Luminaire Tested: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030830
REPORT IS A COMBINATION OF REPORTS P991336 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7536.0 lumens
Efficiency: N/A
Efficacy: 115.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030830

CATALOG NUMBER: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1030830

CATALOG NUMBER: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	88	88	88	88	66	66	66	45	45	45	27	27	27	18		
1	91	86	83	79	80	76	73	70	57	55	53	40	39	38	24	23	23	15		
2	82	75	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13		
3	75	66	59	54	66	59	53	48	44	40	37	31	28	26	18	17	16	11		
4	69	58	51	45	60	52	45	41	39	35	31	27	25	22	16	15	14	9		
5	63	52	44	38	55	46	39	35	35	30	27	24	22	19	15	13	12	8		
6	58	46	39	33	51	41	35	30	31	27	23	22	19	17	13	12	10	7		
7	53	42	34	29	47	37	30	26	28	24	20	20	17	15	12	10	9	6		
8	49	38	30	25	43	33	27	23	25	21	18	18	15	13	11	9	8	6		
9	46	34	27	22	40	30	24	20	23	19	16	16	14	12	10	9	7	5		
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	5		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5628	5628	5628
5°	5643	5435	5427
10°	5593	5251	5197
15°	5515	5060	4947
20°	5426	4847	4699
25°	5311	4623	4433
30°	5184	4391	4154
35°	5052	4155	3877
40°	4913	3905	3604
45°	4761	3664	3320
50°	4607	3393	3033
55°	4408	3112	2745
60°	4203	2800	2437
65°	4010	2466	2114
70°	3734	2093	1739
75°	3336	1656	1350
80°	2883	1164	956
85°	2248	627	479

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4761 cd/sqm

TEST NUMBER: P1030830

CATALOG NUMBER: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.3	0.7
10°-20°	139.2	1.8
20°-30°	205.6	2.7
30°-40°	240.1	3.2
40°-50°	241.4	3.2
50°-60°	212.1	2.8
60°-70°	157.9	2.1
70°-80°	89.9	1.2
80°-90°	29.6	0.4
90°-100°	71.4	0.9
100°-110°	345.1	4.6
110°-120°	845.7	11.2
120°-130°	1073.6	14.2
130°-140°	1146.9	15.2
140°-150°	1072.5	14.2
150°-160°	865.1	11.5
160°-170°	558.3	7.4
170°-180°	192.4	2.6
0°-30°	394.1	5.2
0°-40°	634.2	8.4
0°-60°	1087.7	14.4
0°-90°	1365.0	18.1
90°-120°	1262.2	16.7
90°-150°	4555.2	60.4
90°-180°	6171.0	81.9
0°-180°	7536.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	523	523	523	523	523	
5°	523	521	516	521	520	50
15°	498	496	491	494	492	140
25°	452	450	444	444	443	208
35°	391	388	383	380	378	245
45°	321	319	313	308	305	248
55°	243	243	237	232	230	218
65°	166	164	159	156	154	164
75°	88	86	84	82	81	94
85°	23	22	22	22	22	25
90°	2	16	36	42	45	7
95°	92	30	47	57	57	110
105°	448	465	329	63	66	475
115°	841	850	863	878	884	830
125°	1185	1197	1203	1206	1209	1059
135°	1475	1484	1490	1495	1490	1136
145°	1702	1713	1716	1719	1719	1066
155°	1875	1872	1874	1881	1872	864
165°	1978	1973	1972	1984	1973	559
175°	2024	2017	2018	2029	2017	193
180°	2024	2024	2024	2024	2024	

TEST NUMBER: P1030830

CATALOG NUMBER: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	522.9	522.9	522.9	522.9	522.9
2.5°	525.2	523.4	518.5	522.9	522.5
5°	523.4	521.1	516.2	520.7	519.8
7.5°	519.4	517.1	512.2	516.2	515.8
10°	514.0	511.7	505.9	509.9	509.0
12.5°	506.8	505.0	499.6	502.3	501.8
15°	498.2	496.4	490.6	494.2	491.5
17.5°	488.8	486.5	480.7	483.4	482.5
20°	478.0	475.3	469.4	471.2	469.9
22.5°	465.8	463.1	457.3	458.6	456.8
25°	452.4	449.7	443.8	444.3	442.9
27.5°	438.4	435.7	429.4	429.9	428.5
30°	423.1	420.9	414.6	414.6	411.4
32.5°	407.8	404.7	400.2	397.0	395.7
35°	391.2	388.5	382.7	380.0	377.7
37.5°	374.6	371.0	365.1	362.0	360.6
40°	357.0	354.3	348.0	344.4	342.6
42.5°	339.5	336.3	330.0	326.4	324.6
45°	320.6	318.8	313.0	307.6	305.3
47.5°	302.2	299.5	294.1	288.7	286.9
50°	283.3	281.0	275.2	270.2	267.5
52.5°	263.5	262.1	255.9	251.8	249.1
55°	243.3	242.8	237.0	232.0	229.8
57.5°	224.4	222.6	218.1	213.6	210.9
60°	203.7	203.2	197.8	193.8	191.6
62.5°	185.3	183.9	178.5	174.5	173.1
65°	165.9	163.7	159.2	155.6	154.2
67.5°	145.2	143.4	139.8	136.7	134.9
70°	126.8	124.1	121.4	118.3	116.0
72.5°	107.5	105.7	102.5	99.8	98.9
75°	87.7	85.9	84.5	82.3	80.9
77.5°	70.1	69.2	67.4	65.6	65.6
80°	53.1	51.7	50.8	50.4	50.4
82.5°	36.4	36.4	36.4	35.5	35.1
85°	23.4	22.5	22.5	21.6	21.6
87.5°	11.7	10.3	9.9	9.4	9.4
90°	1.5	16.5	36.1	42.1	45.1
92.5°	34.6	25.6	39.1	49.6	51.1
95°	91.7	30.1	46.6	57.1	57.1
97.5°	166.9	124.8	48.1	60.2	61.7
100°	254.2	284.2	49.6	61.7	63.2
102.5°	353.4	373.0	111.3	61.7	64.7
105°	448.2	464.7	329.3	63.2	66.2
107.5°	548.9	562.4	585.0	353.4	156.4
110°	649.7	661.7	678.2	628.6	413.6

TEST NUMBER: P1030830

CATALOG NUMBER: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	745.9	756.4	773.0	786.5	783.5
115°	840.7	849.7	863.2	878.3	884.3
117.5°	933.9	944.4	951.9	964.0	965.5
120°	1019.6	1033.2	1037.7	1049.7	1049.7
122.5°	1106.8	1117.4	1123.4	1130.9	1132.4
125°	1185.0	1197.1	1203.1	1206.1	1209.1
127.5°	1263.2	1275.3	1282.8	1287.3	1284.3
130°	1335.4	1347.5	1353.5	1359.5	1356.5
132.5°	1404.6	1416.6	1421.2	1427.2	1422.7
135°	1475.3	1484.3	1490.3	1494.8	1490.3
137.5°	1535.4	1547.5	1550.5	1558.0	1555.0
140°	1595.6	1604.6	1609.1	1615.2	1612.1
142.5°	1651.2	1660.3	1664.8	1669.3	1664.8
145°	1702.4	1712.9	1715.9	1718.9	1718.9
147.5°	1752.0	1759.5	1762.5	1765.5	1758.0
150°	1797.1	1801.6	1804.6	1807.6	1803.1
152.5°	1837.7	1839.2	1840.7	1846.7	1839.2
155°	1875.3	1872.3	1873.8	1881.3	1872.3
157.5°	1905.4	1905.4	1903.9	1912.9	1900.9
160°	1932.5	1931.0	1929.5	1938.5	1928.0
162.5°	1958.0	1953.5	1952.0	1962.5	1953.5
165°	1977.6	1973.1	1971.6	1983.6	1973.1
167.5°	1994.1	1988.1	1988.1	2000.1	1988.1
170°	2007.7	2001.6	2001.6	2013.7	2001.6
172.5°	2016.7	2009.2	2010.7	2022.7	2009.2
175°	2024.2	2016.7	2018.2	2028.7	2016.7
177.5°	2027.2	2019.7	2021.2	2033.2	2018.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2

(END OF REPORT)