

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030831

Luminaire Tested: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030831
REPORT IS A COMBINATION OF REPORTS P991337 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7602.0 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030831

CATALOG NUMBER: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030831

CATALOG NUMBER: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	100	100	100	100	88	88	88	88	66	66	66	45	45	45	27	27	27	18		
1	91	86	83	79	80	76	73	70	57	55	53	40	39	38	24	23	23	15		
2	82	75	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13		
3	75	66	59	54	66	59	53	48	44	40	37	31	28	26	18	17	16	11		
4	69	58	51	45	60	52	45	41	39	35	31	27	25	22	16	15	14	9		
5	63	52	44	38	55	46	39	35	35	30	27	24	22	19	15	13	12	8		
6	58	46	39	33	51	41	35	30	31	27	23	22	19	17	13	12	10	7		
7	53	42	34	29	47	37	30	26	28	24	20	20	17	15	12	10	9	6		
8	49	38	30	25	43	33	27	23	25	21	18	18	15	13	11	9	8	6		
9	46	34	27	22	40	30	24	20	23	19	16	16	14	12	10	9	7	5		
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	5		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5679	5679	5679
5°	5693	5483	5475
10°	5642	5297	5243
15°	5564	5104	4990
20°	5474	4890	4740
25°	5357	4664	4472
30°	5230	4429	4191
35°	5096	4190	3911
40°	4957	3940	3637
45°	4803	3695	3349
50°	4647	3423	3061
55°	4446	3140	2769
60°	4240	2826	2457
65°	4047	2487	2133
70°	3767	2112	1754
75°	3366	1672	1363
80°	2904	1176	963
85°	2267	632	483

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4803 cd/sqm

TEST NUMBER: P1030831

CATALOG NUMBER: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	49.7	0.7
10°-20°	140.4	1.8
20°-30°	207.4	2.7
30°-40°	242.2	3.2
40°-50°	243.5	3.2
50°-60°	213.9	2.8
60°-70°	159.3	2.1
70°-80°	90.7	1.2
80°-90°	29.9	0.4
90°-100°	72.0	0.9
100°-110°	348.1	4.6
110°-120°	853.1	11.2
120°-130°	1083.0	14.2
130°-140°	1156.9	15.2
140°-150°	1081.9	14.2
150°-160°	872.6	11.5
160°-170°	563.2	7.4
170°-180°	194.1	2.6
0°-30°	397.6	5.2
0°-40°	639.8	8.4
0°-60°	1097.2	14.4
0°-90°	1377.1	18.1
90°-120°	1273.3	16.7
90°-150°	4595.1	60.4
90°-180°	6225.0	81.9
0°-180°	7602.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	528	528	528	528	528	
5°	528	526	521	525	524	50
15°	503	501	495	498	496	142
25°	456	454	448	448	447	210
35°	395	392	386	383	381	247
45°	323	322	316	310	308	250
55°	245	245	239	234	232	220
65°	167	165	161	157	156	165
75°	88	87	85	83	82	94
85°	24	23	23	22	22	25
90°	2	17	36	42	46	7
95°	92	30	47	58	58	111
105°	452	469	332	64	67	479
115°	848	857	871	886	892	837
125°	1195	1208	1214	1217	1220	1068
135°	1488	1497	1503	1508	1503	1146
145°	1717	1728	1731	1734	1734	1075
155°	1892	1889	1890	1898	1889	872
165°	1995	1990	1989	2001	1990	564
175°	2042	2034	2036	2046	2034	194
180°	2042	2042	2042	2042	2042	

TEST NUMBER: P1030831

CATALOG NUMBER: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	527.6	527.6	527.6	527.6	527.6
2.5°	529.8	528.0	523.0	527.6	527.1
5°	528.0	525.7	520.8	525.3	524.4
7.5°	523.9	521.7	516.7	520.8	520.3
10°	518.5	516.2	510.3	514.4	513.5
12.5°	511.2	509.4	504.0	506.7	506.2
15°	502.6	500.8	494.9	498.5	495.8
17.5°	493.1	490.8	484.9	487.6	486.7
20°	482.2	479.5	473.6	475.4	474.0
22.5°	469.9	467.2	461.3	462.7	460.9
25°	456.3	453.6	447.7	448.2	446.8
27.5°	442.3	439.6	433.2	433.7	432.3
30°	426.9	424.6	418.2	418.2	415.1
32.5°	411.4	408.3	403.7	400.5	399.2
35°	394.6	391.9	386.0	383.3	381.0
37.5°	377.9	374.2	368.3	365.2	363.8
40°	360.2	357.5	351.1	347.5	345.7
42.5°	342.5	339.3	333.0	329.3	327.5
45°	323.4	321.6	315.7	310.3	308.0
47.5°	304.8	302.1	296.7	291.2	289.4
50°	285.8	283.5	277.6	272.6	269.9
52.5°	265.8	264.5	258.1	254.0	251.3
55°	245.4	245.0	239.1	234.1	231.8
57.5°	226.4	224.5	220.0	215.5	212.7
60°	205.5	205.0	199.6	195.5	193.2
62.5°	186.9	185.5	180.1	176.0	174.6
65°	167.4	165.1	160.6	157.0	155.6
67.5°	146.5	144.7	141.1	137.9	136.1
70°	127.9	125.2	122.5	119.3	117.0
72.5°	108.4	106.6	103.4	100.7	99.8
75°	88.5	86.6	85.3	83.0	81.7
77.5°	70.8	69.9	68.0	66.2	66.2
80°	53.5	52.2	51.3	50.8	50.8
82.5°	36.7	36.7	36.7	35.8	35.4
85°	23.6	22.7	22.7	21.8	21.8
87.5°	11.8	10.4	10.0	9.5	9.5
90°	1.5	16.7	36.4	42.5	45.5
92.5°	34.9	25.8	39.4	50.1	51.6
95°	92.5	30.3	47.0	57.6	57.6
97.5°	168.4	125.9	48.5	60.7	62.2
100°	256.4	286.7	50.1	62.2	63.7
102.5°	356.5	376.2	112.3	62.2	65.2
105°	452.1	468.8	332.2	63.7	66.7
107.5°	553.7	567.4	590.1	356.5	157.8
110°	655.4	667.5	684.2	634.1	417.2

TEST NUMBER: P1030831

CATALOG NUMBER: S123DIW-B340D1535UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	752.4	763.1	779.7	793.4	790.4
115°	848.0	857.1	870.8	885.9	892.0
117.5°	942.1	952.7	960.3	972.4	973.9
120°	1028.5	1042.2	1046.7	1058.9	1058.9
122.5°	1116.5	1127.1	1133.2	1140.8	1142.3
125°	1195.4	1207.5	1213.6	1216.6	1219.7
127.5°	1274.3	1286.4	1294.0	1298.6	1295.5
130°	1347.1	1359.2	1365.3	1371.4	1368.3
132.5°	1416.9	1429.0	1433.6	1439.6	1435.1
135°	1488.2	1497.3	1503.4	1507.9	1503.4
137.5°	1548.9	1561.0	1564.0	1571.6	1568.6
140°	1609.6	1618.7	1623.2	1629.3	1626.2
142.5°	1665.7	1674.8	1679.3	1683.9	1679.3
145°	1717.3	1727.9	1730.9	1734.0	1734.0
147.5°	1767.3	1774.9	1777.9	1781.0	1773.4
150°	1812.8	1817.4	1820.4	1823.5	1818.9
152.5°	1853.8	1855.3	1856.8	1862.9	1855.3
155°	1891.7	1888.7	1890.2	1897.8	1888.7
157.5°	1922.1	1922.1	1920.5	1929.6	1917.5
160°	1949.4	1947.9	1946.3	1955.4	1944.8
162.5°	1975.2	1970.6	1969.1	1979.7	1970.6
165°	1994.9	1990.3	1988.8	2000.9	1990.3
167.5°	2011.6	2005.5	2005.5	2017.6	2005.5
170°	2025.2	2019.2	2019.2	2031.3	2019.2
172.5°	2034.3	2026.7	2028.3	2040.4	2026.7
175°	2041.9	2034.3	2035.8	2046.5	2034.3
177.5°	2044.9	2037.4	2038.9	2051.0	2035.8
180°	2041.9	2041.9	2041.9	2041.9	2041.9

(END OF REPORT)