

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P982671

Luminaire Tested: S122IW-B1240UB2750-4F0-XX-W2A-1\_3000K

Issue Date: 5/2/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P982671  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/2/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122IW-B1240UB2750-4F0-XX-W2A-1\_3000K  
Description: Define 2 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4302.0 lumens  
Efficiency: N/A  
Efficacy: 102.2 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 42.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P982671

CATALOG NUMBER: S122IW-B1240UB2750-4F0-XX-W2A-1\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P982671

CATALOG NUMBER: S122IW-B1240UB2750-4F0-XX-W2A-1\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80 |    |    |    | 70 |    |    |    | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 95 | 95 | 95 | 95 | 81 | 81 | 81 | 81 | 56 | 56 | 56 | 32 | 32 | 32 | 10 | 10 | 10 |
| 1   | 87 | 83 | 79 | 76 | 74 | 71 | 68 | 65 | 48 | 47 | 45 | 28 | 27 | 26 | 9  | 9  | 8  |
| 2   | 79 | 72 | 66 | 62 | 67 | 62 | 57 | 53 | 42 | 40 | 37 | 24 | 23 | 22 | 8  | 7  | 7  |
| 3   | 72 | 63 | 56 | 51 | 61 | 54 | 49 | 44 | 37 | 34 | 31 | 21 | 20 | 18 | 7  | 6  | 6  |
| 4   | 65 | 56 | 48 | 43 | 56 | 48 | 42 | 37 | 33 | 29 | 26 | 19 | 17 | 16 | 6  | 6  | 5  |
| 5   | 60 | 49 | 42 | 36 | 51 | 42 | 36 | 32 | 29 | 25 | 22 | 17 | 15 | 13 | 5  | 5  | 4  |
| 6   | 55 | 44 | 36 | 31 | 47 | 38 | 32 | 27 | 26 | 22 | 19 | 15 | 13 | 11 | 5  | 4  | 4  |
| 7   | 50 | 39 | 32 | 27 | 43 | 34 | 28 | 23 | 23 | 19 | 17 | 14 | 11 | 10 | 4  | 4  | 3  |
| 8   | 47 | 35 | 28 | 23 | 40 | 30 | 24 | 20 | 21 | 17 | 14 | 12 | 10 | 9  | 4  | 3  | 3  |
| 9   | 43 | 32 | 25 | 20 | 37 | 27 | 22 | 18 | 19 | 15 | 13 | 11 | 9  | 8  | 4  | 3  | 3  |
| 10  | 40 | 29 | 22 | 18 | 34 | 25 | 19 | 16 | 17 | 14 | 11 | 10 | 8  | 7  | 3  | 3  | 2  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0° | 45° | 90° |
|-----|----|-----|-----|
| 0°  | 0  | 0   | 0   |
| 5°  | 0  | 0   | 0   |
| 10° | 0  | 0   | 0   |
| 15° | 0  | 0   | 0   |
| 20° | 0  | 0   | 0   |
| 25° | 0  | 0   | 0   |
| 30° | 0  | 0   | 0   |
| 35° | 0  | 0   | 0   |
| 40° | 0  | 0   | 0   |
| 45° | 0  | 0   | 0   |
| 50° | 0  | 0   | 0   |
| 55° | 0  | 0   | 0   |
| 60° | 0  | 0   | 0   |
| 65° | 0  | 0   | 0   |
| 70° | 0  | 0   | 0   |
| 75° | 0  | 0   | 0   |
| 80° | 0  | 0   | 0   |
| 85° | 0  | 0   | 0   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 0°  
Luminance: 0 cd/sqm

TEST NUMBER: P982671

CATALOG NUMBER: S122IW-B1240UB2750-4F0-XX-W2A-1\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 0.0    | 0.0       |
| 10°-20°   | 0.0    | 0.0       |
| 20°-30°   | 0.0    | 0.0       |
| 30°-40°   | 0.0    | 0.0       |
| 40°-50°   | 0.0    | 0.0       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 4.4    | 0.1       |
| 90°-100°  | 95.1   | 2.2       |
| 100°-110° | 302.3  | 7.0       |
| 110°-120° | 517.3  | 12.0      |
| 120°-130° | 680.3  | 15.8      |
| 130°-140° | 763.6  | 17.7      |
| 140°-150° | 748.8  | 17.4      |
| 150°-160° | 628.1  | 14.6      |
| 160°-170° | 416.6  | 9.7       |
| 170°-180° | 145.6  | 3.4       |
| 0°-30°    | 0.0    | 0.0       |
| 0°-40°    | 0.0    | 0.0       |
| 0°-60°    | 0.0    | 0.0       |
| 0°-90°    | 4.4    | 0.1       |
| 90°-120°  | 914.6  | 21.3      |
| 90°-150°  | 3107.3 | 72.2      |
| 90°-180°  | 4298.0 | 99.9      |
| 0°-180°   | 4302.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°   | 22.5° | 45°  | 67.5° | 90°  | Flux |
|------|------|-------|------|-------|------|------|
| 0°   | 0    | 0     | 0    | 0     | 0    |      |
| 5°   | 0    | 0     | 0    | 0     | 0    | 0    |
| 15°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 25°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 35°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 45°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 55°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 65°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 75°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 85°  | 0    | 0     | 0    | 0     | 0    | 0    |
| 90°  | 1    | 17    | 45   | 43    | 44   | 4    |
| 95°  | 68   | 80    | 83   | 83    | 80   | 75   |
| 105° | 279  | 283   | 285  | 288   | 288  | 294  |
| 115° | 519  | 527   | 524  | 523   | 519  | 513  |
| 125° | 755  | 767   | 763  | 759   | 758  | 675  |
| 135° | 977  | 991   | 994  | 992   | 988  | 755  |
| 145° | 1186 | 1195  | 1202 | 1204  | 1199 | 741  |
| 155° | 1356 | 1360  | 1363 | 1370  | 1366 | 624  |
| 165° | 1475 | 1474  | 1474 | 1483  | 1476 | 416  |
| 175° | 1535 | 1531  | 1528 | 1537  | 1529 | 146  |
| 180° | 1537 | 1537  | 1537 | 1537  | 1537 |      |

TEST NUMBER: P982671

CATALOG NUMBER: S122IW-B1240UB2750-4F0-XX-W2A-1\_3000K

**CANDELA DISTRIBUTION (FULL):**

|        | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|--------|-------|-------|-------|-------|-------|
| 0°     | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 2.5°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 5°     | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 7.5°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 10°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 12.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 15°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 17.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 20°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 22.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 25°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 1.3   | 16.9  | 45.4  | 42.8  | 44.1  |
| 92.5°  | 28.5  | 38.9  | 40.2  | 41.5  | 41.5  |
| 95°    | 67.5  | 80.4  | 83.0  | 83.0  | 80.4  |
| 97.5°  | 112.9 | 124.5 | 129.7 | 129.7 | 129.7 |
| 100°   | 164.7 | 175.1 | 179.0 | 179.0 | 177.7 |
| 102.5° | 219.2 | 227.0 | 232.2 | 233.5 | 232.2 |
| 105°   | 278.9 | 282.8 | 285.4 | 288.0 | 288.0 |
| 107.5° | 338.6 | 343.8 | 343.8 | 345.1 | 338.6 |
| 110°   | 395.6 | 403.4 | 403.4 | 403.4 | 399.5 |

TEST NUMBER: P982671

CATALOG NUMBER: S122IW-B1240UB2750-4F0-XX-W2A-1\_3000K

**CANDELA DISTRIBUTION (continued):**

|        | 0°     | 22.5°  | 45°    | 67.5°  | 90°    |
|--------|--------|--------|--------|--------|--------|
| 112.5° | 457.9  | 465.7  | 464.4  | 460.5  | 457.9  |
| 115°   | 518.9  | 526.7  | 524.1  | 522.8  | 518.9  |
| 117.5° | 579.8  | 590.2  | 583.7  | 579.8  | 576.0  |
| 120°   | 640.8  | 651.2  | 640.8  | 640.8  | 636.9  |
| 122.5° | 696.6  | 709.6  | 703.1  | 699.2  | 696.6  |
| 125°   | 755.0  | 766.6  | 762.7  | 758.9  | 757.6  |
| 127.5° | 812.0  | 826.3  | 821.1  | 815.9  | 812.0  |
| 130°   | 865.2  | 882.1  | 879.5  | 876.9  | 871.7  |
| 132.5° | 924.9  | 937.9  | 939.2  | 932.7  | 928.8  |
| 135°   | 976.8  | 991.1  | 993.6  | 992.3  | 988.5  |
| 137.5° | 1033.9 | 1045.5 | 1048.1 | 1046.8 | 1041.6 |
| 140°   | 1084.4 | 1096.1 | 1102.6 | 1102.6 | 1097.4 |
| 142.5° | 1136.3 | 1148.0 | 1151.9 | 1153.2 | 1148.0 |
| 145°   | 1185.6 | 1194.7 | 1202.5 | 1203.8 | 1198.6 |
| 147.5° | 1229.7 | 1241.4 | 1246.6 | 1249.2 | 1244.0 |
| 150°   | 1275.1 | 1282.9 | 1288.1 | 1292.0 | 1288.1 |
| 152.5° | 1315.3 | 1323.1 | 1329.6 | 1334.8 | 1329.6 |
| 155°   | 1355.6 | 1359.5 | 1363.3 | 1369.8 | 1365.9 |
| 157.5° | 1390.6 | 1393.2 | 1395.8 | 1404.9 | 1398.4 |
| 160°   | 1421.7 | 1424.3 | 1425.6 | 1433.4 | 1428.2 |
| 162.5° | 1450.3 | 1450.3 | 1451.6 | 1460.6 | 1454.1 |
| 165°   | 1474.9 | 1473.6 | 1473.6 | 1482.7 | 1476.2 |
| 167.5° | 1497.0 | 1493.1 | 1493.1 | 1502.1 | 1495.7 |
| 170°   | 1513.8 | 1509.9 | 1508.6 | 1517.7 | 1509.9 |
| 172.5° | 1525.5 | 1521.6 | 1520.3 | 1529.4 | 1521.6 |
| 175°   | 1534.6 | 1530.7 | 1528.1 | 1537.2 | 1529.4 |
| 177.5° | 1539.8 | 1535.9 | 1533.3 | 1541.1 | 1533.3 |
| 180°   | 1537.2 | 1537.2 | 1537.2 | 1537.2 | 1537.2 |



TEST NUMBER: P982671

CATALOG NUMBER: S122IW-B1240UB2750-4F0-XX-W2A-1\_3000K

**CIE UGR TABLE:**

| Reflectances:   |      |                  |      |      |      |      |                |      |      |      |      |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling         |      | 0.7              | 0.7  | 0.5  | 0.5  | 0.3  | 0.7            | 0.7  | 0.5  | 0.5  | 0.3  |
| Wall            |      | 0.5              | 0.3  | 0.5  | 0.3  | 0.3  | 0.5            | 0.3  | 0.5  | 0.3  | 0.3  |
| Reference plane |      | 0.2              | 0.2  | 0.2  | 0.2  | 0.2  | 0.2            | 0.2  | 0.2  | 0.2  | 0.2  |
| Room dimensions |      | Viewed crosswise |      |      |      |      | Viewed endwise |      |      |      |      |
| X=2H            | Y=2H | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 3H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 12H  | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
| 4H              | 2H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 3H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 12H  | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
| 8H              | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 12H  | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
| 12H             | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |

END OF REPORT