

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030856

Luminaire Tested: S123DIW-B340D755UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030856
REPORT IS A COMBINATION OF REPORTS P991462 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B340D755UB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4473.0 lumens
Efficiency: N/A
Efficacy: 123.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030856

CATALOG NUMBER: S123DIW-B340D755UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030856

CATALOG NUMBER: S123DIW-B340D755UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37
1	92	88	84	80	82	79	75	72	62	59	57	46	44	43	31	30	30
2	84	76	70	65	75	68	63	59	54	50	47	40	37	35	27	26	24
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	21
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	18
5	64	52	44	38	57	47	40	35	37	32	28	28	24	22	19	17	15
6	59	47	39	33	52	42	35	30	33	28	24	25	21	19	17	15	13
7	54	42	34	29	48	38	31	26	30	25	21	23	19	16	16	13	12
8	50	38	30	25	45	34	28	23	27	22	19	21	17	15	14	12	10
9	46	34	27	22	41	31	25	20	25	20	17	19	15	13	13	11	9
10	43	31	24	20	39	28	22	18	23	18	15	17	14	12	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4481	4481	4481
5°	4493	4349	4346
10°	4451	4232	4199
15°	4392	4102	4044
20°	4308	3957	3877
25°	4205	3793	3704
30°	4101	3646	3530
35°	3981	3490	3389
40°	3869	3349	3239
45°	3744	3211	3116
50°	3620	3075	2982
55°	3484	2936	2859
60°	3349	2793	2733
65°	3213	2641	2586
70°	3004	2470	2433
75°	2743	2276	2277
80°	2438	2079	2098
85°	2132	1919	1970

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3744 cd/sqm

TEST NUMBER: P1030856

CATALOG NUMBER: S123DIW-B340D755UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.5	0.9
10°-20°	112.6	2.5
20°-30°	168.3	3.8
30°-40°	201.0	4.5
40°-50°	210.3	4.7
50°-60°	197.3	4.4
60°-70°	164.8	3.7
70°-80°	117.9	2.6
80°-90°	72.1	1.6
90°-100°	79.6	1.8
100°-110°	204.2	4.6
110°-120°	442.6	9.9
120°-130°	546.8	12.2
130°-140°	576.5	12.9
140°-150°	535.1	12.0
150°-160°	430.6	9.6
160°-170°	277.9	6.2
170°-180°	95.8	2.1
0°-30°	320.4	7.2
0°-40°	521.4	11.7
0°-60°	929.0	20.8
0°-90°	1283.9	28.7
90°-120°	726.4	16.2
90°-150°	2384.8	53.3
90°-180°	3189.0	71.3
0°-180°	4473.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	416	416	416	416	416	
5°	417	416	413	417	416	40
15°	397	398	398	402	402	112
25°	358	363	364	370	370	165
35°	308	316	322	328	330	193
45°	252	263	274	283	287	194
55°	192	207	224	236	239	172
65°	133	150	170	184	189	131
75°	72	93	116	131	136	77
85°	22	45	69	84	89	23
90°	7	36	69	88	94	7
95°	51	38	68	87	92	58
105°	227	246	198	78	84	240
115°	421	431	454	472	479	416
125°	591	597	613	624	629	528
135°	735	739	747	758	758	566
145°	848	853	854	859	861	531
155°	934	932	933	937	932	430
165°	984	982	982	988	982	278
175°	1008	1004	1005	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1030856

CATALOG NUMBER: S123DIW-B340D755UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	416.3	416.3	416.3	416.3	416.3
2.5°	418.5	417.2	413.6	417.2	416.7
5°	416.7	415.8	413.1	416.7	416.3
7.5°	413.6	413.6	410.8	415.4	414.9
10°	409.0	409.9	407.7	412.2	411.3
12.5°	403.6	404.9	403.6	407.7	406.7
15°	396.8	398.1	397.7	402.2	401.8
17.5°	388.6	391.3	390.9	395.0	394.1
20°	379.5	382.3	383.2	387.3	387.7
22.5°	370.0	372.7	374.1	379.5	379.1
25°	358.2	362.8	364.1	370.0	370.0
27.5°	346.9	351.9	354.6	359.6	360.0
30°	334.7	340.5	344.2	349.6	349.6
32.5°	321.0	327.8	332.8	338.7	340.1
35°	308.3	315.6	321.5	328.3	330.1
37.5°	294.7	302.9	309.7	317.4	318.8
40°	281.1	289.3	298.4	306.1	307.9
42.5°	266.2	276.6	286.1	294.7	297.5
45°	252.1	263.0	274.3	283.0	286.6
47.5°	237.2	249.4	262.1	271.6	274.3
50°	222.6	235.3	249.4	259.8	263.0
52.5°	207.2	220.8	236.7	247.6	251.7
55°	192.3	207.2	223.6	235.8	239.4
57.5°	177.8	193.2	210.9	223.1	227.2
60°	162.3	178.7	197.3	209.9	214.9
62.5°	147.8	164.6	184.6	197.3	201.8
65°	132.9	150.5	170.5	184.1	188.6
67.5°	117.9	136.5	156.4	171.4	175.0
70°	102.0	121.5	143.3	157.8	162.3
72.5°	87.5	107.0	129.7	144.7	149.2
75°	72.1	93.4	116.1	131.0	136.5
77.5°	58.9	80.3	102.9	118.8	122.9
80°	44.9	67.1	90.7	106.1	110.6
82.5°	32.6	55.3	79.4	94.8	99.3
85°	22.2	44.9	68.9	84.3	88.9
87.5°	13.6	36.3	59.4	74.8	79.4
90°	6.6	36.3	69.2	87.7	93.7
92.5°	22.6	37.6	67.1	87.3	92.2
95°	50.7	37.7	68.1	87.3	91.9
97.5°	87.6	83.0	66.2	85.7	91.0
100°	130.6	160.1	64.2	83.3	88.5
102.5°	179.5	202.0	92.1	80.1	86.2
105°	226.7	245.8	198.0	78.1	83.7
107.5°	276.5	292.7	322.5	219.4	125.5
110°	326.1	340.3	366.6	353.7	250.3

TEST NUMBER: P1030856

CATALOG NUMBER: S123DIW-B340D755UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	374.0	385.7	411.1	429.1	431.7
115°	420.8	430.7	453.7	472.1	478.7
117.5°	467.2	476.0	495.2	512.1	516.4
120°	509.4	518.4	535.6	552.1	555.2
122.5°	552.8	558.9	576.0	589.8	593.6
125°	591.3	597.3	613.4	624.4	629.1
127.5°	630.3	635.8	650.8	662.1	663.8
130°	666.2	671.7	683.8	695.4	696.6
132.5°	700.1	706.1	715.2	726.4	727.2
135°	735.3	739.4	747.3	757.8	757.8
137.5°	765.3	770.9	775.5	786.5	787.3
140°	794.8	799.3	802.9	812.6	813.4
142.5°	822.5	826.5	828.8	836.9	837.0
145°	848.0	852.7	854.2	859.3	861.1
147.5°	872.2	875.9	877.4	880.3	878.4
150°	894.6	896.9	898.4	899.9	898.5
152.5°	914.8	915.6	916.3	919.3	915.6
155°	933.6	932.1	932.8	936.6	932.1
157.5°	948.5	948.5	947.8	952.3	946.3
160°	962.0	961.3	960.5	965.0	959.8
162.5°	974.7	972.5	971.7	977.0	972.5
165°	984.5	982.2	981.5	987.5	982.2
167.5°	992.7	989.7	989.7	995.7	989.7
170°	999.4	996.4	996.4	1002.4	996.4
172.5°	1003.9	1000.2	1000.9	1006.9	1000.2
175°	1007.7	1003.9	1004.7	1009.9	1003.9
177.5°	1009.2	1005.4	1006.2	1012.2	1004.7
180°	1007.7	1007.7	1007.7	1007.7	1007.7

(END OF REPORT)