

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030921

Luminaire Tested: S123DIW-B560D460UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030921
REPORT IS A COMBINATION OF REPORTS P991733 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D460UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4174.0 lumens
Efficiency: N/A
Efficacy: 112.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 37.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030921

CATALOG NUMBER: S123DIW-B560D460UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030921

CATALOG NUMBER: S123DIW-B560D460UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	87	92	88	85	81	76	73	71	64	62	61	54	53	51
2	90	83	76	71	83	77	71	67	66	62	59	56	53	51	47	45	43
3	82	73	65	59	76	68	61	56	58	53	49	50	46	43	42	39	37
4	75	64	56	50	69	60	53	47	52	46	42	44	40	37	37	34	32
5	69	57	49	43	64	53	46	41	46	41	36	40	35	32	34	30	28
6	64	51	43	37	59	48	41	35	42	36	32	36	31	28	31	27	24
7	59	46	38	33	54	43	36	31	38	32	28	33	28	25	28	24	22
8	55	42	34	29	51	40	32	28	35	29	25	30	25	22	26	22	19
9	51	38	31	26	47	36	29	25	32	26	22	28	23	20	24	20	17
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9550	9550	9550
5°	9574	9221	9207
10°	9488	8908	8817
15°	9356	8584	8392
20°	9205	8223	7971
25°	9009	7843	7521
30°	8795	7450	7048
35°	8571	7048	6578
40°	8336	6626	6115
45°	8078	6214	5632
50°	7815	5757	5147
55°	7478	5279	4656
60°	7131	4753	4133
65°	6805	4183	3588
70°	6334	3551	2951
75°	5660	2811	2291
80°	4886	1976	1620
85°	3813	1061	811

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8078 cd/sqm

TEST NUMBER: P1030921

CATALOG NUMBER: S123DIW-B560D460UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	2.0
10°-20°	236.2	5.7
20°-30°	348.8	8.4
30°-40°	407.4	9.8
40°-50°	409.5	9.8
50°-60°	359.8	8.6
60°-70°	267.9	6.4
70°-80°	152.5	3.7
80°-90°	44.6	1.1
90°-100°	21.6	0.5
100°-110°	104.2	2.5
110°-120°	255.4	6.1
120°-130°	324.3	7.8
130°-140°	346.4	8.3
140°-150°	323.9	7.8
150°-160°	261.3	6.3
160°-170°	168.6	4.0
170°-180°	58.1	1.4
0°-30°	668.6	16.0
0°-40°	1076.0	25.8
0°-60°	1845.2	44.2
0°-90°	2310.2	55.3
90°-120°	381.2	9.1
90°-150°	1375.8	33.0
90°-180°	1864.0	44.7
0°-180°	4174.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	887	887	887	887	887	
5°	888	884	876	883	882	84
15°	845	842	832	838	834	238
25°	767	763	753	754	751	354
35°	664	659	649	645	641	415
45°	544	541	531	522	518	420
55°	413	412	402	394	390	370
65°	282	278	270	264	262	278
75°	149	146	143	140	137	159
85°	40	38	38	37	37	43
90°	0	5	11	13	14	4
95°	28	9	14	17	17	33
105°	135	140	100	19	20	144
115°	254	257	261	265	267	251
125°	358	362	363	364	365	320
135°	446	448	450	452	450	343
145°	514	517	518	519	519	322
155°	566	566	566	568	566	261
165°	597	596	596	599	596	169
175°	611	609	610	613	609	58
180°	611	611	611	611	611	

TEST NUMBER: P1030921

CATALOG NUMBER: S123DIW-B560D460UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	887.2	887.2	887.2	887.2	887.2
2.5°	891.0	888.0	879.6	887.2	886.4
5°	888.0	884.2	875.8	883.4	881.9
7.5°	881.1	877.3	868.9	875.8	875.0
10°	871.9	868.1	858.2	865.1	863.6
12.5°	859.7	856.7	847.5	852.1	851.4
15°	845.2	842.2	832.3	838.4	833.8
17.5°	829.2	825.4	815.5	820.1	818.5
20°	810.9	806.3	796.4	799.5	797.2
22.5°	790.3	785.7	775.8	778.1	775.1
25°	767.4	762.9	752.9	753.7	751.4
27.5°	743.8	739.2	728.5	729.3	727.0
30°	717.8	714.0	703.4	703.4	698.0
32.5°	691.9	686.6	678.9	673.6	671.3
35°	663.7	659.1	649.2	644.6	640.8
37.5°	635.5	629.4	619.4	614.1	611.8
40°	605.7	601.1	590.5	584.3	581.3
42.5°	576.0	570.6	559.9	553.8	550.8
45°	543.9	540.9	530.9	521.8	518.0
47.5°	512.6	508.1	498.9	489.8	486.7
50°	480.6	476.8	466.9	458.5	453.9
52.5°	447.0	444.7	434.1	427.2	422.6
55°	412.7	411.9	402.0	393.6	389.8
57.5°	380.7	377.6	370.0	362.4	357.8
60°	345.6	344.8	335.7	328.8	325.0
62.5°	314.3	312.0	302.9	296.0	293.7
65°	281.5	277.7	270.1	263.9	261.7
67.5°	246.4	243.4	237.2	231.9	228.9
70°	215.1	210.5	206.0	200.6	196.8
72.5°	182.3	179.3	173.9	169.4	167.8
75°	148.8	145.7	143.4	139.6	137.3
77.5°	119.0	117.5	114.4	111.4	111.4
80°	90.0	87.7	86.2	85.4	85.4
82.5°	61.8	61.8	61.8	60.3	59.5
85°	39.7	38.1	38.1	36.6	36.6
87.5°	19.8	17.5	16.8	16.0	16.0
90°	0.5	5.0	10.9	12.7	13.6
92.5°	10.4	7.7	11.8	15.0	15.4
95°	27.7	9.1	14.1	17.3	17.3
97.5°	50.4	37.7	14.5	18.2	18.6
100°	76.8	85.8	15.0	18.6	19.1
102.5°	106.7	112.6	33.6	18.6	19.5
105°	135.4	140.3	99.5	19.1	20.0
107.5°	165.8	169.9	176.7	106.7	47.2
110°	196.2	199.8	204.8	189.9	124.9



TEST NUMBER: P1030921

CATALOG NUMBER: S123DIW-B560D460UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.3	228.5	233.5	237.5	236.6
115°	253.9	256.6	260.7	265.3	267.1
117.5°	282.1	285.2	287.5	291.1	291.6
120°	308.0	312.0	313.4	317.0	317.0
122.5°	334.3	337.5	339.3	341.6	342.0
125°	357.9	361.5	363.4	364.3	365.2
127.5°	381.5	385.2	387.4	388.8	387.9
130°	403.3	407.0	408.8	410.6	409.7
132.5°	424.2	427.9	429.2	431.0	429.7
135°	445.6	448.3	450.1	451.5	450.1
137.5°	463.7	467.4	468.3	470.6	469.6
140°	481.9	484.6	486.0	487.8	486.9
142.5°	498.7	501.4	502.8	504.2	502.8
145°	514.2	517.3	518.2	519.2	519.2
147.5°	529.1	531.4	532.3	533.2	531.0
150°	542.8	544.1	545.0	546.0	544.6
152.5°	555.0	555.5	555.9	557.8	555.5
155°	566.4	565.5	565.9	568.2	565.5
157.5°	575.5	575.5	575.0	577.7	574.1
160°	583.7	583.2	582.7	585.5	582.3
162.5°	591.4	590.0	589.6	592.7	590.0
165°	597.3	595.9	595.5	599.1	595.9
167.5°	602.3	600.5	600.5	604.1	600.5
170°	606.4	604.5	604.5	608.2	604.5
172.5°	609.1	606.8	607.3	610.9	606.8
175°	611.4	609.1	609.5	612.7	609.1
177.5°	612.3	610.0	610.5	614.1	609.5
180°	611.4	611.4	611.4	611.4	611.4

(END OF REPORT)