

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030931

Luminaire Tested: S123DIW-B560D755UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030931
REPORT IS A COMBINATION OF REPORTS P991792 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D755UB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5428.0 lumens
Efficiency: N/A
Efficacy: 115.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 47.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030931

CATALOG NUMBER: S123DIW-B560D755UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030931

CATALOG NUMBER: S123DIW-B560D755UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47			40
1	95	90	86	82	86	82	78	75	67	64	62	53	51	49	40	39	38			32
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	31			26
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26			22
4	71	60	52	46	64	55	48	43	45	40	36	36	32	29	27	24	22			18
5	65	54	45	39	59	49	42	36	40	35	30	32	28	25	24	21	19			16
6	60	48	40	34	54	44	37	31	36	31	26	29	25	22	22	19	17			14
7	55	43	35	29	50	39	32	27	33	27	23	26	22	19	20	17	15			12
8	51	39	31	26	46	36	29	24	30	24	20	24	20	17	18	15	13			11
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12			10
10	45	32	25	20	40	30	23	19	25	20	16	20	16	14	16	13	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7539	7539	7539
5°	7560	7318	7312
10°	7489	7120	7065
15°	7390	6901	6804
20°	7249	6657	6523
25°	7077	6382	6232
30°	6899	6133	5940
35°	6700	5873	5702
40°	6511	5634	5451
45°	6300	5403	5243
50°	6091	5174	5018
55°	5862	4940	4812
60°	5637	4699	4600
65°	5405	4444	4351
70°	5056	4156	4096
75°	4614	3828	3832
80°	4099	3498	3531
85°	3592	3230	3314

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6300 cd/sqm

TEST NUMBER: P1030931

CATALOG NUMBER: S123DIW-B560D755UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.4	1.2
10°-20°	189.4	3.5
20°-30°	283.3	5.2
30°-40°	338.2	6.2
40°-50°	353.8	6.5
50°-60°	332.1	6.1
60°-70°	277.4	5.1
70°-80°	198.3	3.7
80°-90°	120.0	2.2
90°-100°	109.7	2.0
100°-110°	226.3	4.2
110°-120°	457.4	8.4
120°-130°	555.2	10.2
130°-140°	580.3	10.7
140°-150°	535.8	9.9
150°-160°	430.7	7.9
160°-170°	277.9	5.1
170°-180°	95.8	1.8
0°-30°	539.1	9.9
0°-40°	877.3	16.2
0°-60°	1563.2	28.8
0°-90°	2158.9	39.8
90°-120°	793.4	14.6
90°-150°	2464.8	45.4
90°-180°	3269.0	60.2
0°-180°	5428.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	700	700	700	700	700	
5°	701	700	695	701	700	67
15°	668	670	669	677	676	188
25°	603	610	613	623	623	278
35°	519	531	541	552	556	324
45°	424	442	462	476	482	327
55°	324	349	376	397	403	290
65°	224	253	287	310	317	221
75°	121	157	195	220	230	130
85°	37	76	116	142	150	38
90°	11	56	104	133	142	10
95°	54	53	99	128	135	61
105°	229	256	221	110	118	243
115°	422	436	470	496	505	417
125°	592	598	623	641	648	529
135°	736	740	751	767	769	567
145°	848	853	854	862	865	531
155°	934	932	933	937	932	430
165°	984	982	982	988	982	278
175°	1008	1004	1005	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1030931

CATALOG NUMBER: S123DIW-B560D755UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	700.4	700.4	700.4	700.4	700.4
2.5°	704.2	702.0	695.9	702.0	701.2
5°	701.2	699.7	695.1	701.2	700.4
7.5°	695.9	695.9	691.3	698.9	698.1
10°	688.2	689.7	685.9	693.6	692.0
12.5°	679.1	681.4	679.1	685.9	684.4
15°	667.6	669.9	669.1	676.8	676.0
17.5°	653.9	658.5	657.7	664.6	663.0
20°	638.6	643.2	644.7	651.6	652.4
22.5°	622.6	627.2	629.5	638.6	637.9
25°	602.8	610.4	612.7	622.6	622.6
27.5°	583.7	592.1	596.7	605.1	605.8
30°	563.1	573.0	579.1	588.3	588.3
32.5°	540.2	551.6	560.0	570.0	572.2
35°	518.8	531.0	541.0	552.4	555.5
37.5°	495.9	509.7	521.1	534.1	536.4
40°	473.1	486.8	502.1	515.0	518.1
42.5°	447.9	465.4	481.5	495.9	500.5
45°	424.2	442.5	461.6	476.1	482.2
47.5°	399.0	419.6	441.0	457.0	461.6
50°	374.6	396.0	419.6	437.2	442.5
52.5°	348.7	371.6	398.3	416.6	423.5
55°	323.5	348.7	376.2	396.8	402.9
57.5°	299.1	325.0	354.8	375.4	382.3
60°	273.2	300.6	331.9	353.3	361.7
62.5°	248.7	277.0	310.5	331.9	339.5
65°	223.6	253.3	286.9	309.8	317.4
67.5°	198.4	229.7	263.2	288.4	294.5
70°	171.7	204.5	241.1	265.5	273.2
72.5°	147.3	180.1	218.2	243.4	251.0
75°	121.3	157.2	195.3	220.5	229.7
77.5°	99.2	135.1	173.2	199.9	206.8
80°	75.5	112.9	152.6	178.5	186.2
82.5°	54.9	93.1	133.5	159.5	167.1
85°	37.4	75.5	116.0	141.9	149.5
87.5°	22.9	61.0	100.0	125.9	133.5
90°	10.6	55.5	104.2	133.2	142.3
92.5°	26.4	54.7	99.6	130.0	137.7
95°	54.1	53.1	98.7	127.6	135.2
97.5°	90.7	97.2	95.0	123.7	132.2
100°	133.4	172.8	91.1	119.2	127.5
102.5°	182.0	213.2	117.2	113.9	123.0
105°	229.2	255.7	221.2	110.0	118.4
107.5°	278.6	301.4	343.8	249.1	158.0
110°	328.0	347.7	386.4	381.6	280.7

TEST NUMBER: P1030931

CATALOG NUMBER: S123DIW-B560D755UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	375.9	391.9	429.1	454.8	460.2
115°	422.3	436.0	470.1	496.0	505.1
117.5°	468.7	480.0	509.8	534.1	540.9
120°	510.7	521.2	548.6	572.2	577.5
122.5°	554.1	560.8	587.4	608.0	614.1
125°	592.2	598.2	623.3	640.8	647.7
127.5°	631.2	636.4	659.2	676.7	680.5
130°	667.1	672.3	690.6	708.1	711.2
132.5°	700.7	706.7	720.5	737.2	740.2
135°	735.9	739.7	751.1	767.1	768.6
137.5°	765.9	771.2	778.0	793.9	796.2
140°	795.1	799.6	804.2	818.5	820.8
142.5°	822.8	826.5	828.8	840.9	842.5
145°	848.3	852.7	854.2	861.8	864.9
147.5°	872.2	875.9	877.4	881.2	880.5
150°	894.6	896.9	898.4	899.9	899.1
152.5°	914.8	915.6	916.3	919.3	915.6
155°	933.6	932.1	932.8	936.6	932.1
157.5°	948.5	948.5	947.8	952.3	946.3
160°	962.0	961.3	960.5	965.0	959.8
162.5°	974.7	972.5	971.7	977.0	972.5
165°	984.5	982.2	981.5	987.5	982.2
167.5°	992.7	989.7	989.7	995.7	989.7
170°	999.4	996.4	996.4	1002.4	996.4
172.5°	1003.9	1000.2	1000.9	1006.9	1000.2
175°	1007.7	1003.9	1004.7	1009.9	1003.9
177.5°	1009.2	1005.4	1006.2	1012.2	1004.7
180°	1007.7	1007.7	1007.7	1007.7	1007.7

(END OF REPORT)