

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P982740

Luminaire Tested: S122IW-B710UB30-4F0-XX-W2A-1

Issue Date: 5/2/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P982740  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8)  
Test Lab: INNOVATION CENTER  
Issue Date: 5/2/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: S122IW-B710UB30-4F0-XX-W2A-1  
Description: Define 2 Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2503.0 lumens  
Efficiency: N/A  
Efficacy: 107.9 lumens/watt  
Spacing Criteria (0/90/45): - / - / -  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Indirect

Input Watts (W): 23.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P982740

CATALOG NUMBER: S122IW-B710UB30-4F0-XX-W2A-1

### Luminous Intensity Polar Plot



TEST NUMBER: P982740

CATALOG NUMBER: S122IW-B710UB30-4F0-XX-W2A-1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
|-----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|
| RF  | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |    |    |    | 20 |
| RC  | 80 |    |    |    | 70 |    |    |    | 50 |    |    |    | 30 |    |    |    | 10 |
| RW  | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 |
| RCR |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |
| 0   | 95 | 95 | 95 | 95 | 81 | 81 | 81 | 81 | 56 | 56 | 56 | 32 | 32 | 32 | 10 | 10 | 10 |
| 1   | 87 | 83 | 79 | 76 | 74 | 71 | 68 | 65 | 48 | 47 | 45 | 28 | 27 | 26 | 9  | 9  | 8  |
| 2   | 79 | 72 | 66 | 62 | 67 | 62 | 57 | 53 | 42 | 40 | 37 | 24 | 23 | 22 | 8  | 7  | 7  |
| 3   | 72 | 63 | 56 | 51 | 61 | 54 | 49 | 44 | 37 | 34 | 31 | 21 | 20 | 18 | 7  | 6  | 6  |
| 4   | 65 | 56 | 48 | 43 | 56 | 48 | 42 | 37 | 33 | 29 | 26 | 19 | 17 | 16 | 6  | 6  | 5  |
| 5   | 60 | 49 | 42 | 36 | 51 | 42 | 36 | 32 | 29 | 25 | 22 | 17 | 15 | 13 | 5  | 5  | 4  |
| 6   | 55 | 44 | 36 | 31 | 47 | 38 | 32 | 27 | 26 | 22 | 19 | 15 | 13 | 11 | 5  | 4  | 4  |
| 7   | 50 | 39 | 32 | 27 | 43 | 34 | 28 | 23 | 23 | 19 | 17 | 14 | 11 | 10 | 4  | 4  | 3  |
| 8   | 47 | 35 | 28 | 23 | 40 | 30 | 24 | 20 | 21 | 17 | 14 | 12 | 10 | 9  | 4  | 3  | 3  |
| 9   | 43 | 32 | 25 | 20 | 37 | 27 | 22 | 18 | 19 | 15 | 13 | 11 | 9  | 8  | 4  | 3  | 3  |
| 10  | 40 | 29 | 22 | 18 | 34 | 25 | 19 | 16 | 17 | 14 | 11 | 10 | 8  | 7  | 3  | 3  | 2  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0° | 45° | 90° |
|-----|----|-----|-----|
| 0°  | 0  | 0   | 0   |
| 5°  | 0  | 0   | 0   |
| 10° | 0  | 0   | 0   |
| 15° | 0  | 0   | 0   |
| 20° | 0  | 0   | 0   |
| 25° | 0  | 0   | 0   |
| 30° | 0  | 0   | 0   |
| 35° | 0  | 0   | 0   |
| 40° | 0  | 0   | 0   |
| 45° | 0  | 0   | 0   |
| 50° | 0  | 0   | 0   |
| 55° | 0  | 0   | 0   |
| 60° | 0  | 0   | 0   |
| 65° | 0  | 0   | 0   |
| 70° | 0  | 0   | 0   |
| 75° | 0  | 0   | 0   |
| 80° | 0  | 0   | 0   |
| 85° | 0  | 0   | 0   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 0°  
Luminance: 0 cd/sqm

TEST NUMBER: P982740

CATALOG NUMBER: S122IW-B710UB30-4F0-XX-W2A-1

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 0.0    | 0.0       |
| 10°-20°   | 0.0    | 0.0       |
| 20°-30°   | 0.0    | 0.0       |
| 30°-40°   | 0.0    | 0.0       |
| 40°-50°   | 0.0    | 0.0       |
| 50°-60°   | 0.0    | 0.0       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 2.5    | 0.1       |
| 90°-100°  | 55.3   | 2.2       |
| 100°-110° | 175.9  | 7.0       |
| 110°-120° | 300.9  | 12.0      |
| 120°-130° | 395.8  | 15.8      |
| 130°-140° | 444.3  | 17.7      |
| 140°-150° | 435.7  | 17.4      |
| 150°-160° | 365.5  | 14.6      |
| 160°-170° | 242.4  | 9.7       |
| 170°-180° | 84.7   | 3.4       |
| 0°-30°    | 0.0    | 0.0       |
| 0°-40°    | 0.0    | 0.0       |
| 0°-60°    | 0.0    | 0.0       |
| 0°-90°    | 2.5    | 0.1       |
| 90°-120°  | 532.2  | 21.3      |
| 90°-150°  | 1807.9 | 72.2      |
| 90°-180°  | 2500.0 | 99.9      |
| 0°-180°   | 2503.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|      | 0°  | 22.5° | 45° | 67.5° | 90° | Flux |
|------|-----|-------|-----|-------|-----|------|
| 0°   | 0   | 0     | 0   | 0     | 0   |      |
| 5°   | 0   | 0     | 0   | 0     | 0   | 0    |
| 15°  | 0   | 0     | 0   | 0     | 0   | 0    |
| 25°  | 0   | 0     | 0   | 0     | 0   | 0    |
| 35°  | 0   | 0     | 0   | 0     | 0   | 0    |
| 45°  | 0   | 0     | 0   | 0     | 0   | 0    |
| 55°  | 0   | 0     | 0   | 0     | 0   | 0    |
| 65°  | 0   | 0     | 0   | 0     | 0   | 0    |
| 75°  | 0   | 0     | 0   | 0     | 0   | 0    |
| 85°  | 0   | 0     | 0   | 0     | 0   | 0    |
| 90°  | 1   | 10    | 26  | 25    | 26  | 2    |
| 95°  | 39  | 47    | 48  | 48    | 47  | 44   |
| 105° | 162 | 164   | 166 | 168   | 168 | 171  |
| 115° | 302 | 306   | 305 | 304   | 302 | 299  |
| 125° | 439 | 446   | 444 | 442   | 441 | 393  |
| 135° | 568 | 577   | 578 | 577   | 575 | 439  |
| 145° | 690 | 695   | 700 | 700   | 697 | 431  |
| 155° | 789 | 791   | 793 | 797   | 795 | 363  |
| 165° | 858 | 857   | 857 | 863   | 859 | 242  |
| 175° | 893 | 891   | 889 | 894   | 890 | 85   |
| 180° | 894 | 894   | 894 | 894   | 894 |      |

TEST NUMBER: P982740

CATALOG NUMBER: S122IW-B710UB30-4F0-XX-W2A-1

**CANDELA DISTRIBUTION (FULL):**

|        | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|--------|-------|-------|-------|-------|-------|
| 0°     | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 2.5°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 5°     | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 7.5°   | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 10°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 12.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 15°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 17.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 20°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 22.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 25°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 27.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 30°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 32.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 35°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 37.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 40°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 42.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 45°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 47.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 50°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 52.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 55°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 57.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 60°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 62.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 65°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 67.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 70°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 72.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 75°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 77.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 80°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 82.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 85°    | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 87.5°  | 0.0   | 0.0   | 0.0   | 0.0   | 0.0   |
| 90°    | 0.8   | 9.8   | 26.4  | 24.9  | 25.7  |
| 92.5°  | 16.6  | 22.6  | 23.4  | 24.2  | 24.2  |
| 95°    | 39.2  | 46.8  | 48.3  | 48.3  | 46.8  |
| 97.5°  | 65.7  | 72.5  | 75.5  | 75.5  | 75.5  |
| 100°   | 95.9  | 101.9 | 104.2 | 104.2 | 103.4 |
| 102.5° | 127.5 | 132.1 | 135.1 | 135.9 | 135.1 |
| 105°   | 162.3 | 164.5 | 166.0 | 167.6 | 167.6 |
| 107.5° | 197.0 | 200.0 | 200.0 | 200.8 | 197.0 |
| 110°   | 230.2 | 234.7 | 234.7 | 234.7 | 232.5 |

TEST NUMBER: P982740

CATALOG NUMBER: S122IW-B710UB30-4F0-XX-W2A-1

**CANDELA DISTRIBUTION (continued):**

|        | 0°    | 22.5° | 45°   | 67.5° | 90°   |
|--------|-------|-------|-------|-------|-------|
| 112.5° | 266.4 | 270.9 | 270.2 | 267.9 | 266.4 |
| 115°   | 301.9 | 306.4 | 304.9 | 304.2 | 301.9 |
| 117.5° | 337.4 | 343.4 | 339.6 | 337.4 | 335.1 |
| 120°   | 372.8 | 378.9 | 372.8 | 372.8 | 370.6 |
| 122.5° | 405.3 | 412.8 | 409.1 | 406.8 | 405.3 |
| 125°   | 439.3 | 446.0 | 443.8 | 441.5 | 440.8 |
| 127.5° | 472.5 | 480.8 | 477.7 | 474.7 | 472.5 |
| 130°   | 503.4 | 513.2 | 511.7 | 510.2 | 507.2 |
| 132.5° | 538.1 | 545.7 | 546.4 | 542.7 | 540.4 |
| 135°   | 568.3 | 576.6 | 578.1 | 577.4 | 575.1 |
| 137.5° | 601.5 | 608.3 | 609.8 | 609.1 | 606.1 |
| 140°   | 631.0 | 637.7 | 641.5 | 641.5 | 638.5 |
| 142.5° | 661.1 | 667.9 | 670.2 | 671.0 | 667.9 |
| 145°   | 689.8 | 695.1 | 699.6 | 700.4 | 697.4 |
| 147.5° | 715.5 | 722.3 | 725.3 | 726.8 | 723.8 |
| 150°   | 741.9 | 746.4 | 749.4 | 751.7 | 749.4 |
| 152.5° | 765.3 | 769.8 | 773.6 | 776.6 | 773.6 |
| 155°   | 788.7 | 791.0 | 793.2 | 797.0 | 794.7 |
| 157.5° | 809.1 | 810.6 | 812.1 | 817.4 | 813.6 |
| 160°   | 827.2 | 828.7 | 829.5 | 834.0 | 831.0 |
| 162.5° | 843.8 | 843.8 | 844.5 | 849.8 | 846.1 |
| 165°   | 858.1 | 857.4 | 857.4 | 862.7 | 858.9 |
| 167.5° | 871.0 | 868.7 | 868.7 | 874.0 | 870.2 |
| 170°   | 880.8 | 878.5 | 877.8 | 883.0 | 878.5 |
| 172.5° | 887.6 | 885.3 | 884.5 | 889.8 | 885.3 |
| 175°   | 892.8 | 890.6 | 889.1 | 894.4 | 889.8 |
| 177.5° | 895.9 | 893.6 | 892.1 | 896.6 | 892.1 |
| 180°   | 894.4 | 894.4 | 894.4 | 894.4 | 894.4 |



TEST NUMBER: P982740

CATALOG NUMBER: S122IW-B710UB30-4F0-XX-W2A-1

**CIE UGR TABLE:**

| Reflectances:   |      |                  |      |      |      |      |                |      |      |      |      |
|-----------------|------|------------------|------|------|------|------|----------------|------|------|------|------|
| Ceiling         |      | 0.7              | 0.7  | 0.5  | 0.5  | 0.3  | 0.7            | 0.7  | 0.5  | 0.5  | 0.3  |
| Wall            |      | 0.5              | 0.3  | 0.5  | 0.3  | 0.3  | 0.5            | 0.3  | 0.5  | 0.3  | 0.3  |
| Reference plane |      | 0.2              | 0.2  | 0.2  | 0.2  | 0.2  | 0.2            | 0.2  | 0.2  | 0.2  | 0.2  |
| Room dimensions |      | Viewed crosswise |      |      |      |      | Viewed endwise |      |      |      |      |
| X=2H            | Y=2H | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 3H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 12H  | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
| 4H              | 2H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 3H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 12H  | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
| 8H              | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 12H  | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
| 12H             | 4H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 6H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |
|                 | 8H   | 0.00             | 0.00 | 0.00 | 0.00 | 0.00 | 0.00           | 0.00 | 0.00 | 0.00 | 0.00 |

END OF REPORT