

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030645

Luminaire Tested: S123DIW-B1000D1030UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030645
REPORT IS A COMBINATION OF REPORTS P990537 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D1030UB2750-4F0-XX-W2A-D_2700K
Description: Define 3 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8285.0 lumens
Efficiency: N/A
Efficacy: 105.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030645

CATALOG NUMBER: S123DIW-B1000D1030UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1030645

CATALOG NUMBER: S123DIW-B1000D1030UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	96	91	87	83	88	84	80	77	70	67	64	57	55	53	45	43	42
2	87	79	73	67	79	73	67	62	60	56	53	49	46	43	39	37	35
3	79	69	62	55	72	64	57	51	53	48	44	43	39	36	34	31	29
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22
6	61	48	40	34	55	45	37	32	38	32	28	31	26	23	25	21	19
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	22	19	17
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	20	17	15
9	48	36	28	23	44	33	27	22	28	23	19	23	19	16	19	16	13
10	45	33	26	21	41	31	24	20	26	21	17	22	17	15	18	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13254	13254	13254
5°	13289	12864	12854
10°	13165	12516	12420
15°	12991	12131	11960
20°	12743	11702	11467
25°	12439	11219	10956
30°	12127	10782	10442
35°	11778	10323	10023
40°	11445	9903	9581
45°	11075	9499	9217
50°	10708	9096	8821
55°	10304	8682	8458
60°	9909	8260	8084
65°	9500	7811	7650
70°	8888	7306	7200
75°	8114	6732	6735
80°	7210	6147	6207
85°	6311	5678	5827

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11075 cd/sqm

TEST NUMBER: P1030645

CATALOG NUMBER: S123DIW-B1000D1030UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.8	1.4
10°-20°	333.0	4.0
20°-30°	497.9	6.0
30°-40°	594.5	7.2
40°-50°	622.0	7.5
50°-60°	583.7	7.0
60°-70°	487.5	5.9
70°-80°	348.6	4.2
80°-90°	210.2	2.5
90°-100°	178.3	2.2
100°-110°	327.6	4.0
110°-120°	631.9	7.6
120°-130°	757.5	9.1
130°-140°	786.6	9.5
140°-150°	723.7	8.7
150°-160°	581.0	7.0
160°-170°	374.9	4.5
170°-180°	129.2	1.6
0°-30°	947.7	11.4
0°-40°	1542.2	18.6
0°-60°	2747.9	33.2
0°-90°	3794.3	45.8
90°-120°	1137.8	13.7
90°-150°	3405.6	41.1
90°-180°	4491.0	54.2
0°-180°	8285.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1231	1231	1231	1231	1231	
5°	1233	1230	1222	1233	1231	117
15°	1174	1178	1176	1190	1188	331
25°	1060	1073	1077	1094	1094	488
35°	912	934	951	971	976	570
45°	746	778	812	837	848	575
55°	569	613	661	697	708	509
65°	393	445	504	544	558	388
75°	213	276	343	388	404	228
85°	66	133	204	250	263	68
90°	18	94	176	226	241	16
95°	76	87	164	213	226	85
105°	312	355	322	180	195	330
115°	571	593	651	693	708	565
125°	800	808	851	881	892	715
135°	994	998	1017	1044	1048	765
145°	1145	1150	1152	1165	1170	716
155°	1259	1257	1258	1264	1257	580
165°	1328	1325	1324	1332	1325	375
175°	1359	1354	1355	1362	1354	129
180°	1359	1359	1359	1359	1359	

TEST NUMBER: P1030645

CATALOG NUMBER: S123DIW-B1000D1030UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1231.3	1231.3	1231.3	1231.3	1231.3
2.5°	1238.0	1233.9	1223.2	1233.9	1232.6
5°	1232.6	1229.9	1221.9	1232.6	1231.3
7.5°	1223.2	1223.2	1215.2	1228.6	1227.2
10°	1209.8	1212.5	1205.8	1219.2	1216.5
12.5°	1193.7	1197.7	1193.7	1205.8	1203.1
15°	1173.6	1177.6	1176.3	1189.7	1188.3
17.5°	1149.4	1157.5	1156.2	1168.2	1165.5
20°	1122.6	1130.7	1133.3	1145.4	1146.8
22.5°	1094.5	1102.5	1106.5	1122.6	1121.3
25°	1059.6	1073.0	1077.0	1094.5	1094.5
27.5°	1026.1	1040.8	1048.9	1063.6	1064.9
30°	989.8	1007.3	1018.0	1034.1	1034.1
32.5°	949.6	969.7	984.5	1001.9	1005.9
35°	912.0	933.5	950.9	971.1	976.4
37.5°	871.8	895.9	916.1	938.9	942.9
40°	831.6	855.7	882.5	905.3	910.7
42.5°	787.3	818.2	846.3	871.8	879.9
45°	745.7	777.9	811.5	836.9	847.7
47.5°	701.5	737.7	775.2	803.4	811.5
50°	658.5	696.1	737.7	768.5	777.9
52.5°	612.9	653.2	700.1	732.3	744.4
55°	568.7	612.9	661.2	697.4	708.2
57.5°	525.8	571.4	623.7	659.9	672.0
60°	480.2	528.4	583.4	621.0	635.7
62.5°	437.2	486.9	545.9	583.4	596.9
65°	393.0	445.3	504.3	544.5	558.0
67.5°	348.7	403.7	462.7	507.0	517.7
70°	301.8	359.5	423.8	466.8	480.2
72.5°	258.9	316.5	383.6	427.9	441.3
75°	213.3	276.3	343.4	387.6	403.7
77.5°	174.4	237.4	304.5	351.4	363.5
80°	132.8	198.5	268.2	313.9	327.3
82.5°	96.6	163.6	234.7	280.3	293.7
85°	65.7	132.8	203.9	249.5	262.9
87.5°	40.2	107.3	175.7	221.3	234.7
90°	18.4	94.3	175.8	225.5	240.9
92.5°	39.3	91.0	167.1	218.4	231.5
95°	76.4	87.3	164.1	212.8	226.2
97.5°	125.5	145.5	157.0	205.4	219.8
100°	182.8	245.9	150.0	197.0	211.4
102.5°	248.0	298.8	183.3	187.6	203.0
105°	311.7	355.0	321.8	180.5	194.6
107.5°	378.0	415.3	485.4	366.1	245.8
110°	444.3	476.6	541.3	542.9	409.1

TEST NUMBER: P1030645

CATALOG NUMBER: S123DIW-B1000D1030UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	508.9	534.8	596.9	639.5	649.6
115°	571.3	593.4	650.8	693.1	707.9
117.5°	633.9	651.7	702.3	742.6	754.4
120°	690.2	705.9	753.2	792.2	801.6
122.5°	748.7	758.4	804.0	838.6	849.0
125°	799.9	807.9	850.9	881.1	892.5
127.5°	852.4	859.2	897.7	927.5	934.9
130°	900.8	907.6	938.5	968.0	974.0
132.5°	946.0	954.1	977.2	1005.4	1011.7
135°	993.5	998.1	1017.0	1044.1	1047.8
137.5°	1033.9	1040.6	1052.0	1078.5	1083.2
140°	1072.9	1078.9	1086.1	1110.2	1114.9
142.5°	1110.2	1115.0	1118.0	1138.5	1142.1
145°	1144.6	1150.4	1152.4	1165.1	1170.5
147.5°	1176.6	1181.7	1183.7	1189.7	1190.0
150°	1206.9	1209.9	1212.0	1214.0	1213.6
152.5°	1234.2	1235.2	1236.2	1240.2	1235.2
155°	1259.4	1257.4	1258.4	1263.5	1257.4
157.5°	1279.6	1279.6	1278.6	1284.7	1276.6
160°	1297.8	1296.8	1295.8	1301.8	1294.8
162.5°	1315.0	1311.9	1310.9	1318.0	1311.9
165°	1328.1	1325.1	1324.1	1332.1	1325.1
167.5°	1339.2	1335.2	1335.2	1343.3	1335.2
170°	1348.3	1344.3	1344.3	1352.3	1344.3
172.5°	1354.4	1349.3	1350.3	1358.4	1349.3
175°	1359.4	1354.4	1355.4	1362.4	1354.4
177.5°	1361.4	1356.4	1357.4	1365.5	1355.4
180°	1359.4	1359.4	1359.4	1359.4	1359.4

(END OF REPORT)