

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030973

Luminaire Tested: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030973
REPORT IS A COMBINATION OF REPORTS P991986 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K
Description: Define 3 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9141.0 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	103	103	103	103	93	93	93	93	75	75	75	58	58	58	42	42	42			35
1	95	90	87	83	85	82	79	76	66	64	62	51	50	48	37	36	36			29
2	86	79	73	68	78	72	67	62	58	54	51	45	43	41	33	32	30			25
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	28	26			21
4	72	62	54	48	65	56	49	44	45	41	37	36	32	30	26	24	22			18
5	66	55	47	41	59	50	43	38	41	36	32	32	28	26	24	21	20			16
6	61	49	41	36	55	45	38	33	36	31	28	29	25	22	22	19	17			14
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	17	15			13
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14			11
9	48	36	29	24	44	33	27	23	27	23	19	22	18	16	17	14	12			10
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	11241	11241	11241	11241
5°	11248	12953	11282	9666
10°	11177	15673	11189	8442
15°	11023	18588	11113	7598
20°	10889	21401	10913	6992
25°	10693	21940	10716	6675
30°	10552	18127	10552	6468
35°	10377	12123	10311	6284
40°	10166	8751	10041	6004
45°	9904	6932	9619	5655
50°	9264	5887	8936	5313
55°	8563	5173	8215	4931
60°	7851	4504	7435	4530
65°	7071	3856	6728	3995
70°	6258	3201	5840	3369
75°	5352	2414	5006	2599
80°	4229	1612	3898	1709
85°	2920	740	2334	674

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 18129 cd/sqm

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.7	1.1
10°-20°	329.9	3.6
20°-30°	555.1	6.1
30°-40°	627.3	6.9
40°-50°	561.8	6.1
50°-60°	453.5	5.0
60°-70°	316.0	3.5
70°-80°	165.9	1.8
80°-90°	43.7	0.5
90°-100°	69.2	0.8
100°-110°	334.7	3.7
110°-120°	820.2	9.0
120°-130°	1041.3	11.4
130°-140°	1112.4	12.2
140°-150°	1040.2	11.4
150°-160°	839.0	9.2
160°-170°	541.5	5.9
170°-180°	186.6	2.0
0°-30°	987.7	10.8
0°-40°	1615.0	17.7
0°-60°	2630.3	28.8
0°-90°	3155.9	34.5
90°-120°	1224.2	13.4
90°-150°	4418.0	48.3
90°-180°	5985.0	65.5
0°-180°	9141.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1044	1044	1044	1044	1044	
5°	1043	1241	1046	926	1043	99
15°	996	1847	1004	755	996	281
25°	911	2192	913	667	911	420
35°	804	1181	798	612	804	503
45°	667	638	648	520	667	510
55°	473	433	453	413	473	423
65°	292	281	278	291	292	291
75°	141	145	132	156	141	151
85°	30	33	24	30	30	35
90°	2	44	2	44	2	7
95°	89	55	89	55	89	106
105°	435	64	435	64	435	461
115°	815	858	815	858	815	805
125°	1149	1173	1149	1173	1149	1027
135°	1431	1445	1431	1445	1431	1102
145°	1651	1667	1651	1667	1651	1034
155°	1819	1816	1819	1816	1819	838
165°	1918	1914	1918	1914	1918	542
175°	1963	1956	1963	1956	1963	187
180°	1963	1963	1963	1963	1963	

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1047.4	1055.5	1059.5	1065.6	1071.7	1080.8	1083.8	1088.9	1086.8	1090.9	1092.9
5°	1043.3	1057.5	1069.6	1084.8	1099.0	1109.1	1119.2	1135.4	1147.6	1149.6	1158.7
7.5°	1036.2	1056.5	1077.7	1099.0	1126.3	1142.5	1160.7	1183.0	1201.2	1230.5	1241.7
10°	1027.1	1055.5	1085.8	1115.2	1152.6	1177.9	1200.2	1237.6	1275.1	1305.4	1333.8
12.5°	1013.0	1048.4	1087.9	1131.4	1179.9	1209.3	1239.7	1289.2	1345.9	1392.5	1422.8
15°	995.8	1040.3	1090.9	1137.4	1191.1	1245.7	1278.1	1333.8	1414.7	1458.2	1536.2
17.5°	981.6	1027.1	1077.7	1150.6	1223.5	1278.1	1301.4	1403.6	1459.2	1532.1	1620.2
20°	959.3	1017.0	1081.8	1154.6	1248.8	1282.2	1329.7	1432.9	1501.8	1596.9	1705.2
22.5°	936.1	997.8	1075.7	1151.6	1256.9	1292.3	1357.0	1439.0	1548.3	1642.4	1761.8
25°	910.8	977.6	1056.5	1146.6	1249.8	1301.4	1362.1	1463.3	1581.7	1700.1	1810.4
27.5°	885.5	958.3	1040.3	1130.4	1230.5	1291.3	1352.0	1457.2	1609.0	1737.5	1878.2
30°	861.2	934.0	1016.0	1108.1	1213.3	1272.0	1329.7	1461.3	1630.3	1775.0	1916.7
32.5°	834.9	909.8	995.8	1072.7	1178.9	1241.7	1306.4	1461.3	1643.4	1797.2	1926.8
35°	803.5	880.4	954.3	1031.2	1136.4	1206.3	1279.1	1451.2	1655.6	1804.3	1884.3
37.5°	773.1	840.9	904.7	979.6	1089.9	1164.8	1248.8	1439.0	1649.5	1774.0	1796.2
40°	738.7	806.5	858.1	928.0	1044.3	1131.4	1216.4	1422.8	1623.2	1702.1	1637.4
42.5°	705.3	759.0	803.5	871.3	997.8	1082.8	1174.9	1393.5	1571.6	1587.8	1442.0
45°	666.9	705.3	744.8	821.7	947.2	1034.2	1136.4	1351.0	1488.6	1442.0	1257.9
47.5°	617.3	651.7	695.2	766.1	893.6	983.6	1080.8	1296.3	1368.2	1271.0	1069.6
50°	569.7	599.1	639.6	708.4	836.9	924.9	1028.2	1210.3	1245.7	1092.9	921.9
52.5°	522.2	544.4	583.9	652.7	781.2	866.2	960.4	1122.3	1102.0	938.1	786.3
55°	472.6	491.8	529.3	597.1	716.5	797.4	887.5	1014.0	961.4	805.5	684.1
57.5°	424.0	444.3	482.7	539.4	651.7	730.6	802.5	901.7	822.7	698.3	591.0
60°	380.5	397.7	427.0	482.7	584.9	648.7	714.4	782.2	716.5	596.0	514.1
62.5°	335.0	351.2	378.5	429.1	517.1	573.8	626.4	682.1	609.2	521.2	448.3
65°	292.5	305.6	330.9	377.5	449.3	495.9	538.4	576.8	518.1	437.2	382.5
67.5°	254.0	265.1	286.4	327.9	388.6	422.0	456.4	488.8	439.2	374.4	327.9
70°	212.5	221.6	240.8	271.2	319.8	354.2	379.5	403.8	359.2	307.6	276.3
72.5°	176.1	185.2	197.3	228.7	262.1	283.3	310.7	323.8	298.5	256.0	224.7
75°	140.7	147.7	158.9	179.1	210.5	224.7	241.9	252.0	228.7	200.4	181.1
77.5°	110.3	113.3	121.4	135.6	156.9	173.0	186.2	192.3	176.1	157.9	141.7
80°	77.9	82.0	88.0	100.2	116.4	121.4	129.5	136.6	126.5	110.3	100.2
82.5°	51.6	56.7	59.7	64.8	74.9	81.0	83.0	89.1	79.9	73.9	69.8
85°	30.4	32.4	33.4	36.4	41.5	44.5	47.6	48.6	46.6	45.5	41.5
87.5°	15.2	15.2	15.2	17.2	18.2	20.2	21.3	21.3	21.3	20.2	19.2
90°	1.5	4.7	7.9	11.2	14.4	16.0	18.1	22.3	26.6	30.8	35.0
92.5°	33.5	31.6	29.6	27.7	25.8	24.8	26.3	29.2	32.1	35.0	37.9
95°	89.0	75.7	62.4	49.1	35.8	29.2	31.0	34.5	38.1	41.6	45.2
97.5°	161.9	152.8	143.8	134.7	125.6	121.1	112.8	96.3	79.8	63.2	46.7
100°	246.5	253.0	259.5	266.0	272.5	275.7	250.4	199.8	149.3	98.7	48.1
102.5°	342.8	347.0	351.2	355.4	359.6	361.7	333.5	277.1	220.7	164.3	107.9
105°	434.7	438.3	441.8	445.4	448.9	450.7	436.1	406.9	377.8	348.6	319.4
107.5°	532.4	535.3	538.2	541.1	544.0	545.5	547.9	552.8	557.7	562.5	567.4
110°	630.1	632.7	635.3	637.9	640.5	641.8	643.6	647.1	650.7	654.2	657.8

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	723.4	725.7	728.0	730.3	732.6	733.7	735.5	739.0	742.6	746.1	749.7
115°	815.3	817.3	819.2	821.2	823.1	824.1	825.6	828.5	831.4	834.3	837.2
117.5°	905.8	908.1	910.3	912.6	914.9	916.0	916.8	918.4	920.1	921.7	923.3
120°	988.9	991.8	994.7	997.6	1000.5	1002.0	1002.5	1003.5	1004.4	1005.4	1006.4
122.5°	1073.5	1075.8	1078.0	1080.3	1082.6	1083.7	1084.3	1085.6	1086.9	1088.2	1089.5
125°	1149.4	1152.0	1154.6	1157.1	1159.7	1161.0	1161.7	1163.0	1164.3	1165.6	1166.9
127.5°	1225.2	1227.8	1230.4	1233.0	1235.6	1236.9	1237.7	1239.3	1241.0	1242.6	1244.2
130°	1295.2	1297.8	1300.4	1303.0	1305.6	1306.9	1307.5	1308.8	1310.1	1311.4	1312.7
132.5°	1362.3	1364.9	1367.5	1370.1	1372.7	1374.0	1374.5	1375.4	1376.4	1377.3	1378.3
135°	1430.9	1432.8	1434.8	1436.7	1438.6	1439.6	1440.2	1441.5	1442.8	1444.1	1445.4
137.5°	1489.2	1491.8	1494.4	1497.0	1499.6	1500.9	1501.2	1501.9	1502.5	1503.2	1503.8
140°	1547.5	1549.5	1551.4	1553.4	1555.3	1556.3	1556.8	1557.8	1558.7	1559.7	1560.7
142.5°	1601.5	1603.5	1605.4	1607.4	1609.3	1610.3	1610.8	1611.7	1612.7	1613.6	1614.6
145°	1651.1	1653.4	1655.6	1657.9	1660.2	1661.3	1661.6	1662.3	1662.9	1663.6	1664.2
147.5°	1699.2	1700.8	1702.4	1704.1	1705.7	1706.5	1706.8	1707.5	1708.1	1708.8	1709.4
150°	1743.0	1744.0	1745.0	1745.9	1746.9	1747.4	1747.7	1748.4	1749.0	1749.7	1750.3
152.5°	1782.4	1782.7	1783.0	1783.3	1783.6	1783.8	1784.0	1784.3	1784.6	1785.0	1785.3
155°	1818.8	1818.2	1817.5	1816.9	1816.2	1815.9	1816.1	1816.4	1816.7	1817.1	1817.4
157.5°	1848.0	1848.0	1848.0	1848.0	1848.0	1848.0	1847.8	1847.5	1847.2	1846.8	1846.5
160°	1874.3	1874.0	1873.6	1873.3	1873.0	1872.8	1872.6	1872.3	1872.0	1871.6	1871.3
162.5°	1899.1	1898.1	1897.1	1896.2	1895.2	1894.7	1894.5	1894.2	1893.9	1893.5	1893.2
165°	1918.0	1917.0	1916.0	1915.1	1914.1	1913.6	1913.4	1913.1	1912.8	1912.5	1912.2
167.5°	1934.1	1932.8	1931.5	1930.2	1928.9	1928.2	1928.2	1928.2	1928.2	1928.2	1928.2
170°	1947.2	1945.9	1944.6	1943.3	1942.0	1941.4	1941.4	1941.4	1941.4	1941.4	1941.4
172.5°	1955.9	1954.3	1952.7	1951.0	1949.4	1948.6	1948.8	1949.1	1949.4	1949.8	1950.1
175°	1963.2	1961.6	1960.0	1958.3	1956.7	1955.9	1956.1	1956.4	1956.7	1957.1	1957.4
177.5°	1966.1	1964.5	1962.9	1961.3	1959.7	1958.9	1959.1	1959.4	1959.7	1960.0	1960.3
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1100.0	1102.0	1109.1	1114.2	1124.3	1123.3	1123.3	1122.3	1119.2	1124.3	1127.3
5°	1176.9	1194.1	1196.1	1218.4	1219.4	1228.5	1234.6	1229.5	1241.7	1240.7	1231.6
7.5°	1272.0	1295.3	1306.4	1327.7	1352.0	1345.9	1369.2	1373.2	1371.2	1381.3	1388.4
10°	1376.3	1416.7	1445.1	1484.5	1494.7	1500.7	1515.9	1529.1	1555.4	1535.1	1548.3
12.5°	1495.7	1525.0	1562.5	1625.2	1656.6	1676.8	1683.9	1693.0	1711.2	1700.1	1701.1
15°	1595.9	1635.3	1699.1	1777.0	1786.1	1811.4	1805.3	1860.0	1886.3	1846.8	1869.1
17.5°	1700.1	1752.7	1828.6	1896.4	1934.9	1952.1	1968.3	2020.9	2018.9	2012.8	2017.9
20°	1766.9	1852.9	1947.0	2037.1	2048.2	2061.4	2104.9	2127.1	2123.1	2140.3	2151.4
22.5°	1861.0	1952.1	2052.3	2112.0	2137.3	2152.4	2186.8	2201.0	2207.1	2211.1	2204.1
25°	1939.9	2037.1	2111.0	2163.6	2178.8	2186.8	2198.0	2202.0	2199.0	2191.9	2198.0
27.5°	1993.6	2071.5	2122.1	2146.4	2138.3	2125.1	2103.9	2089.7	2058.3	2043.2	2061.4
30°	2015.8	2050.2	2065.4	2024.9	1984.5	1952.1	1911.6	1836.7	1778.0	1795.2	1771.9
32.5°	1980.4	1958.1	1885.3	1781.1	1749.7	1697.1	1582.7	1494.7	1497.7	1451.2	1470.4
35°	1876.2	1775.0	1637.4	1479.5	1438.0	1409.7	1284.2	1265.0	1224.5	1181.0	1193.1
37.5°	1692.0	1544.3	1377.3	1260.9	1199.2	1137.4	1066.6	1024.1	999.8	981.6	995.8
40°	1467.3	1287.2	1149.6	1045.4	992.7	953.3	904.7	862.2	834.9	831.8	836.9
42.5°	1246.7	1094.9	968.4	869.3	852.1	805.5	774.2	740.8	732.7	719.5	726.6
45°	1055.5	932.0	827.8	746.8	726.6	714.4	676.0	654.7	645.6	637.5	649.7
47.5°	916.8	787.3	711.4	662.8	642.6	622.4	601.1	586.9	579.9	580.9	579.9
50°	783.3	688.1	621.3	583.9	571.8	557.6	540.4	531.3	528.2	519.1	526.2
52.5°	674.0	605.2	558.6	523.2	514.1	504.0	489.8	484.7	477.6	475.6	475.6
55°	585.9	532.3	494.8	471.6	460.4	452.3	444.3	438.2	433.1	433.1	433.1
57.5°	517.1	470.6	443.2	423.0	419.0	410.9	401.7	401.7	394.7	393.7	396.7
60°	458.4	416.9	395.7	378.5	372.4	370.4	361.3	361.3	359.2	354.2	358.2
62.5°	398.7	368.4	350.1	337.0	330.9	330.9	323.8	318.8	318.8	319.8	317.8
65°	344.1	321.8	305.6	295.5	292.5	288.4	287.4	283.3	280.3	281.3	280.3
67.5°	295.5	278.3	267.2	259.1	254.0	252.0	248.9	248.9	246.9	247.9	242.9
70°	252.0	234.8	225.7	217.6	215.5	215.5	211.5	212.5	210.5	213.5	211.5
72.5°	207.5	194.3	187.2	184.2	182.2	181.1	179.1	177.1	176.1	178.1	177.1
75°	168.0	156.9	151.8	149.8	147.7	147.7	146.7	145.7	144.7	144.7	144.7
77.5°	130.5	123.5	117.4	119.4	116.4	117.4	114.4	114.4	115.4	114.4	114.4
80°	96.1	91.1	91.1	89.1	85.0	87.0	87.0	84.0	83.0	85.0	82.0
82.5°	63.8	62.7	60.7	59.7	57.7	58.7	57.7	56.7	55.7	57.7	55.7
85°	37.4	37.4	36.4	34.4	36.4	35.4	34.4	34.4	33.4	33.4	33.4
87.5°	19.2	17.2	17.2	16.2	17.2	15.2	16.2	15.2	14.2	15.2	14.2
90°	36.3	37.6	38.9	40.2	40.8	41.1	41.8	42.5	43.1	43.8	43.1
92.5°	40.2	42.4	44.7	47.0	48.1	48.3	48.6	48.9	49.3	49.6	49.3
95°	47.5	49.7	52.0	54.3	55.4	55.4	55.4	55.4	55.4	55.4	55.4
97.5°	49.3	51.9	54.4	57.0	58.3	58.5	58.8	59.1	59.5	59.8	59.5
100°	50.7	53.3	55.9	58.5	59.8	60.0	60.3	60.6	61.0	61.3	61.0
102.5°	97.2	86.5	75.8	65.1	59.8	60.1	60.8	61.4	62.1	62.7	62.1
105°	262.0	204.7	147.3	90.0	61.3	61.6	62.3	62.9	63.6	64.2	63.6
107.5°	517.5	467.6	417.7	367.8	342.8	321.6	279.1	236.6	194.2	151.7	194.2
110°	647.1	636.4	625.7	615.0	609.7	586.5	540.2	493.8	447.5	401.1	447.5

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	752.6	755.5	758.4	761.3	762.8	762.5	761.8	761.2	760.5	759.9	760.5
115°	840.4	843.7	846.9	850.2	851.8	852.4	853.7	855.0	856.3	857.6	856.3
117.5°	925.9	928.5	931.0	933.6	934.9	935.1	935.4	935.7	936.1	936.4	936.1
120°	1009.0	1011.6	1014.2	1016.8	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1
122.5°	1091.1	1092.7	1094.4	1096.0	1096.8	1097.0	1097.3	1097.6	1098.0	1098.3	1098.0
125°	1167.5	1168.2	1168.8	1169.5	1169.8	1170.1	1170.8	1171.4	1172.1	1172.7	1172.1
127.5°	1245.2	1246.1	1247.1	1248.0	1248.5	1248.2	1247.5	1246.9	1246.2	1245.6	1246.2
130°	1314.0	1315.3	1316.6	1317.9	1318.5	1318.2	1317.5	1316.9	1316.2	1315.6	1316.2
132.5°	1379.6	1380.9	1382.2	1383.5	1384.2	1383.7	1382.7	1381.8	1380.8	1379.8	1380.8
135°	1446.4	1447.4	1448.3	1449.3	1449.8	1449.3	1448.3	1447.4	1446.4	1445.4	1446.4
137.5°	1505.4	1507.0	1508.7	1510.3	1511.1	1510.8	1510.1	1509.5	1508.8	1508.2	1508.8
140°	1562.0	1563.3	1564.6	1565.9	1566.5	1566.2	1565.5	1564.9	1564.2	1563.6	1564.2
142.5°	1615.6	1616.6	1617.5	1618.5	1619.0	1618.5	1617.5	1616.6	1615.6	1614.6	1615.6
145°	1664.8	1665.5	1666.1	1666.8	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1
147.5°	1710.1	1710.7	1711.4	1712.1	1712.4	1711.6	1710.0	1708.3	1706.7	1705.1	1706.7
150°	1750.9	1751.6	1752.2	1752.9	1753.2	1752.7	1751.7	1750.8	1749.8	1748.8	1749.8
152.5°	1786.6	1787.9	1789.2	1790.5	1791.1	1790.3	1788.7	1787.0	1785.4	1783.8	1785.4
155°	1819.0	1820.6	1822.3	1823.9	1824.7	1823.7	1821.8	1819.8	1817.9	1815.9	1817.9
157.5°	1848.5	1850.4	1852.4	1854.3	1855.3	1854.0	1851.4	1848.8	1846.2	1843.6	1846.2
160°	1873.3	1875.2	1877.2	1879.1	1880.1	1879.0	1876.7	1874.4	1872.2	1869.9	1872.2
162.5°	1895.5	1897.7	1900.0	1902.3	1903.4	1902.4	1900.5	1898.6	1896.6	1894.7	1896.6
165°	1914.8	1917.4	1920.0	1922.6	1923.9	1922.8	1920.5	1918.2	1915.9	1913.6	1915.9
167.5°	1930.8	1933.4	1936.0	1938.6	1939.9	1938.6	1936.0	1933.4	1930.8	1928.2	1930.8
170°	1944.0	1946.6	1949.1	1951.7	1953.0	1951.7	1949.1	1946.6	1944.0	1941.4	1944.0
172.5°	1952.7	1955.3	1957.9	1960.5	1961.8	1960.3	1957.4	1954.5	1951.5	1948.6	1951.5
175°	1959.7	1961.9	1964.2	1966.5	1967.6	1966.3	1963.7	1961.1	1958.5	1955.9	1958.5
177.5°	1962.9	1965.5	1968.1	1970.7	1972.0	1970.4	1967.1	1963.9	1960.6	1957.4	1960.6
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1119.2	1122.3	1114.2	1112.1	1112.1	1116.2	1113.2	1085.8	1090.9	1084.8	1082.8
5°	1242.7	1236.6	1228.5	1224.5	1219.4	1205.2	1204.2	1172.9	1166.8	1146.6	1137.4
7.5°	1378.3	1373.2	1348.9	1345.9	1343.9	1330.7	1297.3	1263.9	1239.7	1216.4	1194.1
10°	1533.1	1517.9	1506.8	1484.5	1473.4	1455.2	1411.7	1380.3	1338.8	1303.4	1256.9
12.5°	1719.3	1702.1	1664.7	1648.5	1634.3	1583.7	1540.2	1504.8	1423.8	1399.5	1341.9
15°	1855.9	1819.5	1815.5	1780.0	1778.0	1722.4	1639.4	1600.9	1538.2	1449.1	1389.4
17.5°	2003.7	1971.3	1946.0	1903.5	1897.4	1844.8	1784.1	1690.0	1621.2	1536.2	1460.3
20°	2112.0	2094.8	2051.2	2034.0	1998.6	1954.1	1891.4	1775.0	1691.0	1606.0	1512.9
22.5°	2198.0	2180.8	2146.4	2123.1	2102.9	2045.2	1970.3	1871.1	1755.8	1644.4	1548.3
25°	2197.0	2191.9	2177.7	2166.6	2151.4	2108.9	2046.2	1951.1	1822.5	1700.1	1566.5
27.5°	2072.5	2086.7	2111.0	2123.1	2120.1	2114.0	2078.6	1998.6	1883.3	1737.5	1587.8
30°	1813.4	1865.0	1910.6	1971.3	1989.5	2034.0	2054.3	2008.7	1916.7	1781.1	1615.1
32.5°	1503.8	1578.7	1677.8	1711.2	1768.9	1854.9	1951.1	1968.3	1910.6	1806.4	1632.3
35°	1233.6	1295.3	1372.2	1424.8	1476.5	1616.1	1737.5	1842.8	1862.0	1793.2	1628.2
37.5°	1021.1	1064.6	1132.4	1176.9	1224.5	1343.9	1513.9	1650.5	1746.6	1748.7	1617.1
40°	867.3	886.5	945.2	977.6	1023.1	1126.3	1278.1	1456.2	1596.9	1661.6	1587.8
42.5°	734.7	760.0	808.6	832.8	862.2	952.3	1052.4	1221.4	1395.5	1534.1	1533.1
45°	655.8	674.0	696.2	716.5	749.9	803.5	917.8	1044.3	1211.3	1368.2	1429.9
47.5°	585.9	603.1	625.4	631.5	653.7	704.3	774.2	884.5	1040.3	1196.1	1312.5
50°	527.2	541.4	556.6	567.7	577.8	619.3	671.9	765.0	889.5	1040.3	1185.0
52.5°	481.7	491.8	505.0	511.0	520.1	550.5	591.0	659.8	762.0	899.6	1040.3
55°	439.2	446.3	454.4	464.5	468.5	490.8	522.2	580.9	656.8	780.2	913.8
57.5°	399.7	402.8	407.8	413.9	419.0	438.2	465.5	505.0	571.8	666.9	793.4
60°	355.2	363.3	366.3	372.4	375.4	390.6	411.9	445.3	496.9	578.8	674.0
62.5°	317.8	322.8	327.9	330.9	338.0	343.1	360.3	390.6	433.1	493.8	579.9
65°	284.4	286.4	289.4	292.5	294.5	300.6	316.7	337.0	369.4	423.0	489.8
67.5°	245.9	247.9	252.0	253.0	255.0	263.1	272.2	289.4	316.7	357.2	411.9
70°	208.5	211.5	213.5	215.5	218.6	221.6	231.7	245.9	267.2	295.5	338.0
72.5°	176.1	179.1	179.1	181.1	180.1	184.2	194.3	204.4	218.6	241.9	279.3
75°	143.7	143.7	145.7	146.7	147.7	151.8	155.8	163.9	175.1	193.3	216.6
77.5°	113.3	112.3	114.4	114.4	114.4	117.4	121.4	125.5	132.6	145.7	163.9
80°	83.0	83.0	85.0	86.0	84.0	85.0	87.0	91.1	96.1	105.2	115.4
82.5°	54.6	58.7	57.7	58.7	57.7	59.7	60.7	61.7	63.8	67.8	74.9
85°	33.4	33.4	33.4	34.4	33.4	34.4	34.4	34.4	35.4	37.4	40.5
87.5°	14.2	14.2	14.2	15.2	14.2	14.2	15.2	14.2	15.2	15.2	16.2
90°	42.5	41.8	41.1	40.8	40.2	38.9	37.6	36.3	35.0	30.8	26.6
92.5°	48.9	48.6	48.3	48.1	47.0	44.7	42.4	40.2	37.9	35.0	32.1
95°	55.4	55.4	55.4	55.4	54.3	52.0	49.7	47.5	45.2	41.6	38.1
97.5°	59.1	58.8	58.5	58.3	57.0	54.4	51.9	49.3	46.7	63.2	79.8
100°	60.6	60.3	60.0	59.8	58.5	55.9	53.3	50.7	48.1	98.7	149.3
102.5°	61.4	60.8	60.1	59.8	65.1	75.8	86.5	97.2	107.9	164.3	220.7
105°	62.9	62.3	61.6	61.3	90.0	147.3	204.7	262.0	319.4	348.6	377.8
107.5°	236.6	279.1	321.6	342.8	367.8	417.7	467.6	517.5	567.4	562.5	557.7
110°	493.8	540.2	586.5	609.7	615.0	625.7	636.4	647.1	657.8	654.2	650.7

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	761.2	761.8	762.5	762.8	761.3	758.4	755.5	752.6	749.7	746.1	742.6
115°	855.0	853.7	852.4	851.8	850.2	846.9	843.7	840.4	837.2	834.3	831.4
117.5°	935.7	935.4	935.1	934.9	933.6	931.0	928.5	925.9	923.3	921.7	920.1
120°	1018.1	1018.1	1018.1	1018.1	1016.8	1014.2	1011.6	1009.0	1006.4	1005.4	1004.4
122.5°	1097.6	1097.3	1097.0	1096.8	1096.0	1094.4	1092.7	1091.1	1089.5	1088.2	1086.9
125°	1171.4	1170.8	1170.1	1169.8	1169.5	1168.8	1168.2	1167.5	1166.9	1165.6	1164.3
127.5°	1246.9	1247.5	1248.2	1248.5	1248.0	1247.1	1246.1	1245.2	1244.2	1242.6	1241.0
130°	1316.9	1317.5	1318.2	1318.5	1317.9	1316.6	1315.3	1314.0	1312.7	1311.4	1310.1
132.5°	1381.8	1382.7	1383.7	1384.2	1383.5	1382.2	1380.9	1379.6	1378.3	1377.3	1376.4
135°	1447.4	1448.3	1449.3	1449.8	1449.3	1448.3	1447.4	1446.4	1445.4	1444.1	1442.8
137.5°	1509.5	1510.1	1510.8	1511.1	1510.3	1508.7	1507.0	1505.4	1503.8	1503.2	1502.5
140°	1564.9	1565.5	1566.2	1566.5	1565.9	1564.6	1563.3	1562.0	1560.7	1559.7	1558.7
142.5°	1616.6	1617.5	1618.5	1619.0	1618.5	1617.5	1616.6	1615.6	1614.6	1613.6	1612.7
145°	1667.1	1667.1	1667.1	1667.1	1666.8	1666.1	1665.5	1664.8	1664.2	1663.6	1662.9
147.5°	1708.3	1710.0	1711.6	1712.4	1712.1	1711.4	1710.7	1710.1	1709.4	1708.8	1708.1
150°	1750.8	1751.7	1752.7	1753.2	1752.9	1752.2	1751.6	1750.9	1750.3	1749.7	1749.0
152.5°	1787.0	1788.7	1790.3	1791.1	1790.5	1789.2	1787.9	1786.6	1785.3	1785.0	1784.6
155°	1819.8	1821.8	1823.7	1824.7	1823.9	1822.3	1820.6	1819.0	1817.4	1817.1	1816.7
157.5°	1848.8	1851.4	1854.0	1855.3	1854.3	1852.4	1850.4	1848.5	1846.5	1846.8	1847.2
160°	1874.4	1876.7	1879.0	1880.1	1879.1	1877.2	1875.2	1873.3	1871.3	1871.6	1872.0
162.5°	1898.6	1900.5	1902.4	1903.4	1902.3	1900.0	1897.7	1895.5	1893.2	1893.5	1893.9
165°	1918.2	1920.5	1922.8	1923.9	1922.6	1920.0	1917.4	1914.8	1912.2	1912.5	1912.8
167.5°	1933.4	1936.0	1938.6	1939.9	1938.6	1936.0	1933.4	1930.8	1928.2	1928.2	1928.2
170°	1946.6	1949.1	1951.7	1953.0	1951.7	1949.1	1946.6	1944.0	1941.4	1941.4	1941.4
172.5°	1954.5	1957.4	1960.3	1961.8	1960.5	1957.9	1955.3	1952.7	1950.1	1949.8	1949.4
175°	1961.1	1963.7	1966.3	1967.6	1966.5	1964.2	1961.9	1959.7	1957.4	1957.1	1956.7
177.5°	1963.9	1967.1	1970.4	1972.0	1970.7	1968.1	1965.5	1962.9	1960.3	1960.0	1959.7
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1072.7	1069.6	1069.6	1067.6	1061.5	1050.4	1049.4	1051.4	1045.4	1039.3	1030.2
5°	1125.3	1106.1	1100.0	1093.9	1081.8	1061.5	1053.5	1046.4	1035.2	1022.1	1007.9
7.5°	1169.8	1142.5	1134.4	1123.3	1099.0	1070.7	1052.4	1037.3	1022.1	1003.9	986.7
10°	1225.5	1186.0	1166.8	1150.6	1117.2	1077.7	1050.4	1028.2	1003.9	981.6	959.3
12.5°	1288.2	1224.5	1218.4	1178.9	1140.5	1081.8	1048.4	1016.0	983.6	956.3	933.0
15°	1340.8	1271.0	1245.7	1219.4	1145.5	1072.7	1040.3	1003.9	966.4	937.1	902.7
17.5°	1374.2	1316.6	1262.9	1227.5	1150.6	1085.8	1023.1	981.6	942.1	901.7	873.3
20°	1414.7	1330.7	1284.2	1236.6	1160.7	1075.7	1013.0	961.4	912.8	876.4	842.0
22.5°	1455.2	1341.9	1303.4	1251.8	1162.7	1065.6	994.8	943.1	887.5	851.1	813.6
25°	1451.2	1358.1	1294.3	1250.8	1142.5	1056.5	973.5	912.8	861.2	814.6	777.2
27.5°	1454.2	1339.8	1275.1	1224.5	1128.3	1043.3	951.2	887.5	833.9	785.3	745.8
30°	1455.2	1312.5	1255.8	1195.1	1102.0	1012.0	925.9	861.2	804.5	751.9	716.5
32.5°	1452.2	1290.3	1219.4	1164.8	1060.5	981.6	896.6	827.8	770.1	721.5	688.1
35°	1445.1	1263.9	1182.0	1113.2	1018.0	938.1	869.3	798.4	736.7	692.2	653.7
37.5°	1425.9	1235.6	1142.5	1074.7	968.4	887.5	826.8	768.1	708.4	655.8	623.4
40°	1411.7	1197.2	1103.0	1029.2	914.8	835.9	785.3	729.6	670.9	623.4	592.0
42.5°	1379.3	1160.7	1062.6	974.5	862.2	781.2	733.7	689.1	638.5	592.0	563.7
45°	1326.7	1121.3	1013.0	923.9	804.5	727.6	684.1	647.7	603.1	558.6	530.3
47.5°	1252.8	1064.6	960.4	871.3	747.8	669.9	626.4	599.1	563.7	526.2	501.9
50°	1172.9	1002.9	906.7	818.7	693.2	617.3	574.8	549.5	526.2	491.8	468.5
52.5°	1068.6	937.1	845.0	761.0	634.5	561.6	524.2	506.0	481.7	457.4	437.2
55°	967.4	852.1	776.2	696.2	576.8	509.0	472.6	453.4	439.2	419.0	402.8
57.5°	850.0	773.1	703.3	630.5	523.2	461.5	427.0	403.8	394.7	385.6	370.4
60°	741.8	683.1	626.4	565.7	467.5	411.9	378.5	360.3	351.2	345.1	335.0
62.5°	642.6	597.1	548.5	499.9	410.9	360.3	335.0	316.7	308.6	307.6	298.5
65°	547.5	515.1	475.6	428.1	358.2	313.7	289.4	278.3	269.2	269.2	262.1
67.5°	452.3	430.1	398.7	365.3	310.7	269.2	246.9	236.8	231.7	231.7	226.7
70°	376.4	361.3	332.9	303.6	256.0	224.7	207.5	198.3	195.3	196.3	192.3
72.5°	305.6	289.4	266.1	244.9	209.5	186.2	174.1	163.9	158.9	159.9	158.9
75°	236.8	228.7	208.5	192.3	163.9	147.7	136.6	131.6	127.5	128.5	126.5
77.5°	178.1	166.0	154.8	143.7	126.5	113.3	104.2	99.2	96.1	96.1	96.1
80°	121.4	119.4	110.3	104.2	90.1	79.9	72.9	71.8	68.8	68.8	68.8
82.5°	78.9	73.9	68.8	64.8	56.7	50.6	47.6	45.5	44.5	43.5	45.5
85°	43.5	40.5	38.5	34.4	31.4	28.3	25.3	24.3	23.3	24.3	23.3
87.5°	17.2	14.2	14.2	13.2	12.1	11.1	11.1	9.1	9.1	8.1	8.1
90°	22.3	18.1	16.0	14.4	11.2	7.9	4.7	1.5	4.7	7.9	11.2
92.5°	29.2	26.3	24.8	25.8	27.7	29.6	31.6	33.5	31.6	29.6	27.7
95°	34.5	31.0	29.2	35.8	49.1	62.4	75.7	89.0	75.7	62.4	49.1
97.5°	96.3	112.8	121.1	125.6	134.7	143.8	152.8	161.9	152.8	143.8	134.7
100°	199.8	250.4	275.7	272.5	266.0	259.5	253.0	246.5	253.0	259.5	266.0
102.5°	277.1	333.5	361.7	359.6	355.4	351.2	347.0	342.8	347.0	351.2	355.4
105°	406.9	436.1	450.7	448.9	445.4	441.8	438.3	434.7	438.3	441.8	445.4
107.5°	552.8	547.9	545.5	544.0	541.1	538.2	535.3	532.4	535.3	538.2	541.1
110°	647.1	643.6	641.8	640.5	637.9	635.3	632.7	630.1	632.7	635.3	637.9

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	739.0	735.5	733.7	732.6	730.3	728.0	725.7	723.4	725.7	728.0	730.3
115°	828.5	825.6	824.1	823.1	821.2	819.2	817.3	815.3	817.3	819.2	821.2
117.5°	918.4	916.8	916.0	914.9	912.6	910.3	908.1	905.8	908.1	910.3	912.6
120°	1003.5	1002.5	1002.0	1000.5	997.6	994.7	991.8	988.9	991.8	994.7	997.6
122.5°	1085.6	1084.3	1083.7	1082.6	1080.3	1078.0	1075.8	1073.5	1075.8	1078.0	1080.3
125°	1163.0	1161.7	1161.0	1159.7	1157.1	1154.6	1152.0	1149.4	1152.0	1154.6	1157.1
127.5°	1239.3	1237.7	1236.9	1235.6	1233.0	1230.4	1227.8	1225.2	1227.8	1230.4	1233.0
130°	1308.8	1307.5	1306.9	1305.6	1303.0	1300.4	1297.8	1295.2	1297.8	1300.4	1303.0
132.5°	1375.4	1374.5	1374.0	1372.7	1370.1	1367.5	1364.9	1362.3	1364.9	1367.5	1370.1
135°	1441.5	1440.2	1439.6	1438.6	1436.7	1434.8	1432.8	1430.9	1432.8	1434.8	1436.7
137.5°	1501.9	1501.2	1500.9	1499.6	1497.0	1494.4	1491.8	1489.2	1491.8	1494.4	1497.0
140°	1557.8	1556.8	1556.3	1555.3	1553.4	1551.4	1549.5	1547.5	1549.5	1551.4	1553.4
142.5°	1611.7	1610.8	1610.3	1609.3	1607.4	1605.4	1603.5	1601.5	1603.5	1605.4	1607.4
145°	1662.3	1661.6	1661.3	1660.2	1657.9	1655.6	1653.4	1651.1	1653.4	1655.6	1657.9
147.5°	1707.5	1706.8	1706.5	1705.7	1704.1	1702.4	1700.8	1699.2	1700.8	1702.4	1704.1
150°	1748.4	1747.7	1747.4	1746.9	1745.9	1745.0	1744.0	1743.0	1744.0	1745.0	1745.9
152.5°	1784.3	1784.0	1783.8	1783.6	1783.3	1783.0	1782.7	1782.4	1782.7	1783.0	1783.3
155°	1816.4	1816.1	1815.9	1816.2	1816.9	1817.5	1818.2	1818.8	1818.2	1817.5	1816.9
157.5°	1847.5	1847.8	1848.0	1848.0	1848.0	1848.0	1848.0	1848.0	1848.0	1848.0	1848.0
160°	1872.3	1872.6	1872.8	1873.0	1873.3	1873.6	1874.0	1874.3	1874.0	1873.6	1873.3
162.5°	1894.2	1894.5	1894.7	1895.2	1896.2	1897.1	1898.1	1899.1	1898.1	1897.1	1896.2
165°	1913.1	1913.4	1913.6	1914.1	1915.1	1916.0	1917.0	1918.0	1917.0	1916.0	1915.1
167.5°	1928.2	1928.2	1928.2	1928.9	1930.2	1931.5	1932.8	1934.1	1932.8	1931.5	1930.2
170°	1941.4	1941.4	1941.4	1942.0	1943.3	1944.6	1945.9	1947.2	1945.9	1944.6	1943.3
172.5°	1949.1	1948.8	1948.6	1949.4	1951.0	1952.7	1954.3	1955.9	1954.3	1952.7	1951.0
175°	1956.4	1956.1	1955.9	1956.7	1958.3	1960.0	1961.6	1963.2	1961.6	1960.0	1958.3
177.5°	1959.4	1959.1	1958.9	1959.7	1961.3	1962.9	1964.5	1966.1	1964.5	1962.9	1961.3
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	1028.2	1027.1	1029.2	1023.1	1013.0	1007.9	993.7	990.7	989.7	990.7	991.7
5°	999.8	998.8	995.8	985.7	973.5	964.4	947.2	946.2	940.1	934.0	937.1
7.5°	972.5	968.4	962.4	949.2	933.0	922.9	908.7	898.6	890.5	885.5	881.4
10°	945.2	939.1	933.0	915.8	895.6	880.4	863.2	855.1	846.0	842.0	837.9
12.5°	909.8	903.7	892.6	872.3	860.2	840.9	823.7	815.6	810.6	802.5	797.4
15°	881.4	869.3	863.2	842.0	816.7	814.6	783.3	781.2	771.1	771.1	763.0
17.5°	849.0	839.9	828.8	807.5	789.3	771.1	754.9	748.9	739.7	737.7	733.7
20°	817.7	805.5	801.5	780.2	761.0	738.7	721.5	715.5	711.4	707.4	710.4
22.5°	785.3	775.2	765.0	745.8	731.6	709.4	699.3	693.2	687.1	685.1	686.1
25°	753.9	744.8	734.7	715.5	700.3	682.1	673.0	669.9	666.9	666.9	665.9
27.5°	723.6	714.4	705.3	688.1	673.0	659.8	652.7	649.7	646.6	648.7	650.7
30°	692.2	684.1	676.0	660.8	648.7	636.5	632.5	630.5	629.4	634.5	634.5
32.5°	663.8	656.8	650.7	636.5	624.4	614.3	611.2	612.2	613.2	616.3	618.3
35°	634.5	629.4	623.4	611.2	601.1	592.0	593.0	593.0	595.0	600.1	604.1
37.5°	608.2	601.1	596.0	585.9	577.8	569.7	572.8	575.8	577.8	583.9	585.9
40°	576.8	573.8	569.7	559.6	552.5	551.5	552.5	554.6	558.6	561.6	564.7
42.5°	551.5	547.5	542.4	534.3	528.2	529.3	530.3	532.3	534.3	539.4	542.4
45°	523.2	520.1	516.1	509.0	504.0	505.0	506.0	506.0	508.0	514.1	516.1
47.5°	491.8	492.8	487.8	480.7	477.6	477.6	477.6	479.7	484.7	486.8	487.8
50°	461.5	459.4	458.4	451.3	449.3	448.3	449.3	450.3	457.4	456.4	459.4
52.5°	429.1	429.1	428.1	424.0	421.0	421.0	419.0	424.0	426.0	428.1	431.1
55°	397.7	394.7	393.7	391.6	387.6	386.6	388.6	394.7	396.7	398.7	401.7
57.5°	363.3	363.3	361.3	358.2	358.2	358.2	358.2	362.3	365.3	367.3	373.4
60°	331.9	327.9	324.8	324.8	324.8	323.8	329.9	329.9	336.0	337.0	339.0
62.5°	294.5	292.5	290.4	291.4	290.4	292.5	294.5	298.5	299.5	302.6	305.6
65°	259.1	259.1	257.0	263.1	259.1	259.1	264.1	264.1	266.1	269.2	273.2
67.5°	224.7	225.7	223.6	223.6	225.7	226.7	227.7	231.7	232.8	236.8	241.9
70°	189.2	191.3	192.3	190.2	192.3	194.3	196.3	197.3	201.4	203.4	206.4
72.5°	157.9	159.9	156.9	157.9	158.9	160.9	161.9	163.9	166.0	172.0	174.1
75°	126.5	125.5	124.5	128.5	126.5	130.5	131.6	131.6	133.6	138.6	140.7
77.5°	97.1	97.1	98.2	96.1	99.2	98.2	99.2	102.2	105.2	105.2	113.3
80°	67.8	69.8	69.8	69.8	70.8	71.8	69.8	74.9	75.9	75.9	78.9
82.5°	43.5	44.5	43.5	45.5	45.5	47.6	46.6	47.6	49.6	51.6	52.6
85°	23.3	23.3	25.3	25.3	24.3	25.3	24.3	25.3	27.3	27.3	28.3
87.5°	8.1	8.1	8.1	8.1	9.1	8.1	9.1	9.1	8.1	8.1	11.1
90°	14.4	16.0	18.1	22.3	26.6	30.8	35.0	36.3	37.6	38.9	40.2
92.5°	25.8	24.8	26.3	29.2	32.1	35.0	37.9	40.2	42.4	44.7	47.0
95°	35.8	29.2	31.0	34.5	38.1	41.6	45.2	47.5	49.7	52.0	54.3
97.5°	125.6	121.1	112.8	96.3	79.8	63.2	46.7	49.3	51.9	54.4	57.0
100°	272.5	275.7	250.4	199.8	149.3	98.7	48.1	50.7	53.3	55.9	58.5
102.5°	359.6	361.7	333.5	277.1	220.7	164.3	107.9	97.2	86.5	75.8	65.1
105°	448.9	450.7	436.1	406.9	377.8	348.6	319.4	262.0	204.7	147.3	90.0
107.5°	544.0	545.5	547.9	552.8	557.7	562.5	567.4	517.5	467.6	417.7	367.8
110°	640.5	641.8	643.6	647.1	650.7	654.2	657.8	647.1	636.4	625.7	615.0

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	732.6	733.7	735.5	739.0	742.6	746.1	749.7	752.6	755.5	758.4	761.3
115°	823.1	824.1	825.6	828.5	831.4	834.3	837.2	840.4	843.7	846.9	850.2
117.5°	914.9	916.0	916.8	918.4	920.1	921.7	923.3	925.9	928.5	931.0	933.6
120°	1000.5	1002.0	1002.5	1003.5	1004.4	1005.4	1006.4	1009.0	1011.6	1014.2	1016.8
122.5°	1082.6	1083.7	1084.3	1085.6	1086.9	1088.2	1089.5	1091.1	1092.7	1094.4	1096.0
125°	1159.7	1161.0	1161.7	1163.0	1164.3	1165.6	1166.9	1167.5	1168.2	1168.8	1169.5
127.5°	1235.6	1236.9	1237.7	1239.3	1241.0	1242.6	1244.2	1245.2	1246.1	1247.1	1248.0
130°	1305.6	1306.9	1307.5	1308.8	1310.1	1311.4	1312.7	1314.0	1315.3	1316.6	1317.9
132.5°	1372.7	1374.0	1374.5	1375.4	1376.4	1377.3	1378.3	1379.6	1380.9	1382.2	1383.5
135°	1438.6	1439.6	1440.2	1441.5	1442.8	1444.1	1445.4	1446.4	1447.4	1448.3	1449.3
137.5°	1499.6	1500.9	1501.2	1501.9	1502.5	1503.2	1503.8	1505.4	1507.0	1508.7	1510.3
140°	1555.3	1556.3	1556.8	1557.8	1558.7	1559.7	1560.7	1562.0	1563.3	1564.6	1565.9
142.5°	1609.3	1610.3	1610.8	1611.7	1612.7	1613.6	1614.6	1615.6	1616.6	1617.5	1618.5
145°	1660.2	1661.3	1661.6	1662.3	1662.9	1663.6	1664.2	1664.8	1665.5	1666.1	1666.8
147.5°	1705.7	1706.5	1706.8	1707.5	1708.1	1708.8	1709.4	1710.1	1710.7	1711.4	1712.1
150°	1746.9	1747.4	1747.7	1748.4	1749.0	1749.7	1750.3	1750.9	1751.6	1752.2	1752.9
152.5°	1783.6	1783.8	1784.0	1784.3	1784.6	1785.0	1785.3	1786.6	1787.9	1789.2	1790.5
155°	1816.2	1815.9	1816.1	1816.4	1816.7	1817.1	1817.4	1819.0	1820.6	1822.3	1823.9
157.5°	1848.0	1848.0	1847.8	1847.5	1847.2	1846.8	1846.5	1848.5	1850.4	1852.4	1854.3
160°	1873.0	1872.8	1872.6	1872.3	1872.0	1871.6	1871.3	1873.3	1875.2	1877.2	1879.1
162.5°	1895.2	1894.7	1894.5	1894.2	1893.9	1893.5	1893.2	1895.5	1897.7	1900.0	1902.3
165°	1914.1	1913.6	1913.4	1913.1	1912.8	1912.5	1912.2	1914.8	1917.4	1920.0	1922.6
167.5°	1928.9	1928.2	1928.2	1928.2	1928.2	1928.2	1928.2	1930.8	1933.4	1936.0	1938.6
170°	1942.0	1941.4	1941.4	1941.4	1941.4	1941.4	1941.4	1944.0	1946.6	1949.1	1951.7
172.5°	1949.4	1948.6	1948.8	1949.1	1949.4	1949.8	1950.1	1952.7	1955.3	1957.9	1960.5
175°	1956.7	1955.9	1956.1	1956.4	1956.7	1957.1	1957.4	1959.7	1961.9	1964.2	1966.5
177.5°	1959.7	1958.9	1959.1	1959.4	1959.7	1960.0	1960.3	1962.9	1965.5	1968.1	1970.7
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	990.7	991.7	987.7	984.6	992.7	987.7	987.7	988.7	986.7	989.7	988.7
5°	935.1	936.1	929.0	931.0	927.0	925.9	924.9	931.0	930.0	929.0	931.0
7.5°	880.4	880.4	877.4	875.3	875.3	872.3	876.4	875.3	877.4	877.4	880.4
10°	834.9	836.9	831.8	826.8	825.8	826.8	826.8	827.8	828.8	835.9	834.9
12.5°	797.4	794.4	793.4	790.3	785.3	783.3	781.2	792.4	789.3	789.3	789.3
15°	755.9	763.0	762.0	752.9	750.9	754.9	752.9	752.9	763.0	762.0	761.0
17.5°	733.7	731.6	729.6	724.6	725.6	724.6	725.6	725.6	731.6	731.6	731.6
20°	708.4	704.3	704.3	702.3	702.3	699.3	703.3	704.3	708.4	708.4	709.4
22.5°	686.1	683.1	683.1	682.1	684.1	680.0	684.1	685.1	685.1	688.1	688.1
25°	666.9	664.9	664.9	666.9	666.9	666.9	666.9	670.9	667.9	668.9	667.9
27.5°	649.7	650.7	651.7	652.7	651.7	652.7	653.7	655.8	656.8	655.8	653.7
30°	633.5	636.5	637.5	637.5	639.6	640.6	641.6	641.6	642.6	639.6	641.6
32.5°	621.3	621.3	623.4	624.4	626.4	627.4	627.4	629.4	628.4	625.4	626.4
35°	604.1	604.1	608.2	610.2	613.2	612.2	613.2	613.2	614.3	612.2	609.2
37.5°	586.9	589.0	589.0	593.0	594.0	595.0	594.0	596.0	595.0	593.0	592.0
40°	566.7	565.7	566.7	569.7	570.7	570.7	570.7	572.8	572.8	572.8	571.8
42.5°	541.4	544.4	543.4	546.5	545.4	545.4	547.5	549.5	550.5	547.5	548.5
45°	517.1	517.1	519.1	519.1	520.1	520.1	524.2	522.2	524.2	522.2	523.2
47.5°	490.8	491.8	491.8	492.8	494.8	496.9	494.8	495.9	495.9	496.9	494.8
50°	461.5	461.5	463.5	466.5	470.6	468.5	467.5	471.6	468.5	468.5	466.5
52.5°	431.1	434.1	435.1	438.2	441.2	442.2	443.2	441.2	442.2	439.2	440.2
55°	401.7	402.8	406.8	409.8	412.9	412.9	411.9	412.9	413.9	409.8	409.8
57.5°	372.4	375.4	379.5	379.5	383.5	383.5	382.5	382.5	383.5	380.5	379.5
60°	341.0	344.1	349.1	349.1	355.2	356.2	354.2	352.2	352.2	349.1	350.1
62.5°	307.6	310.7	313.7	318.8	322.8	320.8	324.8	320.8	321.8	315.7	315.7
65°	278.3	279.3	284.4	289.4	289.4	291.4	289.4	290.4	287.4	287.4	283.3
67.5°	243.9	243.9	248.9	254.0	259.1	259.1	259.1	256.0	256.0	253.0	253.0
70°	213.5	212.5	217.6	220.6	223.6	224.7	222.6	221.6	219.6	216.6	215.5
72.5°	176.1	178.1	183.2	185.2	190.2	189.2	194.3	188.2	188.2	183.2	182.2
75°	142.7	144.7	149.8	152.8	155.8	155.8	158.9	155.8	151.8	149.8	148.8
77.5°	113.3	112.3	116.4	121.4	122.4	121.4	123.5	122.4	118.4	118.4	116.4
80°	81.0	84.0	88.0	87.0	91.1	90.1	90.1	88.0	88.0	85.0	87.0
82.5°	53.6	56.7	57.7	56.7	57.7	59.7	60.7	59.7	59.7	57.7	58.7
85°	28.3	28.3	30.4	31.4	30.4	30.4	31.4	34.4	32.4	30.4	32.4
87.5°	9.1	8.1	8.1	9.1	8.1	8.1	9.1	9.1	10.1	10.1	10.1
90°	40.8	41.1	41.8	42.5	43.1	43.8	43.1	42.5	41.8	41.1	40.8
92.5°	48.1	48.3	48.6	48.9	49.3	49.6	49.3	48.9	48.6	48.3	48.1
95°	55.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4
97.5°	58.3	58.5	58.8	59.1	59.5	59.8	59.5	59.1	58.8	58.5	58.3
100°	59.8	60.0	60.3	60.6	61.0	61.3	61.0	60.6	60.3	60.0	59.8
102.5°	59.8	60.1	60.8	61.4	62.1	62.7	62.1	61.4	60.8	60.1	59.8
105°	61.3	61.6	62.3	62.9	63.6	64.2	63.6	62.9	62.3	61.6	61.3
107.5°	342.8	321.6	279.1	236.6	194.2	151.7	194.2	236.6	279.1	321.6	342.8
110°	609.7	586.5	540.2	493.8	447.5	401.1	447.5	493.8	540.2	586.5	609.7

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	762.8	762.5	761.8	761.2	760.5	759.9	760.5	761.2	761.8	762.5	762.8
115°	851.8	852.4	853.7	855.0	856.3	857.6	856.3	855.0	853.7	852.4	851.8
117.5°	934.9	935.1	935.4	935.7	936.1	936.4	936.1	935.7	935.4	935.1	934.9
120°	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1
122.5°	1096.8	1097.0	1097.3	1097.6	1098.0	1098.3	1098.0	1097.6	1097.3	1097.0	1096.8
125°	1169.8	1170.1	1170.8	1171.4	1172.1	1172.7	1172.1	1171.4	1170.8	1170.1	1169.8
127.5°	1248.5	1248.2	1247.5	1246.9	1246.2	1245.6	1246.2	1246.9	1247.5	1248.2	1248.5
130°	1318.5	1318.2	1317.5	1316.9	1316.2	1315.6	1316.2	1316.9	1317.5	1318.2	1318.5
132.5°	1384.2	1383.7	1382.7	1381.8	1380.8	1379.8	1380.8	1381.8	1382.7	1383.7	1384.2
135°	1449.8	1449.3	1448.3	1447.4	1446.4	1445.4	1446.4	1447.4	1448.3	1449.3	1449.8
137.5°	1511.1	1510.8	1510.1	1509.5	1508.8	1508.2	1508.8	1509.5	1510.1	1510.8	1511.1
140°	1566.5	1566.2	1565.5	1564.9	1564.2	1563.6	1564.2	1564.9	1565.5	1566.2	1566.5
142.5°	1619.0	1618.5	1617.5	1616.6	1615.6	1614.6	1615.6	1616.6	1617.5	1618.5	1619.0
145°	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1
147.5°	1712.4	1711.6	1710.0	1708.3	1706.7	1705.1	1706.7	1708.3	1710.0	1711.6	1712.4
150°	1753.2	1752.7	1751.7	1750.8	1749.8	1748.8	1749.8	1750.8	1751.7	1752.7	1753.2
152.5°	1791.1	1790.3	1788.7	1787.0	1785.4	1783.8	1785.4	1787.0	1788.7	1790.3	1791.1
155°	1824.7	1823.7	1821.8	1819.8	1817.9	1815.9	1817.9	1819.8	1821.8	1823.7	1824.7
157.5°	1855.3	1854.0	1851.4	1848.8	1846.2	1843.6	1846.2	1848.8	1851.4	1854.0	1855.3
160°	1880.1	1879.0	1876.7	1874.4	1872.2	1869.9	1872.2	1874.4	1876.7	1879.0	1880.1
162.5°	1903.4	1902.4	1900.5	1898.6	1896.6	1894.7	1896.6	1898.6	1900.5	1902.4	1903.4
165°	1923.9	1922.8	1920.5	1918.2	1915.9	1913.6	1915.9	1918.2	1920.5	1922.8	1923.9
167.5°	1939.9	1938.6	1936.0	1933.4	1930.8	1928.2	1930.8	1933.4	1936.0	1938.6	1939.9
170°	1953.0	1951.7	1949.1	1946.6	1944.0	1941.4	1944.0	1946.6	1949.1	1951.7	1953.0
172.5°	1961.8	1960.3	1957.4	1954.5	1951.5	1948.6	1951.5	1954.5	1957.4	1960.3	1961.8
175°	1967.6	1966.3	1963.7	1961.1	1958.5	1955.9	1958.5	1961.1	1963.7	1966.3	1967.6
177.5°	1972.0	1970.4	1967.1	1963.9	1960.6	1957.4	1960.6	1963.9	1967.1	1970.4	1972.0
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3	1044.3
2.5°	991.7	993.7	994.8	990.7	987.7	992.7	999.8	1004.9	1008.9	1014.0	1017.0
5°	933.0	940.1	940.1	942.1	945.2	950.2	963.4	972.5	980.6	986.7	991.7
7.5°	883.4	888.5	891.5	896.6	901.7	908.7	923.9	937.1	949.2	956.3	964.4
10°	838.9	843.0	848.0	851.1	860.2	870.3	889.5	900.6	914.8	925.9	936.1
12.5°	796.4	810.6	813.6	812.6	820.7	831.8	851.1	868.3	883.4	894.6	905.7
15°	766.1	771.1	777.2	776.2	793.4	796.4	812.6	832.8	853.1	860.2	870.3
17.5°	732.7	740.8	746.8	749.9	754.9	766.1	781.2	796.4	822.7	823.7	850.0
20°	706.3	714.4	718.5	722.5	725.6	738.7	751.9	769.1	790.3	801.5	815.6
22.5°	689.1	693.2	696.2	699.3	703.3	710.4	726.6	745.8	760.0	772.1	781.2
25°	668.9	673.0	677.0	679.0	682.1	686.1	698.3	713.4	733.7	741.8	750.9
27.5°	654.7	654.7	656.8	656.8	660.8	664.9	674.0	688.1	704.3	714.4	726.6
30°	639.6	638.5	639.6	638.5	637.5	643.6	651.7	663.8	675.0	687.1	695.2
32.5°	624.4	623.4	623.4	624.4	620.3	623.4	627.4	638.5	650.7	656.8	665.9
35°	608.2	606.2	606.2	606.2	604.1	602.1	606.2	616.3	624.4	632.5	639.6
37.5°	592.0	589.0	589.0	586.9	584.9	581.9	581.9	590.0	601.1	604.1	613.2
40°	569.7	569.7	567.7	566.7	564.7	562.7	559.6	566.7	576.8	579.9	586.9
42.5°	547.5	544.4	543.4	543.4	543.4	540.4	538.4	543.4	549.5	554.6	558.6
45°	522.2	520.1	521.2	520.1	518.1	517.1	516.1	518.1	525.2	527.2	532.3
47.5°	494.8	493.8	493.8	492.8	491.8	492.8	488.8	493.8	495.9	497.9	501.9
50°	466.5	465.5	464.5	463.5	463.5	464.5	463.5	463.5	467.5	469.6	473.6
52.5°	438.2	435.1	435.1	434.1	434.1	432.1	434.1	435.1	437.2	439.2	441.2
55°	407.8	407.8	404.8	404.8	402.8	402.8	403.8	402.8	406.8	408.8	408.8
57.5°	378.5	374.4	375.4	373.4	371.4	370.4	370.4	372.4	374.4	374.4	376.4
60°	347.1	343.1	342.0	338.0	340.0	337.0	338.0	338.0	342.0	340.0	342.0
62.5°	315.7	310.7	307.6	305.6	305.6	306.6	304.6	303.6	305.6	307.6	311.7
65°	282.3	279.3	276.3	273.2	273.2	272.2	274.2	271.2	270.2	271.2	273.2
67.5°	247.9	244.9	241.9	238.8	239.8	236.8	234.8	237.8	235.8	236.8	238.8
70°	214.5	212.5	206.4	204.4	203.4	204.4	203.4	201.4	204.4	203.4	204.4
72.5°	181.1	179.1	176.1	171.0	171.0	170.0	169.0	169.0	168.0	168.0	168.0
75°	148.8	144.7	141.7	140.7	138.6	137.6	136.6	134.6	135.6	136.6	134.6
77.5°	115.4	110.3	109.3	109.3	106.3	106.3	107.3	106.3	105.2	105.2	105.2
80°	85.0	81.0	81.0	78.9	76.9	76.9	76.9	76.9	75.9	74.9	75.9
82.5°	54.6	53.6	52.6	52.6	54.6	50.6	52.6	51.6	50.6	50.6	49.6
85°	30.4	31.4	30.4	31.4	29.3	30.4	30.4	30.4	29.3	30.4	28.3
87.5°	11.1	11.1	11.1	12.1	12.1	12.1	12.1	12.1	13.2	12.1	12.1
90°	40.2	38.9	37.6	36.3	35.0	30.8	26.6	22.3	18.1	16.0	14.4
92.5°	47.0	44.7	42.4	40.2	37.9	35.0	32.1	29.2	26.3	24.8	25.8
95°	54.3	52.0	49.7	47.5	45.2	41.6	38.1	34.5	31.0	29.2	35.8
97.5°	57.0	54.4	51.9	49.3	46.7	63.2	79.8	96.3	112.8	121.1	125.6
100°	58.5	55.9	53.3	50.7	48.1	98.7	149.3	199.8	250.4	275.7	272.5
102.5°	65.1	75.8	86.5	97.2	107.9	164.3	220.7	277.1	333.5	361.7	359.6
105°	90.0	147.3	204.7	262.0	319.4	348.6	377.8	406.9	436.1	450.7	448.9
107.5°	367.8	417.7	467.6	517.5	567.4	562.5	557.7	552.8	547.9	545.5	544.0
110°	615.0	625.7	636.4	647.1	657.8	654.2	650.7	647.1	643.6	641.8	640.5

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	761.3	758.4	755.5	752.6	749.7	746.1	742.6	739.0	735.5	733.7	732.6
115°	850.2	846.9	843.7	840.4	837.2	834.3	831.4	828.5	825.6	824.1	823.1
117.5°	933.6	931.0	928.5	925.9	923.3	921.7	920.1	918.4	916.8	916.0	914.9
120°	1016.8	1014.2	1011.6	1009.0	1006.4	1005.4	1004.4	1003.5	1002.5	1002.0	1000.5
122.5°	1096.0	1094.4	1092.7	1091.1	1089.5	1088.2	1086.9	1085.6	1084.3	1083.7	1082.6
125°	1169.5	1168.8	1168.2	1167.5	1166.9	1165.6	1164.3	1163.0	1161.7	1161.0	1159.7
127.5°	1248.0	1247.1	1246.1	1245.2	1244.2	1242.6	1241.0	1239.3	1237.7	1236.9	1235.6
130°	1317.9	1316.6	1315.3	1314.0	1312.7	1311.4	1310.1	1308.8	1307.5	1306.9	1305.6
132.5°	1383.5	1382.2	1380.9	1379.6	1378.3	1377.3	1376.4	1375.4	1374.5	1374.0	1372.7
135°	1449.3	1448.3	1447.4	1446.4	1445.4	1444.1	1442.8	1441.5	1440.2	1439.6	1438.6
137.5°	1510.3	1508.7	1507.0	1505.4	1503.8	1503.2	1502.5	1501.9	1501.2	1500.9	1499.6
140°	1565.9	1564.6	1563.3	1562.0	1560.7	1559.7	1558.7	1557.8	1556.8	1556.3	1555.3
142.5°	1618.5	1617.5	1616.6	1615.6	1614.6	1613.6	1612.7	1611.7	1610.8	1610.3	1609.3
145°	1666.8	1666.1	1665.5	1664.8	1664.2	1663.6	1662.9	1662.3	1661.6	1661.3	1660.2
147.5°	1712.1	1711.4	1710.7	1710.1	1709.4	1708.8	1708.1	1707.5	1706.8	1706.5	1705.7
150°	1752.9	1752.2	1751.6	1750.9	1750.3	1749.7	1749.0	1748.4	1747.7	1747.4	1746.9
152.5°	1790.5	1789.2	1787.9	1786.6	1785.3	1785.0	1784.6	1784.3	1784.0	1783.8	1783.6
155°	1823.9	1822.3	1820.6	1819.0	1817.4	1817.1	1816.7	1816.4	1816.1	1815.9	1816.2
157.5°	1854.3	1852.4	1850.4	1848.5	1846.5	1846.8	1847.2	1847.5	1847.8	1848.0	1848.0
160°	1879.1	1877.2	1875.2	1873.3	1871.3	1871.6	1872.0	1872.3	1872.6	1872.8	1873.0
162.5°	1902.3	1900.0	1897.7	1895.5	1893.2	1893.5	1893.9	1894.2	1894.5	1894.7	1895.2
165°	1922.6	1920.0	1917.4	1914.8	1912.2	1912.5	1912.8	1913.1	1913.4	1913.6	1914.1
167.5°	1938.6	1936.0	1933.4	1930.8	1928.2	1928.2	1928.2	1928.2	1928.2	1928.2	1928.9
170°	1951.7	1949.1	1946.6	1944.0	1941.4	1941.4	1941.4	1941.4	1941.4	1941.4	1942.0
172.5°	1960.5	1957.9	1955.3	1952.7	1950.1	1949.8	1949.4	1949.1	1948.8	1948.6	1949.4
175°	1966.5	1964.2	1961.9	1959.7	1957.4	1957.1	1956.7	1956.4	1956.1	1955.9	1956.7
177.5°	1970.7	1968.1	1965.5	1962.9	1960.3	1960.0	1959.7	1959.4	1959.1	1958.9	1959.7
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1044.3	1044.3	1044.3	1044.3
2.5°	1022.1	1025.1	1035.2	1047.4
5°	1001.8	1009.9	1024.1	1043.3
7.5°	979.6	991.7	1012.0	1036.2
10°	954.3	971.5	996.8	1027.1
12.5°	927.0	949.2	981.6	1013.0
15°	909.8	932.0	961.4	995.8
17.5°	876.4	902.7	933.0	981.6
20°	842.0	871.3	910.8	959.3
22.5°	815.6	847.0	884.5	936.1
25°	784.3	816.7	857.1	910.8
27.5°	750.9	783.3	828.8	885.5
30°	725.6	756.9	800.5	861.2
32.5°	695.2	725.6	771.1	834.9
35°	660.8	695.2	738.7	803.5
37.5°	634.5	665.9	711.4	773.1
40°	606.2	633.5	678.0	738.7
42.5°	575.8	606.2	644.6	705.3
45°	547.5	569.7	609.2	666.9
47.5°	517.1	542.4	572.8	617.3
50°	484.7	506.0	539.4	569.7
52.5°	453.4	470.6	498.9	522.2
55°	420.0	437.2	458.4	472.6
57.5°	388.6	400.7	414.9	424.0
60°	350.1	362.3	371.4	380.5
62.5°	315.7	324.8	329.9	335.0
65°	280.3	285.4	288.4	292.5
67.5°	241.9	246.9	247.9	254.0
70°	206.4	207.5	209.5	212.5
72.5°	173.0	175.1	174.1	176.1
75°	138.6	140.7	138.6	140.7
77.5°	105.2	107.3	107.3	110.3
80°	75.9	76.9	77.9	77.9
82.5°	49.6	52.6	50.6	51.6
85°	28.3	29.3	29.3	30.4
87.5°	13.2	14.2	13.2	15.2
90°	11.2	7.9	4.7	1.5
92.5°	27.7	29.6	31.6	33.5
95°	49.1	62.4	75.7	89.0
97.5°	134.7	143.8	152.8	161.9
100°	266.0	259.5	253.0	246.5
102.5°	355.4	351.2	347.0	342.8
105°	445.4	441.8	438.3	434.7
107.5°	541.1	538.2	535.3	532.4
110°	637.9	635.3	632.7	630.1

TEST NUMBER: P1030973

CATALOG NUMBER: S123DIW-B775D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	730.3	728.0	725.7	723.4
115°	821.2	819.2	817.3	815.3
117.5°	912.6	910.3	908.1	905.8
120°	997.6	994.7	991.8	988.9
122.5°	1080.3	1078.0	1075.8	1073.5
125°	1157.1	1154.6	1152.0	1149.4
127.5°	1233.0	1230.4	1227.8	1225.2
130°	1303.0	1300.4	1297.8	1295.2
132.5°	1370.1	1367.5	1364.9	1362.3
135°	1436.7	1434.8	1432.8	1430.9
137.5°	1497.0	1494.4	1491.8	1489.2
140°	1553.4	1551.4	1549.5	1547.5
142.5°	1607.4	1605.4	1603.5	1601.5
145°	1657.9	1655.6	1653.4	1651.1
147.5°	1704.1	1702.4	1700.8	1699.2
150°	1745.9	1745.0	1744.0	1743.0
152.5°	1783.3	1783.0	1782.7	1782.4
155°	1816.9	1817.5	1818.2	1818.8
157.5°	1848.0	1848.0	1848.0	1848.0
160°	1873.3	1873.6	1874.0	1874.3
162.5°	1896.2	1897.1	1898.1	1899.1
165°	1915.1	1916.0	1917.0	1918.0
167.5°	1930.2	1931.5	1932.8	1934.1
170°	1943.3	1944.6	1945.9	1947.2
172.5°	1951.0	1952.7	1954.3	1955.9
175°	1958.3	1960.0	1961.6	1963.2
177.5°	1961.3	1962.9	1964.5	1966.1
180°	1963.2	1963.2	1963.2	1963.2

(END OF REPORT)