

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030649

Luminaire Tested: S123DIW-B1000D1030UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030649
REPORT IS A COMBINATION OF REPORTS P990542 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D1030UB2750-4F0-XX-W2A-F1_5000K
Description: Define 3 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7425.0 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 78.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030649

CATALOG NUMBER: S123DIW-B1000D1030UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030649

CATALOG NUMBER: S123DIW-B1000D1030UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	48	49	45	42	40	38	36
4	75	64	56	50	69	59	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	35	31	35	31	27	30	26	23
7	58	46	38	32	54	43	36	31	37	32	27	32	27	24	27	23	21
8	54	42	34	29	50	39	32	27	34	28	24	29	25	21	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	22	19	23	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	17	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16283	16283	16283
5°	16323	15721	15697
10°	16178	15189	15033
15°	15953	14635	14309
20°	15696	14022	13592
25°	15362	13373	12824
30°	14997	12702	12018
35°	14614	12016	11216
40°	14214	11298	10428
45°	13773	10596	9603
50°	13326	9815	8776
55°	12751	9001	7939
60°	12158	8103	7047
65°	11603	7132	6116
70°	10802	6054	5032
75°	9647	4793	3906
80°	8333	3369	2763
85°	6493	1810	1383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13773 cd/sqm

TEST NUMBER: P1030649

CATALOG NUMBER: S123DIW-B1000D1030UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	1.9
10°-20°	402.7	5.4
20°-30°	594.7	8.0
30°-40°	694.6	9.4
40°-50°	698.3	9.4
50°-60°	613.4	8.3
60°-70°	456.8	6.2
70°-80°	260.0	3.5
80°-90°	76.6	1.0
90°-100°	81.0	1.1
100°-110°	245.1	3.3
110°-120°	417.2	5.6
120°-130°	548.9	7.4
130°-140°	617.0	8.3
140°-150°	606.5	8.2
150°-160°	510.6	6.9
160°-170°	340.0	4.6
170°-180°	119.0	1.6
0°-30°	1140.0	15.4
0°-40°	1834.6	24.7
0°-60°	3146.3	42.4
0°-90°	3939.7	53.1
90°-120°	743.3	10.0
90°-150°	2515.7	33.9
90°-180°	3485.0	46.9
0°-180°	7425.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1513	1513	1513	1513	1513	
5°	1514	1508	1493	1506	1504	144
15°	1441	1436	1419	1430	1422	406
25°	1308	1301	1284	1285	1281	603
35°	1132	1124	1107	1099	1093	708
45°	927	922	905	890	883	716
55°	704	702	686	671	665	630
65°	480	474	460	450	446	474
75°	254	248	244	238	234	271
85°	68	65	65	62	62	73
90°	1	11	24	28	30	9
95°	58	65	73	77	77	64
105°	222	224	233	233	235	238
115°	420	423	421	422	421	416
125°	615	618	616	612	608	548
135°	797	803	802	798	796	614
145°	967	969	972	971	967	604
155°	1108	1108	1109	1113	1106	510
165°	1206	1204	1204	1210	1202	340
175°	1255	1251	1251	1257	1250	119
180°	1258	1258	1258	1258	1258	

TEST NUMBER: P1030649

CATALOG NUMBER: S123DIW-B1000D1030UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1512.7	1512.7	1512.7	1512.7	1512.7
2.5°	1519.2	1514.0	1499.7	1512.7	1511.4
5°	1514.0	1507.5	1493.2	1506.2	1503.6
7.5°	1502.3	1495.8	1481.5	1493.2	1491.9
10°	1486.7	1480.2	1463.3	1475.0	1472.4
12.5°	1465.9	1460.7	1445.1	1452.9	1451.6
15°	1441.2	1436.0	1419.1	1429.5	1421.7
17.5°	1413.9	1407.4	1390.5	1398.3	1395.7
20°	1382.7	1374.9	1358.0	1363.2	1359.3
22.5°	1347.6	1339.7	1322.8	1326.7	1321.5
25°	1308.5	1300.7	1283.8	1285.1	1281.2
27.5°	1268.2	1260.4	1242.2	1243.5	1239.6
30°	1224.0	1217.5	1199.3	1199.3	1190.2
32.5°	1179.8	1170.7	1157.6	1148.5	1144.6
35°	1131.6	1123.8	1106.9	1099.1	1092.6
37.5°	1083.5	1073.1	1056.2	1047.1	1043.2
40°	1032.8	1025.0	1006.8	996.4	991.2
42.5°	982.0	972.9	954.7	944.3	939.1
45°	927.4	922.2	905.3	889.7	883.2
47.5°	874.1	866.3	850.7	835.1	829.9
50°	819.5	813.0	796.0	781.7	773.9
52.5°	762.2	758.3	740.1	728.4	720.6
55°	703.7	702.4	685.5	671.2	664.7
57.5°	649.1	643.9	630.9	617.8	610.0
60°	589.2	587.9	572.3	560.6	554.1
62.5°	535.9	532.0	516.4	504.7	500.8
65°	480.0	473.5	460.5	450.1	446.1
67.5°	420.1	414.9	404.5	395.4	390.2
70°	366.8	359.0	351.2	342.1	335.6
72.5°	310.9	305.7	296.6	288.8	286.2
75°	253.6	248.4	244.5	238.0	234.1
77.5°	202.9	200.3	195.1	189.9	189.9
80°	153.5	149.6	147.0	145.7	145.7
82.5°	105.4	105.4	105.4	102.8	101.5
85°	67.6	65.0	65.0	62.4	62.4
87.5°	33.8	29.9	28.6	27.3	27.3
90°	1.0	10.9	23.7	27.7	29.6
92.5°	29.6	35.6	41.5	44.5	42.5
95°	58.3	65.2	73.1	77.1	77.1
97.5°	95.8	100.8	106.7	111.7	110.7
100°	134.4	140.3	145.3	148.2	150.2
102.5°	178.8	181.8	188.7	191.7	190.7
105°	222.3	224.3	233.2	233.2	235.2
107.5°	273.7	274.7	278.6	281.6	280.6
110°	321.1	323.1	325.1	329.0	327.1

TEST NUMBER: P1030649

CATALOG NUMBER: S123DIW-B1000D1030UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	370.5	371.5	371.5	376.5	376.5
115°	420.0	422.9	420.9	421.9	420.9
117.5°	470.3	471.3	469.4	469.4	466.4
120°	516.8	522.7	517.8	516.8	514.8
122.5°	565.2	569.2	567.2	564.2	561.3
125°	614.6	617.6	615.6	611.6	607.7
127.5°	660.1	666.0	664.0	658.1	654.1
130°	705.5	713.4	710.5	706.5	699.6
132.5°	751.0	758.9	756.9	752.0	747.0
135°	797.4	803.3	802.4	798.4	796.4
137.5°	839.9	844.8	847.8	842.9	839.9
140°	884.4	889.3	890.3	889.3	882.4
142.5°	924.9	929.8	931.8	930.8	925.9
145°	967.4	969.3	972.3	971.3	967.4
147.5°	1003.9	1007.9	1010.8	1010.8	1004.9
150°	1042.5	1044.4	1046.4	1046.4	1040.5
152.5°	1074.1	1077.0	1078.0	1080.0	1075.1
155°	1107.7	1107.7	1108.7	1112.6	1105.7
157.5°	1136.3	1135.3	1136.3	1140.3	1134.4
160°	1163.0	1161.0	1161.0	1166.0	1162.0
162.5°	1186.7	1183.8	1184.8	1189.7	1182.8
165°	1206.5	1203.5	1203.5	1209.5	1202.5
167.5°	1223.3	1219.3	1220.3	1226.3	1220.3
170°	1237.1	1233.2	1233.2	1240.1	1233.2
172.5°	1248.0	1244.0	1244.0	1250.0	1243.1
175°	1254.9	1251.0	1251.0	1256.9	1250.0
177.5°	1258.9	1254.9	1254.9	1260.8	1253.9
180°	1257.9	1257.9	1257.9	1257.9	1257.9

(END OF REPORT)