

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030679

Luminaire Tested: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030679
REPORT IS A COMBINATION OF REPORTS P990674 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F1_5000K
Description: Define 3 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9130.0 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030679

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030679

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	39	37	35
3	80	70	63	57	73	65	58	53	54	49	45	44	40	37	34	32	30
4	73	62	54	48	66	57	50	45	48	43	38	39	35	32	31	28	26
5	67	55	47	41	61	51	44	39	43	37	33	35	31	28	28	25	22
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20
7	57	45	37	31	52	41	34	29	35	29	25	29	24	21	23	20	18
8	53	41	33	28	48	38	31	26	32	26	22	26	22	19	21	18	16
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16283	16283	16283
5°	16323	15721	15697
10°	16178	15189	15033
15°	15953	14635	14309
20°	15696	14022	13592
25°	15362	13373	12824
30°	14997	12702	12018
35°	14614	12016	11216
40°	14214	11298	10428
45°	13773	10596	9603
50°	13326	9815	8776
55°	12751	9001	7939
60°	12158	8103	7047
65°	11603	7132	6116
70°	10802	6054	5032
75°	9647	4793	3906
80°	8333	3369	2763
85°	6493	1810	1383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13773 cd/sqm

TEST NUMBER: P1030679

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	1.6
10°-20°	402.7	4.4
20°-30°	594.7	6.5
30°-40°	694.6	7.6
40°-50°	698.3	7.6
50°-60°	613.4	6.7
60°-70°	456.8	5.0
70°-80°	260.0	2.8
80°-90°	77.9	0.9
90°-100°	120.6	1.3
100°-110°	364.9	4.0
110°-120°	621.2	6.8
120°-130°	817.2	9.0
130°-140°	918.6	10.1
140°-150°	903.0	9.9
150°-160°	760.3	8.3
160°-170°	506.1	5.5
170°-180°	177.2	1.9
0°-30°	1140.0	12.5
0°-40°	1834.6	20.1
0°-60°	3146.3	34.5
0°-90°	3941.0	43.2
90°-120°	1106.6	12.1
90°-150°	3745.4	41.0
90°-180°	5189.0	56.8
0°-180°	9130.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1513	1513	1513	1513	1513	
5°	1514	1508	1493	1506	1504	144
15°	1441	1436	1419	1430	1422	406
25°	1308	1301	1284	1285	1281	603
35°	1132	1124	1107	1099	1093	708
45°	927	922	905	890	883	716
55°	704	702	686	671	665	630
65°	480	474	460	450	446	474
75°	254	248	244	238	234	271
85°	68	65	65	62	62	73
90°	2	16	35	41	44	11
95°	87	97	109	115	115	96
105°	331	334	347	347	350	354
115°	625	630	627	628	627	619
125°	915	920	916	911	905	816
135°	1187	1196	1195	1189	1186	915
145°	1440	1443	1448	1446	1440	900
155°	1649	1649	1651	1656	1646	759
165°	1796	1792	1792	1801	1790	507
175°	1868	1862	1862	1871	1861	178
180°	1873	1873	1873	1873	1873	

TEST NUMBER: P1030679

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1512.7	1512.7	1512.7	1512.7	1512.7
2.5°	1519.2	1514.0	1499.7	1512.7	1511.4
5°	1514.0	1507.5	1493.2	1506.2	1503.6
7.5°	1502.3	1495.8	1481.5	1493.2	1491.9
10°	1486.7	1480.2	1463.3	1475.0	1472.4
12.5°	1465.9	1460.7	1445.1	1452.9	1451.6
15°	1441.2	1436.0	1419.1	1429.5	1421.7
17.5°	1413.9	1407.4	1390.5	1398.3	1395.7
20°	1382.7	1374.9	1358.0	1363.2	1359.3
22.5°	1347.6	1339.7	1322.8	1326.7	1321.5
25°	1308.5	1300.7	1283.8	1285.1	1281.2
27.5°	1268.2	1260.4	1242.2	1243.5	1239.6
30°	1224.0	1217.5	1199.3	1199.3	1190.2
32.5°	1179.8	1170.7	1157.6	1148.5	1144.6
35°	1131.6	1123.8	1106.9	1099.1	1092.6
37.5°	1083.5	1073.1	1056.2	1047.1	1043.2
40°	1032.8	1025.0	1006.8	996.4	991.2
42.5°	982.0	972.9	954.7	944.3	939.1
45°	927.4	922.2	905.3	889.7	883.2
47.5°	874.1	866.3	850.7	835.1	829.9
50°	819.5	813.0	796.0	781.7	773.9
52.5°	762.2	758.3	740.1	728.4	720.6
55°	703.7	702.4	685.5	671.2	664.7
57.5°	649.1	643.9	630.9	617.8	610.0
60°	589.2	587.9	572.3	560.6	554.1
62.5°	535.9	532.0	516.4	504.7	500.8
65°	480.0	473.5	460.5	450.1	446.1
67.5°	420.1	414.9	404.5	395.4	390.2
70°	366.8	359.0	351.2	342.1	335.6
72.5°	310.9	305.7	296.6	288.8	286.2
75°	253.6	248.4	244.5	238.0	234.1
77.5°	202.9	200.3	195.1	189.9	189.9
80°	153.5	149.6	147.0	145.7	145.7
82.5°	105.4	105.4	105.4	102.8	101.5
85°	67.6	65.0	65.0	62.4	62.4
87.5°	33.8	29.9	28.6	27.3	27.3
90°	1.5	16.2	35.3	41.2	44.1
92.5°	44.1	53.0	61.8	66.2	63.3
95°	86.8	97.1	108.9	114.7	114.7
97.5°	142.7	150.1	158.9	166.2	164.8
100°	200.1	208.9	216.3	220.7	223.6
102.5°	266.3	270.7	281.0	285.4	283.9
105°	331.0	333.9	347.2	347.2	350.1
107.5°	407.5	409.0	414.9	419.3	417.8
110°	478.1	481.1	484.0	489.9	486.9

TEST NUMBER: P1030679

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	551.7	553.1	553.1	560.5	560.5
115°	625.2	629.6	626.7	628.2	626.7
117.5°	700.3	701.7	698.8	698.8	694.4
120°	769.4	778.2	770.9	769.4	766.5
122.5°	841.5	847.4	844.4	840.0	835.6
125°	915.0	919.5	916.5	910.6	904.7
127.5°	982.7	991.5	988.6	979.8	973.9
130°	1050.4	1062.2	1057.7	1051.9	1041.6
132.5°	1118.1	1129.8	1126.9	1119.5	1112.2
135°	1187.2	1196.0	1194.6	1188.7	1185.7
137.5°	1250.5	1257.8	1262.2	1254.9	1250.5
140°	1316.7	1324.0	1325.5	1324.0	1313.7
142.5°	1377.0	1384.3	1387.3	1385.8	1378.4
145°	1440.2	1443.2	1447.6	1446.1	1440.2
147.5°	1494.7	1500.6	1505.0	1505.0	1496.1
150°	1552.0	1555.0	1557.9	1557.9	1549.1
152.5°	1599.1	1603.5	1605.0	1607.9	1600.6
155°	1649.1	1649.1	1650.6	1656.5	1646.2
157.5°	1691.8	1690.3	1691.8	1697.7	1688.9
160°	1731.5	1728.6	1728.6	1735.9	1730.0
162.5°	1766.8	1762.4	1763.9	1771.2	1760.9
165°	1796.2	1791.8	1791.8	1800.7	1790.4
167.5°	1821.3	1815.4	1816.8	1825.7	1816.8
170°	1841.9	1836.0	1836.0	1846.3	1836.0
172.5°	1858.0	1852.2	1852.2	1861.0	1850.7
175°	1868.3	1862.4	1862.4	1871.3	1861.0
177.5°	1874.2	1868.3	1868.3	1877.2	1866.9
180°	1872.7	1872.7	1872.7	1872.7	1872.7

(END OF REPORT)