

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030682

Luminaire Tested: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030682
REPORT IS A COMBINATION OF REPORTS P990678 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10368.0 lumens
Efficiency: N/A
Efficacy: 104.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030682

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1030682

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47	47	47	47
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39	39	39	33
2	87	80	73	68	79	73	67	63	59	56	53	47	45	43	36	35	33	33	33	28
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28	28	28	24
4	72	62	54	48	66	56	50	44	46	41	38	37	34	31	29	26	24	24	24	20
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21	21	21	18
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	21	18	18	18	15
7	56	44	37	31	51	41	34	29	34	29	25	27	23	21	21	19	16	16	16	14
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	20	17	15	15	15	12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13	13	13	11
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12	12	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17011	17011	17011
5°	17053	16424	16400
10°	16902	15868	15705
15°	16666	15289	14948
20°	16397	14649	14199
25°	16048	13971	13398
30°	15667	13270	12555
35°	15267	12554	11718
40°	14848	11803	10894
45°	14389	11071	10033
50°	13921	10253	9168
55°	13321	9403	8294
60°	12702	8465	7362
65°	12121	7450	6390
70°	11285	6325	5257
75°	10080	5009	4081
80°	8703	3521	2886
85°	6791	1891	1445

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14389 cd/sqm

TEST NUMBER: P1030682

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	1.4
10°-20°	420.7	4.1
20°-30°	621.3	6.0
30°-40°	725.6	7.0
40°-50°	729.5	7.0
50°-60°	640.8	6.2
60°-70°	477.3	4.6
70°-80°	271.6	2.6
80°-90°	81.3	0.8
90°-100°	72.3	0.7
100°-110°	349.6	3.4
110°-120°	856.7	8.3
120°-130°	1087.5	10.5
130°-140°	1161.8	11.2
140°-150°	1086.4	10.5
150°-160°	876.3	8.5
160°-170°	565.5	5.5
170°-180°	194.9	1.9
0°-30°	1191.0	11.5
0°-40°	1916.6	18.5
0°-60°	3286.9	31.7
0°-90°	4117.1	39.7
90°-120°	1278.6	12.3
90°-150°	4614.2	44.5
90°-180°	6251.0	60.3
0°-180°	10368.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1582	1575	1560	1574	1571	150
15°	1506	1500	1482	1493	1485	425
25°	1367	1359	1341	1343	1338	630
35°	1182	1174	1156	1148	1142	740
45°	969	963	946	930	923	748
55°	735	734	716	701	694	659
65°	501	495	481	470	466	495
75°	265	260	256	249	245	283
85°	71	68	68	65	65	76
90°	2	17	37	43	46	10
95°	93	30	47	58	58	111
105°	454	471	334	64	67	481
115°	852	861	874	890	896	841
125°	1200	1213	1219	1222	1225	1073
135°	1494	1504	1510	1514	1510	1151
145°	1724	1735	1738	1741	1741	1080
155°	1900	1897	1898	1906	1897	875
165°	2003	1999	1997	2009	1999	566
175°	2050	2043	2044	2055	2043	195
180°	2050	2050	2050	2050	2050	

TEST NUMBER: P1030682

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.4	1580.4	1580.4	1580.4	1580.4
2.5°	1587.2	1581.7	1566.8	1580.4	1579.0
5°	1581.7	1574.9	1560.0	1573.6	1570.9
7.5°	1569.5	1562.7	1547.8	1560.0	1558.6
10°	1553.2	1546.4	1528.7	1541.0	1538.2
12.5°	1531.4	1526.0	1509.7	1517.9	1516.5
15°	1505.6	1500.2	1482.5	1493.4	1485.2
17.5°	1477.1	1470.3	1452.6	1460.8	1458.1
20°	1444.5	1436.3	1418.7	1424.1	1420.0
22.5°	1407.8	1399.6	1382.0	1386.1	1380.6
25°	1367.0	1358.9	1341.2	1342.6	1338.5
27.5°	1324.9	1316.7	1297.7	1299.1	1295.0
30°	1278.7	1271.9	1252.9	1252.9	1243.4
32.5°	1232.5	1223.0	1209.4	1199.9	1195.8
35°	1182.2	1174.1	1156.4	1148.2	1141.5
37.5°	1131.9	1121.1	1103.4	1093.9	1089.8
40°	1078.9	1070.8	1051.8	1040.9	1035.5
42.5°	1025.9	1016.4	997.4	986.5	981.1
45°	968.9	963.4	945.8	929.5	922.7
47.5°	913.2	905.0	888.7	872.4	867.0
50°	856.1	849.3	831.6	816.7	808.5
52.5°	796.3	792.2	773.2	761.0	752.8
55°	735.2	733.8	716.1	701.2	694.4
57.5°	678.1	672.6	659.1	645.5	637.3
60°	615.6	614.2	597.9	585.7	578.9
62.5°	559.9	555.8	539.5	527.2	523.2
65°	501.4	494.6	481.0	470.2	466.1
67.5°	438.9	433.5	422.6	413.1	407.7
70°	383.2	375.0	366.9	357.4	350.6
72.5°	324.8	319.3	309.8	301.7	299.0
75°	265.0	259.5	255.5	248.7	244.6
77.5°	212.0	209.3	203.8	198.4	198.4
80°	160.3	156.3	153.6	152.2	152.2
82.5°	110.1	110.1	110.1	107.4	106.0
85°	70.7	67.9	67.9	65.2	65.2
87.5°	35.3	31.3	29.9	28.5	28.5
90°	1.5	16.8	36.6	42.7	45.7
92.5°	35.0	25.9	39.6	50.3	51.8
95°	92.9	30.5	47.2	57.9	57.9
97.5°	169.1	126.4	48.7	60.9	62.5
100°	257.4	287.9	50.3	62.5	64.0
102.5°	358.0	377.8	112.7	62.5	65.5
105°	454.0	470.7	333.6	64.0	67.0
107.5°	556.0	569.7	592.6	358.0	158.4
110°	658.1	670.3	687.0	636.8	418.9

TEST NUMBER: P1030682

CATALOG NUMBER: S123DIW-B1000D1535UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	755.6	766.2	783.0	796.7	793.7
115°	851.6	860.7	874.4	889.6	895.7
117.5°	946.0	956.7	964.3	976.5	978.0
120°	1032.8	1046.5	1051.1	1063.3	1063.3
122.5°	1121.2	1131.8	1137.9	1145.6	1147.1
125°	1200.4	1212.6	1218.7	1221.7	1224.8
127.5°	1279.6	1291.8	1299.4	1304.0	1300.9
130°	1352.7	1364.9	1371.0	1377.1	1374.1
132.5°	1422.8	1435.0	1439.6	1445.7	1441.1
135°	1494.4	1503.5	1509.6	1514.2	1509.6
137.5°	1555.3	1567.5	1570.6	1578.2	1575.1
140°	1616.3	1625.4	1630.0	1636.1	1633.0
142.5°	1672.6	1681.8	1686.3	1690.9	1686.3
145°	1724.4	1735.1	1738.1	1741.2	1741.2
147.5°	1774.7	1782.3	1785.4	1788.4	1780.8
150°	1820.4	1825.0	1828.0	1831.1	1826.5
152.5°	1861.5	1863.1	1864.6	1870.7	1863.1
155°	1899.6	1896.6	1898.1	1905.7	1896.6
157.5°	1930.1	1930.1	1928.6	1937.7	1925.5
160°	1957.5	1956.0	1954.5	1963.6	1952.9
162.5°	1983.4	1978.8	1977.3	1988.0	1978.8
165°	2003.2	1998.6	1997.1	2009.3	1998.6
167.5°	2020.0	2013.9	2013.9	2026.1	2013.9
170°	2033.7	2027.6	2027.6	2039.8	2027.6
172.5°	2042.8	2035.2	2036.7	2048.9	2035.2
175°	2050.4	2042.8	2044.3	2055.0	2042.8
177.5°	2053.5	2045.9	2047.4	2059.6	2044.3
180°	2050.4	2050.4	2050.4	2050.4	2050.4

(END OF REPORT)