

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031036

Luminaire Tested: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031036
REPORT IS A COMBINATION OF REPORTS P993816 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10164.0 lumens
Efficiency: N/A
Efficacy: 102.7 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	61	61	61	46	46	46	39		
1	96	92	88	85	87	83	80	78	68	66	64	54	53	51	41	40	40	34		
2	88	81	75	70	79	73	69	64	60	57	54	48	46	44	37	35	34	29		
3	80	71	64	59	73	65	59	54	54	49	46	43	40	37	33	31	29	25		
4	73	63	56	50	67	58	51	46	48	43	39	38	35	32	30	28	26	22		
5	67	56	49	43	61	52	45	40	43	38	34	35	31	28	27	25	23	19		
6	62	51	43	37	56	47	40	35	39	34	30	31	28	25	25	22	20	17		
7	58	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18	15		
8	53	42	34	29	49	38	32	27	32	27	23	26	23	20	21	18	16	14		
9	50	38	31	26	45	35	29	24	29	25	21	24	20	18	19	17	15	13		
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	17010	17010	17010	17010
5°	17023	19591	17067	14534
10°	16873	23649	16947	12695
15°	16699	26840	16699	11194
20°	16356	28951	16448	9930
25°	16106	27505	16074	9060
30°	15814	19058	15781	8210
35°	15464	12236	15394	7570
40°	15027	8640	14952	6932
45°	14266	6914	14247	6311
50°	13333	5784	13289	5585
55°	12281	4767	12183	4734
60°	11252	3940	11138	4026
65°	10042	3153	10107	3412
70°	8926	2191	9164	2759
75°	7566	1625	7874	2122
80°	6021	1077	6536	1591
85°	4284	510	4678	989

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 22709 cd/sqm

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.2	1.5
10°-20°	485.8	4.8
20°-30°	765.1	7.5
30°-40°	795.6	7.8
40°-50°	680.7	6.7
50°-60°	518.9	5.1
60°-70°	332.5	3.3
70°-80°	159.3	1.6
80°-90°	46.0	0.5
90°-100°	72.0	0.7
100°-110°	348.1	3.4
110°-120°	853.1	8.4
120°-130°	1083.0	10.7
130°-140°	1156.9	11.4
140°-150°	1081.9	10.6
150°-160°	872.6	8.6
160°-170°	563.2	5.5
170°-180°	194.1	1.9
0°-30°	1406.1	13.8
0°-40°	2201.7	21.7
0°-60°	3401.4	33.5
0°-90°	3939.1	38.8
90°-120°	1273.3	12.5
90°-150°	4595.1	45.2
90°-180°	6225.0	61.2
0°-180°	10164.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1580	1580	1580	1580	1580	
5°	1579	1877	1583	1392	1579	150
15°	1509	2667	1509	1112	1509	424
25°	1372	2748	1369	905	1372	632
35°	1197	1192	1192	737	1197	749
45°	961	636	959	580	961	740
55°	678	399	672	396	678	607
65°	415	230	418	249	415	415
75°	199	97	207	127	199	215
85°	45	23	49	45	45	50
90°	2	46	2	46	2	8
95°	92	58	92	58	92	111
105°	452	67	452	67	452	479
115°	848	892	848	892	848	837
125°	1195	1220	1195	1220	1195	1068
135°	1488	1503	1488	1503	1488	1146
145°	1717	1734	1717	1734	1717	1075
155°	1892	1889	1892	1889	1892	872
165°	1995	1990	1995	1990	1995	564
175°	2042	2034	2042	2034	2042	194
180°	2042	2042	2042	2042	2042	

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1584.3	1595.2	1603.3	1608.7	1622.2	1630.3	1637.1	1649.3	1649.3	1652.0	1657.4
5°	1578.9	1601.9	1618.2	1639.8	1668.2	1681.8	1700.7	1716.9	1739.9	1752.1	1764.3
7.5°	1566.8	1599.2	1633.1	1665.5	1707.5	1734.5	1753.5	1795.4	1825.2	1861.7	1890.1
10°	1550.5	1595.2	1638.5	1688.5	1745.4	1785.9	1814.4	1869.8	1926.7	1978.1	2021.4
12.5°	1530.2	1584.3	1646.6	1707.5	1787.3	1827.9	1873.9	1942.9	2024.1	2089.0	2147.2
15°	1508.6	1570.8	1641.2	1715.6	1815.7	1872.5	1938.8	2022.7	2113.4	2206.7	2286.5
17.5°	1474.8	1553.2	1631.7	1739.9	1857.6	1891.5	1948.3	2063.3	2175.6	2259.5	2356.9
20°	1440.9	1528.9	1627.6	1725.1	1852.2	1930.7	1983.5	2105.2	2225.7	2327.1	2420.5
22.5°	1409.8	1501.8	1604.6	1727.8	1846.8	1925.3	1991.6	2118.8	2258.1	2371.8	2486.8
25°	1371.9	1472.0	1585.7	1702.1	1846.8	1906.4	1979.4	2126.9	2274.4	2405.6	2547.7
27.5°	1331.3	1432.8	1545.1	1664.2	1796.8	1884.7	1956.4	2114.7	2294.7	2435.4	2581.5
30°	1290.7	1394.9	1503.2	1610.1	1758.9	1842.8	1925.3	2099.8	2305.5	2466.5	2578.8
32.5°	1251.5	1339.5	1446.3	1550.5	1698.0	1790.0	1883.4	2084.9	2309.5	2444.8	2499.0
35°	1197.4	1289.4	1376.0	1486.9	1635.8	1726.4	1836.0	2083.6	2292.0	2375.8	2348.8
37.5°	1147.3	1224.5	1307.0	1405.8	1558.6	1676.3	1790.0	2048.4	2233.8	2239.2	2086.3
40°	1091.9	1155.4	1224.5	1328.6	1493.7	1610.1	1733.2	1994.3	2128.2	2048.4	1779.2
42.5°	1028.3	1085.1	1139.2	1240.7	1420.6	1550.5	1683.1	1926.7	1975.4	1791.4	1511.3
45°	960.6	1006.6	1056.7	1163.6	1343.5	1472.0	1604.6	1822.5	1772.4	1512.6	1246.1
47.5°	890.3	929.5	978.2	1075.6	1261.0	1392.2	1518.0	1673.6	1546.5	1267.7	1044.5
50°	819.9	851.0	898.4	998.5	1177.1	1296.2	1412.5	1514.0	1335.4	1087.8	863.2
52.5°	750.9	775.3	824.0	909.2	1082.4	1196.0	1279.9	1319.2	1137.9	898.4	749.6
55°	677.8	704.9	737.4	824.0	995.8	1079.7	1135.2	1133.8	947.1	761.7	619.7
57.5°	607.5	631.8	660.3	746.8	886.2	943.0	990.4	967.4	790.1	623.7	531.7
60°	545.3	558.8	589.9	663.0	768.5	817.2	844.3	805.0	645.4	526.3	439.7
62.5°	477.6	491.1	516.8	585.8	650.8	676.5	699.5	649.4	533.1	428.9	376.1
65°	415.4	433.0	449.2	504.7	539.8	571.0	568.3	526.3	416.7	349.1	305.8
67.5°	361.2	368.0	381.5	415.4	431.6	454.6	456.0	408.6	335.5	284.1	258.4
70°	303.1	309.8	319.3	335.5	346.4	351.8	349.1	307.1	253.0	221.9	198.9
72.5°	253.0	251.7	258.4	258.4	269.2	267.9	259.8	227.3	192.1	166.4	152.9
75°	198.9	200.2	201.6	198.9	194.8	189.4	182.7	158.3	135.3	123.1	110.9
77.5°	155.6	152.9	154.2	144.8	139.4	133.9	124.5	112.3	93.4	90.6	85.2
80°	110.9	109.6	108.2	104.2	92.0	86.6	79.8	73.1	69.0	66.3	64.9
82.5°	74.4	74.4	71.7	63.6	56.8	52.8	51.4	48.7	44.6	44.6	43.3
85°	44.6	43.3	40.6	32.5	28.4	28.4	28.4	28.4	25.7	25.7	24.4
87.5°	17.6	16.2	12.2	12.2	10.8	10.8	10.8	9.5	9.5	8.1	8.1
90°	1.5	4.9	8.3	11.6	15.0	16.7	18.9	23.3	27.6	32.0	36.4
92.5°	34.9	32.9	30.9	28.8	26.8	25.8	27.3	30.3	33.4	36.4	39.4
95°	92.5	78.7	64.9	51.0	37.2	30.3	32.2	35.9	39.6	43.3	47.0
97.5°	168.4	159.0	149.5	140.1	130.6	125.9	117.3	100.1	82.9	65.7	48.5
100°	256.4	263.1	269.9	276.6	283.3	286.7	260.4	207.8	155.3	102.7	50.1
102.5°	356.5	360.9	365.3	369.6	374.0	376.2	346.9	288.2	229.6	170.9	112.3
105°	452.1	455.8	459.5	463.2	466.9	468.8	453.6	423.3	392.9	362.6	332.2
107.5°	553.7	556.7	559.8	562.8	565.9	567.4	569.9	575.0	580.0	585.1	590.1
110°	655.4	658.1	660.8	663.5	666.2	667.5	669.4	673.1	676.8	680.5	684.2



TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	752.4	754.8	757.2	759.5	761.9	763.1	764.9	768.6	772.3	776.0	779.7
115°	848.0	850.0	852.0	854.1	856.1	857.1	858.6	861.7	864.7	867.8	870.8
117.5°	942.1	944.5	946.8	949.2	951.5	952.7	953.5	955.2	956.9	958.6	960.3
120°	1028.5	1031.5	1034.6	1037.6	1040.7	1042.2	1042.7	1043.7	1044.7	1045.7	1046.7
122.5°	1116.5	1118.9	1121.2	1123.6	1125.9	1127.1	1127.8	1129.1	1130.5	1131.8	1133.2
125°	1195.4	1198.1	1200.8	1203.5	1206.2	1207.5	1208.2	1209.5	1210.9	1212.2	1213.6
127.5°	1274.3	1277.0	1279.7	1282.4	1285.1	1286.4	1287.2	1288.9	1290.6	1292.3	1294.0
130°	1347.1	1349.8	1352.5	1355.2	1357.9	1359.2	1359.9	1361.2	1362.6	1363.9	1365.3
132.5°	1416.9	1419.6	1422.3	1425.0	1427.7	1429.0	1429.5	1430.5	1431.6	1432.6	1433.6
135°	1488.2	1490.2	1492.2	1494.3	1496.3	1497.3	1498.0	1499.3	1500.7	1502.0	1503.4
137.5°	1548.9	1551.6	1554.3	1557.0	1559.7	1561.0	1561.3	1562.0	1562.7	1563.3	1564.0
140°	1609.6	1611.6	1613.6	1615.7	1617.7	1618.7	1619.2	1620.2	1621.2	1622.2	1623.2
142.5°	1665.7	1667.7	1669.7	1671.8	1673.8	1674.8	1675.3	1676.3	1677.3	1678.3	1679.3
145°	1717.3	1719.7	1722.0	1724.4	1726.7	1727.9	1728.2	1728.9	1729.6	1730.2	1730.9
147.5°	1767.3	1769.0	1770.7	1772.4	1774.1	1774.9	1775.2	1775.9	1776.6	1777.2	1777.9
150°	1812.8	1813.8	1814.8	1815.9	1816.9	1817.4	1817.7	1818.4	1819.1	1819.7	1820.4
152.5°	1853.8	1854.1	1854.5	1854.8	1855.1	1855.3	1855.5	1855.8	1856.1	1856.5	1856.8
155°	1891.7	1891.0	1890.4	1889.7	1889.0	1888.7	1888.9	1889.2	1889.5	1889.9	1890.2
157.5°	1922.1	1922.1	1922.1	1922.1	1922.1	1922.1	1921.9	1921.6	1921.2	1920.9	1920.5
160°	1949.4	1949.1	1948.7	1948.4	1948.1	1947.9	1947.7	1947.4	1947.0	1946.7	1946.3
162.5°	1975.2	1974.2	1973.2	1972.1	1971.1	1970.6	1970.4	1970.1	1969.8	1969.4	1969.1
165°	1994.9	1993.9	1992.9	1991.8	1990.8	1990.3	1990.1	1989.8	1989.5	1989.1	1988.8
167.5°	2011.6	2010.2	2008.9	2007.5	2006.2	2005.5	2005.5	2005.5	2005.5	2005.5	2005.5
170°	2025.2	2023.9	2022.5	2021.2	2019.9	2019.2	2019.2	2019.2	2019.2	2019.2	2019.2
172.5°	2034.3	2032.6	2030.9	2029.2	2027.5	2026.7	2026.9	2027.2	2027.6	2027.9	2028.3
175°	2041.9	2040.2	2038.5	2036.8	2035.1	2034.3	2034.5	2034.8	2035.1	2035.5	2035.8
177.5°	2044.9	2043.2	2041.6	2039.9	2038.2	2037.4	2037.6	2037.9	2038.2	2038.6	2038.9
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1668.2	1668.2	1680.4	1692.6	1685.8	1689.9	1704.8	1699.3	1710.2	1708.8	1712.9
5°	1794.1	1808.9	1821.1	1846.8	1850.9	1846.8	1872.5	1879.3	1891.5	1876.6	1883.4
7.5°	1936.1	1967.2	1997.0	2034.9	2047.1	2049.8	2063.3	2082.2	2098.5	2068.7	2083.6
10°	2074.1	2121.5	2182.4	2216.2	2246.0	2256.8	2267.6	2279.8	2298.7	2316.3	2302.8
12.5°	2223.0	2292.0	2350.1	2411.0	2447.5	2443.5	2474.6	2482.7	2497.6	2501.7	2507.1
15°	2344.7	2442.1	2478.7	2569.3	2577.4	2604.5	2639.7	2670.8	2674.9	2666.7	2666.7
17.5°	2461.1	2545.0	2609.9	2683.0	2697.9	2720.9	2765.5	2780.4	2785.8	2784.4	2784.4
20°	2555.8	2611.3	2720.9	2781.7	2806.1	2835.9	2867.0	2885.9	2890.0	2895.4	2887.3
22.5°	2618.0	2701.9	2791.2	2841.3	2861.6	2872.4	2892.7	2898.1	2891.3	2892.7	2894.0
25°	2666.7	2749.3	2803.4	2816.9	2815.6	2802.0	2787.1	2761.4	2758.7	2747.9	2726.3
27.5°	2680.3	2711.4	2704.6	2649.1	2593.7	2588.3	2499.0	2450.3	2394.8	2402.9	2371.8
30°	2607.2	2566.6	2470.6	2329.8	2271.7	2177.0	2076.8	1972.7	1932.1	1887.4	1969.9
32.5°	2428.6	2283.8	2113.4	1930.7	1833.3	1749.4	1642.5	1566.8	1523.5	1486.9	1557.3
35°	2159.4	1933.4	1707.5	1534.3	1454.5	1378.7	1278.6	1240.7	1186.6	1192.0	1198.7
37.5°	1813.0	1564.1	1393.6	1223.1	1170.3	1139.2	1066.2	1008.0	989.0	983.6	983.6
40°	1488.3	1284.0	1132.4	998.5	957.9	932.2	874.0	847.0	826.7	821.3	828.0
42.5°	1231.2	1056.7	939.0	849.7	821.3	788.8	764.4	730.6	726.6	717.1	729.3
45°	1033.7	882.1	794.2	729.3	704.9	692.7	665.7	645.4	637.3	635.9	645.4
47.5°	876.7	759.0	681.9	641.3	622.4	610.2	587.2	579.1	571.0	573.7	569.6
50°	736.0	648.1	598.0	561.5	549.3	537.1	522.3	514.1	510.1	510.1	508.7
52.5°	631.8	558.8	526.3	492.5	487.1	480.3	464.1	458.7	451.9	450.5	456.0
55°	541.2	491.1	458.7	438.4	433.0	419.4	412.7	405.9	401.8	399.1	400.5
57.5°	462.7	424.8	403.2	385.6	376.1	370.7	358.5	357.2	354.5	354.5	353.1
60°	397.8	370.7	345.0	334.2	327.4	320.7	319.3	311.2	307.1	309.8	308.5
62.5°	336.9	315.2	300.4	288.2	284.1	278.7	274.7	271.9	267.9	269.2	269.2
65°	281.4	263.8	253.0	242.2	240.8	235.4	234.1	231.4	231.4	230.0	232.7
67.5°	231.4	219.2	209.7	202.9	198.9	200.2	194.8	190.8	190.8	189.4	193.5
70°	184.0	177.2	167.8	159.7	154.2	154.2	147.5	146.1	146.1	146.1	144.8
72.5°	142.1	129.9	125.8	123.1	123.1	123.1	120.4	120.4	119.1	120.4	119.1
75°	105.5	104.2	101.5	100.1	100.1	98.8	97.4	97.4	97.4	97.4	97.4
77.5°	82.5	82.5	79.8	78.5	78.5	78.5	77.1	77.1	75.8	75.8	75.8
80°	60.9	60.9	58.2	58.2	58.2	56.8	56.8	56.8	58.2	56.8	56.8
82.5°	41.9	41.9	40.6	41.9	40.6	39.2	39.2	39.2	37.9	39.2	39.2
85°	24.4	24.4	23.0	21.6	23.0	23.0	21.6	23.0	21.6	23.0	21.6
87.5°	9.5	8.1	8.1	8.1	6.8	8.1	6.8	6.8	8.1	6.8	8.1
90°	37.8	39.1	40.5	41.8	42.5	42.8	43.5	44.2	44.8	45.5	44.8
92.5°	41.8	44.2	46.5	48.9	50.1	50.3	50.6	50.9	51.3	51.6	51.3
95°	49.4	51.7	54.1	56.4	57.6	57.6	57.6	57.6	57.6	57.6	57.6
97.5°	51.2	53.9	56.6	59.3	60.7	60.9	61.2	61.5	61.9	62.2	61.9
100°	52.8	55.5	58.2	60.9	62.2	62.4	62.7	63.0	63.4	63.7	63.4
102.5°	101.2	90.0	78.9	67.8	62.2	62.5	63.2	63.9	64.5	65.2	64.5
105°	272.5	212.9	153.2	93.5	63.7	64.0	64.7	65.4	66.0	66.7	66.0
107.5°	538.2	486.3	434.4	382.5	356.5	334.4	290.3	246.1	202.0	157.8	202.0
110°	673.1	661.9	650.8	639.7	634.1	610.0	561.8	513.6	465.4	417.2	465.4

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	782.7	785.8	788.8	791.9	793.4	793.1	792.4	791.7	791.1	790.4	791.1
115°	874.2	877.5	880.9	884.2	885.9	886.6	887.9	889.3	890.6	892.0	890.6
117.5°	963.0	965.7	968.4	971.1	972.4	972.6	972.9	973.2	973.6	973.9	973.6
120°	1049.4	1052.1	1054.8	1057.5	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9
122.5°	1134.9	1136.6	1138.3	1140.0	1140.8	1141.0	1141.3	1141.6	1142.0	1142.3	1142.0
125°	1214.3	1214.9	1215.6	1216.3	1216.6	1216.9	1217.6	1218.3	1219.0	1219.7	1219.0
127.5°	1295.0	1296.0	1297.1	1298.1	1298.6	1298.3	1297.6	1296.9	1296.2	1295.5	1296.2
130°	1366.7	1368.0	1369.4	1370.7	1371.4	1371.1	1370.4	1369.7	1369.0	1368.3	1369.0
132.5°	1434.9	1436.3	1437.6	1438.9	1439.6	1439.1	1438.1	1437.1	1436.1	1435.1	1436.1
135°	1504.4	1505.4	1506.4	1507.4	1507.9	1507.4	1506.4	1505.4	1504.4	1503.4	1504.4
137.5°	1565.7	1567.4	1569.1	1570.8	1571.6	1571.3	1570.6	1569.9	1569.3	1568.6	1569.3
140°	1624.6	1625.9	1627.3	1628.6	1629.3	1629.0	1628.3	1627.6	1626.9	1626.2	1626.9
142.5°	1680.3	1681.3	1682.4	1683.4	1683.9	1683.4	1682.4	1681.3	1680.3	1679.3	1680.3
145°	1731.6	1732.3	1733.0	1733.7	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0
147.5°	1778.6	1779.3	1780.0	1780.7	1781.0	1780.2	1778.5	1776.8	1775.1	1773.4	1775.1
150°	1821.1	1821.8	1822.5	1823.2	1823.5	1823.0	1822.0	1820.9	1819.9	1818.9	1819.9
152.5°	1858.2	1859.5	1860.9	1862.2	1862.9	1862.1	1860.4	1858.7	1857.0	1855.3	1857.0
155°	1891.9	1893.6	1895.3	1897.0	1897.8	1896.8	1894.8	1892.7	1890.7	1888.7	1890.7
157.5°	1922.5	1924.5	1926.6	1928.6	1929.6	1928.3	1925.6	1922.9	1920.2	1917.5	1920.2
160°	1948.3	1950.3	1952.4	1954.4	1955.4	1954.2	1951.9	1949.5	1947.2	1944.8	1947.2
162.5°	1971.5	1973.8	1976.2	1978.5	1979.7	1978.7	1976.7	1974.6	1972.6	1970.6	1972.6
165°	1991.5	1994.2	1996.9	1999.6	2000.9	1999.7	1997.4	1995.0	1992.7	1990.3	1992.7
167.5°	2008.2	2010.9	2013.6	2016.3	2017.6	2016.3	2013.6	2010.9	2008.2	2005.5	2008.2
170°	2021.9	2024.6	2027.3	2030.0	2031.3	2030.0	2027.3	2024.6	2021.9	2019.2	2021.9
172.5°	2031.0	2033.7	2036.4	2039.1	2040.4	2038.9	2035.8	2032.8	2029.7	2026.7	2029.7
175°	2038.2	2040.6	2042.9	2045.3	2046.5	2045.1	2042.4	2039.7	2037.0	2034.3	2037.0
177.5°	2041.6	2044.3	2047.0	2049.7	2051.0	2049.3	2045.9	2042.6	2039.2	2035.8	2039.2
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1706.1	1698.0	1692.6	1688.5	1684.5	1696.6	1680.4	1662.8	1650.6	1642.5	1639.8
5°	1884.7	1867.1	1852.2	1840.1	1842.8	1842.8	1814.4	1783.2	1756.2	1741.3	1725.1
7.5°	2091.7	2072.8	2043.0	2036.2	2030.8	1997.0	1968.6	1911.8	1877.9	1844.1	1814.4
10°	2297.4	2273.0	2244.6	2235.1	2221.6	2179.7	2136.4	2063.3	2021.4	1959.1	1919.9
12.5°	2489.5	2459.7	2431.3	2424.5	2404.3	2367.7	2293.3	2217.5	2145.8	2079.5	2010.5
15°	2650.5	2642.4	2599.1	2572.0	2527.4	2477.3	2461.1	2358.3	2267.6	2198.6	2074.1
17.5°	2785.8	2747.9	2707.3	2689.7	2672.1	2614.0	2555.8	2450.3	2352.8	2251.4	2171.5
20°	2894.0	2852.1	2823.7	2798.0	2789.9	2723.6	2631.6	2538.2	2431.3	2317.7	2213.5
22.5°	2899.4	2894.0	2875.1	2860.2	2844.0	2800.7	2727.6	2611.3	2497.6	2373.1	2236.5
25°	2787.1	2779.0	2833.2	2819.6	2830.4	2814.2	2775.0	2677.6	2545.0	2398.8	2260.8
27.5°	2448.9	2531.4	2616.7	2646.4	2666.7	2724.9	2743.9	2689.7	2582.8	2427.3	2273.0
30°	1988.9	2098.5	2236.5	2310.9	2367.7	2476.0	2616.7	2634.3	2584.2	2459.7	2270.3
32.5°	1561.3	1661.5	1772.4	1860.4	1936.1	2158.0	2347.4	2484.1	2508.4	2443.5	2277.1
35°	1258.3	1301.6	1407.1	1491.0	1593.8	1783.2	2006.5	2227.0	2375.8	2384.0	2256.8
37.5°	1037.7	1060.7	1152.7	1200.1	1261.0	1427.4	1635.8	1923.9	2155.3	2264.9	2200.0
40°	859.1	911.9	964.7	991.7	1035.0	1150.0	1350.3	1576.2	1863.1	2066.0	2112.0
42.5°	745.5	768.5	802.3	840.2	867.3	967.4	1101.3	1308.3	1566.8	1849.5	1976.7
45°	657.6	665.7	700.8	725.2	753.6	824.0	918.7	1091.9	1319.2	1597.9	1814.4
47.5°	584.5	600.7	619.7	634.5	653.5	707.6	788.8	914.6	1114.9	1363.8	1596.5
50°	519.5	529.0	553.4	560.1	573.7	611.5	673.8	769.8	934.9	1133.8	1374.6
52.5°	458.7	476.3	485.7	495.2	507.4	538.5	579.1	657.6	782.0	968.7	1173.0
55°	411.3	416.7	430.2	438.4	447.8	469.5	504.7	562.8	660.3	809.1	1002.6
57.5°	365.3	365.3	378.8	385.6	395.1	411.3	442.4	487.1	557.4	668.4	845.6
60°	316.6	318.0	328.8	336.9	339.6	355.8	381.5	416.7	470.8	552.0	696.8
62.5°	273.3	280.1	285.5	288.2	297.7	307.1	328.8	353.1	391.0	462.7	565.5
65°	236.8	238.1	242.2	244.9	248.9	259.8	276.0	292.2	324.7	377.5	461.4
67.5°	194.8	200.2	205.7	205.7	209.7	215.1	231.4	244.9	269.2	300.4	357.2
70°	146.1	148.8	156.9	161.0	166.4	175.9	184.0	192.1	211.1	234.1	277.4
72.5°	121.8	121.8	124.5	125.8	125.8	132.6	144.8	152.9	162.4	178.6	208.4
75°	97.4	97.4	101.5	100.1	102.8	105.5	106.9	112.3	117.7	129.9	147.5
77.5°	77.1	78.5	78.5	79.8	79.8	81.2	82.5	85.2	87.9	94.7	102.8
80°	56.8	58.2	58.2	59.5	59.5	60.9	62.2	63.6	66.3	69.0	73.1
82.5°	39.2	40.6	40.6	41.9	40.6	41.9	43.3	43.3	44.6	47.4	48.7
85°	23.0	23.0	24.4	23.0	23.0	23.0	24.4	24.4	25.7	29.8	29.8
87.5°	6.8	8.1	6.8	8.1	8.1	8.1	8.1	9.5	9.5	10.8	12.2
90°	44.2	43.5	42.8	42.5	41.8	40.5	39.1	37.8	36.4	32.0	27.6
92.5°	50.9	50.6	50.3	50.1	48.9	46.5	44.2	41.8	39.4	36.4	33.4
95°	57.6	57.6	57.6	57.6	56.4	54.1	51.7	49.4	47.0	43.3	39.6
97.5°	61.5	61.2	60.9	60.7	59.3	56.6	53.9	51.2	48.5	65.7	82.9
100°	63.0	62.7	62.4	62.2	60.9	58.2	55.5	52.8	50.1	102.7	155.3
102.5°	63.9	63.2	62.5	62.2	67.8	78.9	90.0	101.2	112.3	170.9	229.6
105°	65.4	64.7	64.0	63.7	93.5	153.2	212.9	272.5	332.2	362.6	392.9
107.5°	246.1	290.3	334.4	356.5	382.5	434.4	486.3	538.2	590.1	585.1	580.0
110°	513.6	561.8	610.0	634.1	639.7	650.8	661.9	673.1	684.2	680.5	676.8

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	791.7	792.4	793.1	793.4	791.9	788.8	785.8	782.7	779.7	776.0	772.3
115°	889.3	887.9	886.6	885.9	884.2	880.9	877.5	874.2	870.8	867.8	864.7
117.5°	973.2	972.9	972.6	972.4	971.1	968.4	965.7	963.0	960.3	958.6	956.9
120°	1058.9	1058.9	1058.9	1058.9	1057.5	1054.8	1052.1	1049.4	1046.7	1045.7	1044.7
122.5°	1141.6	1141.3	1141.0	1140.8	1140.0	1138.3	1136.6	1134.9	1133.2	1131.8	1130.5
125°	1218.3	1217.6	1216.9	1216.6	1216.3	1215.6	1214.9	1214.3	1213.6	1212.2	1210.9
127.5°	1296.9	1297.6	1298.3	1298.6	1298.1	1297.1	1296.0	1295.0	1294.0	1292.3	1290.6
130°	1369.7	1370.4	1371.1	1371.4	1370.7	1369.4	1368.0	1366.7	1365.3	1363.9	1362.6
132.5°	1437.1	1438.1	1439.1	1439.6	1438.9	1437.6	1436.3	1434.9	1433.6	1432.6	1431.6
135°	1505.4	1506.4	1507.4	1507.9	1507.4	1506.4	1505.4	1504.4	1503.4	1502.0	1500.7
137.5°	1569.9	1570.6	1571.3	1571.6	1570.8	1569.1	1567.4	1565.7	1564.0	1563.3	1562.7
140°	1627.6	1628.3	1629.0	1629.3	1628.6	1627.3	1625.9	1624.6	1623.2	1622.2	1621.2
142.5°	1681.3	1682.4	1683.4	1683.9	1683.4	1682.4	1681.3	1680.3	1679.3	1678.3	1677.3
145°	1734.0	1734.0	1734.0	1734.0	1733.7	1733.0	1732.3	1731.6	1730.9	1730.2	1729.6
147.5°	1776.8	1778.5	1780.2	1781.0	1780.7	1780.0	1779.3	1778.6	1777.9	1777.2	1776.6
150°	1820.9	1822.0	1823.0	1823.5	1823.2	1822.5	1821.8	1821.1	1820.4	1819.7	1819.1
152.5°	1858.7	1860.4	1862.1	1862.9	1862.2	1860.9	1859.5	1858.2	1856.8	1856.5	1856.1
155°	1892.7	1894.8	1896.8	1897.8	1897.0	1895.3	1893.6	1891.9	1890.2	1889.9	1889.5
157.5°	1922.9	1925.6	1928.3	1929.6	1928.6	1926.6	1924.5	1922.5	1920.5	1920.9	1921.2
160°	1949.5	1951.9	1954.2	1955.4	1954.4	1952.4	1950.3	1948.3	1946.3	1946.7	1947.0
162.5°	1974.6	1976.7	1978.7	1979.7	1978.5	1976.2	1973.8	1971.5	1969.1	1969.4	1969.8
165°	1995.0	1997.4	1999.7	2000.9	1999.6	1996.9	1994.2	1991.5	1988.8	1989.1	1989.5
167.5°	2010.9	2013.6	2016.3	2017.6	2016.3	2013.6	2010.9	2008.2	2005.5	2005.5	2005.5
170°	2024.6	2027.3	2030.0	2031.3	2030.0	2027.3	2024.6	2021.9	2019.2	2019.2	2019.2
172.5°	2032.8	2035.8	2038.9	2040.4	2039.1	2036.4	2033.7	2031.0	2028.3	2027.9	2027.6
175°	2039.7	2042.4	2045.1	2046.5	2045.3	2042.9	2040.6	2038.2	2035.8	2035.5	2035.1
177.5°	2042.6	2045.9	2049.3	2051.0	2049.7	2047.0	2044.3	2041.6	2038.9	2038.6	2038.2
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1635.8	1629.0	1622.2	1622.2	1607.3	1593.8	1587.1	1589.8	1581.6	1570.8	1560.0
5°	1707.5	1680.4	1675.0	1660.1	1639.8	1611.4	1596.5	1583.0	1566.8	1545.1	1524.8
7.5°	1773.8	1738.6	1719.6	1704.8	1665.5	1626.3	1593.8	1572.2	1543.8	1511.3	1486.9
10°	1860.4	1795.4	1775.1	1741.3	1685.8	1630.3	1592.5	1557.3	1518.0	1480.2	1447.7
12.5°	1929.4	1854.9	1817.1	1783.2	1711.5	1641.2	1577.6	1534.3	1486.9	1445.0	1403.0
15°	2007.8	1923.9	1857.6	1817.1	1726.4	1641.2	1569.5	1508.6	1455.8	1404.4	1367.9
17.5°	2045.7	1940.2	1910.4	1852.2	1721.0	1635.8	1547.8	1482.9	1419.3	1359.7	1316.5
20°	2105.2	1982.1	1907.7	1868.5	1752.1	1626.3	1523.5	1449.0	1382.8	1319.2	1273.2
22.5°	2109.3	1975.4	1926.7	1852.2	1708.8	1597.9	1501.8	1411.2	1334.0	1274.5	1227.2
25°	2099.8	1963.2	1895.5	1836.0	1716.9	1581.6	1458.5	1369.2	1293.5	1224.5	1169.0
27.5°	2095.8	1928.0	1864.4	1804.9	1670.9	1534.3	1432.8	1331.3	1244.7	1183.9	1127.0
30°	2090.4	1890.1	1813.0	1744.0	1620.9	1497.8	1376.0	1288.0	1205.5	1128.4	1071.6
32.5°	2055.2	1838.7	1760.2	1687.2	1554.6	1431.5	1335.4	1242.0	1152.7	1081.0	1029.6
35°	2044.4	1791.4	1688.5	1610.1	1480.2	1370.6	1269.1	1192.0	1108.1	1036.4	975.5
37.5°	2013.2	1742.6	1631.7	1531.6	1396.3	1292.1	1217.7	1140.6	1059.4	982.3	933.6
40°	1959.1	1685.8	1560.0	1457.2	1317.8	1212.3	1143.3	1086.4	1006.6	937.6	878.1
42.5°	1879.3	1627.6	1492.3	1384.1	1229.9	1131.1	1074.3	1020.2	952.5	880.8	832.1
45°	1787.3	1550.5	1424.7	1304.3	1147.3	1051.3	991.7	959.3	897.0	836.1	779.3
47.5°	1661.5	1470.7	1346.2	1221.7	1062.1	968.7	921.4	888.9	845.6	779.3	733.3
50°	1503.2	1367.9	1250.2	1139.2	978.2	888.9	841.6	817.2	780.7	733.3	688.7
52.5°	1327.3	1248.8	1151.4	1048.6	893.0	809.1	765.8	746.8	719.8	675.1	637.3
55°	1150.0	1116.2	1049.9	948.4	803.7	734.7	696.8	672.4	652.1	619.7	587.2
57.5°	991.7	975.5	929.5	851.0	729.3	657.6	625.1	608.8	592.6	568.3	535.8
60°	828.0	845.6	798.3	759.0	648.1	585.8	557.4	539.8	531.7	510.1	489.8
62.5°	686.0	702.2	675.1	645.4	566.9	511.4	493.8	477.6	472.2	453.2	433.0
65°	557.4	577.7	557.4	541.2	493.8	447.8	426.2	418.1	412.7	400.5	384.2
67.5°	443.8	464.1	454.6	434.3	419.4	381.5	369.4	361.2	358.5	349.1	335.5
70°	334.2	362.6	365.3	353.1	339.6	322.0	313.9	311.2	304.4	296.3	288.2
72.5°	240.8	273.3	274.7	274.7	266.5	266.5	258.4	254.4	254.4	246.2	236.8
75°	177.2	198.9	201.6	204.3	208.4	212.4	207.0	207.0	205.7	197.5	193.5
77.5°	117.7	136.7	143.4	152.9	158.3	158.3	161.0	163.7	161.0	156.9	154.2
80°	75.8	89.3	97.4	102.8	110.9	115.0	119.1	120.4	117.7	116.4	112.3
82.5°	50.1	54.1	58.2	64.9	74.4	81.2	81.2	79.8	82.5	81.2	79.8
85°	28.4	31.1	32.5	33.8	39.2	46.0	47.4	48.7	51.4	48.7	46.0
87.5°	10.8	12.2	12.2	12.2	14.9	16.2	20.3	25.7	24.4	21.6	21.6
90°	23.3	18.9	16.7	15.0	11.6	8.3	4.9	1.5	4.9	8.3	11.6
92.5°	30.3	27.3	25.8	26.8	28.8	30.9	32.9	34.9	32.9	30.9	28.8
95°	35.9	32.2	30.3	37.2	51.0	64.9	78.7	92.5	78.7	64.9	51.0
97.5°	100.1	117.3	125.9	130.6	140.1	149.5	159.0	168.4	159.0	149.5	140.1
100°	207.8	260.4	286.7	283.3	276.6	269.9	263.1	256.4	263.1	269.9	276.6
102.5°	288.2	346.9	376.2	374.0	369.6	365.3	360.9	356.5	360.9	365.3	369.6
105°	423.3	453.6	468.8	466.9	463.2	459.5	455.8	452.1	455.8	459.5	463.2
107.5°	575.0	569.9	567.4	565.9	562.8	559.8	556.7	553.7	556.7	559.8	562.8
110°	673.1	669.4	667.5	666.2	663.5	660.8	658.1	655.4	658.1	660.8	663.5

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	768.6	764.9	763.1	761.9	759.5	757.2	754.8	752.4	754.8	757.2	759.5
115°	861.7	858.6	857.1	856.1	854.1	852.0	850.0	848.0	850.0	852.0	854.1
117.5°	955.2	953.5	952.7	951.5	949.2	946.8	944.5	942.1	944.5	946.8	949.2
120°	1043.7	1042.7	1042.2	1040.7	1037.6	1034.6	1031.5	1028.5	1031.5	1034.6	1037.6
122.5°	1129.1	1127.8	1127.1	1125.9	1123.6	1121.2	1118.9	1116.5	1118.9	1121.2	1123.6
125°	1209.5	1208.2	1207.5	1206.2	1203.5	1200.8	1198.1	1195.4	1198.1	1200.8	1203.5
127.5°	1288.9	1287.2	1286.4	1285.1	1282.4	1279.7	1277.0	1274.3	1277.0	1279.7	1282.4
130°	1361.2	1359.9	1359.2	1357.9	1355.2	1352.5	1349.8	1347.1	1349.8	1352.5	1355.2
132.5°	1430.5	1429.5	1429.0	1427.7	1425.0	1422.3	1419.6	1416.9	1419.6	1422.3	1425.0
135°	1499.3	1498.0	1497.3	1496.3	1494.3	1492.2	1490.2	1488.2	1490.2	1492.2	1494.3
137.5°	1562.0	1561.3	1561.0	1559.7	1557.0	1554.3	1551.6	1548.9	1551.6	1554.3	1557.0
140°	1620.2	1619.2	1618.7	1617.7	1615.7	1613.6	1611.6	1609.6	1611.6	1613.6	1615.7
142.5°	1676.3	1675.3	1674.8	1673.8	1671.8	1669.7	1667.7	1665.7	1667.7	1669.7	1671.8
145°	1728.9	1728.2	1727.9	1726.7	1724.4	1722.0	1719.7	1717.3	1719.7	1722.0	1724.4
147.5°	1775.9	1775.2	1774.9	1774.1	1772.4	1770.7	1769.0	1767.3	1769.0	1770.7	1772.4
150°	1818.4	1817.7	1817.4	1816.9	1815.9	1814.8	1813.8	1812.8	1813.8	1814.8	1815.9
152.5°	1855.8	1855.5	1855.3	1855.1	1854.8	1854.5	1854.1	1853.8	1854.1	1854.5	1854.8
155°	1889.2	1888.9	1888.7	1889.0	1889.7	1890.4	1891.0	1891.7	1891.0	1890.4	1889.7
157.5°	1921.6	1921.9	1922.1	1922.1	1922.1	1922.1	1922.1	1922.1	1922.1	1922.1	1922.1
160°	1947.4	1947.7	1947.9	1948.1	1948.4	1948.7	1949.1	1949.4	1949.1	1948.7	1948.4
162.5°	1970.1	1970.4	1970.6	1971.1	1972.1	1973.2	1974.2	1975.2	1974.2	1973.2	1972.1
165°	1989.8	1990.1	1990.3	1990.8	1991.8	1992.9	1993.9	1994.9	1993.9	1992.9	1991.8
167.5°	2005.5	2005.5	2005.5	2006.2	2007.5	2008.9	2010.2	2011.6	2010.2	2008.9	2007.5
170°	2019.2	2019.2	2019.2	2019.9	2021.2	2022.5	2023.9	2025.2	2023.9	2022.5	2021.2
172.5°	2027.2	2026.9	2026.7	2027.5	2029.2	2030.9	2032.6	2034.3	2032.6	2030.9	2029.2
175°	2034.8	2034.5	2034.3	2035.1	2036.8	2038.5	2040.2	2041.9	2040.2	2038.5	2036.8
177.5°	2037.9	2037.6	2037.4	2038.2	2039.9	2041.6	2043.2	2044.9	2043.2	2041.6	2039.9
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1560.0	1553.2	1550.5	1543.8	1527.5	1516.7	1504.5	1496.4	1497.8	1491.0	1495.0
5°	1511.3	1509.9	1500.5	1486.9	1463.9	1451.8	1430.1	1419.3	1413.9	1415.2	1407.1
7.5°	1470.7	1458.5	1451.8	1430.1	1408.5	1382.8	1365.2	1355.7	1347.6	1339.5	1334.0
10°	1424.7	1413.9	1403.0	1380.0	1350.3	1325.9	1301.6	1292.1	1279.9	1274.5	1270.5
12.5°	1376.0	1369.2	1355.7	1328.6	1294.8	1271.8	1243.4	1238.0	1221.7	1210.9	1208.2
15°	1331.3	1327.3	1302.9	1271.8	1238.0	1215.0	1190.6	1174.4	1147.3	1152.7	1143.3
17.5°	1284.0	1266.4	1251.5	1209.6	1193.3	1158.2	1129.7	1121.6	1102.7	1090.5	1078.3
20°	1231.2	1220.4	1201.5	1174.4	1135.2	1094.6	1072.9	1059.4	1048.6	1029.6	1024.2
22.5°	1181.2	1167.6	1151.4	1116.2	1082.4	1048.6	1018.8	1006.6	993.1	979.6	971.4
25°	1141.9	1121.6	1104.0	1060.7	1026.9	998.5	979.6	959.3	940.3	932.2	929.5
27.5°	1081.0	1068.9	1051.3	1010.7	979.6	948.4	930.9	917.3	897.0	887.6	879.4
30°	1041.8	1017.4	997.1	964.7	933.6	899.7	883.5	867.3	855.1	842.9	833.4
32.5°	989.0	970.1	953.9	921.4	890.3	859.1	841.6	817.2	810.4	801.0	790.1
35°	937.6	925.4	907.9	872.7	838.9	817.2	798.3	775.3	767.1	760.4	750.9
37.5°	888.9	871.3	859.1	825.3	795.6	769.8	755.0	736.0	730.6	722.5	715.7
40°	847.0	829.4	817.2	783.4	752.3	725.2	715.7	696.8	688.7	679.2	675.1
42.5°	799.6	784.7	768.5	744.1	711.7	684.6	665.7	654.8	644.0	640.0	631.8
45°	749.6	736.0	723.8	696.8	663.0	644.0	627.8	612.9	604.8	598.0	592.6
47.5°	706.3	694.1	677.8	648.1	621.0	603.4	587.2	572.3	564.2	556.1	549.3
50°	656.2	649.4	631.8	603.4	577.7	557.4	542.5	529.0	523.6	514.1	503.3
52.5°	611.5	599.4	584.5	561.5	538.5	514.1	493.8	485.7	476.3	470.8	461.4
55°	558.8	550.7	534.4	514.1	489.8	469.5	454.6	443.8	431.6	426.2	414.0
57.5°	514.1	499.3	491.1	465.4	442.4	422.1	411.3	400.5	387.0	378.8	373.4
60°	465.4	451.9	439.7	418.1	401.8	380.2	364.0	354.5	345.0	334.2	328.8
62.5°	418.1	407.2	392.4	374.8	354.5	336.9	324.7	311.2	305.8	295.0	290.9
65°	366.7	358.5	346.4	326.1	309.8	295.0	282.8	271.9	266.5	262.5	259.8
67.5°	320.7	309.8	301.7	284.1	266.5	254.4	247.6	240.8	234.1	230.0	225.9
70°	273.3	265.2	257.1	240.8	228.7	217.8	212.4	207.0	202.9	198.9	194.8
72.5°	224.6	220.5	212.4	201.6	192.1	184.0	179.9	173.2	169.1	162.4	159.7
75°	185.4	178.6	174.5	165.1	156.9	150.2	144.8	136.7	131.2	128.5	127.2
77.5°	146.1	143.4	138.0	129.9	125.8	119.1	110.9	108.2	105.5	105.5	104.2
80°	109.6	105.5	101.5	94.7	90.6	85.2	85.2	85.2	83.9	85.2	83.9
82.5°	74.4	71.7	69.0	64.9	63.6	63.6	64.9	64.9	64.9	64.9	64.9
85°	43.3	43.3	43.3	44.6	43.3	43.3	44.6	46.0	44.6	44.6	43.3
87.5°	20.3	20.3	21.6	21.6	23.0	23.0	23.0	23.0	23.0	23.0	24.4
90°	15.0	16.7	18.9	23.3	27.6	32.0	36.4	37.8	39.1	40.5	41.8
92.5°	26.8	25.8	27.3	30.3	33.4	36.4	39.4	41.8	44.2	46.5	48.9
95°	37.2	30.3	32.2	35.9	39.6	43.3	47.0	49.4	51.7	54.1	56.4
97.5°	130.6	125.9	117.3	100.1	82.9	65.7	48.5	51.2	53.9	56.6	59.3
100°	283.3	286.7	260.4	207.8	155.3	102.7	50.1	52.8	55.5	58.2	60.9
102.5°	374.0	376.2	346.9	288.2	229.6	170.9	112.3	101.2	90.0	78.9	67.8
105°	466.9	468.8	453.6	423.3	392.9	362.6	332.2	272.5	212.9	153.2	93.5
107.5°	565.9	567.4	569.9	575.0	580.0	585.1	590.1	538.2	486.3	434.4	382.5
110°	666.2	667.5	669.4	673.1	676.8	680.5	684.2	673.1	661.9	650.8	639.7

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	761.9	763.1	764.9	768.6	772.3	776.0	779.7	782.7	785.8	788.8	791.9
115°	856.1	857.1	858.6	861.7	864.7	867.8	870.8	874.2	877.5	880.9	884.2
117.5°	951.5	952.7	953.5	955.2	956.9	958.6	960.3	963.0	965.7	968.4	971.1
120°	1040.7	1042.2	1042.7	1043.7	1044.7	1045.7	1046.7	1049.4	1052.1	1054.8	1057.5
122.5°	1125.9	1127.1	1127.8	1129.1	1130.5	1131.8	1133.2	1134.9	1136.6	1138.3	1140.0
125°	1206.2	1207.5	1208.2	1209.5	1210.9	1212.2	1213.6	1214.3	1214.9	1215.6	1216.3
127.5°	1285.1	1286.4	1287.2	1288.9	1290.6	1292.3	1294.0	1295.0	1296.0	1297.1	1298.1
130°	1357.9	1359.2	1359.9	1361.2	1362.6	1363.9	1365.3	1366.7	1368.0	1369.4	1370.7
132.5°	1427.7	1429.0	1429.5	1430.5	1431.6	1432.6	1433.6	1434.9	1436.3	1437.6	1438.9
135°	1496.3	1497.3	1498.0	1499.3	1500.7	1502.0	1503.4	1504.4	1505.4	1506.4	1507.4
137.5°	1559.7	1561.0	1561.3	1562.0	1562.7	1563.3	1564.0	1565.7	1567.4	1569.1	1570.8
140°	1617.7	1618.7	1619.2	1620.2	1621.2	1622.2	1623.2	1624.6	1625.9	1627.3	1628.6
142.5°	1673.8	1674.8	1675.3	1676.3	1677.3	1678.3	1679.3	1680.3	1681.3	1682.4	1683.4
145°	1726.7	1727.9	1728.2	1728.9	1729.6	1730.2	1730.9	1731.6	1732.3	1733.0	1733.7
147.5°	1774.1	1774.9	1775.2	1775.9	1776.6	1777.2	1777.9	1778.6	1779.3	1780.0	1780.7
150°	1816.9	1817.4	1817.7	1818.4	1819.1	1819.7	1820.4	1821.1	1821.8	1822.5	1823.2
152.5°	1855.1	1855.3	1855.5	1855.8	1856.1	1856.5	1856.8	1858.2	1859.5	1860.9	1862.2
155°	1889.0	1888.7	1888.9	1889.2	1889.5	1889.9	1890.2	1891.9	1893.6	1895.3	1897.0
157.5°	1922.1	1922.1	1921.9	1921.6	1921.2	1920.9	1920.5	1922.5	1924.5	1926.6	1928.6
160°	1948.1	1947.9	1947.7	1947.4	1947.0	1946.7	1946.3	1948.3	1950.3	1952.4	1954.4
162.5°	1971.1	1970.6	1970.4	1970.1	1969.8	1969.4	1969.1	1971.5	1973.8	1976.2	1978.5
165°	1990.8	1990.3	1990.1	1989.8	1989.5	1989.1	1988.8	1991.5	1994.2	1996.9	1999.6
167.5°	2006.2	2005.5	2005.5	2005.5	2005.5	2005.5	2005.5	2008.2	2010.9	2013.6	2016.3
170°	2019.9	2019.2	2019.2	2019.2	2019.2	2019.2	2019.2	2021.9	2024.6	2027.3	2030.0
172.5°	2027.5	2026.7	2026.9	2027.2	2027.6	2027.9	2028.3	2031.0	2033.7	2036.4	2039.1
175°	2035.1	2034.3	2034.5	2034.8	2035.1	2035.5	2035.8	2038.2	2040.6	2042.9	2045.3
177.5°	2038.2	2037.4	2037.6	2037.9	2038.2	2038.6	2038.9	2041.6	2044.3	2047.0	2049.7
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1493.7	1495.0	1491.0	1482.9	1481.5	1484.2	1492.3	1489.6	1482.9	1495.0	1484.2
5°	1411.2	1404.4	1401.7	1404.4	1396.3	1392.2	1400.3	1396.3	1400.3	1401.7	1405.8
7.5°	1331.3	1332.7	1324.6	1325.9	1315.1	1317.8	1317.8	1317.8	1321.9	1324.6	1330.0
10°	1262.3	1265.0	1255.6	1256.9	1248.8	1243.4	1247.5	1255.6	1255.6	1255.6	1258.3
12.5°	1206.9	1194.7	1187.9	1186.6	1177.1	1174.4	1182.5	1185.2	1192.0	1192.0	1196.0
15°	1137.9	1135.2	1129.7	1129.7	1106.7	1112.2	1114.9	1124.3	1137.9	1127.0	1129.7
17.5°	1075.6	1068.9	1062.1	1059.4	1056.7	1048.6	1059.4	1058.0	1066.2	1067.5	1071.6
20°	1020.2	1014.7	1001.2	1002.6	1005.3	993.1	999.9	999.9	1008.0	1016.1	1025.6
22.5°	966.0	960.6	953.9	956.6	948.4	945.7	945.7	952.5	962.0	968.7	967.4
25°	924.1	914.6	910.6	906.5	902.4	905.1	901.1	907.9	914.6	918.7	914.6
27.5°	876.7	872.7	864.6	860.5	853.7	856.4	859.1	864.6	868.6	868.6	872.7
30°	830.7	825.3	822.6	818.6	818.6	813.1	814.5	819.9	824.0	828.0	833.4
32.5°	786.1	782.0	778.0	778.0	775.3	773.9	772.6	780.7	780.7	788.8	788.8
35°	749.6	742.8	742.8	736.0	738.7	737.4	734.7	740.1	741.4	746.8	745.5
37.5°	709.0	709.0	706.3	699.5	694.1	695.4	702.2	702.2	706.3	704.9	709.0
40°	668.4	665.7	665.7	661.6	660.3	658.9	660.3	661.6	668.4	667.0	668.4
42.5°	627.8	629.1	622.4	622.4	622.4	618.3	619.7	621.0	623.7	626.4	630.5
45°	588.5	585.8	584.5	581.8	579.1	580.4	579.1	584.5	583.1	585.8	589.9
47.5°	546.6	542.5	541.2	535.8	535.8	538.5	537.1	541.2	542.5	546.6	543.9
50°	506.0	500.6	496.5	497.9	489.8	492.5	492.5	496.5	500.6	502.0	504.7
52.5°	458.7	457.3	456.0	449.2	447.8	446.5	447.8	449.2	454.6	458.7	460.0
55°	412.7	411.3	403.2	400.5	396.4	396.4	399.1	400.5	410.0	411.3	416.7
57.5°	370.7	366.7	357.2	355.8	355.8	355.8	351.8	357.2	359.9	366.7	366.7
60°	324.7	324.7	316.6	316.6	318.0	316.6	316.6	318.0	318.0	323.4	326.1
62.5°	288.2	286.8	286.8	284.1	282.8	284.1	282.8	282.8	284.1	288.2	292.2
65°	255.7	254.4	253.0	251.7	248.9	248.9	250.3	253.0	253.0	255.7	257.1
67.5°	224.6	224.6	221.9	221.9	220.5	219.2	220.5	219.2	224.6	224.6	225.9
70°	193.5	192.1	188.1	186.7	182.7	184.0	184.0	188.1	189.4	192.1	194.8
72.5°	155.6	155.6	152.9	150.2	151.5	148.8	148.8	150.2	150.2	154.2	155.6
75°	128.5	125.8	124.5	125.8	124.5	127.2	124.5	124.5	127.2	127.2	127.2
77.5°	105.5	105.5	104.2	104.2	105.5	104.2	105.5	105.5	105.5	104.2	105.5
80°	86.6	85.2	85.2	85.2	83.9	83.9	83.9	83.9	83.9	83.9	83.9
82.5°	64.9	64.9	63.6	64.9	64.9	63.6	64.9	63.6	63.6	64.9	64.9
85°	43.3	46.0	43.3	43.3	44.6	44.6	46.0	44.6	46.0	43.3	44.6
87.5°	23.0	24.4	24.4	23.0	23.0	24.4	24.4	24.4	25.7	23.0	24.4
90°	42.5	42.8	43.5	44.2	44.8	45.5	44.8	44.2	43.5	42.8	42.5
92.5°	50.1	50.3	50.6	50.9	51.3	51.6	51.3	50.9	50.6	50.3	50.1
95°	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6
97.5°	60.7	60.9	61.2	61.5	61.9	62.2	61.9	61.5	61.2	60.9	60.7
100°	62.2	62.4	62.7	63.0	63.4	63.7	63.4	63.0	62.7	62.4	62.2
102.5°	62.2	62.5	63.2	63.9	64.5	65.2	64.5	63.9	63.2	62.5	62.2
105°	63.7	64.0	64.7	65.4	66.0	66.7	66.0	65.4	64.7	64.0	63.7
107.5°	356.5	334.4	290.3	246.1	202.0	157.8	202.0	246.1	290.3	334.4	356.5
110°	634.1	610.0	561.8	513.6	465.4	417.2	465.4	513.6	561.8	610.0	634.1



TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	793.4	793.1	792.4	791.7	791.1	790.4	791.1	791.7	792.4	793.1	793.4
115°	885.9	886.6	887.9	889.3	890.6	892.0	890.6	889.3	887.9	886.6	885.9
117.5°	972.4	972.6	972.9	973.2	973.6	973.9	973.6	973.2	972.9	972.6	972.4
120°	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9
122.5°	1140.8	1141.0	1141.3	1141.6	1142.0	1142.3	1142.0	1141.6	1141.3	1141.0	1140.8
125°	1216.6	1216.9	1217.6	1218.3	1219.0	1219.7	1219.0	1218.3	1217.6	1216.9	1216.6
127.5°	1298.6	1298.3	1297.6	1296.9	1296.2	1295.5	1296.2	1296.9	1297.6	1298.3	1298.6
130°	1371.4	1371.1	1370.4	1369.7	1369.0	1368.3	1369.0	1369.7	1370.4	1371.1	1371.4
132.5°	1439.6	1439.1	1438.1	1437.1	1436.1	1435.1	1436.1	1437.1	1438.1	1439.1	1439.6
135°	1507.9	1507.4	1506.4	1505.4	1504.4	1503.4	1504.4	1505.4	1506.4	1507.4	1507.9
137.5°	1571.6	1571.3	1570.6	1569.9	1569.3	1568.6	1569.3	1569.9	1570.6	1571.3	1571.6
140°	1629.3	1629.0	1628.3	1627.6	1626.9	1626.2	1626.9	1627.6	1628.3	1629.0	1629.3
142.5°	1683.9	1683.4	1682.4	1681.3	1680.3	1679.3	1680.3	1681.3	1682.4	1683.4	1683.9
145°	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0
147.5°	1781.0	1780.2	1778.5	1776.8	1775.1	1773.4	1775.1	1776.8	1778.5	1780.2	1781.0
150°	1823.5	1823.0	1822.0	1820.9	1819.9	1818.9	1819.9	1820.9	1822.0	1823.0	1823.5
152.5°	1862.9	1862.1	1860.4	1858.7	1857.0	1855.3	1857.0	1858.7	1860.4	1862.1	1862.9
155°	1897.8	1896.8	1894.8	1892.7	1890.7	1888.7	1890.7	1892.7	1894.8	1896.8	1897.8
157.5°	1929.6	1928.3	1925.6	1922.9	1920.2	1917.5	1920.2	1922.9	1925.6	1928.3	1929.6
160°	1955.4	1954.2	1951.9	1949.5	1947.2	1944.8	1947.2	1949.5	1951.9	1954.2	1955.4
162.5°	1979.7	1978.7	1976.7	1974.6	1972.6	1970.6	1972.6	1974.6	1976.7	1978.7	1979.7
165°	2000.9	1999.7	1997.4	1995.0	1992.7	1990.3	1992.7	1995.0	1997.4	1999.7	2000.9
167.5°	2017.6	2016.3	2013.6	2010.9	2008.2	2005.5	2008.2	2010.9	2013.6	2016.3	2017.6
170°	2031.3	2030.0	2027.3	2024.6	2021.9	2019.2	2021.9	2024.6	2027.3	2030.0	2031.3
172.5°	2040.4	2038.9	2035.8	2032.8	2029.7	2026.7	2029.7	2032.8	2035.8	2038.9	2040.4
175°	2046.5	2045.1	2042.4	2039.7	2037.0	2034.3	2037.0	2039.7	2042.4	2045.1	2046.5
177.5°	2051.0	2049.3	2045.9	2042.6	2039.2	2035.8	2039.2	2042.6	2045.9	2049.3	2051.0
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3	1580.3
2.5°	1495.0	1500.5	1495.0	1484.2	1495.0	1501.8	1508.6	1519.4	1524.8	1524.8	1532.9
5°	1409.8	1420.6	1416.6	1413.9	1424.7	1431.5	1442.3	1455.8	1470.7	1480.2	1491.0
7.5°	1334.0	1340.8	1347.6	1347.6	1358.4	1373.3	1389.5	1405.8	1424.7	1438.2	1446.3
10°	1267.7	1273.2	1277.2	1282.6	1298.9	1315.1	1336.7	1357.0	1373.3	1388.2	1401.7
12.5°	1204.2	1212.3	1221.7	1225.8	1238.0	1258.3	1278.6	1302.9	1328.6	1343.5	1357.0
15°	1143.3	1147.3	1158.2	1170.3	1181.2	1202.8	1228.5	1254.2	1275.9	1298.9	1311.0
17.5°	1081.0	1082.4	1110.8	1104.0	1139.2	1159.5	1173.0	1197.4	1232.6	1251.5	1270.5
20°	1020.2	1033.7	1045.9	1052.6	1071.6	1094.6	1133.8	1152.7	1181.2	1198.7	1215.0
22.5°	972.8	993.1	993.1	1009.3	1018.8	1040.4	1068.9	1105.4	1136.5	1148.7	1171.7
25°	930.9	940.3	956.6	962.0	979.6	998.5	1017.4	1056.7	1090.5	1106.7	1123.0
27.5°	876.7	888.9	910.6	910.6	933.6	953.9	976.9	1002.6	1036.4	1059.4	1077.0
30°	834.8	847.0	856.4	871.3	880.8	899.7	940.3	959.3	989.0	1009.3	1031.0
32.5°	795.6	805.0	813.1	829.4	840.2	861.9	883.5	917.3	943.0	962.0	985.0
35°	752.3	761.7	772.6	784.7	801.0	821.3	841.6	870.0	895.7	913.3	932.2
37.5°	711.7	718.4	734.7	742.8	756.3	775.3	801.0	830.7	853.7	867.3	886.2
40°	672.4	677.8	690.0	704.9	714.4	729.3	756.3	782.0	810.4	826.7	841.6
42.5°	630.5	637.3	648.1	663.0	677.8	694.1	709.0	738.7	764.4	778.0	794.2
45°	594.0	598.0	606.1	621.0	635.9	648.1	671.1	698.1	722.5	733.3	750.9
47.5°	550.7	554.7	566.9	573.7	589.9	606.1	629.1	656.2	677.8	688.7	704.9
50°	506.0	510.1	518.2	533.1	543.9	561.5	581.8	604.8	631.8	646.7	656.2
52.5°	462.7	470.8	477.6	489.8	503.3	520.9	539.8	561.5	584.5	599.4	610.2
55°	419.4	426.2	434.3	441.1	457.3	473.5	495.2	515.5	535.8	549.3	561.5
57.5°	370.7	380.2	388.3	401.8	414.0	427.5	451.9	468.1	492.5	502.0	512.8
60°	328.8	338.2	345.0	355.8	366.7	384.2	400.5	420.8	441.1	453.2	466.8
62.5°	293.6	297.7	301.7	312.5	323.4	339.6	355.8	376.1	397.8	404.5	415.4
65°	258.4	262.5	269.2	278.7	286.8	296.3	313.9	330.1	350.4	361.2	365.3
67.5°	228.7	232.7	234.1	240.8	247.6	258.4	267.9	284.1	303.1	309.8	318.0
70°	194.8	201.6	202.9	208.4	211.1	217.8	228.7	240.8	255.7	267.9	274.7
72.5°	155.6	165.1	167.8	175.9	179.9	186.7	194.8	204.3	213.8	219.2	224.6
75°	127.2	129.9	131.2	138.0	144.8	154.2	158.3	163.7	171.8	178.6	184.0
77.5°	105.5	106.9	108.2	108.2	109.6	115.0	123.1	129.9	135.3	138.0	142.1
80°	85.2	83.9	83.9	85.2	85.2	85.2	87.9	97.4	100.1	106.9	105.5
82.5°	66.3	63.6	64.9	63.6	63.6	63.6	63.6	64.9	64.9	69.0	71.7
85°	43.3	44.6	43.3	43.3	41.9	43.3	41.9	41.9	40.6	40.6	39.2
87.5°	23.0	24.4	23.0	23.0	21.6	23.0	21.6	21.6	20.3	20.3	17.6
90°	41.8	40.5	39.1	37.8	36.4	32.0	27.6	23.3	18.9	16.7	15.0
92.5°	48.9	46.5	44.2	41.8	39.4	36.4	33.4	30.3	27.3	25.8	26.8
95°	56.4	54.1	51.7	49.4	47.0	43.3	39.6	35.9	32.2	30.3	37.2
97.5°	59.3	56.6	53.9	51.2	48.5	65.7	82.9	100.1	117.3	125.9	130.6
100°	60.9	58.2	55.5	52.8	50.1	102.7	155.3	207.8	260.4	286.7	283.3
102.5°	67.8	78.9	90.0	101.2	112.3	170.9	229.6	288.2	346.9	376.2	374.0
105°	93.5	153.2	212.9	272.5	332.2	362.6	392.9	423.3	453.6	468.8	466.9
107.5°	382.5	434.4	486.3	538.2	590.1	585.1	580.0	575.0	569.9	567.4	565.9
110°	639.7	650.8	661.9	673.1	684.2	680.5	676.8	673.1	669.4	667.5	666.2

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	791.9	788.8	785.8	782.7	779.7	776.0	772.3	768.6	764.9	763.1	761.9
115°	884.2	880.9	877.5	874.2	870.8	867.8	864.7	861.7	858.6	857.1	856.1
117.5°	971.1	968.4	965.7	963.0	960.3	958.6	956.9	955.2	953.5	952.7	951.5
120°	1057.5	1054.8	1052.1	1049.4	1046.7	1045.7	1044.7	1043.7	1042.7	1042.2	1040.7
122.5°	1140.0	1138.3	1136.6	1134.9	1133.2	1131.8	1130.5	1129.1	1127.8	1127.1	1125.9
125°	1216.3	1215.6	1214.9	1214.3	1213.6	1212.2	1210.9	1209.5	1208.2	1207.5	1206.2
127.5°	1298.1	1297.1	1296.0	1295.0	1294.0	1292.3	1290.6	1288.9	1287.2	1286.4	1285.1
130°	1370.7	1369.4	1368.0	1366.7	1365.3	1363.9	1362.6	1361.2	1359.9	1359.2	1357.9
132.5°	1438.9	1437.6	1436.3	1434.9	1433.6	1432.6	1431.6	1430.5	1429.5	1429.0	1427.7
135°	1507.4	1506.4	1505.4	1504.4	1503.4	1502.0	1500.7	1499.3	1498.0	1497.3	1496.3
137.5°	1570.8	1569.1	1567.4	1565.7	1564.0	1563.3	1562.7	1562.0	1561.3	1561.0	1559.7
140°	1628.6	1627.3	1625.9	1624.6	1623.2	1622.2	1621.2	1620.2	1619.2	1618.7	1617.7
142.5°	1683.4	1682.4	1681.3	1680.3	1679.3	1678.3	1677.3	1676.3	1675.3	1674.8	1673.8
145°	1733.7	1733.0	1732.3	1731.6	1730.9	1730.2	1729.6	1728.9	1728.2	1727.9	1726.7
147.5°	1780.7	1780.0	1779.3	1778.6	1777.9	1777.2	1776.6	1775.9	1775.2	1774.9	1774.1
150°	1823.2	1822.5	1821.8	1821.1	1820.4	1819.7	1819.1	1818.4	1817.7	1817.4	1816.9
152.5°	1862.2	1860.9	1859.5	1858.2	1856.8	1856.5	1856.1	1855.8	1855.5	1855.3	1855.1
155°	1897.0	1895.3	1893.6	1891.9	1890.2	1889.9	1889.5	1889.2	1888.9	1888.7	1889.0
157.5°	1928.6	1926.6	1924.5	1922.5	1920.5	1920.9	1921.2	1921.6	1921.9	1922.1	1922.1
160°	1954.4	1952.4	1950.3	1948.3	1946.3	1946.7	1947.0	1947.4	1947.7	1947.9	1948.1
162.5°	1978.5	1976.2	1973.8	1971.5	1969.1	1969.4	1969.8	1970.1	1970.4	1970.6	1971.1
165°	1999.6	1996.9	1994.2	1991.5	1988.8	1989.1	1989.5	1989.8	1990.1	1990.3	1990.8
167.5°	2016.3	2013.6	2010.9	2008.2	2005.5	2005.5	2005.5	2005.5	2005.5	2005.5	2006.2
170°	2030.0	2027.3	2024.6	2021.9	2019.2	2019.2	2019.2	2019.2	2019.2	2019.2	2019.9
172.5°	2039.1	2036.4	2033.7	2031.0	2028.3	2027.9	2027.6	2027.2	2026.9	2026.7	2027.5
175°	2045.3	2042.9	2040.6	2038.2	2035.8	2035.5	2035.1	2034.8	2034.5	2034.3	2035.1
177.5°	2049.7	2047.0	2044.3	2041.6	2038.9	2038.6	2038.2	2037.9	2037.6	2037.4	2038.2
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1580.3	1580.3	1580.3	1580.3
2.5°	1539.7	1549.2	1568.1	1584.3
5°	1507.2	1522.1	1550.5	1578.9
7.5°	1468.0	1491.0	1527.5	1566.8
10°	1430.1	1459.9	1504.5	1550.5
12.5°	1392.2	1423.3	1470.7	1530.2
15°	1347.6	1380.0	1436.9	1508.6
17.5°	1308.3	1351.6	1403.0	1474.8
20°	1266.4	1298.9	1365.2	1440.9
22.5°	1213.6	1267.7	1330.0	1409.8
25°	1171.7	1219.0	1281.3	1371.9
27.5°	1120.3	1175.7	1251.5	1331.3
30°	1078.3	1124.3	1194.7	1290.7
32.5°	1029.6	1083.7	1156.8	1251.5
35°	986.3	1032.3	1101.3	1197.4
37.5°	934.9	985.0	1062.1	1147.3
40°	890.3	939.0	1012.0	1091.9
42.5°	836.1	887.6	960.6	1028.3
45°	792.8	840.2	898.4	960.6
47.5°	740.1	790.1	847.0	890.3
50°	692.7	738.7	783.4	819.9
52.5°	641.3	683.3	723.8	750.9
55°	594.0	626.4	658.9	677.8
57.5°	538.5	569.6	596.7	607.5
60°	489.8	515.5	533.1	545.3
62.5°	438.4	457.3	470.8	477.6
65°	388.3	401.8	408.6	415.4
67.5°	336.9	349.1	353.1	361.2
70°	282.8	296.3	299.0	303.1
72.5°	242.2	242.2	247.6	253.0
75°	193.5	196.2	198.9	198.9
77.5°	151.5	151.5	154.2	155.6
80°	110.9	112.3	112.3	110.9
82.5°	75.8	78.5	75.8	74.4
85°	41.9	47.4	44.6	44.6
87.5°	17.6	17.6	20.3	17.6
90°	11.6	8.3	4.9	1.5
92.5°	28.8	30.9	32.9	34.9
95°	51.0	64.9	78.7	92.5
97.5°	140.1	149.5	159.0	168.4
100°	276.6	269.9	263.1	256.4
102.5°	369.6	365.3	360.9	356.5
105°	463.2	459.5	455.8	452.1
107.5°	562.8	559.8	556.7	553.7
110°	663.5	660.8	658.1	655.4

TEST NUMBER: P1031036

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	759.5	757.2	754.8	752.4
115°	854.1	852.0	850.0	848.0
117.5°	949.2	946.8	944.5	942.1
120°	1037.6	1034.6	1031.5	1028.5
122.5°	1123.6	1121.2	1118.9	1116.5
125°	1203.5	1200.8	1198.1	1195.4
127.5°	1282.4	1279.7	1277.0	1274.3
130°	1355.2	1352.5	1349.8	1347.1
132.5°	1425.0	1422.3	1419.6	1416.9
135°	1494.3	1492.2	1490.2	1488.2
137.5°	1557.0	1554.3	1551.6	1548.9
140°	1615.7	1613.6	1611.6	1609.6
142.5°	1671.8	1669.7	1667.7	1665.7
145°	1724.4	1722.0	1719.7	1717.3
147.5°	1772.4	1770.7	1769.0	1767.3
150°	1815.9	1814.8	1813.8	1812.8
152.5°	1854.8	1854.5	1854.1	1853.8
155°	1889.7	1890.4	1891.0	1891.7
157.5°	1922.1	1922.1	1922.1	1922.1
160°	1948.4	1948.7	1949.1	1949.4
162.5°	1972.1	1973.2	1974.2	1975.2
165°	1991.8	1992.9	1993.9	1994.9
167.5°	2007.5	2008.9	2010.2	2011.6
170°	2021.2	2022.5	2023.9	2025.2
172.5°	2029.2	2030.9	2032.6	2034.3
175°	2036.8	2038.5	2040.2	2041.9
177.5°	2039.9	2041.6	2043.2	2044.9
180°	2041.9	2041.9	2041.9	2041.9

(END OF REPORT)