

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031041

Luminaire Tested: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031041
REPORT IS A COMBINATION OF REPORTS P993823 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9998.0 lumens
Efficiency: N/A
Efficacy: 101.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031041

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031041

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	63	59	56	53	47	45	42	35	34	33
3	79	70	63	58	72	64	58	53	52	48	45	42	39	36	32	30	28
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	37	32	52	41	34	30	34	29	25	28	24	21	21	19	17
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17957	17957	17957
5°	17987	17322	17276
10°	17845	16671	16343
15°	17614	15866	15321
20°	17310	14990	14179
25°	16997	14081	13097
30°	16594	13112	11818
35°	16180	12162	10653
40°	15791	11130	9366
45°	15292	10120	8209
50°	14741	9043	7011
55°	14171	7889	5914
60°	13625	6705	4801
65°	12921	5491	3747
70°	12033	4151	2678
75°	10758	2811	2122
80°	9180	1953	1489
85°	6887	1055	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15292 cd/sqm

TEST NUMBER: P1031041

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	1.6
10°-20°	436.3	4.4
20°-30°	628.2	6.3
30°-40°	707.4	7.1
40°-50°	676.7	6.8
50°-60°	553.9	5.5
60°-70°	373.5	3.7
70°-80°	187.3	1.9
80°-90°	53.1	0.5
90°-100°	72.0	0.7
100°-110°	348.1	3.5
110°-120°	853.1	8.5
120°-130°	1083.0	10.8
130°-140°	1156.9	11.6
140°-150°	1081.9	10.8
150°-160°	872.6	8.7
160°-170°	563.2	5.6
170°-180°	194.1	1.9
0°-30°	1221.3	12.2
0°-40°	1928.7	19.3
0°-60°	3159.3	31.6
0°-90°	3773.1	37.7
90°-120°	1273.3	12.7
90°-150°	4595.1	46.0
90°-180°	6225.0	62.3
0°-180°	9998.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1668	1668	1668	1668	1668	
5°	1668	1662	1645	1658	1655	158
15°	1591	1576	1538	1532	1522	448
25°	1448	1414	1352	1323	1308	666
35°	1253	1204	1120	1062	1038	784
45°	1030	969	865	788	755	795
55°	782	716	601	522	495	701
65°	534	460	354	288	273	529
75°	283	218	143	130	127	301
85°	72	42	38	35	35	79
90°	2	17	36	42	46	10
95°	92	30	47	58	58	111
105°	452	469	332	64	67	479
115°	848	857	871	886	892	837
125°	1195	1208	1214	1217	1220	1068
135°	1488	1497	1503	1508	1503	1146
145°	1717	1728	1731	1734	1734	1075
155°	1892	1889	1890	1898	1889	872
165°	1995	1990	1989	2001	1990	564
175°	2042	2034	2036	2046	2034	194
180°	2042	2042	2042	2042	2042	

TEST NUMBER: P1031041

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1668.3	1668.3	1668.3	1668.3	1668.3
2.5°	1675.1	1669.7	1653.4	1668.3	1665.6
5°	1668.3	1661.5	1645.3	1657.5	1654.8
7.5°	1656.1	1649.4	1629.1	1637.2	1633.1
10°	1639.9	1630.4	1606.1	1607.4	1600.7
12.5°	1616.9	1606.1	1574.9	1573.6	1565.5
15°	1591.2	1576.3	1538.4	1531.6	1522.2
17.5°	1560.1	1543.8	1496.5	1482.9	1469.4
20°	1524.9	1503.2	1451.8	1434.2	1418.0
22.5°	1485.6	1459.9	1404.5	1381.5	1366.6
25°	1447.8	1413.9	1351.7	1323.3	1308.4
27.5°	1401.8	1365.2	1297.6	1259.7	1236.7
30°	1354.4	1313.8	1238.0	1192.0	1170.4
32.5°	1307.0	1259.7	1178.5	1127.1	1104.1
35°	1252.9	1204.2	1120.3	1062.1	1037.8
37.5°	1198.8	1146.0	1058.1	993.1	963.4
40°	1147.4	1087.8	991.8	921.4	890.3
42.5°	1089.2	1029.7	929.5	851.1	824.0
45°	1029.7	968.8	864.6	787.5	755.0
47.5°	971.5	903.8	801.0	717.1	688.7
50°	906.5	842.9	733.4	649.5	618.3
52.5°	848.4	778.0	669.8	581.8	554.7
55°	782.1	715.8	600.8	522.3	495.2
57.5°	722.5	650.8	534.5	460.0	437.0
60°	660.3	585.9	473.6	400.5	377.5
62.5°	598.0	523.6	411.3	343.7	319.3
65°	534.5	460.0	354.5	288.2	273.3
67.5°	470.9	395.1	292.3	242.2	226.0
70°	408.6	335.6	240.8	193.5	178.6
72.5°	346.4	274.7	190.8	154.2	150.2
75°	282.8	217.8	143.4	129.9	127.2
77.5°	224.6	165.1	112.3	104.2	101.5
80°	169.1	113.7	85.2	81.2	78.5
82.5°	116.4	70.4	60.9	56.8	56.8
85°	71.7	41.9	37.9	35.2	35.2
87.5°	32.5	17.6	17.6	16.2	14.9
90°	1.5	16.7	36.4	42.5	45.5
92.5°	34.9	25.8	39.4	50.1	51.6
95°	92.5	30.3	47.0	57.6	57.6
97.5°	168.4	125.9	48.5	60.7	62.2
100°	256.4	286.7	50.1	62.2	63.7
102.5°	356.5	376.2	112.3	62.2	65.2
105°	452.1	468.8	332.2	63.7	66.7
107.5°	553.7	567.4	590.1	356.5	157.8
110°	655.4	667.5	684.2	634.1	417.2

TEST NUMBER: P1031041

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	752.4	763.1	779.7	793.4	790.4
115°	848.0	857.1	870.8	885.9	892.0
117.5°	942.1	952.7	960.3	972.4	973.9
120°	1028.5	1042.2	1046.7	1058.9	1058.9
122.5°	1116.5	1127.1	1133.2	1140.8	1142.3
125°	1195.4	1207.5	1213.6	1216.6	1219.7
127.5°	1274.3	1286.4	1294.0	1298.6	1295.5
130°	1347.1	1359.2	1365.3	1371.4	1368.3
132.5°	1416.9	1429.0	1433.6	1439.6	1435.1
135°	1488.2	1497.3	1503.4	1507.9	1503.4
137.5°	1548.9	1561.0	1564.0	1571.6	1568.6
140°	1609.6	1618.7	1623.2	1629.3	1626.2
142.5°	1665.7	1674.8	1679.3	1683.9	1679.3
145°	1717.3	1727.9	1730.9	1734.0	1734.0
147.5°	1767.3	1774.9	1777.9	1781.0	1773.4
150°	1812.8	1817.4	1820.4	1823.5	1818.9
152.5°	1853.8	1855.3	1856.8	1862.9	1855.3
155°	1891.7	1888.7	1890.2	1897.8	1888.7
157.5°	1922.1	1922.1	1920.5	1929.6	1917.5
160°	1949.4	1947.9	1946.3	1955.4	1944.8
162.5°	1975.2	1970.6	1969.1	1979.7	1970.6
165°	1994.9	1990.3	1988.8	2000.9	1990.3
167.5°	2011.6	2005.5	2005.5	2017.6	2005.5
170°	2025.2	2019.2	2019.2	2031.3	2019.2
172.5°	2034.3	2026.7	2028.3	2040.4	2026.7
175°	2041.9	2034.3	2035.8	2046.5	2034.3
177.5°	2044.9	2037.4	2038.9	2051.0	2035.8
180°	2041.9	2041.9	2041.9	2041.9	2041.9

(END OF REPORT)