

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030697

Luminaire Tested: S123DIW-B1000D460UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030697
REPORT IS A COMBINATION OF REPORTS P990744 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D460UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5986.0 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030697

CATALOG NUMBER: S123DIW-B1000D460UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1030697

CATALOG NUMBER: S123DIW-B1000D460UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69		
1	102	97	93	90	96	92	89	85	82	80	77	73	71	69	65	63	62	58		
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48		
3	85	75	67	61	80	71	64	59	64	58	54	57	52	49	50	47	44	41		
4	78	66	58	52	73	63	55	50	56	50	46	51	46	42	45	41	38	35		
5	71	59	51	44	67	56	49	43	51	44	40	45	40	36	41	37	33	30		
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	33	29	27		
7	61	48	40	34	57	46	38	33	42	35	31	37	32	28	34	29	26	24		
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21		
9	53	40	32	27	50	38	31	26	35	29	24	32	26	23	29	24	21	19		
10	49	37	29	24	47	35	28	24	32	26	22	29	24	21	27	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17011	17011	17011
5°	17053	16424	16400
10°	16902	15868	15705
15°	16666	15289	14948
20°	16397	14649	14199
25°	16048	13971	13398
30°	15667	13270	12555
35°	15267	12554	11718
40°	14848	11803	10894
45°	14389	11071	10033
50°	13921	10253	9168
55°	13321	9403	8294
60°	12702	8465	7362
65°	12121	7450	6390
70°	11285	6325	5257
75°	10080	5009	4081
80°	8703	3521	2886
85°	6791	1891	1445

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14389 cd/sqm

TEST NUMBER: P1030697

CATALOG NUMBER: S123DIW-B1000D460UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	2.5
10°-20°	420.7	7.0
20°-30°	621.3	10.4
30°-40°	725.6	12.1
40°-50°	729.5	12.2
50°-60°	640.8	10.7
60°-70°	477.3	8.0
70°-80°	271.6	4.5
80°-90°	78.4	1.3
90°-100°	21.7	0.4
100°-110°	104.7	1.7
110°-120°	256.5	4.3
120°-130°	325.6	5.4
130°-140°	347.9	5.8
140°-150°	325.3	5.4
150°-160°	262.4	4.4
160°-170°	169.3	2.8
170°-180°	58.4	1.0
0°-30°	1191.0	19.9
0°-40°	1916.6	32.0
0°-60°	3286.9	54.9
0°-90°	4114.2	68.7
90°-120°	382.9	6.4
90°-150°	1381.7	23.1
90°-180°	1872.0	31.3
0°-180°	5986.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1582	1575	1560	1574	1571	150
15°	1506	1500	1482	1493	1485	425
25°	1367	1359	1341	1343	1338	630
35°	1182	1174	1156	1148	1142	740
45°	969	963	946	930	923	748
55°	735	734	716	701	694	659
65°	501	495	481	470	466	495
75°	265	260	256	249	245	283
85°	71	68	68	65	65	76
90°	0	5	11	13	14	6
95°	28	9	14	17	17	33
105°	136	141	100	19	20	144
115°	255	258	262	266	268	252
125°	359	363	365	366	367	321
135°	448	450	452	453	452	345
145°	516	520	520	521	521	323
155°	569	568	568	571	568	262
165°	600	598	598	602	598	169
175°	614	612	612	615	612	58
180°	614	614	614	614	614	

TEST NUMBER: P1030697

CATALOG NUMBER: S123DIW-B1000D460UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.4	1580.4	1580.4	1580.4	1580.4
2.5°	1587.2	1581.7	1566.8	1580.4	1579.0
5°	1581.7	1574.9	1560.0	1573.6	1570.9
7.5°	1569.5	1562.7	1547.8	1560.0	1558.6
10°	1553.2	1546.4	1528.7	1541.0	1538.2
12.5°	1531.4	1526.0	1509.7	1517.9	1516.5
15°	1505.6	1500.2	1482.5	1493.4	1485.2
17.5°	1477.1	1470.3	1452.6	1460.8	1458.1
20°	1444.5	1436.3	1418.7	1424.1	1420.0
22.5°	1407.8	1399.6	1382.0	1386.1	1380.6
25°	1367.0	1358.9	1341.2	1342.6	1338.5
27.5°	1324.9	1316.7	1297.7	1299.1	1295.0
30°	1278.7	1271.9	1252.9	1252.9	1243.4
32.5°	1232.5	1223.0	1209.4	1199.9	1195.8
35°	1182.2	1174.1	1156.4	1148.2	1141.5
37.5°	1131.9	1121.1	1103.4	1093.9	1089.8
40°	1078.9	1070.8	1051.8	1040.9	1035.5
42.5°	1025.9	1016.4	997.4	986.5	981.1
45°	968.9	963.4	945.8	929.5	922.7
47.5°	913.2	905.0	888.7	872.4	867.0
50°	856.1	849.3	831.6	816.7	808.5
52.5°	796.3	792.2	773.2	761.0	752.8
55°	735.2	733.8	716.1	701.2	694.4
57.5°	678.1	672.6	659.1	645.5	637.3
60°	615.6	614.2	597.9	585.7	578.9
62.5°	559.9	555.8	539.5	527.2	523.2
65°	501.4	494.6	481.0	470.2	466.1
67.5°	438.9	433.5	422.6	413.1	407.7
70°	383.2	375.0	366.9	357.4	350.6
72.5°	324.8	319.3	309.8	301.7	299.0
75°	265.0	259.5	255.5	248.7	244.6
77.5°	212.0	209.3	203.8	198.4	198.4
80°	160.3	156.3	153.6	152.2	152.2
82.5°	110.1	110.1	110.1	107.4	106.0
85°	70.7	67.9	67.9	65.2	65.2
87.5°	35.3	31.3	29.9	28.5	28.5
90°	0.5	5.0	10.9	12.8	13.7
92.5°	10.5	7.8	11.9	15.1	15.5
95°	27.8	9.1	14.1	17.3	17.3
97.5°	50.6	37.9	14.6	18.2	18.7
100°	77.1	86.2	15.1	18.7	19.2
102.5°	107.2	113.1	33.8	18.7	19.6
105°	135.9	141.0	99.9	19.2	20.1
107.5°	166.5	170.6	177.4	107.2	47.4
110°	197.1	200.7	205.7	190.7	125.4

TEST NUMBER: P1030697

CATALOG NUMBER: S123DIW-B1000D460UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	226.3	229.4	234.5	238.6	237.7
115°	255.0	257.7	261.8	266.4	268.2
117.5°	283.3	286.5	288.7	292.4	292.8
120°	309.3	313.4	314.7	318.4	318.4
122.5°	335.7	338.9	340.7	343.0	343.5
125°	359.4	363.1	364.9	365.8	366.7
127.5°	383.2	386.8	389.1	390.5	389.6
130°	405.1	408.7	410.5	412.4	411.4
132.5°	426.0	429.7	431.1	432.9	431.5
135°	447.5	450.2	452.0	453.4	452.0
137.5°	465.7	469.4	470.3	472.6	471.7
140°	484.0	486.7	488.1	489.9	489.0
142.5°	500.9	503.6	505.0	506.3	505.0
145°	516.4	519.6	520.5	521.4	521.4
147.5°	531.4	533.7	534.6	535.5	533.2
150°	545.1	546.5	547.4	548.3	546.9
152.5°	557.4	557.9	558.3	560.2	557.9
155°	568.8	567.9	568.4	570.6	567.9
157.5°	577.9	577.9	577.5	580.2	576.6
160°	586.2	585.7	585.2	588.0	584.8
162.5°	593.9	592.5	592.1	595.3	592.5
165°	599.8	598.5	598.0	601.7	598.5
167.5°	604.9	603.0	603.0	606.7	603.0
170°	609.0	607.1	607.1	610.8	607.1
172.5°	611.7	609.4	609.9	613.5	609.4
175°	614.0	611.7	612.2	615.3	611.7
177.5°	614.9	612.6	613.1	616.7	612.2
180°	614.0	614.0	614.0	614.0	614.0

(END OF REPORT)