

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030780

Luminaire Tested: S123DIW-B1165D755UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030780
REPORT IS A COMBINATION OF REPORTS P991131 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1165D755UB2750-4F0-XX-W2A-D_2700K
Description: Define 3 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7866.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 84.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030780

CATALOG NUMBER: S123DIW-B1165D755UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1030780

CATALOG NUMBER: S123DIW-B1165D755UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62
1	98	93	89	85	91	87	83	79	74	71	69	63	61	59	53	51	50
2	89	81	74	68	82	75	69	64	64	60	56	55	51	48	46	43	41
3	81	71	63	56	75	66	59	53	56	51	47	48	44	40	40	37	34
4	74	62	54	47	68	58	50	45	50	44	39	43	38	34	36	32	29
5	68	55	47	40	62	52	44	38	45	39	34	38	33	30	32	28	25
6	62	50	41	35	57	46	39	33	40	34	29	34	30	26	29	25	22
7	57	45	36	31	53	42	34	29	36	30	26	31	26	23	26	23	20
8	53	41	32	27	49	38	31	26	33	27	23	29	24	20	24	20	18
9	50	37	29	24	46	35	28	23	30	25	20	26	22	18	22	19	16
10	46	34	26	22	43	32	25	20	28	22	18	24	20	16	21	17	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15434	15434	15434
5°	15477	14982	14969
10°	15332	14576	14464
15°	15129	14128	13929
20°	14841	13628	13354
25°	14487	13066	12758
30°	14123	12556	12160
35°	13716	12022	11673
40°	13328	11534	11158
45°	12898	11061	10734
50°	12471	10593	10273
55°	12000	10112	9850
60°	11539	9621	9416
65°	11064	9096	8908
70°	10348	8509	8384
75°	9449	7839	7845
80°	8393	7161	7228
85°	7348	6611	6785

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12898 cd/sqm

TEST NUMBER: P1030780

CATALOG NUMBER: S123DIW-B1165D755UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.0	1.7
10°-20°	387.8	4.9
20°-30°	579.9	7.4
30°-40°	692.3	8.8
40°-50°	724.4	9.2
50°-60°	679.8	8.6
60°-70°	567.8	7.2
70°-80°	406.0	5.2
80°-90°	243.6	3.1
90°-100°	187.0	2.4
100°-110°	281.9	3.6
110°-120°	491.8	6.3
120°-130°	572.3	7.3
130°-140°	585.0	7.4
140°-150°	533.2	6.8
150°-160°	426.9	5.4
160°-170°	275.5	3.5
170°-180°	94.9	1.2
0°-30°	1103.7	14.0
0°-40°	1796.0	22.8
0°-60°	3200.1	40.7
0°-90°	4417.5	56.2
90°-120°	960.7	12.2
90°-150°	2651.2	33.7
90°-180°	3449.0	43.8
0°-180°	7866.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1434	1434	1434	1434	1434	
5°	1436	1432	1423	1436	1434	136
15°	1367	1371	1370	1386	1384	385
25°	1234	1250	1254	1275	1275	569
35°	1062	1087	1107	1131	1137	664
45°	868	906	945	975	987	670
55°	662	714	770	812	825	593
65°	458	519	587	634	650	452
75°	248	322	400	451	470	265
85°	76	155	237	290	306	79
90°	21	105	194	250	268	17
95°	62	93	178	231	247	67
105°	234	279	280	192	208	247
115°	423	446	509	554	569	418
125°	590	595	644	678	690	527
135°	731	734	754	784	790	563
145°	842	845	847	861	867	527
155°	925	924	925	928	924	426
165°	976	974	973	979	974	276
175°	999	995	996	1001	995	95
180°	999	999	999	999	999	

TEST NUMBER: P1030780

CATALOG NUMBER: S123DIW-B1165D755UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1433.9	1433.9	1433.9	1433.9	1433.9
2.5°	1441.7	1437.0	1424.5	1437.0	1435.5
5°	1435.5	1432.3	1423.0	1435.5	1433.9
7.5°	1424.5	1424.5	1415.1	1430.8	1429.2
10°	1408.9	1412.0	1404.2	1419.8	1416.7
12.5°	1390.2	1394.8	1390.2	1404.2	1401.1
15°	1366.7	1371.4	1369.9	1385.5	1383.9
17.5°	1338.6	1348.0	1346.4	1360.5	1357.4
20°	1307.4	1316.7	1319.9	1333.9	1335.5
22.5°	1274.6	1283.9	1288.6	1307.4	1305.8
25°	1234.0	1249.6	1254.3	1274.6	1274.6
27.5°	1194.9	1212.1	1221.5	1238.6	1240.2
30°	1152.7	1173.0	1185.5	1204.3	1204.3
32.5°	1105.9	1129.3	1146.5	1166.8	1171.5
35°	1062.1	1087.1	1107.4	1130.9	1137.1
37.5°	1015.3	1043.4	1066.8	1093.4	1098.1
40°	968.4	996.5	1027.8	1054.3	1060.6
42.5°	916.9	952.8	985.6	1015.3	1024.7
45°	868.5	905.9	945.0	974.7	987.2
47.5°	816.9	859.1	902.8	935.6	945.0
50°	766.9	810.7	859.1	895.0	905.9
52.5°	713.8	760.7	815.4	852.8	866.9
55°	662.3	713.8	770.1	812.2	824.7
57.5°	612.3	665.4	726.3	768.5	782.5
60°	559.2	615.4	679.5	723.2	740.4
62.5°	509.2	567.0	635.7	679.5	695.1
65°	457.7	518.6	587.3	634.2	649.8
67.5°	406.1	470.2	538.9	590.4	602.9
70°	351.4	418.6	493.6	543.6	559.2
72.5°	301.5	368.6	446.7	498.3	513.9
75°	248.4	321.8	399.9	451.4	470.2
77.5°	203.1	276.5	354.6	409.2	423.3
80°	154.6	231.2	312.4	365.5	381.1
82.5°	112.5	190.6	273.3	326.5	342.1
85°	76.5	154.6	237.4	290.5	306.1
87.5°	46.9	125.0	204.6	257.7	273.3
90°	21.0	105.0	194.3	250.4	267.5
92.5°	35.8	98.5	183.3	240.1	254.8
95°	62.5	92.9	177.6	231.3	246.9
97.5°	98.0	133.5	169.0	221.8	238.1
100°	139.5	204.3	160.4	211.6	228.0
102.5°	186.9	240.2	181.4	200.7	217.8
105°	233.6	279.3	279.6	192.1	207.6
107.5°	281.8	321.2	396.5	324.3	241.2
110°	330.0	364.0	434.7	450.8	357.2

TEST NUMBER: P1030780

CATALOG NUMBER: S123DIW-B1165D755UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	377.5	404.5	472.0	517.7	530.3
115°	422.6	445.9	508.7	553.7	569.1
117.5°	468.6	486.3	543.1	586.6	599.8
120°	509.3	523.9	577.6	619.5	630.5
122.5°	552.4	560.8	612.1	650.2	661.9
125°	589.5	595.4	643.7	677.9	690.3
127.5°	628.0	632.4	675.2	708.6	718.0
130°	663.7	668.0	702.3	734.8	742.7
132.5°	696.2	702.1	727.9	758.9	767.6
135°	731.1	734.0	754.1	784.5	790.1
137.5°	760.8	765.2	777.6	806.3	812.6
140°	788.9	793.4	800.2	826.7	833.0
142.5°	816.4	819.2	821.5	844.0	849.6
145°	841.6	845.2	846.7	860.7	866.9
147.5°	864.5	868.2	869.7	875.9	878.4
150°	886.8	889.0	890.5	892.0	892.8
152.5°	906.8	907.6	908.3	911.3	907.6
155°	925.4	923.9	924.6	928.3	923.9
157.5°	940.2	940.2	939.5	943.9	938.0
160°	953.6	952.8	952.1	956.5	951.3
162.5°	966.2	963.9	963.2	968.4	963.9
165°	975.8	973.6	972.9	978.8	973.6
167.5°	984.0	981.0	981.0	987.0	981.0
170°	990.7	987.7	987.7	993.6	987.7
172.5°	995.1	991.4	992.1	998.1	991.4
175°	998.8	995.1	995.9	1001.1	995.1
177.5°	1000.3	996.6	997.3	1003.3	995.9
180°	998.8	998.8	998.8	998.8	998.8

(END OF REPORT)