

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031136

Luminaire Tested: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031136
REPORT IS A COMBINATION OF REPORTS P994256 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7548.0 lumens
Efficiency: N/A
Efficacy: 115.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	99	99	99	99	88	88	88	88	65	65	65	45	45	45	26	26	26	18		
1	91	87	83	80	80	76	73	71	57	55	54	40	39	38	23	23	22	15		
2	83	76	70	65	73	67	62	58	50	47	45	35	33	32	21	20	19	13		
3	75	67	60	55	66	59	53	49	45	41	38	31	29	27	19	18	17	11		
4	69	59	52	46	61	52	46	41	40	35	32	28	25	23	17	15	14	10		
5	63	52	45	39	56	47	40	35	35	31	28	25	22	20	15	14	13	9		
6	58	47	39	34	51	42	35	31	32	27	24	22	20	18	14	12	11	8		
7	54	42	35	30	47	38	31	27	29	24	21	20	18	15	13	11	10	7		
8	50	38	31	26	44	34	28	23	26	22	19	19	16	14	12	10	9	6		
9	46	35	28	23	41	31	25	21	24	19	16	17	14	12	11	9	8	6		
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	8	7	5		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5702	5702	5702	5702
5°	5707	6567	5721	4872
10°	5655	7927	5680	4255
15°	5598	8997	5598	3752
20°	5483	9704	5513	3329
25°	5399	9220	5389	3037
30°	5302	6389	5289	2753
35°	5184	4101	5159	2538
40°	5037	2896	5012	2324
45°	4782	2318	4775	2116
50°	4469	1939	4454	1872
55°	4117	1598	4084	1587
60°	3772	1321	3735	1349
65°	3365	1057	3387	1143
70°	2992	735	3072	925
75°	2537	546	2640	711
80°	2020	360	2193	533
85°	1441	171	1566	332

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 7612 cd/sqm

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.0	0.7
10°-20°	162.8	2.2
20°-30°	256.5	3.4
30°-40°	266.7	3.5
40°-50°	228.2	3.0
50°-60°	173.9	2.3
60°-70°	111.4	1.5
70°-80°	53.4	0.7
80°-90°	18.1	0.2
90°-100°	72.0	1.0
100°-110°	348.1	4.6
110°-120°	853.1	11.3
120°-130°	1083.0	14.3
130°-140°	1156.9	15.3
140°-150°	1081.9	14.3
150°-160°	872.6	11.6
160°-170°	563.2	7.5
170°-180°	194.1	2.6
0°-30°	471.3	6.2
0°-40°	738.0	9.8
0°-60°	1140.1	15.1
0°-90°	1323.1	17.5
90°-120°	1273.3	16.9
90°-150°	4595.1	60.9
90°-180°	6225.0	82.5
0°-180°	7548.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	530	530	530	530	530	
5°	529	629	531	467	529	50
15°	506	894	506	373	506	142
25°	460	921	459	303	460	212
35°	401	400	400	247	401	251
45°	322	213	322	195	322	248
55°	227	134	225	133	227	204
65°	139	77	140	83	139	139
75°	67	33	69	43	67	72
85°	15	8	16	15	15	17
90°	2	46	2	46	2	6
95°	92	58	92	58	92	111
105°	452	67	452	67	452	479
115°	848	892	848	892	848	837
125°	1195	1220	1195	1220	1195	1068
135°	1488	1503	1488	1503	1488	1146
145°	1717	1734	1717	1734	1717	1075
155°	1892	1889	1892	1889	1892	872
165°	1995	1990	1995	1990	1995	564
175°	2042	2034	2042	2034	2042	194
180°	2042	2042	2042	2042	2042	

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	531.1	534.7	537.4	539.2	543.8	546.5	548.8	552.8	552.8	553.7	555.6
5°	529.3	537.0	542.4	549.7	559.2	563.7	570.1	575.5	583.2	587.3	591.4
7.5°	525.2	536.1	547.4	558.3	572.3	581.4	587.8	601.8	611.8	624.0	633.6
10°	519.7	534.7	549.2	566.0	585.0	598.6	608.2	626.8	645.8	663.0	677.6
12.5°	512.9	531.1	551.9	572.3	599.1	612.7	628.1	651.2	678.5	700.2	719.7
15°	505.7	526.5	550.1	575.1	608.6	627.7	649.9	678.0	708.4	739.7	766.4
17.5°	494.3	520.6	546.9	583.2	622.7	634.0	653.1	691.6	729.3	757.4	790.0
20°	483.0	512.5	545.6	578.2	620.9	647.2	664.9	705.7	746.0	780.0	811.3
22.5°	472.6	503.4	537.9	579.1	619.0	645.4	667.6	710.2	756.9	795.0	833.6
25°	459.9	493.4	531.5	570.5	619.0	639.0	663.5	712.9	762.4	806.4	854.0
27.5°	446.3	480.3	517.9	557.8	602.3	631.7	655.8	708.8	769.2	816.3	865.3
30°	432.7	467.6	503.9	539.7	589.6	617.7	645.4	703.9	772.8	826.8	864.4
32.5°	419.5	449.0	484.8	519.7	569.2	600.0	631.3	698.9	774.2	819.5	837.6
35°	401.4	432.2	461.2	498.4	548.3	578.7	615.4	698.4	768.3	796.4	787.3
37.5°	384.6	410.4	438.1	471.2	522.5	561.9	600.0	686.6	748.8	750.6	699.3
40°	366.0	387.3	410.4	445.4	500.7	539.7	581.0	668.5	713.4	686.6	596.4
42.5°	344.7	363.7	381.9	415.9	476.2	519.7	564.2	645.8	662.1	600.5	506.6
45°	322.0	337.4	354.2	390.0	450.3	493.4	537.9	610.9	594.1	507.0	417.7
47.5°	298.4	311.6	327.9	360.5	422.7	466.7	508.8	561.0	518.4	424.9	350.1
50°	274.8	285.3	301.1	334.7	394.6	434.5	473.5	507.5	447.6	364.6	289.3
52.5°	251.7	259.9	276.2	304.8	362.8	400.9	429.0	442.2	381.4	301.1	251.2
55°	227.2	236.3	247.2	276.2	333.8	361.9	380.5	380.0	317.5	255.3	207.7
57.5°	203.6	211.8	221.3	250.3	297.1	316.1	332.0	324.3	264.9	209.1	178.2
60°	182.8	187.3	197.7	222.2	257.6	273.9	283.0	269.8	216.3	176.4	147.4
62.5°	160.1	164.6	173.2	196.4	218.1	226.8	234.5	217.7	178.7	143.8	126.1
65°	139.2	145.1	150.6	169.2	181.0	191.4	190.5	176.4	139.7	117.0	102.5
67.5°	121.1	123.4	127.9	139.2	144.7	152.4	152.8	137.0	112.5	95.2	86.6
70°	101.6	103.9	107.0	112.5	116.1	117.9	117.0	102.9	84.8	74.4	66.7
72.5°	84.8	84.4	86.6	86.6	90.2	89.8	87.1	76.2	64.4	55.8	51.2
75°	66.7	67.1	67.6	66.7	65.3	63.5	61.2	53.1	45.4	41.3	37.2
77.5°	52.2	51.2	51.7	48.5	46.7	44.9	41.7	37.6	31.3	30.4	28.6
80°	37.2	36.7	36.3	34.9	30.8	29.0	26.8	24.5	23.1	22.2	21.8
82.5°	24.9	24.9	24.0	21.3	19.0	17.7	17.2	16.3	15.0	15.0	14.5
85°	15.0	14.5	13.6	10.9	9.5	9.5	9.5	9.5	8.6	8.6	8.2
87.5°	5.9	5.4	4.1	4.1	3.6	3.6	3.6	3.2	3.2	2.7	2.7
90°	1.5	4.9	8.3	11.6	15.0	16.7	18.9	23.3	27.6	32.0	36.4
92.5°	34.9	32.9	30.9	28.8	26.8	25.8	27.3	30.3	33.4	36.4	39.4
95°	92.5	78.7	64.9	51.0	37.2	30.3	32.2	35.9	39.6	43.3	47.0
97.5°	168.4	159.0	149.5	140.1	130.6	125.9	117.3	100.1	82.9	65.7	48.5
100°	256.4	263.1	269.9	276.6	283.3	286.7	260.4	207.8	155.3	102.7	50.1
102.5°	356.5	360.9	365.3	369.6	374.0	376.2	346.9	288.2	229.6	170.9	112.3
105°	452.1	455.8	459.5	463.2	466.9	468.8	453.6	423.3	392.9	362.6	332.2
107.5°	553.7	556.7	559.8	562.8	565.9	567.4	569.9	575.0	580.0	585.1	590.1
110°	655.4	658.1	660.8	663.5	666.2	667.5	669.4	673.1	676.8	680.5	684.2

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	752.4	754.8	757.2	759.5	761.9	763.1	764.9	768.6	772.3	776.0	779.7
115°	848.0	850.0	852.0	854.1	856.1	857.1	858.6	861.7	864.7	867.8	870.8
117.5°	942.1	944.5	946.8	949.2	951.5	952.7	953.5	955.2	956.9	958.6	960.3
120°	1028.5	1031.5	1034.6	1037.6	1040.7	1042.2	1042.7	1043.7	1044.7	1045.7	1046.7
122.5°	1116.5	1118.9	1121.2	1123.6	1125.9	1127.1	1127.8	1129.1	1130.5	1131.8	1133.2
125°	1195.4	1198.1	1200.8	1203.5	1206.2	1207.5	1208.2	1209.5	1210.9	1212.2	1213.6
127.5°	1274.3	1277.0	1279.7	1282.4	1285.1	1286.4	1287.2	1288.9	1290.6	1292.3	1294.0
130°	1347.1	1349.8	1352.5	1355.2	1357.9	1359.2	1359.9	1361.2	1362.6	1363.9	1365.3
132.5°	1416.9	1419.6	1422.3	1425.0	1427.7	1429.0	1429.5	1430.5	1431.6	1432.6	1433.6
135°	1488.2	1490.2	1492.2	1494.3	1496.3	1497.3	1498.0	1499.3	1500.7	1502.0	1503.4
137.5°	1548.9	1551.6	1554.3	1557.0	1559.7	1561.0	1561.3	1562.0	1562.7	1563.3	1564.0
140°	1609.6	1611.6	1613.6	1615.7	1617.7	1618.7	1619.2	1620.2	1621.2	1622.2	1623.2
142.5°	1665.7	1667.7	1669.7	1671.8	1673.8	1674.8	1675.3	1676.3	1677.3	1678.3	1679.3
145°	1717.3	1719.7	1722.0	1724.4	1726.7	1727.9	1728.2	1728.9	1729.6	1730.2	1730.9
147.5°	1767.3	1769.0	1770.7	1772.4	1774.1	1774.9	1775.2	1775.9	1776.6	1777.2	1777.9
150°	1812.8	1813.8	1814.8	1815.9	1816.9	1817.4	1817.7	1818.4	1819.1	1819.7	1820.4
152.5°	1853.8	1854.1	1854.5	1854.8	1855.1	1855.3	1855.5	1855.8	1856.1	1856.5	1856.8
155°	1891.7	1891.0	1890.4	1889.7	1889.0	1888.7	1888.9	1889.2	1889.5	1889.9	1890.2
157.5°	1922.1	1922.1	1922.1	1922.1	1922.1	1922.1	1921.9	1921.6	1921.2	1920.9	1920.5
160°	1949.4	1949.1	1948.7	1948.4	1948.1	1947.9	1947.7	1947.4	1947.0	1946.7	1946.3
162.5°	1975.2	1974.2	1973.2	1972.1	1971.1	1970.6	1970.4	1970.1	1969.8	1969.4	1969.1
165°	1994.9	1993.9	1992.9	1991.8	1990.8	1990.3	1990.1	1989.8	1989.5	1989.1	1988.8
167.5°	2011.6	2010.2	2008.9	2007.5	2006.2	2005.5	2005.5	2005.5	2005.5	2005.5	2005.5
170°	2025.2	2023.9	2022.5	2021.2	2019.9	2019.2	2019.2	2019.2	2019.2	2019.2	2019.2
172.5°	2034.3	2032.6	2030.9	2029.2	2027.5	2026.7	2026.9	2027.2	2027.6	2027.9	2028.3
175°	2041.9	2040.2	2038.5	2036.8	2035.1	2034.3	2034.5	2034.8	2035.1	2035.5	2035.8
177.5°	2044.9	2043.2	2041.6	2039.9	2038.2	2037.4	2037.6	2037.9	2038.2	2038.6	2038.9
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4FO-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	559.2	559.2	563.3	567.3	565.1	566.4	571.4	569.6	573.2	572.8	574.2
5°	601.4	606.4	610.4	619.0	620.4	619.0	627.7	629.9	634.0	629.0	631.3
7.5°	649.0	659.4	669.4	682.1	686.2	687.1	691.6	698.0	703.4	693.4	698.4
10°	695.2	711.1	731.5	742.9	752.8	756.5	760.1	764.2	770.5	776.4	771.9
12.5°	745.1	768.3	787.8	808.2	820.4	819.1	829.5	832.2	837.2	838.6	840.4
15°	785.9	818.6	830.8	861.2	863.9	873.0	884.8	895.2	896.6	893.9	893.9
17.5°	824.9	853.1	874.8	899.3	904.3	912.0	927.0	932.0	933.8	933.3	933.3
20°	856.7	875.3	912.0	932.4	940.6	950.6	961.0	967.4	968.7	970.5	967.8
22.5°	877.6	905.7	935.6	952.4	959.2	962.8	969.6	971.4	969.2	969.6	970.1
25°	893.9	921.5	939.7	944.2	943.8	939.2	934.2	925.6	924.7	921.1	913.8
27.5°	898.4	908.8	906.6	888.0	869.4	867.6	837.6	821.3	802.7	805.4	795.0
30°	873.9	860.3	828.1	781.0	761.5	729.7	696.1	661.2	647.6	632.7	660.3
32.5°	814.1	765.5	708.4	647.2	614.5	586.4	550.6	525.2	510.7	498.4	522.0
35°	723.8	648.1	572.3	514.3	487.5	462.1	428.6	415.9	397.7	399.5	401.8
37.5°	607.7	524.3	467.1	410.0	392.3	381.9	357.4	337.9	331.5	329.7	329.7
40°	498.9	430.4	379.6	334.7	321.1	312.5	293.0	283.9	277.1	275.3	277.6
42.5°	412.7	354.2	314.7	284.8	275.3	264.4	256.2	244.9	243.5	240.4	244.4
45°	346.5	295.7	266.2	244.4	236.3	232.2	223.1	216.3	213.6	213.2	216.3
47.5°	293.9	254.4	228.6	215.0	208.6	204.5	196.8	194.1	191.4	192.3	190.9
50°	246.7	217.2	200.5	188.2	184.1	180.0	175.1	172.3	171.0	171.0	170.5
52.5°	211.8	187.3	176.4	165.1	163.3	161.0	155.6	153.7	151.5	151.0	152.8
55°	181.4	164.6	153.7	146.9	145.1	140.6	138.3	136.1	134.7	133.8	134.2
57.5°	155.1	142.4	135.1	129.3	126.1	124.3	120.2	119.7	118.8	118.8	118.4
60°	133.3	124.3	115.6	112.0	109.8	107.5	107.0	104.3	102.9	103.9	103.4
62.5°	112.9	105.7	100.7	96.6	95.2	93.4	92.1	91.2	89.8	90.2	90.2
65°	94.3	88.4	84.8	81.2	80.7	78.9	78.5	77.6	77.6	77.1	78.0
67.5°	77.6	73.5	70.3	68.0	66.7	67.1	65.3	63.9	63.9	63.5	64.9
70°	61.7	59.4	56.2	53.5	51.7	51.7	49.4	49.0	49.0	49.0	48.5
72.5°	47.6	43.5	42.2	41.3	41.3	41.3	40.4	40.4	39.9	40.4	39.9
75°	35.4	34.9	34.0	33.6	33.6	33.1	32.7	32.7	32.7	32.7	32.7
77.5°	27.7	27.7	26.8	26.3	26.3	26.3	25.9	25.9	25.4	25.4	25.4
80°	20.4	20.4	19.5	19.5	19.5	19.0	19.0	19.0	19.5	19.0	19.0
82.5°	14.1	14.1	13.6	14.1	13.6	13.2	13.2	13.2	12.7	13.2	13.2
85°	8.2	8.2	7.7	7.3	7.7	7.7	7.3	7.7	7.3	7.7	7.3
87.5°	3.2	2.7	2.7	2.7	2.3	2.7	2.3	2.3	2.7	2.3	2.7
90°	37.8	39.1	40.5	41.8	42.5	42.8	43.5	44.2	44.8	45.5	44.8
92.5°	41.8	44.2	46.5	48.9	50.1	50.3	50.6	50.9	51.3	51.6	51.3
95°	49.4	51.7	54.1	56.4	57.6	57.6	57.6	57.6	57.6	57.6	57.6
97.5°	51.2	53.9	56.6	59.3	60.7	60.9	61.2	61.5	61.9	62.2	61.9
100°	52.8	55.5	58.2	60.9	62.2	62.4	62.7	63.0	63.4	63.7	63.4
102.5°	101.2	90.0	78.9	67.8	62.2	62.5	63.2	63.9	64.5	65.2	64.5
105°	272.5	212.9	153.2	93.5	63.7	64.0	64.7	65.4	66.0	66.7	66.0
107.5°	538.2	486.3	434.4	382.5	356.5	334.4	290.3	246.1	202.0	157.8	202.0
110°	673.1	661.9	650.8	639.7	634.1	610.0	561.8	513.6	465.4	417.2	465.4

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	782.7	785.8	788.8	791.9	793.4	793.1	792.4	791.7	791.1	790.4	791.1
115°	874.2	877.5	880.9	884.2	885.9	886.6	887.9	889.3	890.6	892.0	890.6
117.5°	963.0	965.7	968.4	971.1	972.4	972.6	972.9	973.2	973.6	973.9	973.6
120°	1049.4	1052.1	1054.8	1057.5	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9
122.5°	1134.9	1136.6	1138.3	1140.0	1140.8	1141.0	1141.3	1141.6	1142.0	1142.3	1142.0
125°	1214.3	1214.9	1215.6	1216.3	1216.6	1216.9	1217.6	1218.3	1219.0	1219.7	1219.0
127.5°	1295.0	1296.0	1297.1	1298.1	1298.6	1298.3	1297.6	1296.9	1296.2	1295.5	1296.2
130°	1366.7	1368.0	1369.4	1370.7	1371.4	1371.1	1370.4	1369.7	1369.0	1368.3	1369.0
132.5°	1434.9	1436.3	1437.6	1438.9	1439.6	1439.1	1438.1	1437.1	1436.1	1435.1	1436.1
135°	1504.4	1505.4	1506.4	1507.4	1507.9	1507.4	1506.4	1505.4	1504.4	1503.4	1504.4
137.5°	1565.7	1567.4	1569.1	1570.8	1571.6	1571.3	1570.6	1569.9	1569.3	1568.6	1569.3
140°	1624.6	1625.9	1627.3	1628.6	1629.3	1629.0	1628.3	1627.6	1626.9	1626.2	1626.9
142.5°	1680.3	1681.3	1682.4	1683.4	1683.9	1683.4	1682.4	1681.3	1680.3	1679.3	1680.3
145°	1731.6	1732.3	1733.0	1733.7	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0
147.5°	1778.6	1779.3	1780.0	1780.7	1781.0	1780.2	1778.5	1776.8	1775.1	1773.4	1775.1
150°	1821.1	1821.8	1822.5	1823.2	1823.5	1823.0	1822.0	1820.9	1819.9	1818.9	1819.9
152.5°	1858.2	1859.5	1860.9	1862.2	1862.9	1862.1	1860.4	1858.7	1857.0	1855.3	1857.0
155°	1891.9	1893.6	1895.3	1897.0	1897.8	1896.8	1894.8	1892.7	1890.7	1888.7	1890.7
157.5°	1922.5	1924.5	1926.6	1928.6	1929.6	1928.3	1925.6	1922.9	1920.2	1917.5	1920.2
160°	1948.3	1950.3	1952.4	1954.4	1955.4	1954.2	1951.9	1949.5	1947.2	1944.8	1947.2
162.5°	1971.5	1973.8	1976.2	1978.5	1979.7	1978.7	1976.7	1974.6	1972.6	1970.6	1972.6
165°	1991.5	1994.2	1996.9	1999.6	2000.9	1999.7	1997.4	1995.0	1992.7	1990.3	1992.7
167.5°	2008.2	2010.9	2013.6	2016.3	2017.6	2016.3	2013.6	2010.9	2008.2	2005.5	2008.2
170°	2021.9	2024.6	2027.3	2030.0	2031.3	2030.0	2027.3	2024.6	2021.9	2019.2	2021.9
172.5°	2031.0	2033.7	2036.4	2039.1	2040.4	2038.9	2035.8	2032.8	2029.7	2026.7	2029.7
175°	2038.2	2040.6	2042.9	2045.3	2046.5	2045.1	2042.4	2039.7	2037.0	2034.3	2037.0
177.5°	2041.6	2044.3	2047.0	2049.7	2051.0	2049.3	2045.9	2042.6	2039.2	2035.8	2039.2
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	571.9	569.2	567.3	566.0	564.6	568.7	563.3	557.4	553.3	550.6	549.7
5°	631.7	625.9	620.9	616.8	617.7	617.7	608.2	597.7	588.7	583.7	578.2
7.5°	701.1	694.8	684.8	682.5	680.7	669.4	659.9	640.8	629.5	618.1	608.2
10°	770.1	761.9	752.4	749.2	744.7	730.6	716.1	691.6	677.6	656.7	643.5
12.5°	834.5	824.5	815.0	812.7	805.9	793.7	768.7	743.3	719.3	697.1	673.9
15°	888.4	885.7	871.2	862.1	847.2	830.4	824.9	790.5	760.1	737.0	695.2
17.5°	933.8	921.1	907.5	901.6	895.7	876.2	856.7	821.3	788.7	754.7	727.9
20°	970.1	956.0	946.5	937.9	935.2	912.9	882.1	850.8	815.0	776.9	742.0
22.5°	971.9	970.1	963.7	958.7	953.3	938.8	914.3	875.3	837.2	795.5	749.7
25°	934.2	931.5	949.7	945.1	948.8	943.3	930.2	897.5	853.1	804.1	757.8
27.5°	820.9	848.5	877.1	887.1	893.9	913.4	919.7	901.6	865.8	813.6	761.9
30°	666.7	703.4	749.7	774.6	793.7	829.9	877.1	883.0	866.2	824.5	761.0
32.5°	523.4	556.9	594.1	623.6	649.0	723.4	786.9	832.7	840.8	819.1	763.3
35°	421.8	436.3	471.7	499.8	534.2	597.7	672.6	746.5	796.4	799.1	756.5
37.5°	347.8	355.6	386.4	402.3	422.7	478.5	548.3	644.9	722.5	759.2	737.4
40°	288.0	305.7	323.4	332.4	346.9	385.5	452.6	528.3	624.5	692.5	707.9
42.5°	249.9	257.6	268.9	281.6	290.7	324.3	369.2	438.6	525.2	620.0	662.6
45°	220.4	223.1	234.9	243.1	252.6	276.2	307.9	366.0	442.2	535.6	608.2
47.5°	195.9	201.4	207.7	212.7	219.0	237.2	264.4	306.6	373.7	457.1	535.1
50°	174.2	177.3	185.5	187.8	192.3	205.0	225.9	258.1	313.4	380.0	460.8
52.5°	153.7	159.6	162.8	166.0	170.1	180.5	194.1	220.4	262.1	324.7	393.2
55°	137.9	139.7	144.2	146.9	150.1	157.4	169.2	188.7	221.3	271.2	336.1
57.5°	122.4	122.4	127.0	129.3	132.4	137.9	148.3	163.3	186.8	224.0	283.4
60°	106.1	106.6	110.2	112.9	113.8	119.3	127.9	139.7	157.8	185.0	233.6
62.5°	91.6	93.9	95.7	96.6	99.8	102.9	110.2	118.4	131.1	155.1	189.6
65°	79.4	79.8	81.2	82.1	83.4	87.1	92.5	98.0	108.8	126.5	154.6
67.5°	65.3	67.1	68.9	68.9	70.3	72.1	77.6	82.1	90.2	100.7	119.7
70°	49.0	49.9	52.6	54.0	55.8	59.0	61.7	64.4	70.7	78.5	93.0
72.5°	40.8	40.8	41.7	42.2	42.2	44.4	48.5	51.2	54.4	59.9	69.8
75°	32.7	32.7	34.0	33.6	34.5	35.4	35.8	37.6	39.5	43.5	49.4
77.5°	25.9	26.3	26.3	26.8	26.8	27.2	27.7	28.6	29.5	31.7	34.5
80°	19.0	19.5	19.5	20.0	20.0	20.4	20.9	21.3	22.2	23.1	24.5
82.5°	13.2	13.6	13.6	14.1	13.6	14.1	14.5	14.5	15.0	15.9	16.3
85°	7.7	7.7	8.2	7.7	7.7	7.7	8.2	8.2	8.6	10.0	10.0
87.5°	2.3	2.7	2.3	2.7	2.7	2.7	2.7	3.2	3.2	3.6	4.1
90°	44.2	43.5	42.8	42.5	41.8	40.5	39.1	37.8	36.4	32.0	27.6
92.5°	50.9	50.6	50.3	50.1	48.9	46.5	44.2	41.8	39.4	36.4	33.4
95°	57.6	57.6	57.6	57.6	56.4	54.1	51.7	49.4	47.0	43.3	39.6
97.5°	61.5	61.2	60.9	60.7	59.3	56.6	53.9	51.2	48.5	65.7	82.9
100°	63.0	62.7	62.4	62.2	60.9	58.2	55.5	52.8	50.1	102.7	155.3
102.5°	63.9	63.2	62.5	62.2	67.8	78.9	90.0	101.2	112.3	170.9	229.6
105°	65.4	64.7	64.0	63.7	93.5	153.2	212.9	272.5	332.2	362.6	392.9
107.5°	246.1	290.3	334.4	356.5	382.5	434.4	486.3	538.2	590.1	585.1	580.0
110°	513.6	561.8	610.0	634.1	639.7	650.8	661.9	673.1	684.2	680.5	676.8

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	791.7	792.4	793.1	793.4	791.9	788.8	785.8	782.7	779.7	776.0	772.3
115°	889.3	887.9	886.6	885.9	884.2	880.9	877.5	874.2	870.8	867.8	864.7
117.5°	973.2	972.9	972.6	972.4	971.1	968.4	965.7	963.0	960.3	958.6	956.9
120°	1058.9	1058.9	1058.9	1058.9	1057.5	1054.8	1052.1	1049.4	1046.7	1045.7	1044.7
122.5°	1141.6	1141.3	1141.0	1140.8	1140.0	1138.3	1136.6	1134.9	1133.2	1131.8	1130.5
125°	1218.3	1217.6	1216.9	1216.6	1216.3	1215.6	1214.9	1214.3	1213.6	1212.2	1210.9
127.5°	1296.9	1297.6	1298.3	1298.6	1298.1	1297.1	1296.0	1295.0	1294.0	1292.3	1290.6
130°	1369.7	1370.4	1371.1	1371.4	1370.7	1369.4	1368.0	1366.7	1365.3	1363.9	1362.6
132.5°	1437.1	1438.1	1439.1	1439.6	1438.9	1437.6	1436.3	1434.9	1433.6	1432.6	1431.6
135°	1505.4	1506.4	1507.4	1507.9	1507.4	1506.4	1505.4	1504.4	1503.4	1502.0	1500.7
137.5°	1569.9	1570.6	1571.3	1571.6	1570.8	1569.1	1567.4	1565.7	1564.0	1563.3	1562.7
140°	1627.6	1628.3	1629.0	1629.3	1628.6	1627.3	1625.9	1624.6	1623.2	1622.2	1621.2
142.5°	1681.3	1682.4	1683.4	1683.9	1683.4	1682.4	1681.3	1680.3	1679.3	1678.3	1677.3
145°	1734.0	1734.0	1734.0	1734.0	1733.7	1733.0	1732.3	1731.6	1730.9	1730.2	1729.6
147.5°	1776.8	1778.5	1780.2	1781.0	1780.7	1780.0	1779.3	1778.6	1777.9	1777.2	1776.6
150°	1820.9	1822.0	1823.0	1823.5	1823.2	1822.5	1821.8	1821.1	1820.4	1819.7	1819.1
152.5°	1858.7	1860.4	1862.1	1862.9	1862.2	1860.9	1859.5	1858.2	1856.8	1856.5	1856.1
155°	1892.7	1894.8	1896.8	1897.8	1897.0	1895.3	1893.6	1891.9	1890.2	1889.9	1889.5
157.5°	1922.9	1925.6	1928.3	1929.6	1928.6	1926.6	1924.5	1922.5	1920.5	1920.9	1921.2
160°	1949.5	1951.9	1954.2	1955.4	1954.4	1952.4	1950.3	1948.3	1946.3	1946.7	1947.0
162.5°	1974.6	1976.7	1978.7	1979.7	1978.5	1976.2	1973.8	1971.5	1969.1	1969.4	1969.8
165°	1995.0	1997.4	1999.7	2000.9	1999.6	1996.9	1994.2	1991.5	1988.8	1989.1	1989.5
167.5°	2010.9	2013.6	2016.3	2017.6	2016.3	2013.6	2010.9	2008.2	2005.5	2005.5	2005.5
170°	2024.6	2027.3	2030.0	2031.3	2030.0	2027.3	2024.6	2021.9	2019.2	2019.2	2019.2
172.5°	2032.8	2035.8	2038.9	2040.4	2039.1	2036.4	2033.7	2031.0	2028.3	2027.9	2027.6
175°	2039.7	2042.4	2045.1	2046.5	2045.3	2042.9	2040.6	2038.2	2035.8	2035.5	2035.1
177.5°	2042.6	2045.9	2049.3	2051.0	2049.7	2047.0	2044.3	2041.6	2038.9	2038.6	2038.2
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	548.3	546.0	543.8	543.8	538.8	534.2	532.0	532.9	530.2	526.5	522.9
5°	572.3	563.3	561.5	556.5	549.7	540.1	535.1	530.6	525.2	517.9	511.1
7.5°	594.6	582.8	576.4	571.4	558.3	545.1	534.2	527.0	517.5	506.6	498.4
10°	623.6	601.8	595.0	583.7	565.1	546.5	533.8	522.0	508.8	496.1	485.3
12.5°	646.7	621.8	609.1	597.7	573.7	550.1	528.8	514.3	498.4	484.4	470.3
15°	673.0	644.9	622.7	609.1	578.7	550.1	526.1	505.7	488.0	470.7	458.5
17.5°	685.7	650.3	640.4	620.9	576.9	548.3	518.8	497.1	475.7	455.8	441.3
20°	705.7	664.4	639.5	626.3	587.3	545.1	510.7	485.7	463.5	442.2	426.8
22.5°	707.0	662.1	645.8	620.9	572.8	535.6	503.4	473.0	447.2	427.2	411.3
25°	703.9	658.1	635.4	615.4	575.5	530.2	488.9	459.0	433.6	410.4	391.8
27.5°	702.5	646.3	624.9	605.0	560.1	514.3	480.3	446.3	417.2	396.8	377.8
30°	700.7	633.6	607.7	584.6	543.3	502.0	461.2	431.7	404.1	378.2	359.2
32.5°	688.9	616.3	590.0	565.5	521.1	479.8	447.6	416.3	386.4	362.4	345.1
35°	685.3	600.5	566.0	539.7	496.1	459.4	425.4	399.5	371.4	347.4	327.0
37.5°	674.8	584.1	546.9	513.4	468.0	433.1	408.2	382.3	355.1	329.3	312.9
40°	656.7	565.1	522.9	488.4	441.7	406.4	383.2	364.2	337.4	314.3	294.3
42.5°	629.9	545.6	500.2	463.9	412.2	379.1	360.1	342.0	319.3	295.2	278.9
45°	599.1	519.7	477.6	437.2	384.6	352.4	332.4	321.5	300.7	280.3	261.2
47.5°	556.9	493.0	451.2	409.5	356.0	324.7	308.8	298.0	283.4	261.2	245.8
50°	503.9	458.5	419.0	381.9	327.9	298.0	282.1	273.9	261.7	245.8	230.8
52.5°	444.9	418.6	385.9	351.5	299.3	271.2	256.7	250.3	241.3	226.3	213.6
55°	385.5	374.2	351.9	317.9	269.4	246.3	233.6	225.4	218.6	207.7	196.8
57.5°	332.4	327.0	311.6	285.3	244.4	220.4	209.5	204.1	198.6	190.5	179.6
60°	277.6	283.4	267.6	254.4	217.2	196.4	186.8	181.0	178.2	171.0	164.2
62.5°	229.9	235.4	226.3	216.3	190.0	171.4	165.5	160.1	158.3	151.9	145.1
65°	186.8	193.7	186.8	181.4	165.5	150.1	142.9	140.1	138.3	134.2	128.8
67.5°	148.8	155.6	152.4	145.6	140.6	127.9	123.8	121.1	120.2	117.0	112.5
70°	112.0	121.5	122.4	118.4	113.8	107.9	105.2	104.3	102.0	99.3	96.6
72.5°	80.7	91.6	92.1	92.1	89.3	89.3	86.6	85.3	85.3	82.5	79.4
75°	59.4	66.7	67.6	68.5	69.8	71.2	69.4	69.4	68.9	66.2	64.9
77.5°	39.5	45.8	48.1	51.2	53.1	53.1	54.0	54.9	54.0	52.6	51.7
80°	25.4	29.9	32.7	34.5	37.2	38.5	39.9	40.4	39.5	39.0	37.6
82.5°	16.8	18.1	19.5	21.8	24.9	27.2	27.2	26.8	27.7	27.2	26.8
85°	9.5	10.4	10.9	11.3	13.2	15.4	15.9	16.3	17.2	16.3	15.4
87.5°	3.6	4.1	4.1	4.1	5.0	5.4	6.8	8.6	8.2	7.3	7.3
90°	23.3	18.9	16.7	15.0	11.6	8.3	4.9	1.5	4.9	8.3	11.6
92.5°	30.3	27.3	25.8	26.8	28.8	30.9	32.9	34.9	32.9	30.9	28.8
95°	35.9	32.2	30.3	37.2	51.0	64.9	78.7	92.5	78.7	64.9	51.0
97.5°	100.1	117.3	125.9	130.6	140.1	149.5	159.0	168.4	159.0	149.5	140.1
100°	207.8	260.4	286.7	283.3	276.6	269.9	263.1	256.4	263.1	269.9	276.6
102.5°	288.2	346.9	376.2	374.0	369.6	365.3	360.9	356.5	360.9	365.3	369.6
105°	423.3	453.6	468.8	466.9	463.2	459.5	455.8	452.1	455.8	459.5	463.2
107.5°	575.0	569.9	567.4	565.9	562.8	559.8	556.7	553.7	556.7	559.8	562.8
110°	673.1	669.4	667.5	666.2	663.5	660.8	658.1	655.4	658.1	660.8	663.5

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	768.6	764.9	763.1	761.9	759.5	757.2	754.8	752.4	754.8	757.2	759.5
115°	861.7	858.6	857.1	856.1	854.1	852.0	850.0	848.0	850.0	852.0	854.1
117.5°	955.2	953.5	952.7	951.5	949.2	946.8	944.5	942.1	944.5	946.8	949.2
120°	1043.7	1042.7	1042.2	1040.7	1037.6	1034.6	1031.5	1028.5	1031.5	1034.6	1037.6
122.5°	1129.1	1127.8	1127.1	1125.9	1123.6	1121.2	1118.9	1116.5	1118.9	1121.2	1123.6
125°	1209.5	1208.2	1207.5	1206.2	1203.5	1200.8	1198.1	1195.4	1198.1	1200.8	1203.5
127.5°	1288.9	1287.2	1286.4	1285.1	1282.4	1279.7	1277.0	1274.3	1277.0	1279.7	1282.4
130°	1361.2	1359.9	1359.2	1357.9	1355.2	1352.5	1349.8	1347.1	1349.8	1352.5	1355.2
132.5°	1430.5	1429.5	1429.0	1427.7	1425.0	1422.3	1419.6	1416.9	1419.6	1422.3	1425.0
135°	1499.3	1498.0	1497.3	1496.3	1494.3	1492.2	1490.2	1488.2	1490.2	1492.2	1494.3
137.5°	1562.0	1561.3	1561.0	1559.7	1557.0	1554.3	1551.6	1548.9	1551.6	1554.3	1557.0
140°	1620.2	1619.2	1618.7	1617.7	1615.7	1613.6	1611.6	1609.6	1611.6	1613.6	1615.7
142.5°	1676.3	1675.3	1674.8	1673.8	1671.8	1669.7	1667.7	1665.7	1667.7	1669.7	1671.8
145°	1728.9	1728.2	1727.9	1726.7	1724.4	1722.0	1719.7	1717.3	1719.7	1722.0	1724.4
147.5°	1775.9	1775.2	1774.9	1774.1	1772.4	1770.7	1769.0	1767.3	1769.0	1770.7	1772.4
150°	1818.4	1817.7	1817.4	1816.9	1815.9	1814.8	1813.8	1812.8	1813.8	1814.8	1815.9
152.5°	1855.8	1855.5	1855.3	1855.1	1854.8	1854.5	1854.1	1853.8	1854.1	1854.5	1854.8
155°	1889.2	1888.9	1888.7	1889.0	1889.7	1890.4	1891.0	1891.7	1891.0	1890.4	1889.7
157.5°	1921.6	1921.9	1922.1	1922.1	1922.1	1922.1	1922.1	1922.1	1922.1	1922.1	1922.1
160°	1947.4	1947.7	1947.9	1948.1	1948.4	1948.7	1949.1	1949.4	1949.1	1948.7	1948.4
162.5°	1970.1	1970.4	1970.6	1971.1	1972.1	1973.2	1974.2	1975.2	1974.2	1973.2	1972.1
165°	1989.8	1990.1	1990.3	1990.8	1991.8	1992.9	1993.9	1994.9	1993.9	1992.9	1991.8
167.5°	2005.5	2005.5	2005.5	2006.2	2007.5	2008.9	2010.2	2011.6	2010.2	2008.9	2007.5
170°	2019.2	2019.2	2019.2	2019.9	2021.2	2022.5	2023.9	2025.2	2023.9	2022.5	2021.2
172.5°	2027.2	2026.9	2026.7	2027.5	2029.2	2030.9	2032.6	2034.3	2032.6	2030.9	2029.2
175°	2034.8	2034.5	2034.3	2035.1	2036.8	2038.5	2040.2	2041.9	2040.2	2038.5	2036.8
177.5°	2037.9	2037.6	2037.4	2038.2	2039.9	2041.6	2043.2	2044.9	2043.2	2041.6	2039.9
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	522.9	520.6	519.7	517.5	512.0	508.4	504.3	501.6	502.0	499.8	501.1
5°	506.6	506.1	502.9	498.4	490.7	486.6	479.4	475.7	473.9	474.4	471.7
7.5°	493.0	488.9	486.6	479.4	472.1	463.5	457.6	454.4	451.7	449.0	447.2
10°	477.6	473.9	470.3	462.6	452.6	444.4	436.3	433.1	429.0	427.2	425.9
12.5°	461.2	459.0	454.4	445.4	434.0	426.3	416.8	415.0	409.5	405.9	405.0
15°	446.3	444.9	436.7	426.3	415.0	407.3	399.1	393.7	384.6	386.4	383.2
17.5°	430.4	424.5	419.5	405.4	400.0	388.2	378.7	376.0	369.6	365.5	361.5
20°	412.7	409.1	402.7	393.7	380.5	366.9	359.6	355.1	351.5	345.1	343.3
22.5°	395.9	391.4	385.9	374.2	362.8	351.5	341.5	337.4	332.9	328.3	325.6
25°	382.8	376.0	370.1	355.6	344.2	334.7	328.3	321.5	315.2	312.5	311.6
27.5°	362.4	358.3	352.4	338.8	328.3	317.9	312.0	307.5	300.7	297.5	294.8
30°	349.2	341.0	334.2	323.4	312.9	301.6	296.1	290.7	286.6	282.5	279.4
32.5°	331.5	325.2	319.7	308.8	298.4	288.0	282.1	273.9	271.7	268.5	264.9
35°	314.3	310.2	304.3	292.5	281.2	273.9	267.6	259.9	257.1	254.9	251.7
37.5°	298.0	292.1	288.0	276.6	266.7	258.1	253.1	246.7	244.9	242.2	239.9
40°	283.9	278.0	273.9	262.6	252.2	243.1	239.9	233.6	230.8	227.7	226.3
42.5°	268.0	263.0	257.6	249.4	238.5	229.5	223.1	219.5	215.9	214.5	211.8
45°	251.2	246.7	242.6	233.6	222.2	215.9	210.4	205.4	202.7	200.5	198.6
47.5°	236.7	232.7	227.2	217.2	208.2	202.3	196.8	191.8	189.1	186.4	184.1
50°	220.0	217.7	211.8	202.3	193.7	186.8	181.9	177.3	175.5	172.3	168.7
52.5°	205.0	200.9	195.9	188.2	180.5	172.3	165.5	162.8	159.6	157.8	154.6
55°	187.3	184.6	179.1	172.3	164.2	157.4	152.4	148.8	144.7	142.9	138.8
57.5°	172.3	167.3	164.6	156.0	148.3	141.5	137.9	134.2	129.7	127.0	125.2
60°	156.0	151.5	147.4	140.1	134.7	127.4	122.0	118.8	115.6	112.0	110.2
62.5°	140.1	136.5	131.5	125.6	118.8	112.9	108.8	104.3	102.5	98.9	97.5
65°	122.9	120.2	116.1	109.3	103.9	98.9	94.8	91.2	89.3	88.0	87.1
67.5°	107.5	103.9	101.1	95.2	89.3	85.3	83.0	80.7	78.5	77.1	75.7
70°	91.6	88.9	86.2	80.7	76.6	73.0	71.2	69.4	68.0	66.7	65.3
72.5°	75.3	73.9	71.2	67.6	64.4	61.7	60.3	58.1	56.7	54.4	53.5
75°	62.1	59.9	58.5	55.3	52.6	50.3	48.5	45.8	44.0	43.1	42.6
77.5°	49.0	48.1	46.3	43.5	42.2	39.9	37.2	36.3	35.4	35.4	34.9
80°	36.7	35.4	34.0	31.7	30.4	28.6	28.6	28.6	28.1	28.6	28.1
82.5°	24.9	24.0	23.1	21.8	21.3	21.3	21.8	21.8	21.8	21.8	21.8
85°	14.5	14.5	14.5	15.0	14.5	14.5	15.0	15.4	15.0	15.0	14.5
87.5°	6.8	6.8	7.3	7.3	7.7	7.7	7.7	7.7	7.7	7.7	8.2
90°	15.0	16.7	18.9	23.3	27.6	32.0	36.4	37.8	39.1	40.5	41.8
92.5°	26.8	25.8	27.3	30.3	33.4	36.4	39.4	41.8	44.2	46.5	48.9
95°	37.2	30.3	32.2	35.9	39.6	43.3	47.0	49.4	51.7	54.1	56.4
97.5°	130.6	125.9	117.3	100.1	82.9	65.7	48.5	51.2	53.9	56.6	59.3
100°	283.3	286.7	260.4	207.8	155.3	102.7	50.1	52.8	55.5	58.2	60.9
102.5°	374.0	376.2	346.9	288.2	229.6	170.9	112.3	101.2	90.0	78.9	67.8
105°	466.9	468.8	453.6	423.3	392.9	362.6	332.2	272.5	212.9	153.2	93.5
107.5°	565.9	567.4	569.9	575.0	580.0	585.1	590.1	538.2	486.3	434.4	382.5
110°	666.2	667.5	669.4	673.1	676.8	680.5	684.2	673.1	661.9	650.8	639.7

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	761.9	763.1	764.9	768.6	772.3	776.0	779.7	782.7	785.8	788.8	791.9
115°	856.1	857.1	858.6	861.7	864.7	867.8	870.8	874.2	877.5	880.9	884.2
117.5°	951.5	952.7	953.5	955.2	956.9	958.6	960.3	963.0	965.7	968.4	971.1
120°	1040.7	1042.2	1042.7	1043.7	1044.7	1045.7	1046.7	1049.4	1052.1	1054.8	1057.5
122.5°	1125.9	1127.1	1127.8	1129.1	1130.5	1131.8	1133.2	1134.9	1136.6	1138.3	1140.0
125°	1206.2	1207.5	1208.2	1209.5	1210.9	1212.2	1213.6	1214.3	1214.9	1215.6	1216.3
127.5°	1285.1	1286.4	1287.2	1288.9	1290.6	1292.3	1294.0	1295.0	1296.0	1297.1	1298.1
130°	1357.9	1359.2	1359.9	1361.2	1362.6	1363.9	1365.3	1366.7	1368.0	1369.4	1370.7
132.5°	1427.7	1429.0	1429.5	1430.5	1431.6	1432.6	1433.6	1434.9	1436.3	1437.6	1438.9
135°	1496.3	1497.3	1498.0	1499.3	1500.7	1502.0	1503.4	1504.4	1505.4	1506.4	1507.4
137.5°	1559.7	1561.0	1561.3	1562.0	1562.7	1563.3	1564.0	1565.7	1567.4	1569.1	1570.8
140°	1617.7	1618.7	1619.2	1620.2	1621.2	1622.2	1623.2	1624.6	1625.9	1627.3	1628.6
142.5°	1673.8	1674.8	1675.3	1676.3	1677.3	1678.3	1679.3	1680.3	1681.3	1682.4	1683.4
145°	1726.7	1727.9	1728.2	1728.9	1729.6	1730.2	1730.9	1731.6	1732.3	1733.0	1733.7
147.5°	1774.1	1774.9	1775.2	1775.9	1776.6	1777.2	1777.9	1778.6	1779.3	1780.0	1780.7
150°	1816.9	1817.4	1817.7	1818.4	1819.1	1819.7	1820.4	1821.1	1821.8	1822.5	1823.2
152.5°	1855.1	1855.3	1855.5	1855.8	1856.1	1856.5	1856.8	1858.2	1859.5	1860.9	1862.2
155°	1889.0	1888.7	1888.9	1889.2	1889.5	1889.9	1890.2	1891.9	1893.6	1895.3	1897.0
157.5°	1922.1	1922.1	1921.9	1921.6	1921.2	1920.9	1920.5	1922.5	1924.5	1926.6	1928.6
160°	1948.1	1947.9	1947.7	1947.4	1947.0	1946.7	1946.3	1948.3	1950.3	1952.4	1954.4
162.5°	1971.1	1970.6	1970.4	1970.1	1969.8	1969.4	1969.1	1971.5	1973.8	1976.2	1978.5
165°	1990.8	1990.3	1990.1	1989.8	1989.5	1989.1	1988.8	1991.5	1994.2	1996.9	1999.6
167.5°	2006.2	2005.5	2005.5	2005.5	2005.5	2005.5	2005.5	2008.2	2010.9	2013.6	2016.3
170°	2019.9	2019.2	2019.2	2019.2	2019.2	2019.2	2019.2	2021.9	2024.6	2027.3	2030.0
172.5°	2027.5	2026.7	2026.9	2027.2	2027.6	2027.9	2028.3	2031.0	2033.7	2036.4	2039.1
175°	2035.1	2034.3	2034.5	2034.8	2035.1	2035.5	2035.8	2038.2	2040.6	2042.9	2045.3
177.5°	2038.2	2037.4	2037.6	2037.9	2038.2	2038.6	2038.9	2041.6	2044.3	2047.0	2049.7
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	500.7	501.1	499.8	497.1	496.6	497.5	500.2	499.3	497.1	501.1	497.5
5°	473.0	470.7	469.8	470.7	468.0	466.7	469.4	468.0	469.4	469.8	471.2
7.5°	446.3	446.7	444.0	444.4	440.8	441.7	441.7	441.7	443.1	444.0	445.8
10°	423.1	424.0	420.9	421.3	418.6	416.8	418.1	420.9	420.9	420.9	421.8
12.5°	404.5	400.5	398.2	397.7	394.6	393.7	396.4	397.3	399.5	399.5	400.9
15°	381.4	380.5	378.7	378.7	371.0	372.8	373.7	376.9	381.4	377.8	378.7
17.5°	360.5	358.3	356.0	355.1	354.2	351.5	355.1	354.6	357.4	357.8	359.2
20°	342.0	340.1	335.6	336.1	337.0	332.9	335.1	335.1	337.9	340.6	343.8
22.5°	323.8	322.0	319.7	320.6	317.9	317.0	317.0	319.3	322.5	324.7	324.3
25°	309.8	306.6	305.2	303.9	302.5	303.4	302.0	304.3	306.6	307.9	306.6
27.5°	293.9	292.5	289.8	288.4	286.2	287.1	288.0	289.8	291.2	291.2	292.5
30°	278.5	276.6	275.7	274.4	274.4	272.6	273.0	274.8	276.2	277.6	279.4
32.5°	263.5	262.1	260.8	260.8	259.9	259.4	259.0	261.7	261.7	264.4	264.4
35°	251.2	249.0	249.0	246.7	247.6	247.2	246.3	248.1	248.5	250.3	249.9
37.5°	237.6	237.6	236.7	234.5	232.7	233.1	235.4	235.4	236.7	236.3	237.6
40°	224.0	223.1	223.1	221.8	221.3	220.9	221.3	221.8	224.0	223.6	224.0
42.5°	210.4	210.9	208.6	208.6	208.6	207.3	207.7	208.2	209.1	210.0	211.3
45°	197.3	196.4	195.9	195.0	194.1	194.6	194.1	195.9	195.5	196.4	197.7
47.5°	183.2	181.9	181.4	179.6	179.6	180.5	180.0	181.4	181.9	183.2	182.3
50°	169.6	167.8	166.4	166.9	164.2	165.1	165.1	166.4	167.8	168.3	169.2
52.5°	153.7	153.3	152.8	150.6	150.1	149.7	150.1	150.6	152.4	153.7	154.2
55°	138.3	137.9	135.1	134.2	132.9	132.9	133.8	134.2	137.4	137.9	139.7
57.5°	124.3	122.9	119.7	119.3	119.3	119.3	117.9	119.7	120.6	122.9	122.9
60°	108.8	108.8	106.1	106.1	106.6	106.1	106.1	106.6	106.6	108.4	109.3
62.5°	96.6	96.1	96.1	95.2	94.8	95.2	94.8	94.8	95.2	96.6	98.0
65°	85.7	85.3	84.8	84.4	83.4	83.4	83.9	84.8	84.8	85.7	86.2
67.5°	75.3	75.3	74.4	74.4	73.9	73.5	73.9	73.5	75.3	75.3	75.7
70°	64.9	64.4	63.0	62.6	61.2	61.7	61.7	63.0	63.5	64.4	65.3
72.5°	52.2	52.2	51.2	50.3	50.8	49.9	49.9	50.3	50.3	51.7	52.2
75°	43.1	42.2	41.7	42.2	41.7	42.6	41.7	41.7	42.6	42.6	42.6
77.5°	35.4	35.4	34.9	34.9	35.4	34.9	35.4	35.4	35.4	34.9	35.4
80°	29.0	28.6	28.6	28.6	28.1	28.1	28.1	28.1	28.1	28.1	28.1
82.5°	21.8	21.8	21.3	21.8	21.8	21.3	21.8	21.3	21.3	21.8	21.8
85°	14.5	15.4	14.5	14.5	15.0	15.0	15.4	15.0	15.4	14.5	15.0
87.5°	7.7	8.2	8.2	7.7	7.7	8.2	8.2	8.2	8.6	7.7	8.2
90°	42.5	42.8	43.5	44.2	44.8	45.5	44.8	44.2	43.5	42.8	42.5
92.5°	50.1	50.3	50.6	50.9	51.3	51.6	51.3	50.9	50.6	50.3	50.1
95°	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6	57.6
97.5°	60.7	60.9	61.2	61.5	61.9	62.2	61.9	61.5	61.2	60.9	60.7
100°	62.2	62.4	62.7	63.0	63.4	63.7	63.4	63.0	62.7	62.4	62.2
102.5°	62.2	62.5	63.2	63.9	64.5	65.2	64.5	63.9	63.2	62.5	62.2
105°	63.7	64.0	64.7	65.4	66.0	66.7	66.0	65.4	64.7	64.0	63.7
107.5°	356.5	334.4	290.3	246.1	202.0	157.8	202.0	246.1	290.3	334.4	356.5
110°	634.1	610.0	561.8	513.6	465.4	417.2	465.4	513.6	561.8	610.0	634.1

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	793.4	793.1	792.4	791.7	791.1	790.4	791.1	791.7	792.4	793.1	793.4
115°	885.9	886.6	887.9	889.3	890.6	892.0	890.6	889.3	887.9	886.6	885.9
117.5°	972.4	972.6	972.9	973.2	973.6	973.9	973.6	973.2	972.9	972.6	972.4
120°	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9	1058.9
122.5°	1140.8	1141.0	1141.3	1141.6	1142.0	1142.3	1142.0	1141.6	1141.3	1141.0	1140.8
125°	1216.6	1216.9	1217.6	1218.3	1219.0	1219.7	1219.0	1218.3	1217.6	1216.9	1216.6
127.5°	1298.6	1298.3	1297.6	1296.9	1296.2	1295.5	1296.2	1296.9	1297.6	1298.3	1298.6
130°	1371.4	1371.1	1370.4	1369.7	1369.0	1368.3	1369.0	1369.7	1370.4	1371.1	1371.4
132.5°	1439.6	1439.1	1438.1	1437.1	1436.1	1435.1	1436.1	1437.1	1438.1	1439.1	1439.6
135°	1507.9	1507.4	1506.4	1505.4	1504.4	1503.4	1504.4	1505.4	1506.4	1507.4	1507.9
137.5°	1571.6	1571.3	1570.6	1569.9	1569.3	1568.6	1569.3	1569.9	1570.6	1571.3	1571.6
140°	1629.3	1629.0	1628.3	1627.6	1626.9	1626.2	1626.9	1627.6	1628.3	1629.0	1629.3
142.5°	1683.9	1683.4	1682.4	1681.3	1680.3	1679.3	1680.3	1681.3	1682.4	1683.4	1683.9
145°	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0	1734.0
147.5°	1781.0	1780.2	1778.5	1776.8	1775.1	1773.4	1775.1	1776.8	1778.5	1780.2	1781.0
150°	1823.5	1823.0	1822.0	1820.9	1819.9	1818.9	1819.9	1820.9	1822.0	1823.0	1823.5
152.5°	1862.9	1862.1	1860.4	1858.7	1857.0	1855.3	1857.0	1858.7	1860.4	1862.1	1862.9
155°	1897.8	1896.8	1894.8	1892.7	1890.7	1888.7	1890.7	1892.7	1894.8	1896.8	1897.8
157.5°	1929.6	1928.3	1925.6	1922.9	1920.2	1917.5	1920.2	1922.9	1925.6	1928.3	1929.6
160°	1955.4	1954.2	1951.9	1949.5	1947.2	1944.8	1947.2	1949.5	1951.9	1954.2	1955.4
162.5°	1979.7	1978.7	1976.7	1974.6	1972.6	1970.6	1972.6	1974.6	1976.7	1978.7	1979.7
165°	2000.9	1999.7	1997.4	1995.0	1992.7	1990.3	1992.7	1995.0	1997.4	1999.7	2000.9
167.5°	2017.6	2016.3	2013.6	2010.9	2008.2	2005.5	2008.2	2010.9	2013.6	2016.3	2017.6
170°	2031.3	2030.0	2027.3	2024.6	2021.9	2019.2	2021.9	2024.6	2027.3	2030.0	2031.3
172.5°	2040.4	2038.9	2035.8	2032.8	2029.7	2026.7	2029.7	2032.8	2035.8	2038.9	2040.4
175°	2046.5	2045.1	2042.4	2039.7	2037.0	2034.3	2037.0	2039.7	2042.4	2045.1	2046.5
177.5°	2051.0	2049.3	2045.9	2042.6	2039.2	2035.8	2039.2	2042.6	2045.9	2049.3	2051.0
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7	529.7
2.5°	501.1	502.9	501.1	497.5	501.1	503.4	505.7	509.3	511.1	511.1	513.8
5°	472.6	476.2	474.8	473.9	477.6	479.8	483.4	488.0	493.0	496.1	499.8
7.5°	447.2	449.4	451.7	451.7	455.3	460.3	465.8	471.2	477.6	482.1	484.8
10°	424.9	426.8	428.1	429.9	435.4	440.8	448.1	454.9	460.3	465.3	469.8
12.5°	403.6	406.4	409.5	410.9	415.0	421.8	428.6	436.7	445.4	450.3	454.9
15°	383.2	384.6	388.2	392.3	395.9	403.2	411.8	420.4	427.7	435.4	439.5
17.5°	362.4	362.8	372.3	370.1	381.9	388.7	393.2	401.4	413.2	419.5	425.9
20°	342.0	346.5	350.6	352.8	359.2	366.9	380.0	386.4	395.9	401.8	407.3
22.5°	326.1	332.9	332.9	338.3	341.5	348.8	358.3	370.5	381.0	385.0	392.7
25°	312.0	315.2	320.6	322.5	328.3	334.7	341.0	354.2	365.5	371.0	376.4
27.5°	293.9	298.0	305.2	305.2	312.9	319.7	327.4	336.1	347.4	355.1	361.0
30°	279.8	283.9	287.1	292.1	295.2	301.6	315.2	321.5	331.5	338.3	345.6
32.5°	266.7	269.8	272.6	278.0	281.6	288.9	296.1	307.5	316.1	322.5	330.2
35°	252.2	255.3	259.0	263.0	268.5	275.3	282.1	291.6	300.2	306.1	312.5
37.5°	238.5	240.8	246.3	249.0	253.5	259.9	268.5	278.5	286.2	290.7	297.1
40°	225.4	227.2	231.3	236.3	239.5	244.4	253.5	262.1	271.7	277.1	282.1
42.5°	211.3	213.6	217.2	222.2	227.2	232.7	237.6	247.6	256.2	260.8	266.2
45°	199.1	200.5	203.2	208.2	213.2	217.2	224.9	234.0	242.2	245.8	251.7
47.5°	184.6	185.9	190.0	192.3	197.7	203.2	210.9	220.0	227.2	230.8	236.3
50°	169.6	171.0	173.7	178.7	182.3	188.2	195.0	202.7	211.8	216.8	220.0
52.5°	155.1	157.8	160.1	164.2	168.7	174.6	181.0	188.2	195.9	200.9	204.5
55°	140.6	142.9	145.6	147.8	153.3	158.7	166.0	172.8	179.6	184.1	188.2
57.5°	124.3	127.4	130.2	134.7	138.8	143.3	151.5	156.9	165.1	168.3	171.9
60°	110.2	113.4	115.6	119.3	122.9	128.8	134.2	141.0	147.8	151.9	156.5
62.5°	98.4	99.8	101.1	104.8	108.4	113.8	119.3	126.1	133.3	135.6	139.2
65°	86.6	88.0	90.2	93.4	96.1	99.3	105.2	110.7	117.5	121.1	122.4
67.5°	76.6	78.0	78.5	80.7	83.0	86.6	89.8	95.2	101.6	103.9	106.6
70°	65.3	67.6	68.0	69.8	70.7	73.0	76.6	80.7	85.7	89.8	92.1
72.5°	52.2	55.3	56.2	59.0	60.3	62.6	65.3	68.5	71.7	73.5	75.3
75°	42.6	43.5	44.0	46.3	48.5	51.7	53.1	54.9	57.6	59.9	61.7
77.5°	35.4	35.8	36.3	36.3	36.7	38.5	41.3	43.5	45.4	46.3	47.6
80°	28.6	28.1	28.1	28.6	28.6	28.6	29.5	32.7	33.6	35.8	35.4
82.5°	22.2	21.3	21.8	21.3	21.3	21.3	21.3	21.8	21.8	23.1	24.0
85°	14.5	15.0	14.5	14.5	14.1	14.5	14.1	14.1	13.6	13.6	13.2
87.5°	7.7	8.2	7.7	7.7	7.3	7.7	7.3	7.3	6.8	6.8	5.9
90°	41.8	40.5	39.1	37.8	36.4	32.0	27.6	23.3	18.9	16.7	15.0
92.5°	48.9	46.5	44.2	41.8	39.4	36.4	33.4	30.3	27.3	25.8	26.8
95°	56.4	54.1	51.7	49.4	47.0	43.3	39.6	35.9	32.2	30.3	37.2
97.5°	59.3	56.6	53.9	51.2	48.5	65.7	82.9	100.1	117.3	125.9	130.6
100°	60.9	58.2	55.5	52.8	50.1	102.7	155.3	207.8	260.4	286.7	283.3
102.5°	67.8	78.9	90.0	101.2	112.3	170.9	229.6	288.2	346.9	376.2	374.0
105°	93.5	153.2	212.9	272.5	332.2	362.6	392.9	423.3	453.6	468.8	466.9
107.5°	382.5	434.4	486.3	538.2	590.1	585.1	580.0	575.0	569.9	567.4	565.9
110°	639.7	650.8	661.9	673.1	684.2	680.5	676.8	673.1	669.4	667.5	666.2

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	791.9	788.8	785.8	782.7	779.7	776.0	772.3	768.6	764.9	763.1	761.9
115°	884.2	880.9	877.5	874.2	870.8	867.8	864.7	861.7	858.6	857.1	856.1
117.5°	971.1	968.4	965.7	963.0	960.3	958.6	956.9	955.2	953.5	952.7	951.5
120°	1057.5	1054.8	1052.1	1049.4	1046.7	1045.7	1044.7	1043.7	1042.7	1042.2	1040.7
122.5°	1140.0	1138.3	1136.6	1134.9	1133.2	1131.8	1130.5	1129.1	1127.8	1127.1	1125.9
125°	1216.3	1215.6	1214.9	1214.3	1213.6	1212.2	1210.9	1209.5	1208.2	1207.5	1206.2
127.5°	1298.1	1297.1	1296.0	1295.0	1294.0	1292.3	1290.6	1288.9	1287.2	1286.4	1285.1
130°	1370.7	1369.4	1368.0	1366.7	1365.3	1363.9	1362.6	1361.2	1359.9	1359.2	1357.9
132.5°	1438.9	1437.6	1436.3	1434.9	1433.6	1432.6	1431.6	1430.5	1429.5	1429.0	1427.7
135°	1507.4	1506.4	1505.4	1504.4	1503.4	1502.0	1500.7	1499.3	1498.0	1497.3	1496.3
137.5°	1570.8	1569.1	1567.4	1565.7	1564.0	1563.3	1562.7	1562.0	1561.3	1561.0	1559.7
140°	1628.6	1627.3	1625.9	1624.6	1623.2	1622.2	1621.2	1620.2	1619.2	1618.7	1617.7
142.5°	1683.4	1682.4	1681.3	1680.3	1679.3	1678.3	1677.3	1676.3	1675.3	1674.8	1673.8
145°	1733.7	1733.0	1732.3	1731.6	1730.9	1730.2	1729.6	1728.9	1728.2	1727.9	1726.7
147.5°	1780.7	1780.0	1779.3	1778.6	1777.9	1777.2	1776.6	1775.9	1775.2	1774.9	1774.1
150°	1823.2	1822.5	1821.8	1821.1	1820.4	1819.7	1819.1	1818.4	1817.7	1817.4	1816.9
152.5°	1862.2	1860.9	1859.5	1858.2	1856.8	1856.5	1856.1	1855.8	1855.5	1855.3	1855.1
155°	1897.0	1895.3	1893.6	1891.9	1890.2	1889.9	1889.5	1889.2	1888.9	1888.7	1889.0
157.5°	1928.6	1926.6	1924.5	1922.5	1920.5	1920.9	1921.2	1921.6	1921.9	1922.1	1922.1
160°	1954.4	1952.4	1950.3	1948.3	1946.3	1946.7	1947.0	1947.4	1947.7	1947.9	1948.1
162.5°	1978.5	1976.2	1973.8	1971.5	1969.1	1969.4	1969.8	1970.1	1970.4	1970.6	1971.1
165°	1999.6	1996.9	1994.2	1991.5	1988.8	1989.1	1989.5	1989.8	1990.1	1990.3	1990.8
167.5°	2016.3	2013.6	2010.9	2008.2	2005.5	2005.5	2005.5	2005.5	2005.5	2005.5	2006.2
170°	2030.0	2027.3	2024.6	2021.9	2019.2	2019.2	2019.2	2019.2	2019.2	2019.2	2019.9
172.5°	2039.1	2036.4	2033.7	2031.0	2028.3	2027.9	2027.6	2027.2	2026.9	2026.7	2027.5
175°	2045.3	2042.9	2040.6	2038.2	2035.8	2035.5	2035.1	2034.8	2034.5	2034.3	2035.1
177.5°	2049.7	2047.0	2044.3	2041.6	2038.9	2038.6	2038.2	2037.9	2037.6	2037.4	2038.2
180°	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9	2041.9

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	529.7	529.7	529.7	529.7
2.5°	516.1	519.3	525.6	531.1
5°	505.2	510.2	519.7	529.3
7.5°	492.1	499.8	512.0	525.2
10°	479.4	489.3	504.3	519.7
12.5°	466.7	477.1	493.0	512.9
15°	451.7	462.6	481.6	505.7
17.5°	438.6	453.1	470.3	494.3
20°	424.5	435.4	457.6	483.0
22.5°	406.8	424.9	445.8	472.6
25°	392.7	408.6	429.5	459.9
27.5°	375.5	394.1	419.5	446.3
30°	361.5	376.9	400.5	432.7
32.5°	345.1	363.3	387.8	419.5
35°	330.6	346.0	369.2	401.4
37.5°	313.4	330.2	356.0	384.6
40°	298.4	314.7	339.2	366.0
42.5°	280.3	297.5	322.0	344.7
45°	265.8	281.6	301.1	322.0
47.5°	248.1	264.9	283.9	298.4
50°	232.2	247.6	262.6	274.8
52.5°	215.0	229.0	242.6	251.7
55°	199.1	210.0	220.9	227.2
57.5°	180.5	190.9	200.0	203.6
60°	164.2	172.8	178.7	182.8
62.5°	146.9	153.3	157.8	160.1
65°	130.2	134.7	137.0	139.2
67.5°	112.9	117.0	118.4	121.1
70°	94.8	99.3	100.2	101.6
72.5°	81.2	81.2	83.0	84.8
75°	64.9	65.8	66.7	66.7
77.5°	50.8	50.8	51.7	52.2
80°	37.2	37.6	37.6	37.2
82.5°	25.4	26.3	25.4	24.9
85°	14.1	15.9	15.0	15.0
87.5°	5.9	5.9	6.8	5.9
90°	11.6	8.3	4.9	1.5
92.5°	28.8	30.9	32.9	34.9
95°	51.0	64.9	78.7	92.5
97.5°	140.1	149.5	159.0	168.4
100°	276.6	269.9	263.1	256.4
102.5°	369.6	365.3	360.9	356.5
105°	463.2	459.5	455.8	452.1
107.5°	562.8	559.8	556.7	553.7
110°	663.5	660.8	658.1	655.4

TEST NUMBER: P1031136

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-A_3000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	759.5	757.2	754.8	752.4
115°	854.1	852.0	850.0	848.0
117.5°	949.2	946.8	944.5	942.1
120°	1037.6	1034.6	1031.5	1028.5
122.5°	1123.6	1121.2	1118.9	1116.5
125°	1203.5	1200.8	1198.1	1195.4
127.5°	1282.4	1279.7	1277.0	1274.3
130°	1355.2	1352.5	1349.8	1347.1
132.5°	1425.0	1422.3	1419.6	1416.9
135°	1494.3	1492.2	1490.2	1488.2
137.5°	1557.0	1554.3	1551.6	1548.9
140°	1615.7	1613.6	1611.6	1609.6
142.5°	1671.8	1669.7	1667.7	1665.7
145°	1724.4	1722.0	1719.7	1717.3
147.5°	1772.4	1770.7	1769.0	1767.3
150°	1815.9	1814.8	1813.8	1812.8
152.5°	1854.8	1854.5	1854.1	1853.8
155°	1889.7	1890.4	1891.0	1891.7
157.5°	1922.1	1922.1	1922.1	1922.1
160°	1948.4	1948.7	1949.1	1949.4
162.5°	1972.1	1973.2	1974.2	1975.2
165°	1991.8	1992.9	1993.9	1994.9
167.5°	2007.5	2008.9	2010.2	2011.6
170°	2021.2	2022.5	2023.9	2025.2
172.5°	2029.2	2030.9	2032.6	2034.3
175°	2036.8	2038.5	2040.2	2041.9
177.5°	2039.9	2041.6	2043.2	2044.9
180°	2041.9	2041.9	2041.9	2041.9

(END OF REPORT)