

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031139

Luminaire Tested: S123RDIW-B340D1535UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031139
REPORT IS A COMBINATION OF REPORTS P994260 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1535UB2750-4F0-XX-W2A-F1_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6408.0 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031139

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031139

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	28	28	28
1	91	87	83	80	80	77	74	71	58	56	54	41	39	38	25	24	24
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20
3	76	67	60	54	66	59	53	49	45	41	38	32	29	27	19	18	17
4	69	59	52	46	61	52	46	41	40	36	32	28	26	23	17	16	15
5	63	52	45	39	56	47	40	35	36	31	28	25	22	20	16	14	13
6	58	47	39	34	51	42	35	30	32	27	24	23	20	18	14	13	11
7	54	42	35	29	47	38	31	27	29	24	21	21	18	15	13	11	10
8	50	38	31	26	44	34	28	23	26	22	18	19	16	14	12	10	9
9	46	35	28	23	41	31	25	21	24	19	16	17	14	12	11	9	8
10	43	32	25	20	38	28	22	18	22	18	15	16	13	11	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5789	5789	5789
5°	5798	5584	5569
10°	5752	5374	5268
15°	5678	5114	4939
20°	5580	4832	4571
25°	5479	4539	4222
30°	5349	4227	3810
35°	5216	3921	3434
40°	5091	3588	3019
45°	4929	3262	2647
50°	4752	2915	2260
55°	4568	2543	1906
60°	4393	2162	1548
65°	4165	1770	1208
70°	3878	1338	864
75°	3469	906	684
80°	2959	630	480
85°	2219	340	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4929 cd/sqm

TEST NUMBER: P1031139

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	0.8
10°-20°	140.6	2.2
20°-30°	202.5	3.2
30°-40°	228.0	3.6
40°-50°	218.1	3.4
50°-60°	178.6	2.8
60°-70°	120.4	1.9
70°-80°	60.4	0.9
80°-90°	19.7	0.3
90°-100°	120.6	1.9
100°-110°	364.9	5.7
110°-120°	621.2	9.7
120°-130°	817.2	12.8
130°-140°	918.6	14.3
140°-150°	903.0	14.1
150°-160°	760.3	11.9
160°-170°	506.1	7.9
170°-180°	177.2	2.8
0°-30°	393.7	6.1
0°-40°	621.7	9.7
0°-60°	1018.4	15.9
0°-90°	1219.0	19.0
90°-120°	1106.6	17.3
90°-150°	3745.4	58.4
90°-180°	5189.0	81.0
0°-180°	6408.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	538	538	538	538	538	
5°	538	536	530	534	533	51
15°	513	508	496	494	491	145
25°	467	456	436	427	422	215
35°	404	388	361	342	334	253
45°	332	312	279	254	243	256
55°	252	231	194	168	160	226
65°	172	148	114	93	88	171
75°	91	70	46	42	41	97
85°	23	14	12	11	11	25
90°	2	16	35	41	44	8
95°	87	97	109	115	115	96
105°	331	334	347	347	350	354
115°	625	630	627	628	627	619
125°	915	920	916	911	905	816
135°	1187	1196	1195	1189	1186	915
145°	1440	1443	1448	1446	1440	900
155°	1649	1649	1651	1656	1646	759
165°	1796	1792	1792	1801	1790	507
175°	1868	1862	1862	1871	1861	178
180°	1873	1873	1873	1873	1873	

TEST NUMBER: P1031139

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	537.8	537.8	537.8	537.8	537.8
2.5°	540.0	538.2	533.0	537.8	536.9
5°	537.8	535.6	530.4	534.3	533.4
7.5°	533.9	531.7	525.2	527.8	526.5
10°	528.6	525.6	517.7	518.2	516.0
12.5°	521.2	517.7	507.7	507.3	504.7
15°	512.9	508.1	495.9	493.8	490.7
17.5°	502.9	497.7	482.4	478.1	473.7
20°	491.6	484.6	468.0	462.3	457.1
22.5°	478.9	470.6	452.8	445.3	440.5
25°	466.7	455.8	435.7	426.6	421.8
27.5°	451.9	440.1	418.3	406.1	398.7
30°	436.6	423.5	399.1	384.3	377.3
32.5°	421.3	406.1	379.9	363.3	355.9
35°	403.9	388.2	361.2	342.4	334.5
37.5°	386.5	369.4	341.1	320.2	310.6
40°	369.9	350.7	319.7	297.0	287.0
42.5°	351.1	331.9	299.7	274.4	265.6
45°	331.9	312.3	278.7	253.9	243.4
47.5°	313.2	291.4	258.2	231.2	222.0
50°	292.2	271.7	236.4	209.4	199.3
52.5°	273.5	250.8	215.9	187.6	178.8
55°	252.1	230.7	193.7	168.4	159.6
57.5°	232.9	209.8	172.3	148.3	140.9
60°	212.9	188.9	152.7	129.1	121.7
62.5°	192.8	168.8	132.6	110.8	102.9
65°	172.3	148.3	114.3	92.9	88.1
67.5°	151.8	127.4	94.2	78.1	72.8
70°	131.7	108.2	77.6	62.4	57.6
72.5°	111.7	88.5	61.5	49.7	48.4
75°	91.2	70.2	46.2	41.9	41.0
77.5°	72.4	53.2	36.2	33.6	32.7
80°	54.5	36.6	27.5	26.2	25.3
82.5°	37.5	22.7	19.6	18.3	18.3
85°	23.1	13.5	12.2	11.3	11.3
87.5°	10.5	5.7	5.7	5.2	4.8
90°	1.5	16.2	35.3	41.2	44.1
92.5°	44.1	53.0	61.8	66.2	63.3
95°	86.8	97.1	108.9	114.7	114.7
97.5°	142.7	150.1	158.9	166.2	164.8
100°	200.1	208.9	216.3	220.7	223.6
102.5°	266.3	270.7	281.0	285.4	283.9
105°	331.0	333.9	347.2	347.2	350.1
107.5°	407.5	409.0	414.9	419.3	417.8
110°	478.1	481.1	484.0	489.9	486.9

TEST NUMBER: P1031139

CATALOG NUMBER: S123RDIW-B340D1535UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	551.7	553.1	553.1	560.5	560.5
115°	625.2	629.6	626.7	628.2	626.7
117.5°	700.3	701.7	698.8	698.8	694.4
120°	769.4	778.2	770.9	769.4	766.5
122.5°	841.5	847.4	844.4	840.0	835.6
125°	915.0	919.5	916.5	910.6	904.7
127.5°	982.7	991.5	988.6	979.8	973.9
130°	1050.4	1062.2	1057.7	1051.9	1041.6
132.5°	1118.1	1129.8	1126.9	1119.5	1112.2
135°	1187.2	1196.0	1194.6	1188.7	1185.7
137.5°	1250.5	1257.8	1262.2	1254.9	1250.5
140°	1316.7	1324.0	1325.5	1324.0	1313.7
142.5°	1377.0	1384.3	1387.3	1385.8	1378.4
145°	1440.2	1443.2	1447.6	1446.1	1440.2
147.5°	1494.7	1500.6	1505.0	1505.0	1496.1
150°	1552.0	1555.0	1557.9	1557.9	1549.1
152.5°	1599.1	1603.5	1605.0	1607.9	1600.6
155°	1649.1	1649.1	1650.6	1656.5	1646.2
157.5°	1691.8	1690.3	1691.8	1697.7	1688.9
160°	1731.5	1728.6	1728.6	1735.9	1730.0
162.5°	1766.8	1762.4	1763.9	1771.2	1760.9
165°	1796.2	1791.8	1791.8	1800.7	1790.4
167.5°	1821.3	1815.4	1816.8	1825.7	1816.8
170°	1841.9	1836.0	1836.0	1846.3	1836.0
172.5°	1858.0	1852.2	1852.2	1861.0	1850.7
175°	1868.3	1862.4	1862.4	1871.3	1861.0
177.5°	1874.2	1868.3	1868.3	1877.2	1866.9
180°	1872.7	1872.7	1872.7	1872.7	1872.7

(END OF REPORT)