

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031192

Luminaire Tested: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031192
REPORT IS A COMBINATION OF REPORTS P994484 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8389.0 lumens
Efficiency: N/A
Efficacy: 110.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031192

CATALOG NUMBER: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1031192

CATALOG NUMBER: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	71	67	75	69	64	60	54	50	48	40	38	36	26	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	33	30	24	22	21
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	37	38	33	29	28	25	23	19	17	16
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	22	23	20	17	16	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	15	13	11
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10168	10168	10168
5°	10184	9808	9781
10°	10104	9440	9253
15°	9972	8983	8675
20°	9801	8487	8028
25°	9623	7972	7415
30°	9396	7425	6691
35°	9161	6886	6032
40°	8940	6301	5303
45°	8658	5730	4648
50°	8347	5119	3970
55°	8023	4466	3349
60°	7715	3796	2718
65°	7315	3108	2122
70°	6814	2351	1516
75°	6090	1592	1201
80°	5201	1107	842
85°	3900	599	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8658 cd/sqm

TEST NUMBER: P1031192

CATALOG NUMBER: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	1.1
10°-20°	247.0	2.9
20°-30°	355.7	4.2
30°-40°	400.5	4.8
40°-50°	383.1	4.6
50°-60°	313.6	3.7
60°-70°	211.5	2.5
70°-80°	106.1	1.3
80°-90°	31.8	0.4
90°-100°	72.3	0.9
100°-110°	349.6	4.2
110°-120°	856.7	10.2
120°-130°	1087.5	13.0
130°-140°	1161.8	13.8
140°-150°	1086.4	13.0
150°-160°	876.3	10.4
160°-170°	565.5	6.7
170°-180°	194.9	2.3
0°-30°	691.5	8.2
0°-40°	1092.0	13.0
0°-60°	1788.8	21.3
0°-90°	2138.1	25.5
90°-120°	1278.6	15.2
90°-150°	4614.2	55.0
90°-180°	6251.0	74.5
0°-180°	8389.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	945	945	945	945	945	
5°	945	941	932	938	937	90
15°	901	892	871	867	862	254
25°	820	801	765	749	741	377
35°	709	682	634	601	588	444
45°	583	548	490	446	428	450
55°	443	405	340	296	280	397
65°	303	260	201	163	155	299
75°	160	123	81	74	72	171
85°	41	24	22	20	20	44
90°	2	17	37	43	46	8
95°	93	30	47	58	58	111
105°	454	471	334	64	67	481
115°	852	861	874	890	896	841
125°	1200	1213	1219	1222	1225	1073
135°	1494	1504	1510	1514	1510	1151
145°	1724	1735	1738	1741	1741	1080
155°	1900	1897	1898	1906	1897	875
165°	2003	1999	1997	2009	1999	566
175°	2050	2043	2044	2055	2043	195
180°	2050	2050	2050	2050	2050	

TEST NUMBER: P1031192

CATALOG NUMBER: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	944.6	944.6	944.6	944.6	944.6
2.5°	948.4	945.4	936.2	944.6	943.1
5°	944.6	940.8	931.6	938.5	936.9
7.5°	937.7	933.9	922.4	927.0	924.7
10°	928.5	923.1	909.4	910.1	906.3
12.5°	915.5	909.4	891.7	891.0	886.4
15°	900.9	892.5	871.0	867.2	861.9
17.5°	883.3	874.1	847.3	839.6	832.0
20°	863.4	851.1	822.0	812.1	802.9
22.5°	841.2	826.6	795.2	782.2	773.8
25°	819.7	800.6	765.3	749.2	740.8
27.5°	793.7	773.0	734.7	713.2	700.2
30°	766.9	743.9	701.0	674.9	662.7
32.5°	740.0	713.2	667.3	638.2	625.1
35°	709.4	681.8	634.3	601.4	587.6
37.5°	678.8	648.9	599.1	562.3	545.5
40°	649.6	615.9	561.5	521.7	504.1
42.5°	616.7	583.0	526.3	481.9	466.6
45°	583.0	548.5	489.5	445.9	427.5
47.5°	550.1	511.7	453.5	406.0	389.9
50°	513.3	477.3	415.2	367.7	350.1
52.5°	480.3	440.5	379.2	329.4	314.1
55°	442.8	405.3	340.1	295.7	280.4
57.5°	409.1	368.5	302.6	260.5	247.4
60°	373.9	331.7	268.1	226.8	213.7
62.5°	338.6	296.5	232.9	194.6	180.8
65°	302.6	260.5	200.7	163.2	154.8
67.5°	266.6	223.7	165.5	137.1	127.9
70°	231.4	190.0	136.4	109.6	101.1
72.5°	196.1	155.5	108.0	87.3	85.0
75°	160.1	123.3	81.2	73.5	72.0
77.5°	127.2	93.5	63.6	59.0	57.5
80°	95.8	64.4	48.3	46.0	44.4
82.5°	65.9	39.8	34.5	32.2	32.2
85°	40.6	23.7	21.5	19.9	19.9
87.5°	18.4	10.0	10.0	9.2	8.4
90°	1.5	16.8	36.6	42.7	45.7
92.5°	35.0	25.9	39.6	50.3	51.8
95°	92.9	30.5	47.2	57.9	57.9
97.5°	169.1	126.4	48.7	60.9	62.5
100°	257.4	287.9	50.3	62.5	64.0
102.5°	358.0	377.8	112.7	62.5	65.5
105°	454.0	470.7	333.6	64.0	67.0
107.5°	556.0	569.7	592.6	358.0	158.4
110°	658.1	670.3	687.0	636.8	418.9

TEST NUMBER: P1031192

CATALOG NUMBER: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	755.6	766.2	783.0	796.7	793.7
115°	851.6	860.7	874.4	889.6	895.7
117.5°	946.0	956.7	964.3	976.5	978.0
120°	1032.8	1046.5	1051.1	1063.3	1063.3
122.5°	1121.2	1131.8	1137.9	1145.6	1147.1
125°	1200.4	1212.6	1218.7	1221.7	1224.8
127.5°	1279.6	1291.8	1299.4	1304.0	1300.9
130°	1352.7	1364.9	1371.0	1377.1	1374.1
132.5°	1422.8	1435.0	1439.6	1445.7	1441.1
135°	1494.4	1503.5	1509.6	1514.2	1509.6
137.5°	1555.3	1567.5	1570.6	1578.2	1575.1
140°	1616.3	1625.4	1630.0	1636.1	1633.0
142.5°	1672.6	1681.8	1686.3	1690.9	1686.3
145°	1724.4	1735.1	1738.1	1741.2	1741.2
147.5°	1774.7	1782.3	1785.4	1788.4	1780.8
150°	1820.4	1825.0	1828.0	1831.1	1826.5
152.5°	1861.5	1863.1	1864.6	1870.7	1863.1
155°	1899.6	1896.6	1898.1	1905.7	1896.6
157.5°	1930.1	1930.1	1928.6	1937.7	1925.5
160°	1957.5	1956.0	1954.5	1963.6	1952.9
162.5°	1983.4	1978.8	1977.3	1988.0	1978.8
165°	2003.2	1998.6	1997.1	2009.3	1998.6
167.5°	2020.0	2013.9	2013.9	2026.1	2013.9
170°	2033.7	2027.6	2027.6	2039.8	2027.6
172.5°	2042.8	2035.2	2036.7	2048.9	2035.2
175°	2050.4	2042.8	2044.3	2055.0	2042.8
177.5°	2053.5	2045.9	2047.4	2059.6	2044.3
180°	2050.4	2050.4	2050.4	2050.4	2050.4

(END OF REPORT)