

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031210

Luminaire Tested: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031210
REPORT IS A COMBINATION OF REPORTS P994570 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5154.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 47.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031210

CATALOG NUMBER: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1031210

CATALOG NUMBER: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48			41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	43	42	41			35
2	88	80	75	70	80	74	69	64	61	57	54	49	46	44	38	36	35			30
3	80	71	64	58	73	65	59	54	54	49	46	43	40	38	34	32	30			25
4	73	63	55	49	67	58	51	46	48	43	39	39	35	32	30	28	26			22
5	67	56	48	42	61	52	45	40	43	38	34	35	31	28	27	25	23			19
6	62	50	42	37	56	46	39	34	39	33	30	32	28	25	25	22	20			17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18			15
8	53	41	34	29	49	38	31	27	32	27	23	26	22	20	21	18	16			14
9	50	38	30	25	45	35	28	24	29	24	21	24	20	18	19	17	15			12
10	46	35	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10038	10038	10038
5°	10055	9684	9658
10°	9977	9319	9136
15°	9846	8869	8564
20°	9677	8380	7926
25°	9501	7871	7321
30°	9277	7330	6607
35°	9045	6799	5956
40°	8827	6221	5236
45°	8548	5657	4590
50°	8241	5055	3920
55°	7922	4409	3306
60°	7616	3748	2683
65°	7223	3070	2095
70°	6726	2320	1496
75°	6014	1572	1186
80°	5130	1093	833
85°	3852	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8548 cd/sqm

TEST NUMBER: P1031210

CATALOG NUMBER: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.7
10°-20°	243.9	4.7
20°-30°	351.2	6.8
30°-40°	395.5	7.7
40°-50°	378.3	7.3
50°-60°	309.7	6.0
60°-70°	208.8	4.1
70°-80°	104.7	2.0
80°-90°	29.4	0.6
90°-100°	35.2	0.7
100°-110°	170.3	3.3
110°-120°	417.3	8.1
120°-130°	529.8	10.3
130°-140°	565.9	11.0
140°-150°	529.2	10.3
150°-160°	426.9	8.3
160°-170°	275.5	5.3
170°-180°	94.9	1.8
0°-30°	682.7	13.2
0°-40°	1078.2	20.9
0°-60°	1766.1	34.3
0°-90°	2109.0	40.9
90°-120°	622.8	12.1
90°-150°	2247.8	43.6
90°-180°	3045.0	59.1
0°-180°	5154.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	933	933	933	933	933	
5°	933	929	920	927	925	88
15°	890	881	860	856	851	251
25°	809	790	756	740	731	372
35°	700	673	626	594	580	438
45°	576	542	483	440	422	444
55°	437	400	336	292	277	392
65°	299	257	198	161	153	296
75°	158	122	80	73	71	168
85°	40	23	21	20	20	44
90°	1	8	18	21	22	5
95°	45	15	23	28	28	54
105°	221	229	162	31	33	234
115°	415	419	426	433	436	410
125°	585	591	594	595	597	522
135°	728	732	735	738	735	560
145°	840	845	847	848	848	526
155°	925	924	925	928	924	426
165°	976	974	973	979	974	276
175°	999	995	996	1001	995	95
180°	999	999	999	999	999	

TEST NUMBER: P1031210

CATALOG NUMBER: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	932.6	932.6	932.6	932.6	932.6
2.5°	936.4	933.4	924.3	932.6	931.1
5°	932.6	928.9	919.8	926.6	925.1
7.5°	925.8	922.1	910.7	915.2	913.0
10°	916.8	911.5	897.8	898.6	894.8
12.5°	903.9	897.8	880.4	879.7	875.2
15°	889.5	881.2	860.0	856.2	850.9
17.5°	872.1	863.1	836.6	829.0	821.4
20°	852.5	840.4	811.6	801.8	792.7
22.5°	830.5	816.2	785.1	772.3	764.0
25°	809.3	790.4	755.6	739.8	731.4
27.5°	783.6	763.2	725.4	704.2	691.3
30°	757.2	734.5	692.1	666.4	654.3
32.5°	730.7	704.2	658.8	630.1	617.2
35°	700.4	673.2	626.3	593.8	580.2
37.5°	670.2	640.7	591.5	555.2	538.6
40°	641.4	608.1	554.4	515.1	497.7
42.5°	608.9	575.6	519.6	475.8	460.6
45°	575.6	541.6	483.3	440.2	422.1
47.5°	543.1	505.3	447.8	400.9	385.0
50°	506.8	471.2	410.0	363.1	345.7
52.5°	474.3	434.9	374.4	325.3	310.1
55°	437.2	400.1	335.8	292.0	276.8
57.5°	403.9	363.8	298.8	257.2	244.3
60°	369.1	327.5	264.7	223.9	211.0
62.5°	334.3	292.7	229.9	192.1	178.5
65°	298.8	257.2	198.2	161.1	152.8
67.5°	263.2	220.9	163.4	135.4	126.3
70°	228.4	187.6	134.6	108.2	99.8
72.5°	193.6	153.5	106.7	86.2	84.0
75°	158.1	121.8	80.2	72.6	71.1
77.5°	125.6	92.3	62.8	58.2	56.7
80°	94.5	63.5	47.7	45.4	43.9
82.5°	65.1	39.3	34.0	31.8	31.8
85°	40.1	23.4	21.2	19.7	19.7
87.5°	18.2	9.8	9.8	9.1	8.3
90°	0.7	8.2	17.8	20.8	22.3
92.5°	17.1	12.6	19.3	24.5	25.2
95°	45.3	14.8	23.0	28.2	28.2
97.5°	82.4	61.6	23.7	29.7	30.4
100°	125.4	140.3	24.5	30.4	31.2
102.5°	174.4	184.0	54.9	30.4	31.9
105°	221.1	229.3	162.5	31.2	32.7
107.5°	270.9	277.5	288.7	174.4	77.2
110°	320.6	326.5	334.7	310.2	204.1

TEST NUMBER: P1031210

CATALOG NUMBER: S123RDIW-B560D755UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	368.1	373.3	381.4	388.1	386.6
115°	414.8	419.3	425.9	433.4	436.3
117.5°	460.8	466.0	469.7	475.7	476.4
120°	503.1	509.8	512.0	518.0	518.0
122.5°	546.2	551.4	554.3	558.0	558.8
125°	584.8	590.7	593.7	595.1	596.6
127.5°	623.3	629.3	633.0	635.2	633.7
130°	659.0	664.9	667.9	670.8	669.3
132.5°	693.1	699.0	701.3	704.2	702.0
135°	728.0	732.4	735.4	737.6	735.4
137.5°	757.7	763.6	765.1	768.8	767.3
140°	787.3	791.8	794.0	797.0	795.5
142.5°	814.8	819.2	821.5	823.7	821.5
145°	840.0	845.2	846.7	848.2	848.2
147.5°	864.5	868.2	869.7	871.2	867.5
150°	886.8	889.0	890.5	892.0	889.7
152.5°	906.8	907.6	908.3	911.3	907.6
155°	925.4	923.9	924.6	928.3	923.9
157.5°	940.2	940.2	939.5	943.9	938.0
160°	953.6	952.8	952.1	956.5	951.3
162.5°	966.2	963.9	963.2	968.4	963.9
165°	975.8	973.6	972.9	978.8	973.6
167.5°	984.0	981.0	981.0	987.0	981.0
170°	990.7	987.7	987.7	993.6	987.7
172.5°	995.1	991.4	992.1	998.1	991.4
175°	998.8	995.1	995.9	1001.1	995.1
177.5°	1000.3	996.6	997.3	1003.3	995.9
180°	998.8	998.8	998.8	998.8	998.8

(END OF REPORT)