

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031239

Luminaire Tested: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031239
REPORT IS A COMBINATION OF REPORTS P994700 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F1_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8012.0 lumens
Efficiency: N/A
Efficacy: 90.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031239

CATALOG NUMBER: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031239

CATALOG NUMBER: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36
2	86	79	73	69	78	72	67	63	58	55	52	45	43	41	34	32	31
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	30	28	27
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	27	25	23
5	66	55	47	42	60	50	43	38	41	36	32	32	29	26	24	22	20
6	61	49	42	36	55	45	38	33	37	32	28	29	26	23	22	20	18
7	56	45	37	32	51	41	34	29	33	28	25	27	23	20	20	18	16
8	52	40	33	28	47	37	30	26	30	25	22	24	21	18	19	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	15	13
10	45	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13431	13431	13431
5°	13453	12956	12921
10°	13347	12468	12223
15°	13174	11866	11459
20°	12946	11212	10605
25°	12712	10531	9795
30°	12412	9808	8839
35°	12102	9096	7968
40°	11811	8324	7005
45°	11437	7570	6140
50°	11025	6763	5245
55°	10598	5900	4424
60°	10191	5015	3590
65°	9662	4106	2802
70°	9000	3105	2003
75°	8045	2103	1587
80°	6868	1462	1113
85°	5149	788	583

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11437 cd/sqm

TEST NUMBER: P1031239

CATALOG NUMBER: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.3	1.5
10°-20°	326.3	4.1
20°-30°	469.8	5.9
30°-40°	529.1	6.6
40°-50°	506.1	6.3
50°-60°	414.3	5.2
60°-70°	279.3	3.5
70°-80°	140.1	1.7
80°-90°	40.6	0.5
90°-100°	120.6	1.5
100°-110°	364.9	4.6
110°-120°	621.2	7.8
120°-130°	817.2	10.2
130°-140°	918.6	11.5
140°-150°	903.0	11.3
150°-160°	760.3	9.5
160°-170°	506.1	6.3
170°-180°	177.2	2.2
0°-30°	913.4	11.4
0°-40°	1442.6	18.0
0°-60°	2363.0	29.5
0°-90°	2822.9	35.2
90°-120°	1106.6	13.8
90°-150°	3745.4	46.7
90°-180°	5189.0	64.8
0°-180°	8012.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1248	1248	1248	1248	1248	
5°	1248	1243	1231	1240	1238	118
15°	1190	1179	1151	1146	1138	335
25°	1083	1058	1011	990	979	498
35°	937	901	838	794	776	587
45°	770	725	647	589	565	594
55°	585	535	449	391	370	525
65°	400	344	265	216	204	396
75°	212	163	107	97	95	225
85°	54	31	28	26	26	59
90°	2	16	35	41	44	10
95°	87	97	109	115	115	96
105°	331	334	347	347	350	354
115°	625	630	627	628	627	619
125°	915	920	916	911	905	816
135°	1187	1196	1195	1189	1186	915
145°	1440	1443	1448	1446	1440	900
155°	1649	1649	1651	1656	1646	759
165°	1796	1792	1792	1801	1790	507
175°	1868	1862	1862	1871	1861	178
180°	1873	1873	1873	1873	1873	

TEST NUMBER: P1031239

CATALOG NUMBER: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1247.8	1247.8	1247.8	1247.8	1247.8
2.5°	1252.9	1248.8	1236.7	1247.8	1245.8
5°	1247.8	1242.7	1230.6	1239.7	1237.7
7.5°	1238.7	1233.6	1218.5	1224.5	1221.5
10°	1226.5	1219.5	1201.2	1202.3	1197.2
12.5°	1209.3	1201.2	1178.0	1177.0	1170.9
15°	1190.1	1179.0	1150.6	1145.6	1138.5
17.5°	1166.8	1154.7	1119.3	1109.2	1099.0
20°	1140.5	1124.3	1085.9	1072.7	1060.6
22.5°	1111.2	1092.0	1050.5	1033.3	1022.1
25°	1082.8	1057.5	1011.0	989.7	978.6
27.5°	1048.4	1021.1	970.5	942.2	925.0
30°	1013.0	982.7	926.0	891.6	875.4
32.5°	977.6	942.2	881.5	843.0	825.8
35°	937.1	900.7	837.9	794.4	776.2
37.5°	896.6	857.2	791.4	742.8	720.5
40°	858.2	813.7	741.8	689.2	665.9
42.5°	814.7	770.1	695.2	636.5	616.3
45°	770.1	724.6	646.7	589.0	564.7
47.5°	726.6	676.0	599.1	536.4	515.1
50°	678.0	630.5	548.5	485.8	462.5
52.5°	634.5	581.9	500.9	435.2	414.9
55°	584.9	535.3	449.3	390.6	370.4
57.5°	540.4	486.8	399.7	344.1	326.9
60°	493.9	438.2	354.2	299.6	282.3
62.5°	447.3	391.6	307.6	257.0	238.8
65°	399.7	344.1	265.1	215.6	204.4
67.5°	352.2	295.5	218.6	181.1	169.0
70°	305.6	251.0	180.1	144.7	133.6
72.5°	259.1	205.4	142.7	115.4	112.3
75°	211.5	162.9	107.3	97.2	95.1
77.5°	168.0	123.5	84.0	77.9	75.9
80°	126.5	85.0	63.8	60.7	58.7
82.5°	87.0	52.6	45.5	42.5	42.5
85°	53.6	31.4	28.3	26.3	26.3
87.5°	24.3	13.2	13.2	12.1	11.1
90°	1.5	16.2	35.3	41.2	44.1
92.5°	44.1	53.0	61.8	66.2	63.3
95°	86.8	97.1	108.9	114.7	114.7
97.5°	142.7	150.1	158.9	166.2	164.8
100°	200.1	208.9	216.3	220.7	223.6
102.5°	266.3	270.7	281.0	285.4	283.9
105°	331.0	333.9	347.2	347.2	350.1
107.5°	407.5	409.0	414.9	419.3	417.8
110°	478.1	481.1	484.0	489.9	486.9

TEST NUMBER: P1031239

CATALOG NUMBER: S123RDIW-B775D1535UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	551.7	553.1	553.1	560.5	560.5
115°	625.2	629.6	626.7	628.2	626.7
117.5°	700.3	701.7	698.8	698.8	694.4
120°	769.4	778.2	770.9	769.4	766.5
122.5°	841.5	847.4	844.4	840.0	835.6
125°	915.0	919.5	916.5	910.6	904.7
127.5°	982.7	991.5	988.6	979.8	973.9
130°	1050.4	1062.2	1057.7	1051.9	1041.6
132.5°	1118.1	1129.8	1126.9	1119.5	1112.2
135°	1187.2	1196.0	1194.6	1188.7	1185.7
137.5°	1250.5	1257.8	1262.2	1254.9	1250.5
140°	1316.7	1324.0	1325.5	1324.0	1313.7
142.5°	1377.0	1384.3	1387.3	1385.8	1378.4
145°	1440.2	1443.2	1447.6	1446.1	1440.2
147.5°	1494.7	1500.6	1505.0	1505.0	1496.1
150°	1552.0	1555.0	1557.9	1557.9	1549.1
152.5°	1599.1	1603.5	1605.0	1607.9	1600.6
155°	1649.1	1649.1	1650.6	1656.5	1646.2
157.5°	1691.8	1690.3	1691.8	1697.7	1688.9
160°	1731.5	1728.6	1728.6	1735.9	1730.0
162.5°	1766.8	1762.4	1763.9	1771.2	1760.9
165°	1796.2	1791.8	1791.8	1800.7	1790.4
167.5°	1821.3	1815.4	1816.8	1825.7	1816.8
170°	1841.9	1836.0	1836.0	1846.3	1836.0
172.5°	1858.0	1852.2	1852.2	1861.0	1850.7
175°	1868.3	1862.4	1862.4	1871.3	1861.0
177.5°	1874.2	1868.3	1868.3	1877.2	1866.9
180°	1872.7	1872.7	1872.7	1872.7	1872.7

(END OF REPORT)