

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031260

Luminaire Tested: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031260
REPORT IS A COMBINATION OF REPORTS P994790 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5954.0 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031260

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1031260

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	86	83	80	73	71	69	61	59	58	49	48	47
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23
7	59	47	39	33	54	43	36	32	37	32	28	32	27	24	26	23	21
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	22	19	17
10	47	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13851	13851	13851
5°	13874	13360	13324
10°	13764	12858	12605
15°	13586	12238	11816
20°	13350	11562	10936
25°	13109	10861	10102
30°	12799	10114	9115
35°	12480	9381	8216
40°	12180	8585	7224
45°	11795	7806	6331
50°	11370	6974	5408
55°	10930	6085	4562
60°	10509	5172	3703
65°	9964	4234	2890
70°	9282	3203	2066
75°	8296	2168	1637
80°	7079	1506	1147
85°	5312	813	601

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11795 cd/sqm

TEST NUMBER: P1031260

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.0	2.0
10°-20°	336.5	5.7
20°-30°	484.5	8.1
30°-40°	545.6	9.2
40°-50°	521.9	8.8
50°-60°	427.2	7.2
60°-70°	288.0	4.8
70°-80°	144.5	2.4
80°-90°	39.8	0.7
90°-100°	35.2	0.6
100°-110°	170.3	2.9
110°-120°	417.3	7.0
120°-130°	529.8	8.9
130°-140°	565.9	9.5
140°-150°	529.2	8.9
150°-160°	426.9	7.2
160°-170°	275.5	4.6
170°-180°	94.9	1.6
0°-30°	942.0	15.8
0°-40°	1487.6	25.0
0°-60°	2436.7	40.9
0°-90°	2909.0	48.9
90°-120°	622.8	10.5
90°-150°	2247.8	37.8
90°-180°	3045.0	51.1
0°-180°	5954.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1287	1287	1287	1287	1287	
5°	1287	1282	1269	1278	1276	122
15°	1227	1216	1187	1181	1174	346
25°	1117	1091	1043	1021	1009	514
35°	966	929	864	819	800	605
45°	794	747	667	607	582	613
55°	603	552	463	403	382	541
65°	412	355	273	222	211	408
75°	218	168	111	100	98	232
85°	55	32	29	27	27	61
90°	1	8	18	21	22	6
95°	45	15	23	28	28	54
105°	221	229	162	31	33	234
115°	415	419	426	433	436	410
125°	585	591	594	595	597	522
135°	728	732	735	738	735	560
145°	840	845	847	848	848	526
155°	925	924	925	928	924	426
165°	976	974	973	979	974	276
175°	999	995	996	1001	995	95
180°	999	999	999	999	999	

TEST NUMBER: P1031260

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1286.8	1286.8	1286.8	1286.8	1286.8
2.5°	1292.0	1287.8	1275.3	1286.8	1284.7
5°	1286.8	1281.5	1269.0	1278.4	1276.3
7.5°	1277.4	1272.1	1256.5	1262.7	1259.6
10°	1264.8	1257.5	1238.7	1239.8	1234.6
12.5°	1247.1	1238.7	1214.7	1213.7	1207.4
15°	1227.3	1215.8	1186.6	1181.3	1174.0
17.5°	1203.3	1190.7	1154.2	1143.8	1133.3
20°	1176.1	1159.4	1119.8	1106.2	1093.7
22.5°	1145.9	1126.0	1083.3	1065.5	1054.0
25°	1116.6	1090.6	1042.6	1020.6	1009.2
27.5°	1081.2	1053.0	1000.8	971.6	953.8
30°	1044.6	1013.3	954.9	919.4	902.7
32.5°	1008.1	971.6	909.0	869.3	851.6
35°	966.4	928.8	864.1	819.2	800.4
37.5°	924.6	883.9	816.1	766.0	743.0
40°	885.0	839.0	765.0	710.7	686.7
42.5°	840.1	794.2	716.9	656.4	635.5
45°	794.2	747.2	666.9	607.4	582.3
47.5°	749.3	697.1	617.8	553.1	531.2
50°	699.2	650.2	565.6	500.9	476.9
52.5°	654.3	600.1	516.6	448.7	427.9
55°	603.2	552.1	463.4	402.8	382.0
57.5°	557.3	502.0	412.2	354.8	337.1
60°	509.3	451.9	365.3	308.9	291.2
62.5°	461.3	403.9	317.3	265.1	246.3
65°	412.2	354.8	273.4	222.3	210.8
67.5°	363.2	304.7	225.4	186.8	174.3
70°	315.2	258.8	185.8	149.2	137.8
72.5°	267.2	211.8	147.1	119.0	115.8
75°	218.1	168.0	110.6	100.2	98.1
77.5°	173.2	127.3	86.6	80.4	78.3
80°	130.4	87.7	65.7	62.6	60.5
82.5°	89.7	54.3	47.0	43.8	43.8
85°	55.3	32.4	29.2	27.1	27.1
87.5°	25.0	13.6	13.6	12.5	11.5
90°	0.7	8.2	17.8	20.8	22.3
92.5°	17.1	12.6	19.3	24.5	25.2
95°	45.3	14.8	23.0	28.2	28.2
97.5°	82.4	61.6	23.7	29.7	30.4
100°	125.4	140.3	24.5	30.4	31.2
102.5°	174.4	184.0	54.9	30.4	31.9
105°	221.1	229.3	162.5	31.2	32.7
107.5°	270.9	277.5	288.7	174.4	77.2
110°	320.6	326.5	334.7	310.2	204.1



TEST NUMBER: P1031260

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	368.1	373.3	381.4	388.1	386.6
115°	414.8	419.3	425.9	433.4	436.3
117.5°	460.8	466.0	469.7	475.7	476.4
120°	503.1	509.8	512.0	518.0	518.0
122.5°	546.2	551.4	554.3	558.0	558.8
125°	584.8	590.7	593.7	595.1	596.6
127.5°	623.3	629.3	633.0	635.2	633.7
130°	659.0	664.9	667.9	670.8	669.3
132.5°	693.1	699.0	701.3	704.2	702.0
135°	728.0	732.4	735.4	737.6	735.4
137.5°	757.7	763.6	765.1	768.8	767.3
140°	787.3	791.8	794.0	797.0	795.5
142.5°	814.8	819.2	821.5	823.7	821.5
145°	840.0	845.2	846.7	848.2	848.2
147.5°	864.5	868.2	869.7	871.2	867.5
150°	886.8	889.0	890.5	892.0	889.7
152.5°	906.8	907.6	908.3	911.3	907.6
155°	925.4	923.9	924.6	928.3	923.9
157.5°	940.2	940.2	939.5	943.9	938.0
160°	953.6	952.8	952.1	956.5	951.3
162.5°	966.2	963.9	963.2	968.4	963.9
165°	975.8	973.6	972.9	978.8	973.6
167.5°	984.0	981.0	981.0	987.0	981.0
170°	990.7	987.7	987.7	993.6	987.7
172.5°	995.1	991.4	992.1	998.1	991.4
175°	998.8	995.1	995.9	1001.1	995.1
177.5°	1000.3	996.6	997.3	1003.3	995.9
180°	998.8	998.8	998.8	998.8	998.8

(END OF REPORT)