

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030874

Luminaire Tested: S123DIW-B560D1030UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030874
REPORT IS A COMBINATION OF REPORTS P991532 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D1030UB2750-4F0-XX-W2A-F1_5000K
Description: Define 3 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5708.0 lumens
Efficiency: N/A
Efficacy: 102.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030874

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030874

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46			39
1	95	91	87	84	86	83	80	77	68	65	63	53	52	51	41	40	39			33
2	87	79	73	68	79	72	67	63	59	55	52	47	44	42	36	34	33			27
3	79	70	63	57	72	64	57	52	52	48	44	41	38	36	32	29	28			23
4	72	62	54	48	65	56	50	44	46	41	37	37	33	30	28	26	24			20
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	23	21			17
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18			15
7	56	44	36	31	51	41	34	29	34	28	24	27	23	20	21	18	16			13
8	52	40	32	27	47	37	30	25	31	25	22	25	21	18	19	16	14			12
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13			11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	15	16	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9182	9182	9182
5°	9204	8865	8852
10°	9122	8564	8477
15°	8996	8253	8069
20°	8851	7906	7664
25°	8663	7541	7232
30°	8457	7162	6776
35°	8241	6776	6324
40°	8015	6370	5880
45°	7767	5975	5415
50°	7514	5535	4949
55°	7190	5075	4476
60°	6857	4569	3974
65°	6541	4021	3449
70°	6090	3413	2837
75°	5440	2703	2202
80°	4696	1900	1557
85°	3660	1022	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7767 cd/sqm

TEST NUMBER: P1030874

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.4	1.4
10°-20°	227.1	4.0
20°-30°	335.4	5.9
30°-40°	391.7	6.9
40°-50°	393.8	6.9
50°-60°	345.9	6.1
60°-70°	257.6	4.5
70°-80°	146.6	2.6
80°-90°	44.3	0.8
90°-100°	81.0	1.4
100°-110°	245.1	4.3
110°-120°	417.2	7.3
120°-130°	548.9	9.6
130°-140°	617.0	10.8
140°-150°	606.5	10.6
150°-160°	510.6	8.9
160°-170°	340.0	6.0
170°-180°	119.0	2.1
0°-30°	642.8	11.3
0°-40°	1034.5	18.1
0°-60°	1774.1	31.1
0°-90°	2222.7	38.9
90°-120°	743.3	13.0
90°-150°	2515.7	44.1
90°-180°	3485.0	61.1
0°-180°	5708.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	853	853	853	853	853	
5°	854	850	842	849	848	81
15°	813	810	800	806	802	229
25°	738	734	724	725	722	340
35°	638	634	624	620	616	399
45°	523	520	510	502	498	404
55°	397	396	386	378	375	355
65°	271	267	260	254	252	267
75°	143	140	138	134	132	153
85°	38	37	37	35	35	41
90°	1	11	24	28	30	7
95°	58	65	73	77	77	64
105°	222	224	233	233	235	238
115°	420	423	421	422	421	416
125°	615	618	616	612	608	548
135°	797	803	802	798	796	614
145°	967	969	972	971	967	604
155°	1108	1108	1109	1113	1106	510
165°	1206	1204	1204	1210	1202	340
175°	1255	1251	1251	1257	1250	119
180°	1258	1258	1258	1258	1258	

TEST NUMBER: P1030874

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	853.0	853.0	853.0	853.0	853.0
2.5°	856.7	853.7	845.7	853.0	852.3
5°	853.7	850.1	842.0	849.3	847.9
7.5°	847.1	843.5	835.4	842.0	841.3
10°	838.3	834.7	825.1	831.7	830.3
12.5°	826.6	823.7	814.9	819.3	818.5
15°	812.7	809.7	800.2	806.1	801.7
17.5°	797.3	793.6	784.1	788.5	787.0
20°	779.7	775.3	765.7	768.7	766.5
22.5°	759.9	755.5	745.9	748.1	745.2
25°	737.9	733.5	723.9	724.7	722.5
27.5°	715.1	710.7	700.4	701.2	699.0
30°	690.2	686.5	676.2	676.2	671.1
32.5°	665.2	660.1	652.8	647.6	645.4
35°	638.1	633.7	624.2	619.8	616.1
37.5°	611.0	605.1	595.6	590.4	588.2
40°	582.4	578.0	567.7	561.8	558.9
42.5°	553.8	548.6	538.4	532.5	529.6
45°	523.0	520.0	510.5	501.7	498.0
47.5°	492.9	488.5	479.7	470.9	467.9
50°	462.1	458.4	448.9	440.8	436.4
52.5°	429.8	427.6	417.3	410.7	406.3
55°	396.8	396.1	386.5	378.5	374.8
57.5°	366.0	363.1	355.7	348.4	344.0
60°	332.3	331.5	322.7	316.1	312.5
62.5°	302.2	300.0	291.2	284.6	282.4
65°	270.6	267.0	259.6	253.8	251.6
67.5°	236.9	234.0	228.1	223.0	220.0
70°	206.8	202.4	198.0	192.9	189.2
72.5°	175.3	172.4	167.2	162.8	161.4
75°	143.0	140.1	137.9	134.2	132.0
77.5°	114.4	113.0	110.0	107.1	107.1
80°	86.5	84.3	82.9	82.1	82.1
82.5°	59.4	59.4	59.4	57.9	57.2
85°	38.1	36.7	36.7	35.2	35.2
87.5°	19.1	16.9	16.1	15.4	15.4
90°	1.0	10.9	23.7	27.7	29.6
92.5°	29.6	35.6	41.5	44.5	42.5
95°	58.3	65.2	73.1	77.1	77.1
97.5°	95.8	100.8	106.7	111.7	110.7
100°	134.4	140.3	145.3	148.2	150.2
102.5°	178.8	181.8	188.7	191.7	190.7
105°	222.3	224.3	233.2	233.2	235.2
107.5°	273.7	274.7	278.6	281.6	280.6
110°	321.1	323.1	325.1	329.0	327.1

TEST NUMBER: P1030874

CATALOG NUMBER: S123DIW-B560D1030UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	370.5	371.5	371.5	376.5	376.5
115°	420.0	422.9	420.9	421.9	420.9
117.5°	470.3	471.3	469.4	469.4	466.4
120°	516.8	522.7	517.8	516.8	514.8
122.5°	565.2	569.2	567.2	564.2	561.3
125°	614.6	617.6	615.6	611.6	607.7
127.5°	660.1	666.0	664.0	658.1	654.1
130°	705.5	713.4	710.5	706.5	699.6
132.5°	751.0	758.9	756.9	752.0	747.0
135°	797.4	803.3	802.4	798.4	796.4
137.5°	839.9	844.8	847.8	842.9	839.9
140°	884.4	889.3	890.3	889.3	882.4
142.5°	924.9	929.8	931.8	930.8	925.9
145°	967.4	969.3	972.3	971.3	967.4
147.5°	1003.9	1007.9	1010.8	1010.8	1004.9
150°	1042.5	1044.4	1046.4	1046.4	1040.5
152.5°	1074.1	1077.0	1078.0	1080.0	1075.1
155°	1107.7	1107.7	1108.7	1112.6	1105.7
157.5°	1136.3	1135.3	1136.3	1140.3	1134.4
160°	1163.0	1161.0	1161.0	1166.0	1162.0
162.5°	1186.7	1183.8	1184.8	1189.7	1182.8
165°	1206.5	1203.5	1203.5	1209.5	1202.5
167.5°	1223.3	1219.3	1220.3	1226.3	1220.3
170°	1237.1	1233.2	1233.2	1240.1	1233.2
172.5°	1248.0	1244.0	1244.0	1250.0	1243.1
175°	1254.9	1251.0	1251.0	1256.9	1250.0
177.5°	1258.9	1254.9	1254.9	1260.8	1253.9
180°	1257.9	1257.9	1257.9	1257.9	1257.9

(END OF REPORT)