

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031261

Luminaire Tested: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031261
REPORT IS A COMBINATION OF REPORTS P994791 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6006.0 lumens
Efficiency: N/A
Efficacy: 101.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031261

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031261

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	86	83	80	73	71	69	61	59	58	49	48	47
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23
7	59	47	39	33	54	43	36	32	37	32	28	32	27	24	26	23	21
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	22	19	17
10	47	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13969	13969	13969
5°	13992	13475	13439
10°	13882	12969	12713
15°	13702	12343	11918
20°	13465	11661	11030
25°	13221	10953	10188
30°	12909	10201	9194
35°	12588	9461	8287
40°	12284	8657	7286
45°	11896	7873	6386
50°	11467	7034	5455
55°	11024	6136	4601
60°	10600	5216	3735
65°	10051	4272	2915
70°	9362	3230	2083
75°	8369	2188	1650
80°	7145	1520	1157
85°	5360	821	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11896 cd/sqm

TEST NUMBER: P1031261

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.0	2.0
10°-20°	339.4	5.7
20°-30°	488.7	8.1
30°-40°	550.3	9.2
40°-50°	526.4	8.8
50°-60°	430.9	7.2
60°-70°	290.5	4.8
70°-80°	145.7	2.4
80°-90°	40.1	0.7
90°-100°	35.5	0.6
100°-110°	171.8	2.9
110°-120°	421.0	7.0
120°-130°	534.5	8.9
130°-140°	571.0	9.5
140°-150°	533.9	8.9
150°-160°	430.6	7.2
160°-170°	277.9	4.6
170°-180°	95.8	1.6
0°-30°	950.1	15.8
0°-40°	1500.4	25.0
0°-60°	2457.7	40.9
0°-90°	2934.0	48.9
90°-120°	628.3	10.5
90°-150°	2267.7	37.8
90°-180°	3072.0	51.1
0°-180°	6006.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1298	1298	1298	1298	1298	
5°	1298	1293	1280	1289	1287	123
15°	1238	1226	1197	1192	1184	349
25°	1126	1100	1052	1029	1018	518
35°	975	937	872	826	807	610
45°	801	754	673	613	587	618
55°	608	557	467	406	385	546
65°	416	358	276	224	213	411
75°	220	170	112	101	99	234
85°	56	33	30	27	27	61
90°	1	8	18	21	22	6
95°	46	15	23	28	28	55
105°	223	231	164	31	33	237
115°	418	423	430	437	440	413
125°	590	596	599	600	602	527
135°	734	739	742	744	742	565
145°	848	853	854	856	856	531
155°	934	932	933	937	932	430
165°	984	982	982	988	982	278
175°	1008	1004	1005	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1031261

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1297.8	1297.8	1297.8	1297.8	1297.8
2.5°	1303.1	1298.9	1286.2	1297.8	1295.7
5°	1297.8	1292.6	1279.9	1289.4	1287.3
7.5°	1288.3	1283.1	1267.3	1273.6	1270.5
10°	1275.7	1268.3	1249.4	1250.5	1245.2
12.5°	1257.8	1249.4	1225.2	1224.1	1217.8
15°	1237.8	1226.2	1196.8	1191.5	1184.1
17.5°	1213.6	1201.0	1164.1	1153.6	1143.1
20°	1186.2	1169.4	1129.4	1115.7	1103.1
22.5°	1155.7	1135.7	1092.6	1074.7	1063.1
25°	1126.2	1099.9	1051.5	1029.4	1017.8
27.5°	1090.5	1062.0	1009.4	979.9	962.0
30°	1053.6	1022.0	963.1	927.3	910.5
32.5°	1016.8	979.9	916.8	876.8	858.9
35°	974.7	936.8	871.5	826.3	807.3
37.5°	932.6	891.5	823.1	772.6	749.4
40°	892.6	846.3	771.5	716.8	692.6
42.5°	847.3	801.0	723.1	662.1	641.0
45°	801.0	753.6	672.6	612.6	587.3
47.5°	755.7	703.1	623.1	557.9	535.8
50°	705.2	655.8	570.5	505.2	481.0
52.5°	660.0	605.2	521.0	452.6	431.6
55°	608.4	556.8	467.3	406.3	385.2
57.5°	562.1	506.3	415.8	357.9	340.0
60°	513.7	455.8	368.4	311.6	293.7
62.5°	465.2	407.3	320.0	267.4	248.4
65°	415.8	357.9	275.8	224.2	212.6
67.5°	366.3	307.4	227.4	188.4	175.8
70°	317.9	261.0	187.4	150.5	138.9
72.5°	269.5	213.7	148.4	120.0	116.8
75°	220.0	169.5	111.6	101.0	98.9
77.5°	174.7	128.4	87.4	81.0	78.9
80°	131.6	88.4	66.3	63.2	61.0
82.5°	90.5	54.7	47.4	44.2	44.2
85°	55.8	32.6	29.5	27.4	27.4
87.5°	25.3	13.7	13.7	12.6	11.6
90°	0.7	8.2	18.0	21.0	22.5
92.5°	17.2	12.7	19.5	24.7	25.5
95°	45.7	15.0	23.2	28.4	28.4
97.5°	83.1	62.1	24.0	29.9	30.7
100°	126.5	141.5	24.7	30.7	31.4
102.5°	175.9	185.7	55.4	30.7	32.2
105°	223.1	231.3	164.0	31.4	32.9
107.5°	273.3	280.0	291.2	175.9	77.9
110°	323.4	329.4	337.6	312.9	205.9



TEST NUMBER: P1031261

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.3	376.6	384.8	391.5	390.0
115°	418.5	423.0	429.7	437.2	440.2
117.5°	464.9	470.1	473.9	479.9	480.6
120°	507.6	514.3	516.6	522.6	522.6
122.5°	551.0	556.2	559.2	563.0	563.7
125°	589.9	595.9	598.9	600.4	601.9
127.5°	628.9	634.9	638.6	640.8	639.3
130°	664.8	670.8	673.8	676.8	675.3
132.5°	699.2	705.2	707.5	710.5	708.2
135°	734.4	738.9	741.9	744.2	741.9
137.5°	764.4	770.4	771.9	775.6	774.1
140°	794.3	798.8	801.1	804.0	802.5
142.5°	822.0	826.5	828.8	831.0	828.8
145°	847.5	852.7	854.2	855.7	855.7
147.5°	872.2	875.9	877.4	878.9	875.2
150°	894.6	896.9	898.4	899.9	897.6
152.5°	914.8	915.6	916.3	919.3	915.6
155°	933.6	932.1	932.8	936.6	932.1
157.5°	948.5	948.5	947.8	952.3	946.3
160°	962.0	961.3	960.5	965.0	959.8
162.5°	974.7	972.5	971.7	977.0	972.5
165°	984.5	982.2	981.5	987.5	982.2
167.5°	992.7	989.7	989.7	995.7	989.7
170°	999.4	996.4	996.4	1002.4	996.4
172.5°	1003.9	1000.2	1000.9	1006.9	1000.2
175°	1007.7	1003.9	1004.7	1009.9	1003.9
177.5°	1009.2	1005.4	1006.2	1012.2	1004.7
180°	1007.7	1007.7	1007.7	1007.7	1007.7

(END OF REPORT)