

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031262

Luminaire Tested: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031262
REPORT IS A COMBINATION OF REPORTS P994792 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6032.0 lumens
Efficiency: N/A
Efficacy: 102.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031262

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1031262

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	86	83	80	73	71	69	61	59	58	49	48	47
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23
7	59	47	39	33	54	43	36	32	37	32	28	32	27	24	26	23	21
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	22	19	17
10	47	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14032	14032	14032
5°	14055	13535	13499
10°	13944	13026	12769
15°	13763	12397	11971
20°	13525	11713	11079
25°	13280	11002	10233
30°	12967	10246	9234
35°	12643	9503	8324
40°	12338	8697	7319
45°	11949	7908	6414
50°	11518	7065	5479
55°	11073	6164	4621
60°	10645	5239	3752
65°	10095	4290	2928
70°	9403	3244	2093
75°	8407	2197	1658
80°	7177	1527	1163
85°	5379	824	610

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11949 cd/sqm

TEST NUMBER: P1031262

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	2.0
10°-20°	340.9	5.7
20°-30°	490.8	8.1
30°-40°	552.8	9.2
40°-50°	528.7	8.8
50°-60°	432.8	7.2
60°-70°	291.8	4.8
70°-80°	146.4	2.4
80°-90°	40.3	0.7
90°-100°	35.7	0.6
100°-110°	172.5	2.9
110°-120°	422.8	7.0
120°-130°	536.7	8.9
130°-140°	573.4	9.5
140°-150°	536.2	8.9
150°-160°	432.5	7.2
160°-170°	279.1	4.6
170°-180°	96.2	1.6
0°-30°	954.3	15.8
0°-40°	1507.0	25.0
0°-60°	2468.6	40.9
0°-90°	2947.0	48.9
90°-120°	631.0	10.5
90°-150°	2277.3	37.8
90°-180°	3085.0	51.1
0°-180°	6032.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1243	1232	1202	1197	1189	350
25°	1131	1105	1056	1034	1022	520
35°	979	941	875	830	811	613
45°	805	757	676	615	590	621
55°	611	559	469	408	387	548
65°	418	360	277	225	214	413
75°	221	170	112	102	99	235
85°	56	33	30	28	28	61
90°	1	8	18	21	23	6
95°	46	15	23	29	29	55
105°	224	232	165	32	33	238
115°	420	425	432	439	442	415
125°	592	598	601	603	604	529
135°	738	742	745	747	745	568
145°	851	856	858	859	859	533
155°	938	936	937	940	936	432
165°	989	986	986	992	986	279
175°	1012	1008	1009	1014	1008	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1031262

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1303.6	1303.6	1303.6	1303.6	1303.6
2.5°	1308.9	1304.6	1291.9	1303.6	1301.5
5°	1303.6	1298.3	1285.6	1295.1	1293.0
7.5°	1294.1	1288.8	1272.9	1279.3	1276.1
10°	1281.4	1274.0	1254.9	1256.0	1250.7
12.5°	1263.4	1254.9	1230.6	1229.6	1223.2
15°	1243.3	1231.7	1202.1	1196.8	1189.4
17.5°	1219.0	1206.3	1169.3	1158.7	1148.2
20°	1191.5	1174.6	1134.4	1120.7	1108.0
22.5°	1160.8	1140.8	1097.4	1079.4	1067.8
25°	1131.2	1104.8	1056.2	1034.0	1022.3
27.5°	1095.3	1066.8	1013.9	984.3	966.3
30°	1058.3	1026.6	967.4	931.4	914.5
32.5°	1021.3	984.3	920.9	880.7	862.7
35°	979.0	940.9	875.4	829.9	810.9
37.5°	936.7	895.5	826.8	776.0	752.8
40°	896.5	850.0	775.0	720.0	695.7
42.5°	851.1	804.6	726.3	665.0	643.9
45°	804.6	757.0	675.6	615.3	589.9
47.5°	759.1	706.2	625.9	560.3	538.1
50°	708.3	658.7	573.0	507.5	483.2
52.5°	662.9	607.9	523.3	454.6	433.5
55°	611.1	559.3	469.4	408.1	386.9
57.5°	564.6	508.5	417.6	359.5	341.5
60°	515.9	457.8	370.0	312.9	295.0
62.5°	467.3	409.2	321.4	268.5	249.5
65°	417.6	359.5	277.0	225.2	213.6
67.5°	367.9	308.7	228.4	189.2	176.6
70°	319.3	262.2	188.2	151.2	139.6
72.5°	270.7	214.6	149.1	120.5	117.4
75°	221.0	170.2	112.1	101.5	99.4
77.5°	175.5	129.0	87.8	81.4	79.3
80°	132.2	88.8	66.6	63.4	61.3
82.5°	90.9	55.0	47.6	44.4	44.4
85°	56.0	32.8	29.6	27.5	27.5
87.5°	25.4	13.7	13.7	12.7	11.6
90°	0.8	8.3	18.0	21.1	22.6
92.5°	17.3	12.8	19.5	24.8	25.6
95°	45.9	15.0	23.3	28.6	28.6
97.5°	83.5	62.4	24.1	30.1	30.8
100°	127.1	142.1	24.8	30.8	31.6
102.5°	176.7	186.4	55.6	30.8	32.3
105°	224.0	232.3	164.6	31.6	33.1
107.5°	274.4	281.2	292.5	176.7	78.2
110°	324.8	330.8	339.1	314.3	206.7



TEST NUMBER: P1031262

CATALOG NUMBER: S123RDIW-B775D755UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.9	378.2	386.4	393.2	391.7
115°	420.3	424.8	431.5	439.1	442.1
117.5°	466.9	472.1	475.9	481.9	482.7
120°	509.7	516.5	518.7	524.8	524.8
122.5°	553.3	558.6	561.6	565.4	566.1
125°	592.4	598.4	601.4	603.0	604.5
127.5°	631.5	637.5	641.3	643.6	642.0
130°	667.6	673.6	676.6	679.6	678.1
132.5°	702.2	708.2	710.5	713.5	711.2
135°	737.5	742.0	745.0	747.3	745.0
137.5°	767.6	773.6	775.1	778.9	777.4
140°	797.7	802.2	804.4	807.4	805.9
142.5°	825.5	830.0	832.3	834.5	832.3
145°	851.1	856.3	857.8	859.3	859.3
147.5°	875.9	879.6	881.1	882.6	878.9
150°	898.4	900.7	902.2	903.7	901.4
152.5°	918.7	919.5	920.2	923.2	919.5
155°	937.5	936.0	936.8	940.5	936.0
157.5°	952.5	952.5	951.8	956.3	950.3
160°	966.1	965.3	964.6	969.1	963.8
162.5°	978.9	976.6	975.9	981.1	976.6
165°	988.6	986.4	985.6	991.6	986.4
167.5°	996.9	993.9	993.9	999.9	993.9
170°	1003.7	1000.7	1000.7	1006.7	1000.7
172.5°	1008.2	1004.4	1005.2	1011.2	1004.4
175°	1011.9	1008.2	1008.9	1014.2	1008.2
177.5°	1013.4	1009.7	1010.4	1016.4	1008.9
180°	1011.9	1011.9	1011.9	1011.9	1011.9

(END OF REPORT)