

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030901

Luminaire Tested: S123DIW-B560D1535UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030901
REPORT IS A COMBINATION OF REPORTS P991660 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D1535UB2750-4F0-XX-W2A-D_3000K
Description: Define 3 Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8583.0 lumens
Efficiency: N/A
Efficacy: 112.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030901

CATALOG NUMBER: S123DIW-B560D1535UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030901

CATALOG NUMBER: S123DIW-B560D1535UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33
1	92	87	83	80	81	78	74	72	60	58	56	44	42	41	29	28	27
2	83	76	70	65	74	68	63	58	52	49	46	38	36	34	25	23	22
3	76	66	59	54	67	59	53	48	46	42	38	33	31	28	22	20	19
4	69	59	51	45	61	52	46	41	41	36	32	30	26	24	19	18	16
5	63	52	44	38	56	46	40	35	36	31	27	26	23	21	17	15	14
6	58	46	38	33	51	42	35	30	32	27	24	24	20	18	16	14	12
7	54	42	34	29	47	37	31	26	29	24	21	21	18	16	14	12	11
8	50	38	30	25	44	34	27	23	26	22	18	20	16	14	13	11	9
9	46	34	27	22	41	31	24	20	24	19	16	18	15	12	12	10	8
10	43	31	24	20	38	28	22	18	22	18	14	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7539	7539	7539
5°	7560	7318	7312
10°	7489	7120	7065
15°	7390	6901	6804
20°	7249	6657	6523
25°	7077	6382	6232
30°	6899	6133	5940
35°	6700	5873	5702
40°	6511	5634	5451
45°	6300	5403	5243
50°	6091	5174	5018
55°	5862	4940	4812
60°	5637	4699	4600
65°	5405	4444	4351
70°	5056	4156	4096
75°	4614	3828	3832
80°	4099	3498	3531
85°	3592	3230	3314

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6300 cd/sqm

TEST NUMBER: P1030901

CATALOG NUMBER: S123DIW-B560D1535UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.4	0.8
10°-20°	189.4	2.2
20°-30°	283.3	3.3
30°-40°	338.2	3.9
40°-50°	353.8	4.1
50°-60°	332.1	3.9
60°-70°	277.4	3.2
70°-80°	198.3	2.3
80°-90°	122.1	1.4
90°-100°	146.2	1.7
100°-110°	402.7	4.7
110°-120°	889.5	10.4
120°-130°	1103.8	12.9
130°-140°	1166.3	13.6
140°-150°	1083.8	12.6
150°-160°	872.6	10.2
160°-170°	563.2	6.6
170°-180°	194.1	2.3
0°-30°	539.1	6.3
0°-40°	877.3	10.2
0°-60°	1563.2	18.2
0°-90°	2161.0	25.2
90°-120°	1438.3	16.8
90°-150°	4792.2	55.8
90°-180°	6422.0	74.8
0°-180°	8583.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	700	700	700	700	700	
5°	701	700	695	701	700	67
15°	668	670	669	677	676	188
25°	603	610	613	623	623	278
35°	519	531	541	552	556	324
45°	424	442	462	476	482	327
55°	324	349	376	397	403	290
65°	224	253	287	310	317	221
75°	121	157	195	220	230	130
85°	37	76	116	142	150	38
90°	11	64	123	155	165	12
95°	101	68	122	157	164	117
105°	458	493	389	142	152	485
115°	852	870	911	945	957	841
125°	1198	1210	1238	1257	1266	1070
135°	1490	1498	1513	1531	1530	1147
145°	1718	1728	1731	1740	1743	1075
155°	1892	1889	1890	1898	1889	872
165°	1995	1990	1989	2001	1990	564
175°	2042	2034	2036	2046	2034	194
180°	2042	2042	2042	2042	2042	

TEST NUMBER: P1030901

CATALOG NUMBER: S123DIW-B560D1535UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	700.4	700.4	700.4	700.4	700.4
2.5°	704.2	702.0	695.9	702.0	701.2
5°	701.2	699.7	695.1	701.2	700.4
7.5°	695.9	695.9	691.3	698.9	698.1
10°	688.2	689.7	685.9	693.6	692.0
12.5°	679.1	681.4	679.1	685.9	684.4
15°	667.6	669.9	669.1	676.8	676.0
17.5°	653.9	658.5	657.7	664.6	663.0
20°	638.6	643.2	644.7	651.6	652.4
22.5°	622.6	627.2	629.5	638.6	637.9
25°	602.8	610.4	612.7	622.6	622.6
27.5°	583.7	592.1	596.7	605.1	605.8
30°	563.1	573.0	579.1	588.3	588.3
32.5°	540.2	551.6	560.0	570.0	572.2
35°	518.8	531.0	541.0	552.4	555.5
37.5°	495.9	509.7	521.1	534.1	536.4
40°	473.1	486.8	502.1	515.0	518.1
42.5°	447.9	465.4	481.5	495.9	500.5
45°	424.2	442.5	461.6	476.1	482.2
47.5°	399.0	419.6	441.0	457.0	461.6
50°	374.6	396.0	419.6	437.2	442.5
52.5°	348.7	371.6	398.3	416.6	423.5
55°	323.5	348.7	376.2	396.8	402.9
57.5°	299.1	325.0	354.8	375.4	382.3
60°	273.2	300.6	331.9	353.3	361.7
62.5°	248.7	277.0	310.5	331.9	339.5
65°	223.6	253.3	286.9	309.8	317.4
67.5°	198.4	229.7	263.2	288.4	294.5
70°	171.7	204.5	241.1	265.5	273.2
72.5°	147.3	180.1	218.2	243.4	251.0
75°	121.3	157.2	195.3	220.5	229.7
77.5°	99.2	135.1	173.2	199.9	206.8
80°	75.5	112.9	152.6	178.5	186.2
82.5°	54.9	93.1	133.5	159.5	167.1
85°	37.4	75.5	116.0	141.9	149.5
87.5°	22.9	61.0	100.0	125.9	133.5
90°	11.4	64.0	122.6	154.7	165.3
92.5°	44.1	67.8	119.5	155.4	163.8
95°	100.9	68.4	122.5	156.8	164.4
97.5°	176.0	161.0	119.5	154.5	163.7
100°	263.3	318.0	116.5	150.7	159.8
102.5°	362.6	403.7	174.1	145.4	156.0
105°	458.2	493.2	389.4	142.3	152.2
107.5°	559.0	588.8	642.7	429.7	237.9
110°	660.0	685.8	733.0	702.8	492.0

TEST NUMBER: P1030901

CATALOG NUMBER: S123DIW-B560D1535UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	757.0	778.4	824.0	856.7	860.6
115°	851.8	870.1	911.2	944.7	956.9
117.5°	945.9	962.6	996.2	1026.6	1034.2
120°	1031.6	1049.1	1078.7	1108.5	1113.8
122.5°	1119.6	1131.7	1161.4	1185.8	1192.7
125°	1197.7	1209.8	1238.0	1257.0	1265.5
127.5°	1276.6	1287.9	1314.6	1334.5	1336.7
130°	1349.4	1360.7	1382.1	1402.7	1404.2
132.5°	1418.4	1430.5	1446.6	1466.3	1467.1
135°	1489.7	1498.1	1512.6	1530.8	1530.1
137.5°	1550.4	1561.8	1570.1	1589.9	1590.7
140°	1610.4	1619.5	1626.3	1643.8	1644.5
142.5°	1666.5	1674.8	1679.3	1693.8	1693.0
145°	1718.1	1727.9	1730.9	1740.1	1743.2
147.5°	1767.3	1774.9	1777.9	1783.3	1778.7
150°	1812.8	1817.4	1820.4	1823.5	1820.4
152.5°	1853.8	1855.3	1856.8	1862.9	1855.3
155°	1891.7	1888.7	1890.2	1897.8	1888.7
157.5°	1922.1	1922.1	1920.5	1929.6	1917.5
160°	1949.4	1947.9	1946.3	1955.4	1944.8
162.5°	1975.2	1970.6	1969.1	1979.7	1970.6
165°	1994.9	1990.3	1988.8	2000.9	1990.3
167.5°	2011.6	2005.5	2005.5	2017.6	2005.5
170°	2025.2	2019.2	2019.2	2031.3	2019.2
172.5°	2034.3	2026.7	2028.3	2040.4	2026.7
175°	2041.9	2034.3	2035.8	2046.5	2034.3
177.5°	2044.9	2037.4	2038.9	2051.0	2035.8
180°	2041.9	2041.9	2041.9	2041.9	2041.9

(END OF REPORT)