

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030907

Luminaire Tested: S123DIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030907
REPORT IS A COMBINATION OF REPORTS P991668 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B560D1535UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8574.0 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030907

CATALOG NUMBER: S123DIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1030907

CATALOG NUMBER: S123DIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	29
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	43	40	35	33	30	24	22	21
4	70	60	52	46	62	54	47	42	42	38	34	31	28	26	21	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	47	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14
7	55	43	35	30	49	38	32	27	30	26	22	23	20	17	16	14	12
8	50	39	31	26	45	35	28	24	28	23	19	21	18	15	15	12	11
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	13	11	10
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9591	9591	9591
5°	9615	9261	9246
10°	9529	8946	8855
15°	9397	8621	8428
20°	9245	8259	8005
25°	9049	7877	7554
30°	8834	7482	7078
35°	8609	7078	6607
40°	8372	6654	6142
45°	8113	6241	5656
50°	7849	5781	5170
55°	7510	5302	4676
60°	7162	4773	4151
65°	6834	4200	3603
70°	6364	3567	2964
75°	5683	2823	2301
80°	4908	1985	1627
85°	3823	1067	816

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8113 cd/sqm

TEST NUMBER: P1030907

CATALOG NUMBER: S123DIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.0	1.0
10°-20°	237.2	2.8
20°-30°	350.3	4.1
30°-40°	409.1	4.8
40°-50°	411.3	4.8
50°-60°	361.3	4.2
60°-70°	269.1	3.1
70°-80°	153.1	1.8
80°-90°	47.6	0.6
90°-100°	72.3	0.8
100°-110°	349.6	4.1
110°-120°	856.7	10.0
120°-130°	1087.5	12.7
130°-140°	1161.8	13.5
140°-150°	1086.4	12.7
150°-160°	876.3	10.2
160°-170°	565.5	6.6
170°-180°	194.9	2.3
0°-30°	671.5	7.8
0°-40°	1080.6	12.6
0°-60°	1853.3	21.6
0°-90°	2323.1	27.1
90°-120°	1278.6	14.9
90°-150°	4614.2	53.8
90°-180°	6251.0	72.9
0°-180°	8574.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	892	888	880	887	886	85
15°	849	846	836	842	837	239
25°	771	766	756	757	755	355
35°	667	662	652	647	644	417
45°	546	543	533	524	520	422
55°	414	414	404	395	392	371
65°	283	279	271	265	263	279
75°	149	146	144	140	138	160
85°	40	38	38	37	37	43
90°	2	17	37	43	46	8
95°	93	30	47	58	58	111
105°	454	471	334	64	67	481
115°	852	861	874	890	896	841
125°	1200	1213	1219	1222	1225	1073
135°	1494	1504	1510	1514	1510	1151
145°	1724	1735	1738	1741	1741	1080
155°	1900	1897	1898	1906	1897	875
165°	2003	1999	1997	2009	1999	566
175°	2050	2043	2044	2055	2043	195
180°	2050	2050	2050	2050	2050	

TEST NUMBER: P1030907

CATALOG NUMBER: S123DIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	891.0	891.0	891.0	891.0	891.0
2.5°	894.9	891.8	883.4	891.0	890.3
5°	891.8	888.0	879.6	887.2	885.7
7.5°	884.9	881.1	872.7	879.6	878.8
10°	875.7	871.9	861.9	868.8	867.3
12.5°	863.5	860.4	851.2	855.8	855.0
15°	848.9	845.8	835.9	842.0	837.4
17.5°	832.8	829.0	819.0	823.6	822.1
20°	814.4	809.8	799.9	802.9	800.6
22.5°	793.7	789.1	779.2	781.5	778.4
25°	770.8	766.2	756.2	757.0	754.7
27.5°	747.0	742.4	731.7	732.5	730.2
30°	721.0	717.1	706.4	706.4	701.0
32.5°	694.9	689.5	681.9	676.5	674.2
35°	666.6	662.0	652.0	647.4	643.6
37.5°	638.2	632.1	622.1	616.8	614.5
40°	608.3	603.7	593.0	586.9	583.8
42.5°	578.5	573.1	562.4	556.2	553.2
45°	546.3	543.2	533.2	524.1	520.2
47.5°	514.9	510.3	501.1	491.9	488.8
50°	482.7	478.9	468.9	460.5	455.9
52.5°	449.0	446.7	435.9	429.1	424.5
55°	414.5	413.7	403.8	395.3	391.5
57.5°	382.3	379.3	371.6	363.9	359.3
60°	347.1	346.3	337.1	330.2	326.4
62.5°	315.7	313.4	304.2	297.3	295.0
65°	282.7	278.9	271.2	265.1	262.8
67.5°	247.5	244.4	238.3	232.9	229.8
70°	216.1	211.5	206.9	201.5	197.7
72.5°	183.1	180.0	174.7	170.1	168.6
75°	149.4	146.3	144.0	140.2	137.9
77.5°	119.5	118.0	114.9	111.9	111.9
80°	90.4	88.1	86.6	85.8	85.8
82.5°	62.1	62.1	62.1	60.5	59.8
85°	39.8	38.3	38.3	36.8	36.8
87.5°	19.9	17.6	16.9	16.1	16.1
90°	1.5	16.8	36.6	42.7	45.7
92.5°	35.0	25.9	39.6	50.3	51.8
95°	92.9	30.5	47.2	57.9	57.9
97.5°	169.1	126.4	48.7	60.9	62.5
100°	257.4	287.9	50.3	62.5	64.0
102.5°	358.0	377.8	112.7	62.5	65.5
105°	454.0	470.7	333.6	64.0	67.0
107.5°	556.0	569.7	592.6	358.0	158.4
110°	658.1	670.3	687.0	636.8	418.9

TEST NUMBER: P1030907

CATALOG NUMBER: S123DIW-B560D1535UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	755.6	766.2	783.0	796.7	793.7
115°	851.6	860.7	874.4	889.6	895.7
117.5°	946.0	956.7	964.3	976.5	978.0
120°	1032.8	1046.5	1051.1	1063.3	1063.3
122.5°	1121.2	1131.8	1137.9	1145.6	1147.1
125°	1200.4	1212.6	1218.7	1221.7	1224.8
127.5°	1279.6	1291.8	1299.4	1304.0	1300.9
130°	1352.7	1364.9	1371.0	1377.1	1374.1
132.5°	1422.8	1435.0	1439.6	1445.7	1441.1
135°	1494.4	1503.5	1509.6	1514.2	1509.6
137.5°	1555.3	1567.5	1570.6	1578.2	1575.1
140°	1616.3	1625.4	1630.0	1636.1	1633.0
142.5°	1672.6	1681.8	1686.3	1690.9	1686.3
145°	1724.4	1735.1	1738.1	1741.2	1741.2
147.5°	1774.7	1782.3	1785.4	1788.4	1780.8
150°	1820.4	1825.0	1828.0	1831.1	1826.5
152.5°	1861.5	1863.1	1864.6	1870.7	1863.1
155°	1899.6	1896.6	1898.1	1905.7	1896.6
157.5°	1930.1	1930.1	1928.6	1937.7	1925.5
160°	1957.5	1956.0	1954.5	1963.6	1952.9
162.5°	1983.4	1978.8	1977.3	1988.0	1978.8
165°	2003.2	1998.6	1997.1	2009.3	1998.6
167.5°	2020.0	2013.9	2013.9	2026.1	2013.9
170°	2033.7	2027.6	2027.6	2039.8	2027.6
172.5°	2042.8	2035.2	2036.7	2048.9	2035.2
175°	2050.4	2042.8	2044.3	2055.0	2042.8
177.5°	2053.5	2045.9	2047.4	2059.6	2044.3
180°	2050.4	2050.4	2050.4	2050.4	2050.4

(END OF REPORT)