

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031346

Luminaire Tested: S123DIW-B1000D1535UB50-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031346
REPORT IS A COMBINATION OF REPORTS P990714 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D1535UB50-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9926.0 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031346

CATALOG NUMBER: S123DIW-B1000D1535UB50-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1031346

CATALOG NUMBER: S123DIW-B1000D1535UB50-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47
1	95	91	87	84	87	83	80	77	68	66	64	54	52	51	41	40	39
2	87	80	73	68	79	73	67	63	59	56	53	47	45	43	36	35	33
3	79	70	63	57	72	64	58	53	52	48	44	42	39	36	32	30	28
4	72	62	54	48	66	56	50	44	46	41	38	37	34	31	29	26	24
5	66	55	47	41	60	50	43	38	42	36	32	33	30	27	26	23	21
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	21	18
7	56	44	37	31	51	41	34	29	34	29	25	27	23	20	21	19	16
8	52	40	33	27	47	37	30	25	31	26	22	25	21	18	20	17	15
9	49	37	29	24	44	34	27	23	28	23	19	23	19	16	18	15	13
10	45	34	26	22	41	31	25	20	26	21	17	21	17	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16283	16283	16283
5°	16323	15721	15697
10°	16178	15189	15033
15°	15953	14635	14309
20°	15696	14022	13592
25°	15362	13373	12824
30°	14997	12702	12018
35°	14614	12016	11216
40°	14214	11298	10428
45°	13773	10596	9603
50°	13326	9815	8776
55°	12751	9001	7939
60°	12158	8103	7047
65°	11603	7132	6116
70°	10802	6054	5032
75°	9647	4793	3906
80°	8333	3369	2763
85°	6493	1810	1383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13773 cd/sqm

TEST NUMBER: P1031346

CATALOG NUMBER: S123DIW-B1000D1535UB50-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	142.6	1.4
10°-20°	402.7	4.1
20°-30°	594.7	6.0
30°-40°	694.6	7.0
40°-50°	698.3	7.0
50°-60°	613.4	6.2
60°-70°	456.8	4.6
70°-80°	260.0	2.6
80°-90°	77.8	0.8
90°-100°	69.2	0.7
100°-110°	334.7	3.4
110°-120°	820.2	8.3
120°-130°	1041.3	10.5
130°-140°	1112.4	11.2
140°-150°	1040.2	10.5
150°-160°	839.0	8.5
160°-170°	541.5	5.5
170°-180°	186.6	1.9
0°-30°	1140.0	11.5
0°-40°	1834.6	18.5
0°-60°	3146.3	31.7
0°-90°	3940.9	39.7
90°-120°	1224.2	12.3
90°-150°	4418.0	44.5
90°-180°	5985.0	60.3
0°-180°	9926.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1513	1513	1513	1513	1513	
5°	1514	1508	1493	1506	1504	144
15°	1441	1436	1419	1430	1422	406
25°	1308	1301	1284	1285	1281	603
35°	1132	1124	1107	1099	1093	708
45°	927	922	905	890	883	716
55°	704	702	686	671	665	630
65°	480	474	460	450	446	474
75°	254	248	244	238	234	271
85°	68	65	65	62	62	73
90°	2	16	35	41	44	10
95°	89	29	45	55	55	106
105°	435	451	319	61	64	461
115°	815	824	837	852	858	805
125°	1149	1161	1167	1170	1173	1027
135°	1431	1440	1445	1450	1445	1102
145°	1651	1661	1664	1667	1667	1034
155°	1819	1816	1817	1825	1816	838
165°	1918	1914	1912	1924	1914	542
175°	1963	1956	1957	1968	1956	187
180°	1963	1963	1963	1963	1963	

TEST NUMBER: P1031346

CATALOG NUMBER: S123DIW-B1000D1535UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1512.7	1512.7	1512.7	1512.7	1512.7
2.5°	1519.2	1514.0	1499.7	1512.7	1511.4
5°	1514.0	1507.5	1493.2	1506.2	1503.6
7.5°	1502.3	1495.8	1481.5	1493.2	1491.9
10°	1486.7	1480.2	1463.3	1475.0	1472.4
12.5°	1465.9	1460.7	1445.1	1452.9	1451.6
15°	1441.2	1436.0	1419.1	1429.5	1421.7
17.5°	1413.9	1407.4	1390.5	1398.3	1395.7
20°	1382.7	1374.9	1358.0	1363.2	1359.3
22.5°	1347.6	1339.7	1322.8	1326.7	1321.5
25°	1308.5	1300.7	1283.8	1285.1	1281.2
27.5°	1268.2	1260.4	1242.2	1243.5	1239.6
30°	1224.0	1217.5	1199.3	1199.3	1190.2
32.5°	1179.8	1170.7	1157.6	1148.5	1144.6
35°	1131.6	1123.8	1106.9	1099.1	1092.6
37.5°	1083.5	1073.1	1056.2	1047.1	1043.2
40°	1032.8	1025.0	1006.8	996.4	991.2
42.5°	982.0	972.9	954.7	944.3	939.1
45°	927.4	922.2	905.3	889.7	883.2
47.5°	874.1	866.3	850.7	835.1	829.9
50°	819.5	813.0	796.0	781.7	773.9
52.5°	762.2	758.3	740.1	728.4	720.6
55°	703.7	702.4	685.5	671.2	664.7
57.5°	649.1	643.9	630.9	617.8	610.0
60°	589.2	587.9	572.3	560.6	554.1
62.5°	535.9	532.0	516.4	504.7	500.8
65°	480.0	473.5	460.5	450.1	446.1
67.5°	420.1	414.9	404.5	395.4	390.2
70°	366.8	359.0	351.2	342.1	335.6
72.5°	310.9	305.7	296.6	288.8	286.2
75°	253.6	248.4	244.5	238.0	234.1
77.5°	202.9	200.3	195.1	189.9	189.9
80°	153.5	149.6	147.0	145.7	145.7
82.5°	105.4	105.4	105.4	102.8	101.5
85°	67.6	65.0	65.0	62.4	62.4
87.5°	33.8	29.9	28.6	27.3	27.3
90°	1.5	16.0	35.0	40.8	43.8
92.5°	33.5	24.8	37.9	48.1	49.6
95°	89.0	29.2	45.2	55.4	55.4
97.5°	161.9	121.1	46.7	58.3	59.8
100°	246.5	275.7	48.1	59.8	61.3
102.5°	342.8	361.7	107.9	59.8	62.7
105°	434.7	450.7	319.4	61.3	64.2
107.5°	532.4	545.5	567.4	342.8	151.7
110°	630.1	641.8	657.8	609.7	401.1

TEST NUMBER: P1031346

CATALOG NUMBER: S123DIW-B1000D1535UB50-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	723.4	733.7	749.7	762.8	759.9
115°	815.3	824.1	837.2	851.8	857.6
117.5°	905.8	916.0	923.3	934.9	936.4
120°	988.9	1002.0	1006.4	1018.1	1018.1
122.5°	1073.5	1083.7	1089.5	1096.8	1098.3
125°	1149.4	1161.0	1166.9	1169.8	1172.7
127.5°	1225.2	1236.9	1244.2	1248.5	1245.6
130°	1295.2	1306.9	1312.7	1318.5	1315.6
132.5°	1362.3	1374.0	1378.3	1384.2	1379.8
135°	1430.9	1439.6	1445.4	1449.8	1445.4
137.5°	1489.2	1500.9	1503.8	1511.1	1508.2
140°	1547.5	1556.3	1560.7	1566.5	1563.6
142.5°	1601.5	1610.3	1614.6	1619.0	1614.6
145°	1651.1	1661.3	1664.2	1667.1	1667.1
147.5°	1699.2	1706.5	1709.4	1712.4	1705.1
150°	1743.0	1747.4	1750.3	1753.2	1748.8
152.5°	1782.4	1783.8	1785.3	1791.1	1783.8
155°	1818.8	1815.9	1817.4	1824.7	1815.9
157.5°	1848.0	1848.0	1846.5	1855.3	1843.6
160°	1874.3	1872.8	1871.3	1880.1	1869.9
162.5°	1899.1	1894.7	1893.2	1903.4	1894.7
165°	1918.0	1913.6	1912.2	1923.9	1913.6
167.5°	1934.1	1928.2	1928.2	1939.9	1928.2
170°	1947.2	1941.4	1941.4	1953.0	1941.4
172.5°	1955.9	1948.6	1950.1	1961.8	1948.6
175°	1963.2	1955.9	1957.4	1967.6	1955.9
177.5°	1966.1	1958.9	1960.3	1972.0	1957.4
180°	1963.2	1963.2	1963.2	1963.2	1963.2

(END OF REPORT)