

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031394

Luminaire Tested: S123DIW-B1000D755UB35-4F0-XX-W2A-F

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031394
REPORT IS A COMBINATION OF REPORTS P990828 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1000D755UB35-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7200.0 lumens
Efficiency: N/A
Efficacy: 102.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031394

CATALOG NUMBER: S123DIW-B1000D755UB35-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1031394

CATALOG NUMBER: S123DIW-B1000D755UB35-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	63	63	63
1	99	95	91	87	92	89	85	82	77	74	72	65	64	62	55	54	53
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44
3	82	73	65	59	76	68	61	56	59	54	50	51	47	44	43	40	38
4	75	64	56	50	70	60	53	48	53	47	42	45	41	37	38	35	33
5	69	57	49	43	64	54	46	41	47	41	37	41	36	32	35	31	28
6	64	52	43	37	59	48	41	36	42	36	32	37	32	28	31	28	25
7	59	47	39	33	55	44	36	31	38	33	28	33	29	25	29	25	22
8	55	42	34	29	51	40	33	28	35	29	25	31	26	22	26	23	20
9	51	39	31	26	48	36	30	25	32	26	22	28	24	20	24	21	18
10	48	36	28	23	44	34	27	22	30	24	20	26	22	18	23	19	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17011	17011	17011
5°	17053	16424	16400
10°	16902	15868	15705
15°	16666	15289	14948
20°	16397	14649	14199
25°	16048	13971	13398
30°	15667	13270	12555
35°	15267	12554	11718
40°	14848	11803	10894
45°	14389	11071	10033
50°	13921	10253	9168
55°	13321	9403	8294
60°	12702	8465	7362
65°	12121	7450	6390
70°	11285	6325	5257
75°	10080	5009	4081
80°	8703	3521	2886
85°	6791	1891	1445

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14389 cd/sqm

TEST NUMBER: P1031394

CATALOG NUMBER: S123DIW-B1000D755UB35-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	149.0	2.1
10°-20°	420.7	5.8
20°-30°	621.3	8.6
30°-40°	725.6	10.1
40°-50°	729.5	10.1
50°-60°	640.8	8.9
60°-70°	477.3	6.6
70°-80°	271.6	3.8
80°-90°	79.2	1.1
90°-100°	35.7	0.5
100°-110°	172.5	2.4
110°-120°	422.8	5.9
120°-130°	536.7	7.5
130°-140°	573.4	8.0
140°-150°	536.2	7.4
150°-160°	432.5	6.0
160°-170°	279.1	3.9
170°-180°	96.2	1.3
0°-30°	1191.0	16.5
0°-40°	1916.6	26.6
0°-60°	3286.9	45.7
0°-90°	4115.0	57.2
90°-120°	631.0	8.8
90°-150°	2277.3	31.6
90°-180°	3085.0	42.8
0°-180°	7200.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1580	1580	1580	1580	1580	
5°	1582	1575	1560	1574	1571	150
15°	1506	1500	1482	1493	1485	425
25°	1367	1359	1341	1343	1338	630
35°	1182	1174	1156	1148	1142	740
45°	969	963	946	930	923	748
55°	735	734	716	701	694	659
65°	501	495	481	470	466	495
75°	265	260	256	249	245	283
85°	71	68	68	65	65	76
90°	1	8	18	21	23	7
95°	46	15	23	29	29	55
105°	224	232	165	32	33	238
115°	420	425	432	439	442	415
125°	592	598	601	603	604	529
135°	738	742	745	747	745	568
145°	851	856	858	859	859	533
155°	938	936	937	940	936	432
165°	989	986	986	992	986	279
175°	1012	1008	1009	1014	1008	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1031394

CATALOG NUMBER: S123DIW-B1000D755UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1580.4	1580.4	1580.4	1580.4	1580.4
2.5°	1587.2	1581.7	1566.8	1580.4	1579.0
5°	1581.7	1574.9	1560.0	1573.6	1570.9
7.5°	1569.5	1562.7	1547.8	1560.0	1558.6
10°	1553.2	1546.4	1528.7	1541.0	1538.2
12.5°	1531.4	1526.0	1509.7	1517.9	1516.5
15°	1505.6	1500.2	1482.5	1493.4	1485.2
17.5°	1477.1	1470.3	1452.6	1460.8	1458.1
20°	1444.5	1436.3	1418.7	1424.1	1420.0
22.5°	1407.8	1399.6	1382.0	1386.1	1380.6
25°	1367.0	1358.9	1341.2	1342.6	1338.5
27.5°	1324.9	1316.7	1297.7	1299.1	1295.0
30°	1278.7	1271.9	1252.9	1252.9	1243.4
32.5°	1232.5	1223.0	1209.4	1199.9	1195.8
35°	1182.2	1174.1	1156.4	1148.2	1141.5
37.5°	1131.9	1121.1	1103.4	1093.9	1089.8
40°	1078.9	1070.8	1051.8	1040.9	1035.5
42.5°	1025.9	1016.4	997.4	986.5	981.1
45°	968.9	963.4	945.8	929.5	922.7
47.5°	913.2	905.0	888.7	872.4	867.0
50°	856.1	849.3	831.6	816.7	808.5
52.5°	796.3	792.2	773.2	761.0	752.8
55°	735.2	733.8	716.1	701.2	694.4
57.5°	678.1	672.6	659.1	645.5	637.3
60°	615.6	614.2	597.9	585.7	578.9
62.5°	559.9	555.8	539.5	527.2	523.2
65°	501.4	494.6	481.0	470.2	466.1
67.5°	438.9	433.5	422.6	413.1	407.7
70°	383.2	375.0	366.9	357.4	350.6
72.5°	324.8	319.3	309.8	301.7	299.0
75°	265.0	259.5	255.5	248.7	244.6
77.5°	212.0	209.3	203.8	198.4	198.4
80°	160.3	156.3	153.6	152.2	152.2
82.5°	110.1	110.1	110.1	107.4	106.0
85°	70.7	67.9	67.9	65.2	65.2
87.5°	35.3	31.3	29.9	28.5	28.5
90°	0.8	8.3	18.0	21.1	22.6
92.5°	17.3	12.8	19.5	24.8	25.6
95°	45.9	15.0	23.3	28.6	28.6
97.5°	83.5	62.4	24.1	30.1	30.8
100°	127.1	142.1	24.8	30.8	31.6
102.5°	176.7	186.4	55.6	30.8	32.3
105°	224.0	232.3	164.6	31.6	33.1
107.5°	274.4	281.2	292.5	176.7	78.2
110°	324.8	330.8	339.1	314.3	206.7



TEST NUMBER: P1031394

CATALOG NUMBER: S123DIW-B1000D755UB35-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.9	378.2	386.4	393.2	391.7
115°	420.3	424.8	431.5	439.1	442.1
117.5°	466.9	472.1	475.9	481.9	482.7
120°	509.7	516.5	518.7	524.8	524.8
122.5°	553.3	558.6	561.6	565.4	566.1
125°	592.4	598.4	601.4	603.0	604.5
127.5°	631.5	637.5	641.3	643.6	642.0
130°	667.6	673.6	676.6	679.6	678.1
132.5°	702.2	708.2	710.5	713.5	711.2
135°	737.5	742.0	745.0	747.3	745.0
137.5°	767.6	773.6	775.1	778.9	777.4
140°	797.7	802.2	804.4	807.4	805.9
142.5°	825.5	830.0	832.3	834.5	832.3
145°	851.1	856.3	857.8	859.3	859.3
147.5°	875.9	879.6	881.1	882.6	878.9
150°	898.4	900.7	902.2	903.7	901.4
152.5°	918.7	919.5	920.2	923.2	919.5
155°	937.5	936.0	936.8	940.5	936.0
157.5°	952.5	952.5	951.8	956.3	950.3
160°	966.1	965.3	964.6	969.1	963.8
162.5°	978.9	976.6	975.9	981.1	976.6
165°	988.6	986.4	985.6	991.6	986.4
167.5°	996.9	993.9	993.9	999.9	993.9
170°	1003.7	1000.7	1000.7	1006.7	1000.7
172.5°	1008.2	1004.4	1005.2	1011.2	1004.4
175°	1011.9	1008.2	1008.9	1014.2	1008.2
177.5°	1013.4	1009.7	1010.4	1016.4	1008.9
180°	1011.9	1011.9	1011.9	1011.9	1011.9

(END OF REPORT)