

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1030994

Luminaire Tested: S123DIW-B775D460UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1030994
REPORT IS A COMBINATION OF REPORTS P992060 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B775D460UB2750-4F0-XX-W2A-F1_5000K
Description: Define 3 Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4618.0 lumens
Efficiency: N/A
Efficacy: 94.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 49.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1030994

CATALOG NUMBER: S123DIW-B775D460UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1030994

CATALOG NUMBER: S123DIW-B775D460UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66		
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56		
2	92	85	78	73	87	80	74	69	71	67	63	63	59	56	55	53	50	47		
3	84	74	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	39		
4	77	66	58	51	72	62	55	49	56	50	45	49	45	41	44	40	37	34		
5	71	59	50	44	66	56	48	42	50	44	39	44	39	36	39	35	32	29		
6	65	53	44	38	61	50	43	37	45	39	34	40	35	31	36	32	28	26		
7	60	48	40	34	57	45	38	33	41	35	30	37	31	28	33	28	25	23		
8	56	43	36	30	53	41	34	29	37	31	27	34	28	25	30	26	23	20		
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	20	18		
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12668	12668	12668
5°	12699	12231	12212
10°	12587	11818	11695
15°	12412	11387	11133
20°	12211	10909	10574
25°	11951	10404	9978
30°	11668	9882	9350
35°	11370	9349	8726
40°	11058	8790	8112
45°	10715	8244	7471
50°	10367	7636	6828
55°	9920	7003	6176
60°	9459	6305	5482
65°	9026	5548	4759
70°	8405	4710	3915
75°	7505	3730	3040
80°	6482	2622	2149
85°	5052	1409	1077

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10715 cd/sqm

TEST NUMBER: P1030994

CATALOG NUMBER: S123DIW-B775D460UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.0	2.4
10°-20°	313.3	6.8
20°-30°	462.7	10.0
30°-40°	540.4	11.7
40°-50°	543.3	11.8
50°-60°	477.2	10.3
60°-70°	355.4	7.7
70°-80°	202.3	4.4
80°-90°	58.7	1.3
90°-100°	36.1	0.8
100°-110°	109.3	2.4
110°-120°	186.0	4.0
120°-130°	244.7	5.3
130°-140°	275.0	6.0
140°-150°	270.4	5.9
150°-160°	227.7	4.9
160°-170°	151.6	3.3
170°-180°	53.1	1.1
0°-30°	886.9	19.2
0°-40°	1427.3	30.9
0°-60°	2447.8	53.0
0°-90°	3064.2	66.4
90°-120°	331.4	7.2
90°-150°	1121.5	24.3
90°-180°	1554.0	33.7
0°-180°	4618.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1177	1177	1177	1177	1177	
5°	1178	1173	1162	1172	1170	112
15°	1121	1117	1104	1112	1106	316
25°	1018	1012	999	1000	997	469
35°	880	874	861	855	850	551
45°	722	718	704	692	687	557
55°	548	546	533	522	517	490
65°	373	368	358	350	347	368
75°	197	193	190	185	182	211
85°	53	51	51	49	49	56
90°	0	5	11	12	13	6
95°	26	29	33	34	34	29
105°	99	100	104	104	105	106
115°	187	188	188	188	188	185
125°	274	275	274	273	271	244
135°	356	358	358	356	355	274
145°	431	432	434	433	431	269
155°	494	494	494	496	493	227
165°	538	536	536	539	536	152
175°	560	558	558	560	557	53
180°	561	561	561	561	561	

TEST NUMBER: P1030994

CATALOG NUMBER: S123DIW-B775D460UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1176.9	1176.9	1176.9	1176.9	1176.9
2.5°	1182.0	1177.9	1166.8	1176.9	1175.9
5°	1177.9	1172.9	1161.7	1171.9	1169.8
7.5°	1168.8	1163.8	1152.6	1161.7	1160.7
10°	1156.7	1151.6	1138.5	1147.6	1145.5
12.5°	1140.5	1136.4	1124.3	1130.4	1129.4
15°	1121.3	1117.2	1104.1	1112.2	1106.1
17.5°	1100.0	1095.0	1081.8	1087.9	1085.8
20°	1075.7	1069.7	1056.5	1060.5	1057.5
22.5°	1048.4	1042.3	1029.2	1032.2	1028.2
25°	1018.0	1012.0	998.8	999.8	996.8
27.5°	986.7	980.6	966.4	967.4	964.4
30°	952.3	947.2	933.0	933.0	926.0
32.5°	917.9	910.8	900.7	893.6	890.5
35°	880.4	874.3	861.2	855.1	850.1
37.5°	843.0	834.9	821.7	814.6	811.6
40°	803.5	797.4	783.3	775.2	771.1
42.5°	764.0	757.0	742.8	734.7	730.6
45°	721.5	717.5	704.3	692.2	687.1
47.5°	680.0	674.0	661.8	649.7	645.6
50°	637.5	632.5	619.3	608.2	602.1
52.5°	593.0	590.0	575.8	566.7	560.6
55°	547.5	546.5	533.3	522.2	517.1
57.5°	505.0	500.9	490.8	480.7	474.6
60°	458.4	457.4	445.3	436.2	431.1
62.5°	416.9	413.9	401.8	392.6	389.6
65°	373.4	368.4	358.2	350.1	347.1
67.5°	326.9	322.8	314.7	307.6	303.6
70°	285.4	279.3	273.2	266.1	261.1
72.5°	241.9	237.8	230.7	224.7	222.6
75°	197.3	193.3	190.3	185.2	182.2
77.5°	157.9	155.8	151.8	147.7	147.7
80°	119.4	116.4	114.4	113.3	113.3
82.5°	82.0	82.0	82.0	79.9	78.9
85°	52.6	50.6	50.6	48.6	48.6
87.5°	26.3	23.3	22.3	21.3	21.3
90°	0.4	4.8	10.6	12.3	13.2
92.5°	13.2	15.9	18.5	19.8	18.9
95°	26.0	29.1	32.6	34.4	34.4
97.5°	42.7	44.9	47.6	49.8	49.3
100°	59.9	62.6	64.8	66.1	67.0
102.5°	79.7	81.1	84.1	85.5	85.0
105°	99.1	100.0	104.0	104.0	104.8
107.5°	122.0	122.5	124.2	125.5	125.1
110°	143.2	144.0	144.9	146.7	145.8

TEST NUMBER: P1030994

CATALOG NUMBER: S123DIW-B775D460UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.2	165.6	165.6	167.8	167.8
115°	187.2	188.5	187.7	188.1	187.7
117.5°	209.7	210.1	209.2	209.2	207.9
120°	230.4	233.0	230.8	230.4	229.5
122.5°	252.0	253.7	252.9	251.5	250.2
125°	274.0	275.3	274.4	272.7	270.9
127.5°	294.3	296.9	296.0	293.4	291.6
130°	314.5	318.1	316.7	315.0	311.9
132.5°	334.8	338.3	337.4	335.2	333.0
135°	355.5	358.1	357.7	355.9	355.1
137.5°	374.4	376.6	378.0	375.8	374.4
140°	394.3	396.5	396.9	396.5	393.4
142.5°	412.3	414.5	415.4	415.0	412.8
145°	431.3	432.1	433.5	433.0	431.3
147.5°	447.6	449.3	450.6	450.6	448.0
150°	464.7	465.6	466.5	466.5	463.9
152.5°	478.8	480.2	480.6	481.5	479.3
155°	493.8	493.8	494.3	496.0	492.9
157.5°	506.6	506.2	506.6	508.4	505.7
160°	518.5	517.6	517.6	519.8	518.0
162.5°	529.1	527.7	528.2	530.4	527.3
165°	537.9	536.5	536.5	539.2	536.1
167.5°	545.4	543.6	544.0	546.7	544.0
170°	551.5	549.8	549.8	552.8	549.8
172.5°	556.4	554.6	554.6	557.3	554.2
175°	559.5	557.7	557.7	560.3	557.3
177.5°	561.2	559.5	559.5	562.1	559.0
180°	560.8	560.8	560.8	560.8	560.8

(END OF REPORT)