

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031007

Luminaire Tested: S123DIW-B775D755UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031007
REPORT IS A COMBINATION OF REPORTS P992123 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B775D755UB2750-4F0-XX-W2A-D_3500K
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6348.0 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.25 / 1.37
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 59.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031007

CATALOG NUMBER: S123DIW-B775D755UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1031007

CATALOG NUMBER: S123DIW-B775D755UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53			47
1	96	91	87	83	88	84	80	77	70	67	65	57	55	54	46	44	43			38
2	87	79	73	67	80	73	67	62	61	57	53	50	47	44	40	37	36			31
3	79	69	62	56	72	64	57	52	53	48	44	44	40	37	35	32	30			26
4	72	61	53	47	66	56	49	44	47	42	37	39	35	31	31	28	25			22
5	66	54	46	40	61	50	43	37	42	36	32	35	30	27	28	25	22			19
6	61	49	40	34	56	45	37	32	38	32	28	31	27	23	25	22	19			16
7	56	44	36	30	51	40	33	28	34	29	24	28	24	21	23	20	17			14
8	52	40	32	26	48	37	30	25	31	26	22	26	22	18	21	18	15			13
9	49	36	29	23	44	34	27	22	29	23	19	24	20	16	19	16	14			11
10	45	33	26	21	42	31	24	20	26	21	17	22	18	15	18	15	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10444	10444	10444
5°	10473	10138	10130
10°	10375	9863	9788
15°	10238	9560	9426
20°	10043	9222	9036
25°	9803	8842	8633
30°	9558	8496	8228
35°	9281	8135	7899
40°	9019	7805	7550
45°	8728	7485	7263
50°	8440	7167	6951
55°	8121	6842	6666
60°	7808	6510	6371
65°	7487	6155	6028
70°	7003	5758	5674
75°	6394	5305	5309
80°	5679	4846	4891
85°	4976	4475	4593

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8728 cd/sqm

TEST NUMBER: P1031007

CATALOG NUMBER: S123DIW-B775D755UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	92.0	1.5
10°-20°	262.4	4.1
20°-30°	392.4	6.2
30°-40°	468.5	7.4
40°-50°	490.2	7.7
50°-60°	460.0	7.2
60°-70°	384.2	6.1
70°-80°	274.7	4.3
80°-90°	165.5	2.6
90°-100°	138.4	2.2
100°-110°	248.0	3.9
110°-120°	473.2	7.5
120°-130°	565.5	8.9
130°-140°	586.3	9.2
140°-150°	538.9	8.5
150°-160°	432.5	6.8
160°-170°	279.1	4.4
170°-180°	96.2	1.5
0°-30°	746.8	11.8
0°-40°	1215.3	19.1
0°-60°	2165.5	34.1
0°-90°	2990.0	47.1
90°-120°	859.7	13.5
90°-150°	2550.3	40.2
90°-180°	3358.0	52.9
0°-180°	6348.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	970	970	970	970	970	
5°	971	969	963	971	970	92
15°	925	928	927	938	936	261
25°	835	846	849	862	862	385
35°	719	736	749	765	770	449
45°	588	613	640	660	668	453
55°	448	483	521	550	558	401
65°	310	351	397	429	440	306
75°	168	218	271	306	318	180
85°	52	105	161	197	207	53
90°	14	74	137	176	188	12
95°	58	68	128	166	177	64
105°	232	266	244	140	152	246
115°	426	443	488	520	532	421
125°	596	602	635	659	668	533
135°	740	743	758	779	782	569
145°	852	856	858	868	872	533
155°	938	936	937	940	936	432
165°	989	986	986	992	986	279
175°	1012	1008	1009	1014	1008	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1031007

CATALOG NUMBER: S123DIW-B775D755UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	970.3	970.3	970.3	970.3	970.3
2.5°	975.6	972.4	964.0	972.4	971.4
5°	971.4	969.3	962.9	971.4	970.3
7.5°	964.0	964.0	957.6	968.2	967.1
10°	953.4	955.5	950.2	960.8	958.7
12.5°	940.7	943.9	940.7	950.2	948.1
15°	924.9	928.0	927.0	937.5	936.5
17.5°	905.8	912.2	911.1	920.6	918.5
20°	884.7	891.0	893.1	902.7	903.7
22.5°	862.5	868.8	872.0	884.7	883.6
25°	835.0	845.6	848.8	862.5	862.5
27.5°	808.6	820.2	826.6	838.2	839.2
30°	780.1	793.8	802.2	814.9	814.9
32.5°	748.3	764.2	775.8	789.6	792.7
35°	718.7	735.7	749.4	765.3	769.5
37.5°	687.0	706.1	721.9	739.9	743.1
40°	655.3	674.4	695.5	713.5	717.7
42.5°	620.4	644.8	667.0	687.0	693.4
45°	587.7	613.0	639.5	659.6	668.0
47.5°	552.8	581.3	610.9	633.1	639.5
50°	519.0	548.6	581.3	605.7	613.0
52.5°	483.0	514.8	551.7	577.1	586.6
55°	448.2	483.0	521.1	549.6	558.1
57.5°	414.3	450.3	491.5	520.0	529.5
60°	378.4	416.5	459.8	489.4	501.0
62.5°	344.6	383.7	430.2	459.8	470.4
65°	309.7	350.9	397.4	429.1	439.7
67.5°	274.8	318.2	364.7	399.5	408.0
70°	237.8	283.3	334.0	367.8	378.4
72.5°	204.0	249.4	302.3	337.2	347.7
75°	168.1	217.7	270.6	305.5	318.2
77.5°	137.4	187.1	239.9	276.9	286.4
80°	104.6	156.4	211.4	247.3	257.9
82.5°	76.1	129.0	185.0	220.9	231.5
85°	51.8	104.6	160.7	196.6	207.2
87.5°	31.7	84.6	138.5	174.4	185.0
90°	14.5	73.8	137.4	176.5	188.5
92.5°	30.0	70.9	130.5	170.7	181.0
95°	57.5	67.8	127.9	166.0	176.6
97.5°	94.1	111.0	122.4	160.1	171.4
100°	136.6	185.4	116.8	153.4	164.8
102.5°	185.2	224.5	141.2	146.0	158.1
105°	232.5	266.1	243.9	140.5	151.5
107.5°	281.8	310.8	365.4	278.2	189.2
110°	331.1	356.2	406.7	409.4	310.3

TEST NUMBER: P1031007

CATALOG NUMBER: S123DIW-B775D755UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	379.2	399.3	447.7	480.9	488.9
115°	425.6	442.8	487.5	520.5	531.9
117.5°	472.2	485.8	525.6	556.9	566.2
120°	513.9	526.0	563.1	593.5	600.9
122.5°	557.5	564.9	600.7	627.8	635.9
125°	595.6	601.6	635.2	659.0	667.9
127.5°	634.7	639.6	669.8	693.3	699.1
130°	670.8	675.7	699.9	722.9	727.8
132.5°	704.3	710.3	728.5	750.5	755.6
135°	739.6	743.1	757.7	779.0	782.0
137.5°	769.7	774.7	783.6	804.3	808.1
140°	798.8	803.3	808.6	827.5	831.3
142.5°	826.6	830.0	832.3	848.2	851.3
145°	852.2	856.3	857.8	867.8	872.0
147.5°	875.9	879.6	881.1	885.8	886.3
150°	898.4	900.7	902.2	903.7	903.5
152.5°	918.7	919.5	920.2	923.2	919.5
155°	937.5	936.0	936.8	940.5	936.0
157.5°	952.5	952.5	951.8	956.3	950.3
160°	966.1	965.3	964.6	969.1	963.8
162.5°	978.9	976.6	975.9	981.1	976.6
165°	988.6	986.4	985.6	991.6	986.4
167.5°	996.9	993.9	993.9	999.9	993.9
170°	1003.7	1000.7	1000.7	1006.7	1000.7
172.5°	1008.2	1004.4	1005.2	1011.2	1004.4
175°	1011.9	1008.2	1008.9	1014.2	1008.2
177.5°	1013.4	1009.7	1010.4	1016.4	1008.9
180°	1011.9	1011.9	1011.9	1011.9	1011.9

(END OF REPORT)