

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031440

Luminaire Tested: S123DIW-B1165D1320UB27-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031440
REPORT IS A COMBINATION OF REPORTS P990922 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1165D1320UB27-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9268.0 lumens
Efficiency: N/A
Efficacy: 89.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031440

CATALOG NUMBER: S123DIW-B1165D1320UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1031440

CATALOG NUMBER: S123DIW-B1165D1320UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	57	57	51
1	98	94	90	86	90	87	83	80	73	71	69	61	60	58	50	49	48	48	48	43
2	89	82	76	70	82	76	70	66	64	60	57	54	51	48	44	42	40	40	40	36
3	81	72	64	59	75	67	60	55	57	52	48	48	44	41	39	37	34	34	34	30
4	74	64	56	49	68	59	52	47	50	45	41	42	38	35	35	32	30	30	30	26
5	68	57	48	42	63	53	45	40	45	39	35	38	34	30	32	28	26	26	26	23
6	63	51	43	37	58	47	40	35	41	35	31	34	30	27	29	25	23	23	23	20
7	58	46	38	32	54	43	36	30	37	31	27	31	27	24	26	23	20	20	20	18
8	54	42	34	28	50	39	32	27	34	28	24	29	24	21	24	21	18	18	18	16
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	19	16	16	16	14
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	15	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19550	19550	19550
5°	19600	18876	18848
10°	19425	18237	18050
15°	19155	17572	17181
20°	18845	16834	16318
25°	18444	16057	15398
30°	18006	15251	14429
35°	17547	14428	13467
40°	17066	13565	12519
45°	16537	12723	11530
50°	15999	11785	10537
55°	15309	10807	9531
60°	14599	9730	8461
65°	13931	8563	7344
70°	12969	7269	6041
75°	11583	5755	4690
80°	10006	4046	3317
85°	7800	2175	1662

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16537 cd/sqm

TEST NUMBER: P1031440

CATALOG NUMBER: S123DIW-B1165D1320UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.2	1.8
10°-20°	483.5	5.2
20°-30°	714.1	7.7
30°-40°	834.0	9.0
40°-50°	838.4	9.0
50°-60°	736.5	7.9
60°-70°	548.5	5.9
70°-80°	312.1	3.4
80°-90°	92.2	1.0
90°-100°	105.4	1.1
100°-110°	319.1	3.4
110°-120°	543.2	5.9
120°-130°	714.6	7.7
130°-140°	803.2	8.7
140°-150°	789.7	8.5
150°-160°	664.8	7.2
160°-170°	442.6	4.8
170°-180°	155.0	1.7
0°-30°	1368.8	14.8
0°-40°	2202.7	23.8
0°-60°	3777.6	40.8
0°-90°	4730.5	51.0
90°-120°	967.7	10.4
90°-150°	3275.2	35.3
90°-180°	4538.0	49.0
0°-180°	9268.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1816	1816	1816	1816	1816	
5°	1818	1810	1793	1808	1805	172
15°	1730	1724	1704	1716	1707	488
25°	1571	1562	1541	1543	1538	724
35°	1359	1349	1329	1320	1312	850
45°	1114	1107	1087	1068	1060	860
55°	845	843	823	806	798	757
65°	576	568	553	540	536	569
75°	304	298	294	286	281	325
85°	81	78	78	75	75	87
90°	1	14	31	36	39	11
95°	76	85	95	100	100	84
105°	289	292	304	304	306	310
115°	547	551	548	549	548	541
125°	800	804	801	796	791	714
135°	1038	1046	1045	1039	1037	800
145°	1259	1262	1266	1265	1259	787
155°	1442	1442	1443	1448	1440	664
165°	1571	1567	1567	1575	1566	443
175°	1634	1629	1629	1636	1627	155
180°	1638	1638	1638	1638	1638	

TEST NUMBER: P1031440

CATALOG NUMBER: S123DIW-B1165D1320UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1816.3	1816.3	1816.3	1816.3	1816.3
2.5°	1824.1	1817.9	1800.7	1816.3	1814.7
5°	1817.9	1810.0	1792.9	1808.5	1805.4
7.5°	1803.8	1796.0	1778.8	1792.9	1791.3
10°	1785.1	1777.2	1756.9	1771.0	1767.9
12.5°	1760.1	1753.8	1735.1	1744.5	1742.9
15°	1730.4	1724.1	1703.8	1716.3	1707.0
17.5°	1697.6	1689.8	1669.5	1678.9	1675.7
20°	1660.1	1650.7	1630.4	1636.7	1632.0
22.5°	1618.0	1608.6	1588.3	1593.0	1586.7
25°	1571.1	1561.7	1541.4	1543.0	1538.3
27.5°	1522.7	1513.3	1491.5	1493.0	1488.3
30°	1469.6	1461.8	1439.9	1439.9	1429.0
32.5°	1416.5	1405.6	1389.9	1379.0	1374.3
35°	1358.7	1349.3	1329.0	1319.7	1311.9
37.5°	1300.9	1288.4	1268.1	1257.2	1252.5
40°	1240.0	1230.6	1208.8	1196.3	1190.0
42.5°	1179.1	1168.2	1146.3	1133.8	1127.6
45°	1113.5	1107.3	1087.0	1068.2	1060.4
47.5°	1049.5	1040.1	1021.4	1002.6	996.4
50°	983.9	976.1	955.8	938.6	929.2
52.5°	915.2	910.5	888.6	874.6	865.2
55°	844.9	843.3	823.0	805.9	798.0
57.5°	779.3	773.1	757.4	741.8	732.5
60°	707.5	705.9	687.2	673.1	665.3
62.5°	643.4	638.7	620.0	606.0	601.3
65°	576.3	568.5	552.9	540.4	535.7
67.5°	504.4	498.2	485.7	474.8	468.5
70°	440.4	431.0	421.7	410.7	402.9
72.5°	373.3	367.0	356.1	346.7	343.6
75°	304.5	298.3	293.6	285.8	281.1
77.5°	243.6	240.5	234.3	228.0	228.0
80°	184.3	179.6	176.5	174.9	174.9
82.5°	126.5	126.5	126.5	123.4	121.8
85°	81.2	78.1	78.1	75.0	75.0
87.5°	40.6	35.9	34.4	32.8	32.8
90°	1.3	14.2	30.9	36.0	38.6
92.5°	38.6	46.3	54.0	57.9	55.3
95°	75.9	84.9	95.2	100.3	100.3
97.5°	124.8	131.2	138.9	145.4	144.1
100°	175.0	182.7	189.1	193.0	195.5
102.5°	232.8	236.7	245.7	249.6	248.3
105°	289.4	292.0	303.6	303.6	306.2
107.5°	356.3	357.6	362.8	366.6	365.3
110°	418.1	420.7	423.2	428.4	425.8

TEST NUMBER: P1031440

CATALOG NUMBER: S123DIW-B1165D1320UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	482.4	483.7	483.7	490.1	490.1
115°	546.7	550.6	548.0	549.3	548.0
117.5°	612.3	613.6	611.1	611.1	607.2
120°	672.8	680.5	674.1	672.8	670.2
122.5°	735.8	741.0	738.4	734.5	730.7
125°	800.2	804.0	801.4	796.3	791.2
127.5°	859.3	867.0	864.5	856.8	851.6
130°	918.5	928.8	924.9	919.8	910.8
132.5°	977.7	988.0	985.4	979.0	972.5
135°	1038.1	1045.9	1044.6	1039.4	1036.9
137.5°	1093.5	1099.9	1103.8	1097.3	1093.5
140°	1151.3	1157.8	1159.1	1157.8	1148.8
142.5°	1204.1	1210.5	1213.1	1211.8	1205.4
145°	1259.4	1262.0	1265.8	1264.6	1259.4
147.5°	1307.0	1312.2	1316.0	1316.0	1308.3
150°	1357.2	1359.7	1362.3	1362.3	1354.6
152.5°	1398.3	1402.2	1403.5	1406.1	1399.6
155°	1442.1	1442.1	1443.4	1448.5	1439.5
157.5°	1479.4	1478.1	1479.4	1484.5	1476.8
160°	1514.1	1511.5	1511.5	1518.0	1512.8
162.5°	1545.0	1541.1	1542.4	1548.9	1539.8
165°	1570.7	1566.9	1566.9	1574.6	1565.6
167.5°	1592.6	1587.4	1588.7	1596.5	1588.7
170°	1610.6	1605.5	1605.5	1614.5	1605.5
172.5°	1624.8	1619.6	1619.6	1627.3	1618.3
175°	1633.8	1628.6	1628.6	1636.3	1627.3
177.5°	1638.9	1633.8	1633.8	1641.5	1632.5
180°	1637.6	1637.6	1637.6	1637.6	1637.6

(END OF REPORT)