

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031457

Luminaire Tested: S123DIW-B1165D1320UB40-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031457
REPORT IS A COMBINATION OF REPORTS P990969 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1165D1320UB40-4F0-XX-W2A-F
Description: Define 3 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9993.0 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 103.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031457

CATALOG NUMBER: S123DIW-B1165D1320UB40-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1031457

CATALOG NUMBER: S123DIW-B1165D1320UB40-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54
1	97	93	89	85	89	85	82	79	72	69	67	59	57	56	47	46	45
2	88	81	75	70	81	75	69	65	63	59	56	52	49	47	42	40	38
3	81	71	64	58	74	66	59	54	55	51	47	46	42	39	37	35	32
4	74	63	55	49	68	58	51	46	49	44	40	41	37	34	33	30	28
5	68	56	48	42	62	52	45	39	44	38	34	37	32	29	30	27	24
6	62	50	42	36	57	47	39	34	40	34	30	33	29	26	27	24	21
7	58	45	37	32	53	42	35	30	36	30	26	30	26	23	25	21	19
8	53	41	33	28	49	38	31	26	33	27	23	27	23	20	23	19	17
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	15
10	46	34	27	22	43	32	26	21	28	22	19	23	19	16	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19609	19609	19609
5°	19657	18932	18903
10°	19482	18290	18103
15°	19211	17624	17231
20°	18900	16885	16366
25°	18500	16105	15444
30°	18059	15296	14471
35°	17598	14471	13506
40°	17117	13605	12557
45°	16586	12761	11565
50°	16047	11819	10569
55°	15354	10839	9560
60°	14642	9758	8486
65°	13972	8588	7366
70°	13008	7290	6059
75°	11617	5773	4703
80°	10033	4057	3326
85°	7828	2180	1667

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16586 cd/sqm

TEST NUMBER: P1031457

CATALOG NUMBER: S123DIW-B1165D1320UB40-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.7	1.7
10°-20°	484.9	4.9
20°-30°	716.2	7.2
30°-40°	836.4	8.4
40°-50°	840.9	8.4
50°-60°	738.7	7.4
60°-70°	550.1	5.5
70°-80°	313.1	3.1
80°-90°	92.4	0.9
90°-100°	60.7	0.6
100°-110°	293.5	2.9
110°-120°	719.3	7.2
120°-130°	913.1	9.1
130°-140°	975.5	9.8
140°-150°	912.2	9.1
150°-160°	735.8	7.4
160°-170°	474.8	4.8
170°-180°	163.6	1.6
0°-30°	1372.8	13.7
0°-40°	2209.3	22.1
0°-60°	3788.8	37.9
0°-90°	4744.4	47.5
90°-120°	1073.6	10.7
90°-150°	3874.4	38.8
90°-180°	5249.0	52.5
0°-180°	9993.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1822	1822	1822	1822	1822	
5°	1823	1815	1798	1814	1811	173
15°	1736	1729	1709	1721	1712	489
25°	1576	1566	1546	1548	1543	726
35°	1363	1353	1333	1324	1316	853
45°	1117	1110	1090	1071	1064	862
55°	847	846	826	808	800	759
65°	578	570	554	542	537	570
75°	305	299	294	287	282	326
85°	82	78	78	75	75	87
90°	1	14	31	36	38	10
95°	78	26	40	49	49	93
105°	381	395	280	54	56	404
115°	715	723	734	747	752	706
125°	1008	1018	1023	1026	1028	901
135°	1255	1262	1268	1271	1268	966
145°	1448	1457	1459	1462	1462	906
155°	1595	1592	1594	1600	1592	735
165°	1682	1678	1677	1687	1678	475
175°	1722	1715	1716	1726	1715	164
180°	1722	1722	1722	1722	1722	

TEST NUMBER: P1031457

CATALOG NUMBER: S123DIW-B1165D1320UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1821.7	1821.7	1821.7	1821.7	1821.7
2.5°	1829.5	1823.2	1806.0	1821.7	1820.1
5°	1823.2	1815.4	1798.2	1813.8	1810.7
7.5°	1809.1	1801.3	1784.1	1798.2	1796.6
10°	1790.3	1782.5	1762.1	1776.2	1773.1
12.5°	1765.3	1759.0	1740.2	1749.6	1748.1
15°	1735.5	1729.3	1708.9	1721.4	1712.0
17.5°	1702.6	1694.8	1674.4	1683.8	1680.7
20°	1665.0	1655.6	1635.3	1641.5	1636.8
22.5°	1622.7	1613.3	1593.0	1597.7	1591.4
25°	1575.8	1566.4	1546.0	1547.6	1542.9
27.5°	1527.2	1517.8	1495.9	1497.4	1492.7
30°	1473.9	1466.1	1444.2	1444.2	1433.2
32.5°	1420.7	1409.7	1394.1	1383.1	1378.4
35°	1362.7	1353.3	1333.0	1323.6	1315.7
37.5°	1304.8	1292.2	1271.9	1260.9	1256.2
40°	1243.7	1234.3	1212.4	1199.8	1193.6
42.5°	1182.6	1171.6	1149.7	1137.2	1130.9
45°	1116.8	1110.5	1090.2	1071.4	1063.6
47.5°	1052.6	1043.2	1024.4	1005.6	999.3
50°	986.8	979.0	958.6	941.4	932.0
52.5°	917.9	913.2	891.3	877.2	867.8
55°	847.4	845.8	825.5	808.2	800.4
57.5°	781.6	775.3	759.7	744.0	734.6
60°	709.6	708.0	689.2	675.1	667.3
62.5°	645.3	640.6	621.8	607.7	603.0
65°	578.0	570.2	554.5	542.0	537.3
67.5°	505.9	499.7	487.1	476.2	469.9
70°	441.7	432.3	422.9	412.0	404.1
72.5°	374.4	368.1	357.1	347.7	344.6
75°	305.4	299.2	294.5	286.6	281.9
77.5°	244.4	241.2	235.0	228.7	228.7
80°	184.8	180.1	177.0	175.4	175.4
82.5°	126.9	126.9	126.9	123.7	122.2
85°	81.5	78.3	78.3	75.2	75.2
87.5°	40.7	36.0	34.5	32.9	32.9
90°	1.3	14.1	30.7	35.8	38.4
92.5°	29.4	21.7	33.3	42.2	43.5
95°	78.0	25.6	39.7	48.6	48.6
97.5°	142.0	106.2	40.9	51.2	52.4
100°	216.2	241.7	42.2	52.4	53.7
102.5°	300.6	317.2	94.7	52.4	55.0
105°	381.2	395.2	280.1	53.7	56.3
107.5°	466.9	478.4	497.6	300.6	133.0
110°	552.6	562.8	576.9	534.7	351.7

TEST NUMBER: P1031457

CATALOG NUMBER: S123DIW-B1165D1320UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	634.4	643.4	657.4	669.0	666.4
115°	715.0	722.7	734.2	747.0	752.1
117.5°	794.3	803.3	809.7	819.9	821.2
120°	867.2	878.7	882.6	892.8	892.8
122.5°	941.4	950.4	955.5	961.9	963.1
125°	1007.9	1018.1	1023.3	1025.8	1028.4
127.5°	1074.4	1084.7	1091.1	1094.9	1092.3
130°	1135.8	1146.1	1151.2	1156.3	1153.7
132.5°	1194.7	1204.9	1208.7	1213.8	1210.0
135°	1254.8	1262.4	1267.6	1271.4	1267.6
137.5°	1305.9	1316.2	1318.7	1325.1	1322.6
140°	1357.1	1364.8	1368.6	1373.7	1371.2
142.5°	1404.4	1412.1	1415.9	1419.8	1415.9
145°	1447.9	1456.9	1459.4	1462.0	1462.0
147.5°	1490.1	1496.5	1499.1	1501.6	1495.2
150°	1528.5	1532.3	1534.9	1537.5	1533.6
152.5°	1563.0	1564.3	1565.6	1570.7	1564.3
155°	1595.0	1592.5	1593.7	1600.1	1592.5
157.5°	1620.6	1620.6	1619.3	1627.0	1616.8
160°	1643.6	1642.3	1641.1	1648.7	1639.8
162.5°	1665.4	1661.5	1660.2	1669.2	1661.5
165°	1682.0	1678.2	1676.9	1687.1	1678.2
167.5°	1696.1	1690.9	1690.9	1701.2	1690.9
170°	1707.6	1702.5	1702.5	1712.7	1702.5
172.5°	1715.2	1708.8	1710.1	1720.4	1708.8
175°	1721.6	1715.2	1716.5	1725.5	1715.2
177.5°	1724.2	1717.8	1719.1	1729.3	1716.5
180°	1721.6	1721.6	1721.6	1721.6	1721.6

(END OF REPORT)