

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031043

Luminaire Tested: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031043
REPORT IS A COMBINATION OF REPORTS P993826 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9613.0 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 99
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031043

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031043

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45	38		
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32		
2	87	80	74	69	79	73	68	63	59	56	53	47	45	42	35	34	33	27		
3	79	70	63	58	72	64	58	53	52	48	45	42	39	36	32	30	28	24		
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	28	26	24	20		
5	67	56	48	42	60	51	44	39	42	37	33	33	30	27	26	23	21	18		
6	61	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19	16		
7	57	45	37	32	52	41	34	30	34	29	25	28	24	21	21	19	17	14		
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	20	17	15	13		
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14	11		
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12	10		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17266	17266	17266
5°	17295	16656	16611
10°	17159	16030	15714
15°	16936	15255	14731
20°	16643	14414	13633
25°	16343	13539	12593
30°	15956	12608	11363
35°	15558	11694	10244
40°	15183	10701	9006
45°	14704	9730	7894
50°	14175	8694	6743
55°	13626	7584	5687
60°	13101	6446	4616
65°	12423	5280	3603
70°	11570	3992	2574
75°	10343	2703	2040
80°	8827	1880	1432
85°	6628	1014	749

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14704 cd/sqm

TEST NUMBER: P1031043

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	1.6
10°-20°	419.5	4.4
20°-30°	604.0	6.3
30°-40°	680.2	7.1
40°-50°	650.6	6.8
50°-60°	532.6	5.5
60°-70°	359.1	3.7
70°-80°	180.1	1.9
80°-90°	51.0	0.5
90°-100°	69.2	0.7
100°-110°	334.7	3.5
110°-120°	820.2	8.5
120°-130°	1041.3	10.8
130°-140°	1112.4	11.6
140°-150°	1040.2	10.8
150°-160°	839.0	8.7
160°-170°	541.5	5.6
170°-180°	186.6	1.9
0°-30°	1174.3	12.2
0°-40°	1854.5	19.3
0°-60°	3037.7	31.6
0°-90°	3627.9	37.7
90°-120°	1224.2	12.7
90°-150°	4418.0	46.0
90°-180°	5985.0	62.3
0°-180°	9613.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1604	1604	1604	1604	1604	
5°	1604	1598	1582	1594	1591	152
15°	1530	1516	1479	1473	1464	431
25°	1392	1360	1300	1272	1258	640
35°	1205	1158	1077	1021	998	754
45°	990	932	831	757	726	764
55°	752	688	578	502	476	674
65°	514	442	341	277	263	509
75°	272	210	138	125	122	290
85°	69	40	36	34	34	76
90°	2	16	35	41	44	9
95°	89	29	45	55	55	106
105°	435	451	319	61	64	461
115°	815	824	837	852	858	805
125°	1149	1161	1167	1170	1173	1027
135°	1431	1440	1445	1450	1445	1102
145°	1651	1661	1664	1667	1667	1034
155°	1819	1816	1817	1825	1816	838
165°	1918	1914	1912	1924	1914	542
175°	1963	1956	1957	1968	1956	187
180°	1963	1963	1963	1963	1963	

TEST NUMBER: P1031043

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1604.1	1604.1	1604.1	1604.1	1604.1
2.5°	1610.6	1605.4	1589.8	1604.1	1601.5
5°	1604.1	1597.6	1582.0	1593.7	1591.1
7.5°	1592.4	1585.9	1566.4	1574.2	1570.3
10°	1576.8	1567.7	1544.3	1545.6	1539.1
12.5°	1554.7	1544.3	1514.4	1513.1	1505.2
15°	1530.0	1515.7	1479.2	1472.7	1463.6
17.5°	1500.0	1484.4	1438.9	1425.9	1412.9
20°	1466.2	1445.4	1396.0	1379.1	1363.4
22.5°	1428.5	1403.8	1350.4	1328.3	1314.0
25°	1392.1	1359.5	1299.7	1272.4	1258.1
27.5°	1347.8	1312.7	1247.7	1211.2	1189.1
30°	1302.3	1263.3	1190.4	1146.2	1125.4
32.5°	1256.8	1211.2	1133.2	1083.7	1061.6
35°	1204.7	1157.9	1077.2	1021.3	997.9
37.5°	1152.7	1101.9	1017.4	954.9	926.3
40°	1103.2	1046.0	953.6	886.0	856.1
42.5°	1047.3	990.1	893.8	818.3	792.3
45°	990.1	931.5	831.3	757.2	726.0
47.5°	934.1	869.1	770.2	689.5	662.2
50°	871.7	810.5	705.1	624.5	594.6
52.5°	815.7	748.1	644.0	559.4	533.4
55°	752.0	688.2	577.6	502.2	476.2
57.5°	694.7	625.8	513.9	442.3	420.2
60°	634.9	563.3	455.3	385.1	363.0
62.5°	575.0	503.5	395.5	330.5	307.0
65°	513.9	442.3	340.9	277.1	262.8
67.5°	452.7	379.9	281.0	232.9	217.3
70°	392.9	322.6	231.6	186.0	171.7
72.5°	333.1	264.1	183.4	148.3	144.4
75°	271.9	209.5	137.9	124.9	122.3
77.5°	216.0	158.7	108.0	100.2	97.6
80°	162.6	109.3	82.0	78.1	75.5
82.5°	111.9	67.7	58.5	54.6	54.6
85°	69.0	40.3	36.4	33.8	33.8
87.5°	31.2	16.9	16.9	15.6	14.3
90°	1.5	16.0	35.0	40.8	43.8
92.5°	33.5	24.8	37.9	48.1	49.6
95°	89.0	29.2	45.2	55.4	55.4
97.5°	161.9	121.1	46.7	58.3	59.8
100°	246.5	275.7	48.1	59.8	61.3
102.5°	342.8	361.7	107.9	59.8	62.7
105°	434.7	450.7	319.4	61.3	64.2
107.5°	532.4	545.5	567.4	342.8	151.7
110°	630.1	641.8	657.8	609.7	401.1

TEST NUMBER: P1031043

CATALOG NUMBER: S123RDIW-B1000D1535UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	723.4	733.7	749.7	762.8	759.9
115°	815.3	824.1	837.2	851.8	857.6
117.5°	905.8	916.0	923.3	934.9	936.4
120°	988.9	1002.0	1006.4	1018.1	1018.1
122.5°	1073.5	1083.7	1089.5	1096.8	1098.3
125°	1149.4	1161.0	1166.9	1169.8	1172.7
127.5°	1225.2	1236.9	1244.2	1248.5	1245.6
130°	1295.2	1306.9	1312.7	1318.5	1315.6
132.5°	1362.3	1374.0	1378.3	1384.2	1379.8
135°	1430.9	1439.6	1445.4	1449.8	1445.4
137.5°	1489.2	1500.9	1503.8	1511.1	1508.2
140°	1547.5	1556.3	1560.7	1566.5	1563.6
142.5°	1601.5	1610.3	1614.6	1619.0	1614.6
145°	1651.1	1661.3	1664.2	1667.1	1667.1
147.5°	1699.2	1706.5	1709.4	1712.4	1705.1
150°	1743.0	1747.4	1750.3	1753.2	1748.8
152.5°	1782.4	1783.8	1785.3	1791.1	1783.8
155°	1818.8	1815.9	1817.4	1824.7	1815.9
157.5°	1848.0	1848.0	1846.5	1855.3	1843.6
160°	1874.3	1872.8	1871.3	1880.1	1869.9
162.5°	1899.1	1894.7	1893.2	1903.4	1894.7
165°	1918.0	1913.6	1912.2	1923.9	1913.6
167.5°	1934.1	1928.2	1928.2	1939.9	1928.2
170°	1947.2	1941.4	1941.4	1953.0	1941.4
172.5°	1955.9	1948.6	1950.1	1961.8	1948.6
175°	1963.2	1955.9	1957.4	1967.6	1955.9
177.5°	1966.1	1958.9	1960.3	1972.0	1957.4
180°	1963.2	1963.2	1963.2	1963.2	1963.2

(END OF REPORT)