

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031050

Luminaire Tested: S123RDIW-B1000D460UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031050
REPORT IS A COMBINATION OF REPORTS P993866 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D460UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5585.0 lumens
Efficiency: N/A
Efficacy: 93.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 60
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031050

CATALOG NUMBER: S123RDIW-B1000D460UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1031050

CATALOG NUMBER: S123RDIW-B1000D460UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67		
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	64	63	61	57		
2	93	86	80	75	88	81	76	71	72	68	65	64	61	58	57	55	52	49		
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	51	48	45	42		
4	78	68	60	54	74	64	57	51	57	52	47	51	47	43	46	42	39	36		
5	72	60	52	46	68	57	50	45	52	46	41	46	42	38	41	38	34	32		
6	67	54	46	40	63	52	44	39	47	41	36	42	37	33	38	34	31	28		
7	62	49	41	36	58	47	40	35	43	37	32	38	33	30	35	30	27	25		
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25	22		
9	54	41	34	29	51	39	32	28	36	30	26	33	28	24	29	25	22	20		
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	27	23	20	19		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17800	17800	17800
5°	17829	17170	17124
10°	17689	16525	16199
15°	17460	15727	15186
20°	17158	14859	14055
25°	16848	13958	12981
30°	16449	12998	11714
35°	16039	12056	10560
40°	15652	11032	9284
45°	15159	10031	8138
50°	14612	8963	6950
55°	14046	7819	5863
60°	13505	6646	4759
65°	12807	5442	3714
70°	11927	4115	2654
75°	10662	2788	2104
80°	9099	1937	1475
85°	6829	1047	774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15159 cd/sqm

TEST NUMBER: P1031050

CATALOG NUMBER: S123RDIW-B1000D460UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	155.5	2.8
10°-20°	432.5	7.7
20°-30°	622.7	11.1
30°-40°	701.2	12.6
40°-50°	670.7	12.0
50°-60°	549.1	9.8
60°-70°	370.2	6.6
70°-80°	185.7	3.3
80°-90°	49.8	0.9
90°-100°	21.4	0.4
100°-110°	103.3	1.9
110°-120°	253.2	4.5
120°-130°	321.5	5.8
130°-140°	343.4	6.1
140°-150°	321.1	5.8
150°-160°	259.0	4.6
160°-170°	167.2	3.0
170°-180°	57.6	1.0
0°-30°	1210.6	21.7
0°-40°	1911.8	34.2
0°-60°	3131.6	56.1
0°-90°	3737.2	66.9
90°-120°	378.0	6.8
90°-150°	1364.0	24.4
90°-180°	1848.0	33.1
0°-180°	5585.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1654	1654	1654	1654	1654	
5°	1654	1647	1631	1643	1640	157
15°	1577	1562	1525	1518	1509	444
25°	1435	1402	1340	1312	1297	660
35°	1242	1194	1110	1053	1029	777
45°	1021	960	857	781	748	788
55°	775	710	596	518	491	695
65°	530	456	351	286	271	524
75°	280	216	142	129	126	299
85°	71	42	38	35	35	78
90°	0	5	11	13	14	6
95°	28	9	14	17	17	33
105°	134	139	99	19	20	142
115°	252	254	258	263	265	249
125°	355	358	360	361	362	317
135°	442	444	446	448	446	340
145°	510	513	514	515	515	319
155°	562	561	561	563	561	259
165°	592	591	590	594	591	167
175°	606	604	604	608	604	58
180°	606	606	606	606	606	

TEST NUMBER: P1031050

CATALOG NUMBER: S123RDIW-B1000D460UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1653.7	1653.7	1653.7	1653.7	1653.7
2.5°	1660.4	1655.0	1638.9	1653.7	1651.0
5°	1653.7	1647.0	1630.9	1643.0	1640.3
7.5°	1641.6	1634.9	1614.8	1622.9	1618.8
10°	1625.5	1616.1	1592.0	1593.3	1586.6
12.5°	1602.7	1592.0	1561.2	1559.8	1551.8
15°	1577.3	1562.5	1524.9	1518.2	1508.8
17.5°	1546.4	1530.3	1483.4	1470.0	1456.5
20°	1511.5	1490.1	1439.1	1421.7	1405.6
22.5°	1472.6	1447.2	1392.2	1369.4	1354.6
25°	1435.1	1401.6	1339.9	1311.7	1296.9
27.5°	1389.5	1353.3	1286.2	1248.7	1225.9
30°	1342.5	1302.3	1227.2	1181.6	1160.1
32.5°	1295.6	1248.7	1168.2	1117.2	1094.4
35°	1242.0	1193.7	1110.5	1052.8	1028.7
37.5°	1188.3	1136.0	1048.8	984.4	954.9
40°	1137.3	1078.3	983.1	913.4	882.5
42.5°	1079.7	1020.7	921.4	843.6	816.8
45°	1020.7	960.3	857.0	780.6	748.4
47.5°	963.0	895.9	794.0	710.8	682.7
50°	898.6	835.6	726.9	643.8	612.9
52.5°	840.9	771.2	663.9	576.7	549.9
55°	775.2	709.5	595.5	517.7	490.9
57.5°	716.2	645.1	529.8	456.0	433.2
60°	654.5	580.7	469.4	397.0	374.2
62.5°	592.8	519.0	407.7	340.7	316.5
65°	529.8	456.0	351.4	285.7	270.9
67.5°	466.7	391.6	289.7	240.1	224.0
70°	405.0	332.6	238.7	191.8	177.0
72.5°	343.3	272.3	189.1	152.9	148.9
75°	280.3	215.9	142.2	128.8	126.1
77.5°	222.6	163.6	111.3	103.3	100.6
80°	167.6	112.7	84.5	80.5	77.8
82.5°	115.3	69.7	60.4	56.3	56.3
85°	71.1	41.6	37.6	34.9	34.9
87.5°	32.2	17.4	17.4	16.1	14.8
90°	0.5	5.0	10.8	12.6	13.5
92.5°	10.4	7.7	11.7	14.9	15.3
95°	27.5	9.0	14.0	17.1	17.1
97.5°	50.0	37.4	14.4	18.0	18.5
100°	76.1	85.1	14.9	18.5	18.9
102.5°	105.8	111.7	33.3	18.5	19.4
105°	134.2	139.1	98.6	18.9	19.8
107.5°	164.4	168.4	175.2	105.8	46.8
110°	194.5	198.1	203.1	188.2	123.8

TEST NUMBER: P1031050

CATALOG NUMBER: S123RDIW-B1000D460UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.4	226.5	231.5	235.5	234.6
115°	251.7	254.4	258.5	263.0	264.8
117.5°	279.6	282.8	285.0	288.6	289.1
120°	305.3	309.4	310.7	314.3	314.3
122.5°	331.4	334.6	336.4	338.6	339.1
125°	354.8	358.4	360.2	361.1	362.0
127.5°	378.3	381.9	384.1	385.5	384.6
130°	399.9	403.5	405.3	407.1	406.2
132.5°	420.6	424.2	425.5	427.3	426.0
135°	441.8	444.5	446.3	447.6	446.3
137.5°	459.8	463.4	464.3	466.5	465.6
140°	477.8	480.5	481.8	483.6	482.7
142.5°	494.4	497.1	498.5	499.8	498.5
145°	509.7	512.9	513.8	514.7	514.7
147.5°	524.6	526.9	527.8	528.7	526.4
150°	538.1	539.5	540.4	541.3	539.9
152.5°	550.3	550.7	551.2	553.0	550.7
155°	561.5	560.6	561.1	563.3	560.6
157.5°	570.5	570.5	570.1	572.8	569.2
160°	578.6	578.2	577.7	580.4	577.3
162.5°	586.3	584.9	584.5	587.7	584.9
165°	592.2	590.8	590.4	594.0	590.8
167.5°	597.1	595.3	595.3	598.9	595.3
170°	601.2	599.4	599.4	603.0	599.4
172.5°	603.9	601.6	602.1	605.7	601.6
175°	606.1	603.9	604.3	607.5	603.9
177.5°	607.0	604.8	605.2	608.8	604.3
180°	606.1	606.1	606.1	606.1	606.1

(END OF REPORT)