

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031059

Luminaire Tested: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031059
REPORT IS A COMBINATION OF REPORTS P993908 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F1_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6187.0 lumens
Efficiency: N/A
Efficacy: 88.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031059

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031059

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64
1	100	96	92	89	93	90	86	83	78	75	73	67	65	64	57	56	55
2	91	84	78	73	85	79	74	69	69	65	61	59	56	54	51	49	47
3	84	74	67	61	78	70	63	58	61	56	52	53	49	46	45	43	40
4	77	66	58	52	71	62	55	50	54	49	45	47	43	40	41	38	35
5	71	59	51	45	66	56	48	43	49	43	39	43	38	35	37	33	31
6	65	53	45	39	61	50	43	38	44	38	34	39	34	31	34	30	27
7	60	48	40	35	56	45	38	33	40	34	30	35	31	27	31	27	24
8	56	44	36	31	52	41	34	30	37	31	27	32	28	24	28	25	22
9	52	40	33	28	49	38	31	26	34	28	24	30	25	22	26	23	20
10	49	37	30	25	46	35	28	24	31	26	22	28	23	20	24	21	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17266	17266	17266
5°	17295	16656	16611
10°	17159	16030	15714
15°	16936	15255	14731
20°	16643	14414	13633
25°	16343	13539	12593
30°	15956	12608	11363
35°	15558	11694	10244
40°	15183	10701	9006
45°	14704	9730	7894
50°	14175	8694	6743
55°	13626	7584	5687
60°	13101	6446	4616
65°	12423	5280	3603
70°	11570	3992	2574
75°	10343	2703	2040
80°	8827	1880	1432
85°	6628	1014	749

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14704 cd/sqm

TEST NUMBER: P1031059

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	2.4
10°-20°	419.5	6.8
20°-30°	604.0	9.8
30°-40°	680.2	11.0
40°-50°	650.6	10.5
50°-60°	532.6	8.6
60°-70°	359.1	5.8
70°-80°	180.1	2.9
80°-90°	49.0	0.8
90°-100°	59.5	1.0
100°-110°	180.1	2.9
110°-120°	306.6	5.0
120°-130°	403.3	6.5
130°-140°	453.4	7.3
140°-150°	445.7	7.2
150°-160°	375.2	6.1
160°-170°	249.8	4.0
170°-180°	87.5	1.4
0°-30°	1174.3	19.0
0°-40°	1854.5	30.0
0°-60°	3037.7	49.1
0°-90°	3625.9	58.6
90°-120°	546.2	8.8
90°-150°	1848.5	29.9
90°-180°	2561.0	41.4
0°-180°	6187.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1604	1604	1604	1604	1604	
5°	1604	1598	1582	1594	1591	152
15°	1530	1516	1479	1473	1464	431
25°	1392	1360	1300	1272	1258	640
35°	1205	1158	1077	1021	998	754
45°	990	932	831	757	726	764
55°	752	688	578	502	476	674
65°	514	442	341	277	263	509
75°	272	210	138	125	122	290
85°	69	40	36	34	34	76
90°	1	8	17	20	22	7
95°	43	48	54	57	57	47
105°	163	165	171	171	173	175
115°	309	311	309	310	309	305
125°	452	454	452	449	446	403
135°	586	590	590	587	585	451
145°	711	712	714	714	711	444
155°	814	814	815	818	812	375
165°	886	884	884	889	884	250
175°	922	919	919	924	918	88
180°	924	924	924	924	924	

TEST NUMBER: P1031059

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1604.1	1604.1	1604.1	1604.1	1604.1
2.5°	1610.6	1605.4	1589.8	1604.1	1601.5
5°	1604.1	1597.6	1582.0	1593.7	1591.1
7.5°	1592.4	1585.9	1566.4	1574.2	1570.3
10°	1576.8	1567.7	1544.3	1545.6	1539.1
12.5°	1554.7	1544.3	1514.4	1513.1	1505.2
15°	1530.0	1515.7	1479.2	1472.7	1463.6
17.5°	1500.0	1484.4	1438.9	1425.9	1412.9
20°	1466.2	1445.4	1396.0	1379.1	1363.4
22.5°	1428.5	1403.8	1350.4	1328.3	1314.0
25°	1392.1	1359.5	1299.7	1272.4	1258.1
27.5°	1347.8	1312.7	1247.7	1211.2	1189.1
30°	1302.3	1263.3	1190.4	1146.2	1125.4
32.5°	1256.8	1211.2	1133.2	1083.7	1061.6
35°	1204.7	1157.9	1077.2	1021.3	997.9
37.5°	1152.7	1101.9	1017.4	954.9	926.3
40°	1103.2	1046.0	953.6	886.0	856.1
42.5°	1047.3	990.1	893.8	818.3	792.3
45°	990.1	931.5	831.3	757.2	726.0
47.5°	934.1	869.1	770.2	689.5	662.2
50°	871.7	810.5	705.1	624.5	594.6
52.5°	815.7	748.1	644.0	559.4	533.4
55°	752.0	688.2	577.6	502.2	476.2
57.5°	694.7	625.8	513.9	442.3	420.2
60°	634.9	563.3	455.3	385.1	363.0
62.5°	575.0	503.5	395.5	330.5	307.0
65°	513.9	442.3	340.9	277.1	262.8
67.5°	452.7	379.9	281.0	232.9	217.3
70°	392.9	322.6	231.6	186.0	171.7
72.5°	333.1	264.1	183.4	148.3	144.4
75°	271.9	209.5	137.9	124.9	122.3
77.5°	216.0	158.7	108.0	100.2	97.6
80°	162.6	109.3	82.0	78.1	75.5
82.5°	111.9	67.7	58.5	54.6	54.6
85°	69.0	40.3	36.4	33.8	33.8
87.5°	31.2	16.9	16.9	15.6	14.3
90°	0.7	8.0	17.4	20.3	21.8
92.5°	21.8	26.1	30.5	32.7	31.2
95°	42.8	47.9	53.7	56.6	56.6
97.5°	70.4	74.1	78.4	82.0	81.3
100°	98.7	103.1	106.7	108.9	110.4
102.5°	131.4	133.6	138.7	140.9	140.1
105°	163.4	164.8	171.4	171.4	172.8
107.5°	201.1	201.8	204.8	206.9	206.2
110°	236.0	237.4	238.9	241.8	240.3



TEST NUMBER: P1031059

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	272.3	273.0	273.0	276.6	276.6
115°	308.6	310.8	309.3	310.0	309.3
117.5°	345.6	346.3	344.9	344.9	342.7
120°	379.7	384.1	380.5	379.7	378.3
122.5°	415.3	418.2	416.8	414.6	412.4
125°	451.6	453.8	452.3	449.4	446.5
127.5°	485.0	489.4	487.9	483.6	480.7
130°	518.4	524.2	522.0	519.1	514.1
132.5°	551.8	557.6	556.2	552.5	548.9
135°	585.9	590.3	589.6	586.7	585.2
137.5°	617.2	620.8	623.0	619.3	617.2
140°	649.8	653.5	654.2	653.5	648.4
142.5°	679.6	683.2	684.7	684.0	680.3
145°	710.8	712.3	714.5	713.7	710.8
147.5°	737.7	740.6	742.8	742.8	738.4
150°	766.0	767.5	768.9	768.9	764.6
152.5°	789.2	791.4	792.1	793.6	790.0
155°	813.9	813.9	814.7	817.6	812.5
157.5°	835.0	834.3	835.0	837.9	833.5
160°	854.6	853.1	853.1	856.8	853.9
162.5°	872.0	869.8	870.6	874.2	869.1
165°	886.5	884.4	884.4	888.7	883.6
167.5°	898.9	896.0	896.7	901.1	896.7
170°	909.0	906.1	906.1	911.2	906.1
172.5°	917.0	914.1	914.1	918.5	913.4
175°	922.1	919.2	919.2	923.6	918.5
177.5°	925.0	922.1	922.1	926.5	921.4
180°	924.3	924.3	924.3	924.3	924.3

(END OF REPORT)