

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031061

Luminaire Tested: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031061
REPORT IS A COMBINATION OF REPORTS P993911 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_3000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6843.0 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031061

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031061

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	54	53	52
2	91	83	77	72	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	66	61	77	69	62	57	60	55	51	51	47	44	43	40	38
4	76	65	58	52	70	61	54	49	53	48	44	46	42	38	39	36	33
5	70	58	50	45	65	55	48	42	48	42	38	41	37	33	35	32	29
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26
7	60	48	40	34	55	45	38	33	39	33	29	34	30	26	29	26	23
8	56	43	36	30	52	41	34	29	36	30	26	31	27	23	27	23	21
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17957	17957	17957
5°	17987	17322	17276
10°	17845	16671	16343
15°	17614	15866	15321
20°	17310	14990	14179
25°	16997	14081	13097
30°	16594	13112	11818
35°	16180	12162	10653
40°	15791	11130	9366
45°	15292	10120	8209
50°	14741	9043	7011
55°	14171	7889	5914
60°	13625	6705	4801
65°	12921	5491	3747
70°	12033	4151	2678
75°	10758	2811	2122
80°	9180	1953	1489
85°	6887	1055	780

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 15292 cd/sqm

TEST NUMBER: P1031061

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.8	2.3
10°-20°	436.3	6.4
20°-30°	628.2	9.2
30°-40°	707.4	10.3
40°-50°	676.7	9.9
50°-60°	553.9	8.1
60°-70°	373.5	5.5
70°-80°	187.3	2.7
80°-90°	51.0	0.7
90°-100°	35.5	0.5
100°-110°	171.8	2.5
110°-120°	421.0	6.2
120°-130°	534.5	7.8
130°-140°	571.0	8.3
140°-150°	533.9	7.8
150°-160°	430.6	6.3
160°-170°	277.9	4.1
170°-180°	95.8	1.4
0°-30°	1221.3	17.8
0°-40°	1928.7	28.2
0°-60°	3159.3	46.2
0°-90°	3771.0	55.1
90°-120°	628.3	9.2
90°-150°	2267.7	33.1
90°-180°	3072.0	44.9
0°-180°	6843.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1668	1668	1668	1668	1668	
5°	1668	1662	1645	1658	1655	158
15°	1591	1576	1538	1532	1522	448
25°	1448	1414	1352	1323	1308	666
35°	1253	1204	1120	1062	1038	784
45°	1030	969	865	788	755	795
55°	782	716	601	522	495	701
65°	534	460	354	288	273	529
75°	283	218	143	130	127	301
85°	72	42	38	35	35	79
90°	1	8	18	21	22	7
95°	46	15	23	28	28	55
105°	223	231	164	31	33	237
115°	418	423	430	437	440	413
125°	590	596	599	600	602	527
135°	734	739	742	744	742	565
145°	848	853	854	856	856	531
155°	934	932	933	937	932	430
165°	984	982	982	988	982	278
175°	1008	1004	1005	1010	1004	96
180°	1008	1008	1008	1008	1008	

TEST NUMBER: P1031061

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1668.3	1668.3	1668.3	1668.3	1668.3
2.5°	1675.1	1669.7	1653.4	1668.3	1665.6
5°	1668.3	1661.5	1645.3	1657.5	1654.8
7.5°	1656.1	1649.4	1629.1	1637.2	1633.1
10°	1639.9	1630.4	1606.1	1607.4	1600.7
12.5°	1616.9	1606.1	1574.9	1573.6	1565.5
15°	1591.2	1576.3	1538.4	1531.6	1522.2
17.5°	1560.1	1543.8	1496.5	1482.9	1469.4
20°	1524.9	1503.2	1451.8	1434.2	1418.0
22.5°	1485.6	1459.9	1404.5	1381.5	1366.6
25°	1447.8	1413.9	1351.7	1323.3	1308.4
27.5°	1401.8	1365.2	1297.6	1259.7	1236.7
30°	1354.4	1313.8	1238.0	1192.0	1170.4
32.5°	1307.0	1259.7	1178.5	1127.1	1104.1
35°	1252.9	1204.2	1120.3	1062.1	1037.8
37.5°	1198.8	1146.0	1058.1	993.1	963.4
40°	1147.4	1087.8	991.8	921.4	890.3
42.5°	1089.2	1029.7	929.5	851.1	824.0
45°	1029.7	968.8	864.6	787.5	755.0
47.5°	971.5	903.8	801.0	717.1	688.7
50°	906.5	842.9	733.4	649.5	618.3
52.5°	848.4	778.0	669.8	581.8	554.7
55°	782.1	715.8	600.8	522.3	495.2
57.5°	722.5	650.8	534.5	460.0	437.0
60°	660.3	585.9	473.6	400.5	377.5
62.5°	598.0	523.6	411.3	343.7	319.3
65°	534.5	460.0	354.5	288.2	273.3
67.5°	470.9	395.1	292.3	242.2	226.0
70°	408.6	335.6	240.8	193.5	178.6
72.5°	346.4	274.7	190.8	154.2	150.2
75°	282.8	217.8	143.4	129.9	127.2
77.5°	224.6	165.1	112.3	104.2	101.5
80°	169.1	113.7	85.2	81.2	78.5
82.5°	116.4	70.4	60.9	56.8	56.8
85°	71.7	41.9	37.9	35.2	35.2
87.5°	32.5	17.6	17.6	16.2	14.9
90°	0.7	8.2	18.0	21.0	22.5
92.5°	17.2	12.7	19.5	24.7	25.5
95°	45.7	15.0	23.2	28.4	28.4
97.5°	83.1	62.1	24.0	29.9	30.7
100°	126.5	141.5	24.7	30.7	31.4
102.5°	175.9	185.7	55.4	30.7	32.2
105°	223.1	231.3	164.0	31.4	32.9
107.5°	273.3	280.0	291.2	175.9	77.9
110°	323.4	329.4	337.6	312.9	205.9

TEST NUMBER: P1031061

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	371.3	376.6	384.8	391.5	390.0
115°	418.5	423.0	429.7	437.2	440.2
117.5°	464.9	470.1	473.9	479.9	480.6
120°	507.6	514.3	516.6	522.6	522.6
122.5°	551.0	556.2	559.2	563.0	563.7
125°	589.9	595.9	598.9	600.4	601.9
127.5°	628.9	634.9	638.6	640.8	639.3
130°	664.8	670.8	673.8	676.8	675.3
132.5°	699.2	705.2	707.5	710.5	708.2
135°	734.4	738.9	741.9	744.2	741.9
137.5°	764.4	770.4	771.9	775.6	774.1
140°	794.3	798.8	801.1	804.0	802.5
142.5°	822.0	826.5	828.8	831.0	828.8
145°	847.5	852.7	854.2	855.7	855.7
147.5°	872.2	875.9	877.4	878.9	875.2
150°	894.6	896.9	898.4	899.9	897.6
152.5°	914.8	915.6	916.3	919.3	915.6
155°	933.6	932.1	932.8	936.6	932.1
157.5°	948.5	948.5	947.8	952.3	946.3
160°	962.0	961.3	960.5	965.0	959.8
162.5°	974.7	972.5	971.7	977.0	972.5
165°	984.5	982.2	981.5	987.5	982.2
167.5°	992.7	989.7	989.7	995.7	989.7
170°	999.4	996.4	996.4	1002.4	996.4
172.5°	1003.9	1000.2	1000.9	1006.9	1000.2
175°	1007.7	1003.9	1004.7	1009.9	1003.9
177.5°	1009.2	1005.4	1006.2	1012.2	1004.7
180°	1007.7	1007.7	1007.7	1007.7	1007.7

(END OF REPORT)