

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031515

Luminaire Tested: S123DIW-B1165D460UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031515
REPORT IS A COMBINATION OF REPORTS P991102 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B1165D460UB40-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Wall Mount with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6349.0 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 74.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031515

CATALOG NUMBER: S123DIW-B1165D460UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1031515

CATALOG NUMBER: S123DIW-B1165D460UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	88	88	88	79	79	79
1	103	99	95	91	98	94	90	87	85	82	80	77	75	73	70	68	66
2	94	86	80	74	89	82	76	71	75	70	66	68	64	61	61	58	56
3	86	76	68	62	81	72	65	60	66	60	56	60	55	51	54	51	48
4	79	67	59	53	74	64	57	51	59	52	47	53	48	44	48	44	41
5	72	60	51	45	68	57	50	44	52	46	41	48	43	38	44	39	36
6	67	54	45	39	63	52	44	38	47	41	36	43	38	34	40	35	31
7	62	49	41	35	59	47	39	34	43	37	32	40	34	30	36	32	28
8	57	45	36	31	54	43	35	30	39	33	28	36	31	27	33	29	25
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	31	26	23
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	29	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	19609	19609	19609
5°	19657	18932	18903
10°	19482	18290	18103
15°	19211	17624	17231
20°	18900	16885	16366
25°	18500	16105	15444
30°	18059	15296	14471
35°	17598	14471	13506
40°	17117	13605	12557
45°	16586	12761	11565
50°	16047	11819	10569
55°	15354	10839	9560
60°	14642	9758	8486
65°	13972	8588	7366
70°	13008	7290	6059
75°	11617	5773	4703
80°	10033	4057	3326
85°	7828	2180	1667

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 16586 cd/sqm

TEST NUMBER: P1031515

CATALOG NUMBER: S123DIW-B1165D460UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	171.7	2.7
10°-20°	484.9	7.6
20°-30°	716.2	11.3
30°-40°	836.4	13.2
40°-50°	840.9	13.2
50°-60°	738.7	11.6
60°-70°	550.1	8.7
70°-80°	313.1	4.9
80°-90°	90.2	1.4
90°-100°	37.3	0.6
100°-110°	113.0	1.8
110°-120°	192.4	3.0
120°-130°	253.0	4.0
130°-140°	284.4	4.5
140°-150°	279.6	4.4
150°-160°	235.4	3.7
160°-170°	156.7	2.5
170°-180°	54.9	0.9
0°-30°	1372.8	21.6
0°-40°	2209.3	34.8
0°-60°	3788.8	59.7
0°-90°	4742.2	74.7
90°-120°	342.7	5.4
90°-150°	1159.8	18.3
90°-180°	1607.0	25.3
0°-180°	6349.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1822	1822	1822	1822	1822	
5°	1823	1815	1798	1814	1811	173
15°	1736	1729	1709	1721	1712	489
25°	1576	1566	1546	1548	1543	726
35°	1363	1353	1333	1324	1316	853
45°	1117	1110	1090	1071	1064	862
55°	847	846	826	808	800	759
65°	578	570	554	542	537	570
75°	305	299	294	287	282	326
85°	82	78	78	75	75	87
90°	0	5	11	13	14	8
95°	27	30	34	36	36	30
105°	102	103	108	108	108	110
115°	194	195	194	194	194	192
125°	283	285	284	282	280	253
135°	368	370	370	368	367	283
145°	446	447	448	448	446	279
155°	511	511	511	513	510	235
165°	556	555	555	558	554	157
175°	578	577	577	579	576	55
180°	580	580	580	580	580	

TEST NUMBER: P1031515

CATALOG NUMBER: S123DIW-B1165D460UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1821.7	1821.7	1821.7	1821.7	1821.7
2.5°	1829.5	1823.2	1806.0	1821.7	1820.1
5°	1823.2	1815.4	1798.2	1813.8	1810.7
7.5°	1809.1	1801.3	1784.1	1798.2	1796.6
10°	1790.3	1782.5	1762.1	1776.2	1773.1
12.5°	1765.3	1759.0	1740.2	1749.6	1748.1
15°	1735.5	1729.3	1708.9	1721.4	1712.0
17.5°	1702.6	1694.8	1674.4	1683.8	1680.7
20°	1665.0	1655.6	1635.3	1641.5	1636.8
22.5°	1622.7	1613.3	1593.0	1597.7	1591.4
25°	1575.8	1566.4	1546.0	1547.6	1542.9
27.5°	1527.2	1517.8	1495.9	1497.4	1492.7
30°	1473.9	1466.1	1444.2	1444.2	1433.2
32.5°	1420.7	1409.7	1394.1	1383.1	1378.4
35°	1362.7	1353.3	1333.0	1323.6	1315.7
37.5°	1304.8	1292.2	1271.9	1260.9	1256.2
40°	1243.7	1234.3	1212.4	1199.8	1193.6
42.5°	1182.6	1171.6	1149.7	1137.2	1130.9
45°	1116.8	1110.5	1090.2	1071.4	1063.6
47.5°	1052.6	1043.2	1024.4	1005.6	999.3
50°	986.8	979.0	958.6	941.4	932.0
52.5°	917.9	913.2	891.3	877.2	867.8
55°	847.4	845.8	825.5	808.2	800.4
57.5°	781.6	775.3	759.7	744.0	734.6
60°	709.6	708.0	689.2	675.1	667.3
62.5°	645.3	640.6	621.8	607.7	603.0
65°	578.0	570.2	554.5	542.0	537.3
67.5°	505.9	499.7	487.1	476.2	469.9
70°	441.7	432.3	422.9	412.0	404.1
72.5°	374.4	368.1	357.1	347.7	344.6
75°	305.4	299.2	294.5	286.6	281.9
77.5°	244.4	241.2	235.0	228.7	228.7
80°	184.8	180.1	177.0	175.4	175.4
82.5°	126.9	126.9	126.9	123.7	122.2
85°	81.5	78.3	78.3	75.2	75.2
87.5°	40.7	36.0	34.5	32.9	32.9
90°	0.5	5.0	10.9	12.8	13.7
92.5°	13.7	16.4	19.1	20.5	19.6
95°	26.9	30.1	33.7	35.5	35.5
97.5°	44.2	46.5	49.2	51.5	51.0
100°	62.0	64.7	67.0	68.3	69.2
102.5°	82.5	83.8	87.0	88.4	87.9
105°	102.5	103.4	107.5	107.5	108.4
107.5°	126.2	126.6	128.5	129.8	129.4
110°	148.0	149.0	149.9	151.7	150.8



TEST NUMBER: P1031515

CATALOG NUMBER: S123DIW-B1165D460UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	170.8	171.3	171.3	173.6	173.6
115°	193.6	195.0	194.1	194.5	194.1
117.5°	216.8	217.3	216.4	216.4	215.0
120°	238.2	241.0	238.7	238.2	237.3
122.5°	260.6	262.4	261.5	260.1	258.7
125°	283.3	284.7	283.8	282.0	280.2
127.5°	304.3	307.0	306.1	303.4	301.6
130°	325.2	328.9	327.5	325.7	322.5
132.5°	346.2	349.8	348.9	346.7	344.4
135°	367.6	370.3	369.9	368.1	367.2
137.5°	387.2	389.5	390.8	388.6	387.2
140°	407.7	410.0	410.4	410.0	406.8
142.5°	426.4	428.7	429.6	429.1	426.8
145°	446.0	446.9	448.2	447.8	446.0
147.5°	462.8	464.6	466.0	466.0	463.3
150°	480.6	481.5	482.4	482.4	479.7
152.5°	495.2	496.5	497.0	497.9	495.6
155°	510.7	510.7	511.1	512.9	509.7
157.5°	523.9	523.4	523.9	525.7	523.0
160°	536.2	535.2	535.2	537.5	535.7
162.5°	547.1	545.7	546.2	548.5	545.3
165°	556.2	554.8	554.8	557.6	554.4
167.5°	563.9	562.1	562.6	565.3	562.6
170°	570.3	568.5	568.5	571.7	568.5
172.5°	575.3	573.5	573.5	576.2	573.1
175°	578.5	576.7	576.7	579.4	576.2
177.5°	580.3	578.5	578.5	581.3	578.1
180°	579.9	579.9	579.9	579.9	579.9

(END OF REPORT)