

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031063

Luminaire Tested: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031063
REPORT IS A COMBINATION OF REPORTS P993914 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6579.0 lumens
Efficiency: N/A
Efficacy: 94.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 70
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031063

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031063

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61
1	99	95	91	88	92	88	85	82	76	74	72	65	63	62	54	53	52
2	91	83	77	72	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	66	61	77	69	62	57	60	55	51	51	47	44	43	40	38
4	76	65	58	52	70	61	54	49	53	48	44	46	42	38	39	36	33
5	70	58	50	45	65	55	48	42	48	42	38	41	37	33	35	32	29
6	65	53	45	39	60	49	42	37	43	37	33	37	33	29	32	28	26
7	60	48	40	34	55	45	38	33	39	33	29	34	30	26	29	26	23
8	56	43	36	30	52	41	34	29	36	30	26	31	27	23	27	23	21
9	52	40	32	27	48	37	31	26	33	27	24	29	24	21	25	21	19
10	48	36	29	24	45	34	28	23	30	25	21	27	22	19	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17266	17266	17266
5°	17295	16656	16611
10°	17159	16030	15714
15°	16936	15255	14731
20°	16643	14414	13633
25°	16343	13539	12593
30°	15956	12608	11363
35°	15558	11694	10244
40°	15183	10701	9006
45°	14704	9730	7894
50°	14175	8694	6743
55°	13626	7584	5687
60°	13101	6446	4616
65°	12423	5280	3603
70°	11570	3992	2574
75°	10343	2703	2040
80°	8827	1880	1432
85°	6628	1014	749

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14704 cd/sqm

TEST NUMBER: P1031063

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.8	2.3
10°-20°	419.5	6.4
20°-30°	604.0	9.2
30°-40°	680.2	10.3
40°-50°	650.6	9.9
50°-60°	532.6	8.1
60°-70°	359.1	5.5
70°-80°	180.1	2.7
80°-90°	49.0	0.7
90°-100°	34.1	0.5
100°-110°	165.2	2.5
110°-120°	404.7	6.2
120°-130°	513.8	7.8
130°-140°	548.9	8.3
140°-150°	513.2	7.8
150°-160°	414.0	6.3
160°-170°	267.2	4.1
170°-180°	92.1	1.4
0°-30°	1174.3	17.8
0°-40°	1854.5	28.2
0°-60°	3037.7	46.2
0°-90°	3625.9	55.1
90°-120°	604.0	9.2
90°-150°	2179.9	33.1
90°-180°	2953.0	44.9
0°-180°	6579.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1604	1604	1604	1604	1604	
5°	1604	1598	1582	1594	1591	152
15°	1530	1516	1479	1473	1464	431
25°	1392	1360	1300	1272	1258	640
35°	1205	1158	1077	1021	998	754
45°	990	932	831	757	726	764
55°	752	688	578	502	476	674
65°	514	442	341	277	263	509
75°	272	210	138	125	122	290
85°	69	40	36	34	34	76
90°	1	8	17	20	22	7
95°	44	14	22	27	27	52
105°	214	222	158	30	32	227
115°	402	407	413	420	423	397
125°	567	573	576	577	579	507
135°	706	710	713	715	713	544
145°	815	820	821	823	823	510
155°	897	896	897	900	896	414
165°	946	944	944	949	944	267
175°	969	965	966	971	965	92
180°	969	969	969	969	969	



TEST NUMBER: P1031063

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1604.1	1604.1	1604.1	1604.1	1604.1
2.5°	1610.6	1605.4	1589.8	1604.1	1601.5
5°	1604.1	1597.6	1582.0	1593.7	1591.1
7.5°	1592.4	1585.9	1566.4	1574.2	1570.3
10°	1576.8	1567.7	1544.3	1545.6	1539.1
12.5°	1554.7	1544.3	1514.4	1513.1	1505.2
15°	1530.0	1515.7	1479.2	1472.7	1463.6
17.5°	1500.0	1484.4	1438.9	1425.9	1412.9
20°	1466.2	1445.4	1396.0	1379.1	1363.4
22.5°	1428.5	1403.8	1350.4	1328.3	1314.0
25°	1392.1	1359.5	1299.7	1272.4	1258.1
27.5°	1347.8	1312.7	1247.7	1211.2	1189.1
30°	1302.3	1263.3	1190.4	1146.2	1125.4
32.5°	1256.8	1211.2	1133.2	1083.7	1061.6
35°	1204.7	1157.9	1077.2	1021.3	997.9
37.5°	1152.7	1101.9	1017.4	954.9	926.3
40°	1103.2	1046.0	953.6	886.0	856.1
42.5°	1047.3	990.1	893.8	818.3	792.3
45°	990.1	931.5	831.3	757.2	726.0
47.5°	934.1	869.1	770.2	689.5	662.2
50°	871.7	810.5	705.1	624.5	594.6
52.5°	815.7	748.1	644.0	559.4	533.4
55°	752.0	688.2	577.6	502.2	476.2
57.5°	694.7	625.8	513.9	442.3	420.2
60°	634.9	563.3	455.3	385.1	363.0
62.5°	575.0	503.5	395.5	330.5	307.0
65°	513.9	442.3	340.9	277.1	262.8
67.5°	452.7	379.9	281.0	232.9	217.3
70°	392.9	322.6	231.6	186.0	171.7
72.5°	333.1	264.1	183.4	148.3	144.4
75°	271.9	209.5	137.9	124.9	122.3
77.5°	216.0	158.7	108.0	100.2	97.6
80°	162.6	109.3	82.0	78.1	75.5
82.5°	111.9	67.7	58.5	54.6	54.6
85°	69.0	40.3	36.4	33.8	33.8
87.5°	31.2	16.9	16.9	15.6	14.3
90°	0.7	7.9	17.3	20.2	21.6
92.5°	16.6	12.2	18.7	23.7	24.5
95°	43.9	14.4	22.3	27.3	27.3
97.5°	79.9	59.7	23.0	28.8	29.5
100°	121.6	136.0	23.7	29.5	30.2
102.5°	169.1	178.5	53.3	29.5	30.9
105°	214.5	222.4	157.6	30.2	31.7
107.5°	262.7	269.2	279.9	169.1	74.8
110°	310.9	316.7	324.6	300.8	197.9



TEST NUMBER: P1031063

CATALOG NUMBER: S123RDIW-B1000D755UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	357.0	362.0	369.9	376.4	374.9
115°	402.3	406.6	413.1	420.3	423.2
117.5°	446.9	451.9	455.5	461.3	462.0
120°	487.9	494.4	496.6	502.3	502.3
122.5°	529.7	534.7	537.6	541.2	541.9
125°	567.1	572.9	575.7	577.2	578.6
127.5°	604.5	610.3	613.9	616.0	614.6
130°	639.1	644.8	647.7	650.6	649.1
132.5°	672.2	677.9	680.1	683.0	680.8
135°	706.0	710.3	713.2	715.3	713.2
137.5°	734.8	740.5	742.0	745.6	744.1
140°	763.6	767.9	770.0	772.9	771.5
142.5°	790.2	794.5	796.7	798.8	796.7
145°	814.7	819.7	821.1	822.6	822.6
147.5°	838.4	842.0	843.4	844.9	841.3
150°	860.0	862.2	863.6	865.0	862.9
152.5°	879.4	880.1	880.9	883.7	880.1
155°	897.4	896.0	896.7	900.3	896.0
157.5°	911.8	911.8	911.1	915.4	909.7
160°	924.8	924.0	923.3	927.6	922.6
162.5°	937.0	934.8	934.1	939.2	934.8
165°	946.4	944.2	943.5	949.2	944.2
167.5°	954.3	951.4	951.4	957.2	951.4
170°	960.8	957.9	957.9	963.6	957.9
172.5°	965.1	961.5	962.2	967.9	961.5
175°	968.7	965.1	965.8	970.8	965.1
177.5°	970.1	966.5	967.2	973.0	965.8
180°	968.7	968.7	968.7	968.7	968.7

(END OF REPORT)