

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031088

Luminaire Tested: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031088
REPORT IS A COMBINATION OF REPORTS P994039 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10395.0 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.2 / 1.34
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 113.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	49	49	49	42	42	42
1	97	93	89	86	88	85	82	79	70	68	66	57	55	54	44	43	42	37	37	37
2	88	81	76	71	81	75	70	65	62	58	55	50	48	46	40	38	37	32	32	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	35	33	32	27	27	27
4	74	64	56	51	68	59	52	47	49	44	41	40	37	34	32	30	28	24	24	24
5	68	57	49	44	62	53	46	41	44	39	35	36	33	30	29	26	24	21	21	21
6	63	51	44	38	57	47	41	36	40	35	31	33	29	26	26	24	22	19	19	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17	17	17
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	22	20	17	15	15	15
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14	14	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	16	14	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	19046	19046	19046	19046
5°	19061	21936	19110	16274
10°	18892	26480	18975	14214
15°	18697	30053	18697	12534
20°	18314	32417	18418	11119
25°	18034	30798	17998	10145
30°	17707	21338	17670	9194
35°	17314	13701	17237	8475
40°	16825	9674	16742	7762
45°	15974	7742	15952	7066
50°	14928	6476	14879	6253
55°	13753	5338	13642	5302
60°	12597	4412	12473	4508
65°	11243	3530	11316	3821
70°	9992	2453	10260	3089
75°	8471	1820	8818	2376
80°	6743	1206	7318	1781
85°	4803	572	5235	1108

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 30°

Vertical Angle: 45°

Luminance: 25427 cd/sqm

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.8	1.7
10°-20°	544.0	5.2
20°-30°	856.7	8.2
30°-40°	890.8	8.6
40°-50°	762.1	7.3
50°-60°	581.1	5.6
60°-70°	372.3	3.6
70°-80°	178.4	1.7
80°-90°	50.8	0.5
90°-100°	69.2	0.7
100°-110°	334.7	3.2
110°-120°	820.2	7.9
120°-130°	1041.3	10.0
130°-140°	1112.4	10.7
140°-150°	1040.2	10.0
150°-160°	839.0	8.1
160°-170°	541.5	5.2
170°-180°	186.6	1.8
0°-30°	1574.4	15.1
0°-40°	2465.3	23.7
0°-60°	3808.5	36.6
0°-90°	4409.9	42.4
90°-120°	1224.2	11.8
90°-150°	4418.0	42.5
90°-180°	5985.0	57.6
0°-180°	10395.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1769	1769	1769	1769	1769	
5°	1768	2101	1772	1559	1768	168
15°	1689	2986	1689	1245	1689	475
25°	1536	3077	1533	1014	1536	708
35°	1341	1335	1335	826	1341	839
45°	1076	712	1074	650	1076	828
55°	759	447	753	444	759	680
65°	465	258	468	279	465	465
75°	223	109	232	142	223	240
85°	50	26	54	50	50	56
90°	2	44	2	44	2	8
95°	89	55	89	55	89	106
105°	435	64	435	64	435	461
115°	815	858	815	858	815	805
125°	1149	1173	1149	1173	1149	1027
135°	1431	1445	1431	1445	1431	1102
145°	1651	1667	1651	1667	1651	1034
155°	1819	1816	1819	1816	1819	838
165°	1918	1914	1918	1914	1918	542
175°	1963	1956	1963	1956	1963	187
180°	1963	1963	1963	1963	1963	

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4
2.5°	1774.0	1786.1	1795.2	1801.3	1816.4	1825.5	1833.1	1846.7	1846.7	1849.7	1855.8
5°	1767.9	1793.7	1811.9	1836.1	1867.9	1883.1	1904.3	1922.4	1948.2	1961.8	1975.5
7.5°	1754.3	1790.6	1828.5	1864.9	1911.8	1942.1	1963.3	2010.3	2043.6	2084.5	2116.4
10°	1736.1	1786.1	1834.6	1890.6	1954.3	1999.7	2031.5	2093.6	2157.3	2214.8	2263.3
12.5°	1713.4	1774.0	1843.7	1911.8	2001.2	2046.7	2098.2	2175.4	2266.3	2339.1	2404.2
15°	1689.1	1758.8	1837.6	1920.9	2033.0	2096.7	2170.9	2264.8	2366.3	2470.9	2560.2
17.5°	1651.3	1739.1	1827.0	1948.2	2080.0	2117.9	2181.5	2310.3	2436.0	2529.9	2639.0
20°	1613.4	1711.9	1822.5	1931.5	2073.9	2161.8	2220.9	2357.2	2492.1	2605.7	2710.2
22.5°	1578.6	1681.6	1796.7	1934.6	2067.9	2155.7	2230.0	2372.4	2528.4	2655.7	2784.4
25°	1536.1	1648.2	1775.5	1905.8	2067.9	2134.5	2216.3	2381.5	2546.6	2693.5	2852.6
27.5°	1490.7	1604.3	1730.1	1863.4	2011.8	2110.3	2190.6	2367.8	2569.3	2726.9	2890.5
30°	1445.2	1561.9	1683.1	1802.8	1969.4	2063.3	2155.7	2351.2	2581.4	2761.7	2887.5
32.5°	1401.3	1499.8	1619.5	1736.1	1901.2	2004.3	2108.8	2334.5	2586.0	2737.5	2798.1
35°	1340.7	1443.7	1540.7	1664.9	1831.6	1933.1	2055.8	2333.0	2566.3	2660.2	2629.9
37.5°	1284.7	1371.0	1463.4	1574.0	1745.2	1877.0	2004.3	2293.6	2501.2	2507.2	2336.0
40°	1222.5	1293.8	1371.0	1487.7	1672.5	1802.8	1940.6	2233.0	2383.0	2293.6	1992.1
42.5°	1151.3	1215.0	1275.6	1389.2	1590.7	1736.1	1884.6	2157.3	2211.8	2005.8	1692.2
45°	1075.6	1127.1	1183.2	1302.8	1504.3	1648.2	1796.7	2040.6	1984.6	1693.7	1395.3
47.5°	996.8	1040.8	1095.3	1204.4	1411.9	1558.9	1699.8	1874.0	1731.6	1419.5	1169.5
50°	918.0	952.9	1005.9	1118.0	1318.0	1451.3	1581.6	1695.2	1495.2	1218.0	966.5
52.5°	840.8	868.1	922.6	1018.0	1211.9	1339.2	1433.1	1477.1	1274.1	1005.9	839.3
55°	759.0	789.3	825.6	922.6	1115.0	1208.9	1271.0	1269.5	1060.5	852.9	693.8
57.5°	680.2	707.5	739.3	836.2	992.3	1055.9	1108.9	1083.2	884.7	698.4	595.4
60°	610.5	625.7	660.5	742.3	860.5	915.0	945.3	901.4	722.6	589.3	492.4
62.5°	534.8	549.9	578.7	656.0	728.7	757.5	783.2	727.2	596.9	480.2	421.2
65°	465.1	484.8	503.0	565.1	604.5	639.3	636.3	589.3	466.6	390.9	342.4
67.5°	404.5	412.1	427.2	465.1	483.3	509.0	510.5	457.5	375.7	318.1	289.4
70°	339.3	346.9	357.5	375.7	387.8	393.9	390.9	343.9	283.3	248.4	222.7
72.5°	283.3	281.8	289.4	289.4	301.5	300.0	290.9	254.5	215.1	186.3	171.2
75°	222.7	224.2	225.7	222.7	218.1	212.1	204.5	177.2	151.5	137.9	124.2
77.5°	174.2	171.2	172.7	162.1	156.0	150.0	139.4	125.7	104.5	101.5	95.4
80°	124.2	122.7	121.2	116.6	103.0	97.0	89.4	81.8	77.3	74.2	72.7
82.5°	83.3	83.3	80.3	71.2	63.6	59.1	57.6	54.5	50.0	50.0	48.5
85°	50.0	48.5	45.4	36.4	31.8	31.8	31.8	31.8	28.8	28.8	27.3
87.5°	19.7	18.2	13.6	13.6	12.1	12.1	12.1	10.6	10.6	9.1	9.1
90°	1.5	4.7	7.9	11.2	14.4	16.0	18.1	22.3	26.6	30.8	35.0
92.5°	33.5	31.6	29.6	27.7	25.8	24.8	26.3	29.2	32.1	35.0	37.9
95°	89.0	75.7	62.4	49.1	35.8	29.2	31.0	34.5	38.1	41.6	45.2
97.5°	161.9	152.8	143.8	134.7	125.6	121.1	112.8	96.3	79.8	63.2	46.7
100°	246.5	253.0	259.5	266.0	272.5	275.7	250.4	199.8	149.3	98.7	48.1
102.5°	342.8	347.0	351.2	355.4	359.6	361.7	333.5	277.1	220.7	164.3	107.9
105°	434.7	438.3	441.8	445.4	448.9	450.7	436.1	406.9	377.8	348.6	319.4
107.5°	532.4	535.3	538.2	541.1	544.0	545.5	547.9	552.8	557.7	562.5	567.4
110°	630.1	632.7	635.3	637.9	640.5	641.8	643.6	647.1	650.7	654.2	657.8

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	723.4	725.7	728.0	730.3	732.6	733.7	735.5	739.0	742.6	746.1	749.7
115°	815.3	817.3	819.2	821.2	823.1	824.1	825.6	828.5	831.4	834.3	837.2
117.5°	905.8	908.1	910.3	912.6	914.9	916.0	916.8	918.4	920.1	921.7	923.3
120°	988.9	991.8	994.7	997.6	1000.5	1002.0	1002.5	1003.5	1004.4	1005.4	1006.4
122.5°	1073.5	1075.8	1078.0	1080.3	1082.6	1083.7	1084.3	1085.6	1086.9	1088.2	1089.5
125°	1149.4	1152.0	1154.6	1157.1	1159.7	1161.0	1161.7	1163.0	1164.3	1165.6	1166.9
127.5°	1225.2	1227.8	1230.4	1233.0	1235.6	1236.9	1237.7	1239.3	1241.0	1242.6	1244.2
130°	1295.2	1297.8	1300.4	1303.0	1305.6	1306.9	1307.5	1308.8	1310.1	1311.4	1312.7
132.5°	1362.3	1364.9	1367.5	1370.1	1372.7	1374.0	1374.5	1375.4	1376.4	1377.3	1378.3
135°	1430.9	1432.8	1434.8	1436.7	1438.6	1439.6	1440.2	1441.5	1442.8	1444.1	1445.4
137.5°	1489.2	1491.8	1494.4	1497.0	1499.6	1500.9	1501.2	1501.9	1502.5	1503.2	1503.8
140°	1547.5	1549.5	1551.4	1553.4	1555.3	1556.3	1556.8	1557.8	1558.7	1559.7	1560.7
142.5°	1601.5	1603.5	1605.4	1607.4	1609.3	1610.3	1610.8	1611.7	1612.7	1613.6	1614.6
145°	1651.1	1653.4	1655.6	1657.9	1660.2	1661.3	1661.6	1662.3	1662.9	1663.6	1664.2
147.5°	1699.2	1700.8	1702.4	1704.1	1705.7	1706.5	1706.8	1707.5	1708.1	1708.8	1709.4
150°	1743.0	1744.0	1745.0	1745.9	1746.9	1747.4	1747.7	1748.4	1749.0	1749.7	1750.3
152.5°	1782.4	1782.7	1783.0	1783.3	1783.6	1783.8	1784.0	1784.3	1784.6	1785.0	1785.3
155°	1818.8	1818.2	1817.5	1816.9	1816.2	1815.9	1816.1	1816.4	1816.7	1817.1	1817.4
157.5°	1848.0	1848.0	1848.0	1848.0	1848.0	1848.0	1847.8	1847.5	1847.2	1846.8	1846.5
160°	1874.3	1874.0	1873.6	1873.3	1873.0	1872.8	1872.6	1872.3	1872.0	1871.6	1871.3
162.5°	1899.1	1898.1	1897.1	1896.2	1895.2	1894.7	1894.5	1894.2	1893.9	1893.5	1893.2
165°	1918.0	1917.0	1916.0	1915.1	1914.1	1913.6	1913.4	1913.1	1912.8	1912.5	1912.2
167.5°	1934.1	1932.8	1931.5	1930.2	1928.9	1928.2	1928.2	1928.2	1928.2	1928.2	1928.2
170°	1947.2	1945.9	1944.6	1943.3	1942.0	1941.4	1941.4	1941.4	1941.4	1941.4	1941.4
172.5°	1955.9	1954.3	1952.7	1951.0	1949.4	1948.6	1948.8	1949.1	1949.4	1949.8	1950.1
175°	1963.2	1961.6	1960.0	1958.3	1956.7	1955.9	1956.1	1956.4	1956.7	1957.1	1957.4
177.5°	1966.1	1964.5	1962.9	1961.3	1959.7	1958.9	1959.1	1959.4	1959.7	1960.0	1960.3
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4
2.5°	1867.9	1867.9	1881.5	1895.2	1887.6	1892.1	1908.8	1902.8	1914.9	1913.4	1917.9
5°	2008.8	2025.5	2039.1	2067.9	2072.4	2067.9	2096.7	2104.2	2117.9	2101.2	2108.8
7.5°	2167.9	2202.7	2236.0	2278.5	2292.1	2295.1	2310.3	2331.5	2349.7	2316.3	2333.0
10°	2322.4	2375.4	2443.6	2481.5	2514.8	2526.9	2539.0	2552.7	2573.9	2593.6	2578.4
12.5°	2489.0	2566.3	2631.4	2699.6	2740.5	2736.0	2770.8	2779.9	2796.6	2801.1	2807.2
15°	2625.4	2734.4	2775.4	2876.9	2885.9	2916.2	2955.6	2990.5	2995.0	2985.9	2985.9
17.5°	2755.7	2849.6	2922.3	3004.1	3020.8	3046.5	3096.5	3113.2	3119.2	3117.7	3117.7
20°	2861.7	2923.8	3046.5	3114.7	3142.0	3175.3	3210.1	3231.3	3235.9	3242.0	3232.9
22.5°	2931.4	3025.3	3125.3	3181.4	3204.1	3216.2	3238.9	3245.0	3237.4	3238.9	3240.4
25°	2985.9	3078.3	3138.9	3154.1	3152.6	3137.4	3120.8	3092.0	3088.9	3076.8	3052.6
27.5°	3001.1	3035.9	3028.3	2966.2	2904.1	2898.1	2798.1	2743.5	2681.4	2690.5	2655.7
30°	2919.3	2873.8	2766.3	2608.7	2543.6	2437.5	2325.4	2208.8	2163.3	2113.3	2205.7
32.5°	2719.3	2557.2	2366.3	2161.8	2052.7	1958.8	1839.1	1754.3	1705.8	1664.9	1743.7
35°	2417.8	2164.8	1911.8	1717.9	1628.6	1543.7	1431.6	1389.2	1328.6	1334.7	1342.2
37.5°	2030.0	1751.3	1560.4	1369.5	1310.4	1275.6	1193.8	1128.6	1107.4	1101.4	1101.4
40°	1666.4	1437.7	1268.0	1118.0	1072.6	1043.8	978.6	948.3	925.6	919.6	927.1
42.5°	1378.6	1183.2	1051.4	951.4	919.6	883.2	855.9	818.1	813.5	802.9	816.5
45°	1157.4	987.7	889.3	816.5	789.3	775.6	745.3	722.6	713.5	712.0	722.6
47.5°	981.7	849.9	763.5	718.1	696.9	683.2	657.5	648.4	639.3	642.3	637.8
50°	824.1	725.7	669.6	628.7	615.1	601.4	584.8	575.7	571.1	571.1	569.6
52.5°	707.5	625.7	589.3	551.4	545.4	537.8	519.6	513.6	506.0	504.5	510.5
55°	606.0	549.9	513.6	490.8	484.8	469.6	462.1	454.5	449.9	446.9	448.4
57.5°	518.1	475.7	451.4	431.8	421.2	415.1	401.5	399.9	396.9	396.9	395.4
60°	445.4	415.1	386.3	374.2	366.6	359.0	357.5	348.4	343.9	346.9	345.4
62.5°	377.2	353.0	336.3	322.7	318.1	312.1	307.5	304.5	300.0	301.5	301.5
65°	315.1	295.4	283.3	271.2	269.7	263.6	262.1	259.1	259.1	257.5	260.6
67.5°	259.1	245.4	234.8	227.2	222.7	224.2	218.1	213.6	213.6	212.1	216.6
70°	206.0	198.5	187.9	178.8	172.7	172.7	165.1	163.6	163.6	163.6	162.1
72.5°	159.1	145.4	140.9	137.9	137.9	137.9	134.8	134.8	133.3	134.8	133.3
75°	118.2	116.6	113.6	112.1	112.1	110.6	109.1	109.1	109.1	109.1	109.1
77.5°	92.4	92.4	89.4	87.9	87.9	87.9	86.4	86.4	84.8	84.8	84.8
80°	68.2	68.2	65.1	65.1	65.1	63.6	63.6	63.6	65.1	63.6	63.6
82.5°	47.0	47.0	45.4	47.0	45.4	43.9	43.9	43.9	42.4	43.9	43.9
85°	27.3	27.3	25.8	24.2	25.8	25.8	24.2	25.8	24.2	25.8	24.2
87.5°	10.6	9.1	9.1	9.1	7.6	9.1	7.6	7.6	9.1	7.6	9.1
90°	36.3	37.6	38.9	40.2	40.8	41.1	41.8	42.5	43.1	43.8	43.1
92.5°	40.2	42.4	44.7	47.0	48.1	48.3	48.6	48.9	49.3	49.6	49.3
95°	47.5	49.7	52.0	54.3	55.4	55.4	55.4	55.4	55.4	55.4	55.4
97.5°	49.3	51.9	54.4	57.0	58.3	58.5	58.8	59.1	59.5	59.8	59.5
100°	50.7	53.3	55.9	58.5	59.8	60.0	60.3	60.6	61.0	61.3	61.0
102.5°	97.2	86.5	75.8	65.1	59.8	60.1	60.8	61.4	62.1	62.7	62.1
105°	262.0	204.7	147.3	90.0	61.3	61.6	62.3	62.9	63.6	64.2	63.6
107.5°	517.5	467.6	417.7	367.8	342.8	321.6	279.1	236.6	194.2	151.7	194.2
110°	647.1	636.4	625.7	615.0	609.7	586.5	540.2	493.8	447.5	401.1	447.5

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	752.6	755.5	758.4	761.3	762.8	762.5	761.8	761.2	760.5	759.9	760.5
115°	840.4	843.7	846.9	850.2	851.8	852.4	853.7	855.0	856.3	857.6	856.3
117.5°	925.9	928.5	931.0	933.6	934.9	935.1	935.4	935.7	936.1	936.4	936.1
120°	1009.0	1011.6	1014.2	1016.8	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1
122.5°	1091.1	1092.7	1094.4	1096.0	1096.8	1097.0	1097.3	1097.6	1098.0	1098.3	1098.0
125°	1167.5	1168.2	1168.8	1169.5	1169.8	1170.1	1170.8	1171.4	1172.1	1172.7	1172.1
127.5°	1245.2	1246.1	1247.1	1248.0	1248.5	1248.2	1247.5	1246.9	1246.2	1245.6	1246.2
130°	1314.0	1315.3	1316.6	1317.9	1318.5	1318.2	1317.5	1316.9	1316.2	1315.6	1316.2
132.5°	1379.6	1380.9	1382.2	1383.5	1384.2	1383.7	1382.7	1381.8	1380.8	1379.8	1380.8
135°	1446.4	1447.4	1448.3	1449.3	1449.8	1449.3	1448.3	1447.4	1446.4	1445.4	1446.4
137.5°	1505.4	1507.0	1508.7	1510.3	1511.1	1510.8	1510.1	1509.5	1508.8	1508.2	1508.8
140°	1562.0	1563.3	1564.6	1565.9	1566.5	1566.2	1565.5	1564.9	1564.2	1563.6	1564.2
142.5°	1615.6	1616.6	1617.5	1618.5	1619.0	1618.5	1617.5	1616.6	1615.6	1614.6	1615.6
145°	1664.8	1665.5	1666.1	1666.8	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1
147.5°	1710.1	1710.7	1711.4	1712.1	1712.4	1711.6	1710.0	1708.3	1706.7	1705.1	1706.7
150°	1750.9	1751.6	1752.2	1752.9	1753.2	1752.7	1751.7	1750.8	1749.8	1748.8	1749.8
152.5°	1786.6	1787.9	1789.2	1790.5	1791.1	1790.3	1788.7	1787.0	1785.4	1783.8	1785.4
155°	1819.0	1820.6	1822.3	1823.9	1824.7	1823.7	1821.8	1819.8	1817.9	1815.9	1817.9
157.5°	1848.5	1850.4	1852.4	1854.3	1855.3	1854.0	1851.4	1848.8	1846.2	1843.6	1846.2
160°	1873.3	1875.2	1877.2	1879.1	1880.1	1879.0	1876.7	1874.4	1872.2	1869.9	1872.2
162.5°	1895.5	1897.7	1900.0	1902.3	1903.4	1902.4	1900.5	1898.6	1896.6	1894.7	1896.6
165°	1914.8	1917.4	1920.0	1922.6	1923.9	1922.8	1920.5	1918.2	1915.9	1913.6	1915.9
167.5°	1930.8	1933.4	1936.0	1938.6	1939.9	1938.6	1936.0	1933.4	1930.8	1928.2	1930.8
170°	1944.0	1946.6	1949.1	1951.7	1953.0	1951.7	1949.1	1946.6	1944.0	1941.4	1944.0
172.5°	1952.7	1955.3	1957.9	1960.5	1961.8	1960.3	1957.4	1954.5	1951.5	1948.6	1951.5
175°	1959.7	1961.9	1964.2	1966.5	1967.6	1966.3	1963.7	1961.1	1958.5	1955.9	1958.5
177.5°	1962.9	1965.5	1968.1	1970.7	1972.0	1970.4	1967.1	1963.9	1960.6	1957.4	1960.6
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4
2.5°	1910.3	1901.2	1895.2	1890.6	1886.1	1899.7	1881.5	1861.8	1848.2	1839.1	1836.1
5°	2110.3	2090.6	2073.9	2060.3	2063.3	2063.3	2031.5	1996.7	1966.4	1949.7	1931.5
7.5°	2342.1	2320.9	2287.5	2280.0	2273.9	2236.0	2204.2	2140.6	2102.7	2064.9	2031.5
10°	2572.4	2545.1	2513.3	2502.7	2487.5	2440.6	2392.1	2310.3	2263.3	2193.6	2149.7
12.5°	2787.5	2754.1	2722.3	2714.8	2692.0	2651.1	2567.8	2483.0	2402.7	2328.4	2251.2
15°	2967.7	2958.7	2910.2	2879.9	2829.9	2773.8	2755.7	2640.5	2539.0	2461.8	2322.4
17.5°	3119.2	3076.8	3031.4	3011.7	2992.0	2926.8	2861.7	2743.5	2634.5	2520.8	2431.5
20°	3240.4	3193.5	3161.7	3132.9	3123.8	3049.6	2946.5	2842.0	2722.3	2595.1	2478.4
22.5°	3246.5	3240.4	3219.2	3202.6	3184.4	3135.9	3054.1	2923.8	2796.6	2657.2	2504.2
25°	3120.8	3111.7	3172.3	3157.1	3169.2	3151.1	3107.1	2998.0	2849.6	2686.0	2531.4
27.5°	2742.0	2834.4	2929.9	2963.2	2985.9	3051.1	3072.3	3011.7	2892.0	2717.8	2545.1
30°	2226.9	2349.7	2504.2	2587.5	2651.1	2772.3	2929.9	2949.6	2893.5	2754.1	2542.1
32.5°	1748.2	1860.3	1984.6	2083.0	2167.9	2416.3	2628.4	2781.4	2808.7	2736.0	2549.6
35°	1408.9	1457.4	1575.5	1669.5	1784.6	1996.7	2246.6	2493.6	2660.2	2669.3	2526.9
37.5°	1162.0	1187.7	1290.7	1343.7	1411.9	1598.3	1831.6	2154.2	2413.3	2536.0	2463.3
40°	962.0	1021.1	1080.1	1110.4	1158.9	1287.7	1511.9	1764.9	2086.1	2313.3	2364.8
42.5°	834.7	860.5	898.4	940.8	971.1	1083.2	1233.2	1464.9	1754.3	2070.9	2213.3
45°	736.3	745.3	784.7	812.0	843.8	922.6	1028.6	1222.5	1477.1	1789.1	2031.5
47.5°	654.4	672.6	693.8	710.5	731.7	792.3	883.2	1024.1	1248.3	1527.0	1787.6
50°	581.7	592.3	619.6	627.2	642.3	684.7	754.4	862.0	1046.8	1269.5	1539.2
52.5°	513.6	533.3	543.9	554.5	568.1	602.9	648.4	736.3	875.6	1084.7	1313.4
55°	460.5	466.6	481.7	490.8	501.4	525.7	565.1	630.2	739.3	905.9	1122.6
57.5°	409.0	409.0	424.2	431.8	442.4	460.5	495.4	545.4	624.2	748.4	946.8
60°	354.5	356.0	368.1	377.2	380.2	398.4	427.2	466.6	527.2	618.1	780.2
62.5°	306.0	313.6	319.7	322.7	333.3	343.9	368.1	395.4	437.8	518.1	633.2
65°	265.1	266.6	271.2	274.2	278.7	290.9	309.0	327.2	363.6	422.7	516.6
67.5°	218.1	224.2	230.3	230.3	234.8	240.9	259.1	274.2	301.5	336.3	399.9
70°	163.6	166.6	175.7	180.3	186.3	196.9	206.0	215.1	236.3	262.1	310.6
72.5°	136.3	136.3	139.4	140.9	140.9	148.5	162.1	171.2	181.8	200.0	233.3
75°	109.1	109.1	113.6	112.1	115.1	118.2	119.7	125.7	131.8	145.4	165.1
77.5°	86.4	87.9	87.9	89.4	89.4	90.9	92.4	95.4	98.5	106.0	115.1
80°	63.6	65.1	65.1	66.7	66.7	68.2	69.7	71.2	74.2	77.3	81.8
82.5°	43.9	45.4	45.4	47.0	45.4	47.0	48.5	48.5	50.0	53.0	54.5
85°	25.8	25.8	27.3	25.8	25.8	25.8	27.3	27.3	28.8	33.3	33.3
87.5°	7.6	9.1	7.6	9.1	9.1	9.1	9.1	10.6	10.6	12.1	13.6
90°	42.5	41.8	41.1	40.8	40.2	38.9	37.6	36.3	35.0	30.8	26.6
92.5°	48.9	48.6	48.3	48.1	47.0	44.7	42.4	40.2	37.9	35.0	32.1
95°	55.4	55.4	55.4	55.4	54.3	52.0	49.7	47.5	45.2	41.6	38.1
97.5°	59.1	58.8	58.5	58.3	57.0	54.4	51.9	49.3	46.7	63.2	79.8
100°	60.6	60.3	60.0	59.8	58.5	55.9	53.3	50.7	48.1	98.7	149.3
102.5°	61.4	60.8	60.1	59.8	65.1	75.8	86.5	97.2	107.9	164.3	220.7
105°	62.9	62.3	61.6	61.3	90.0	147.3	204.7	262.0	319.4	348.6	377.8
107.5°	236.6	279.1	321.6	342.8	367.8	417.7	467.6	517.5	567.4	562.5	557.7
110°	493.8	540.2	586.5	609.7	615.0	625.7	636.4	647.1	657.8	654.2	650.7

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	761.2	761.8	762.5	762.8	761.3	758.4	755.5	752.6	749.7	746.1	742.6
115°	855.0	853.7	852.4	851.8	850.2	846.9	843.7	840.4	837.2	834.3	831.4
117.5°	935.7	935.4	935.1	934.9	933.6	931.0	928.5	925.9	923.3	921.7	920.1
120°	1018.1	1018.1	1018.1	1018.1	1016.8	1014.2	1011.6	1009.0	1006.4	1005.4	1004.4
122.5°	1097.6	1097.3	1097.0	1096.8	1096.0	1094.4	1092.7	1091.1	1089.5	1088.2	1086.9
125°	1171.4	1170.8	1170.1	1169.8	1169.5	1168.8	1168.2	1167.5	1166.9	1165.6	1164.3
127.5°	1246.9	1247.5	1248.2	1248.5	1248.0	1247.1	1246.1	1245.2	1244.2	1242.6	1241.0
130°	1316.9	1317.5	1318.2	1318.5	1317.9	1316.6	1315.3	1314.0	1312.7	1311.4	1310.1
132.5°	1381.8	1382.7	1383.7	1384.2	1383.5	1382.2	1380.9	1379.6	1378.3	1377.3	1376.4
135°	1447.4	1448.3	1449.3	1449.8	1449.3	1448.3	1447.4	1446.4	1445.4	1444.1	1442.8
137.5°	1509.5	1510.1	1510.8	1511.1	1510.3	1508.7	1507.0	1505.4	1503.8	1503.2	1502.5
140°	1564.9	1565.5	1566.2	1566.5	1565.9	1564.6	1563.3	1562.0	1560.7	1559.7	1558.7
142.5°	1616.6	1617.5	1618.5	1619.0	1618.5	1617.5	1616.6	1615.6	1614.6	1613.6	1612.7
145°	1667.1	1667.1	1667.1	1667.1	1666.8	1666.1	1665.5	1664.8	1664.2	1663.6	1662.9
147.5°	1708.3	1710.0	1711.6	1712.4	1712.1	1711.4	1710.7	1710.1	1709.4	1708.8	1708.1
150°	1750.8	1751.7	1752.7	1753.2	1752.9	1752.2	1751.6	1750.9	1750.3	1749.7	1749.0
152.5°	1787.0	1788.7	1790.3	1791.1	1790.5	1789.2	1787.9	1786.6	1785.3	1785.0	1784.6
155°	1819.8	1821.8	1823.7	1824.7	1823.9	1822.3	1820.6	1819.0	1817.4	1817.1	1816.7
157.5°	1848.8	1851.4	1854.0	1855.3	1854.3	1852.4	1850.4	1848.5	1846.5	1846.8	1847.2
160°	1874.4	1876.7	1879.0	1880.1	1879.1	1877.2	1875.2	1873.3	1871.3	1871.6	1872.0
162.5°	1898.6	1900.5	1902.4	1903.4	1902.3	1900.0	1897.7	1895.5	1893.2	1893.5	1893.9
165°	1918.2	1920.5	1922.8	1923.9	1922.6	1920.0	1917.4	1914.8	1912.2	1912.5	1912.8
167.5°	1933.4	1936.0	1938.6	1939.9	1938.6	1936.0	1933.4	1930.8	1928.2	1928.2	1928.2
170°	1946.6	1949.1	1951.7	1953.0	1951.7	1949.1	1946.6	1944.0	1941.4	1941.4	1941.4
172.5°	1954.5	1957.4	1960.3	1961.8	1960.5	1957.9	1955.3	1952.7	1950.1	1949.8	1949.4
175°	1961.1	1963.7	1966.3	1967.6	1966.5	1964.2	1961.9	1959.7	1957.4	1957.1	1956.7
177.5°	1963.9	1967.1	1970.4	1972.0	1970.7	1968.1	1965.5	1962.9	1960.3	1960.0	1959.7
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4
2.5°	1831.6	1824.0	1816.4	1816.4	1799.7	1784.6	1777.0	1780.0	1771.0	1758.8	1746.7
5°	1911.8	1881.5	1875.5	1858.8	1836.1	1804.3	1787.6	1772.5	1754.3	1730.1	1707.3
7.5°	1986.1	1946.7	1925.5	1908.8	1864.9	1820.9	1784.6	1760.3	1728.5	1692.2	1664.9
10°	2083.0	2010.3	1987.6	1949.7	1887.6	1825.5	1783.1	1743.7	1699.8	1657.3	1621.0
12.5°	2160.3	2077.0	2034.6	1996.7	1916.4	1837.6	1766.4	1717.9	1664.9	1617.9	1571.0
15°	2248.2	2154.2	2080.0	2034.6	1933.1	1837.6	1757.3	1689.1	1630.1	1572.5	1531.6
17.5°	2290.6	2172.4	2139.1	2073.9	1927.0	1831.6	1733.1	1660.4	1589.2	1522.5	1474.0
20°	2357.2	2219.4	2136.1	2092.1	1961.8	1820.9	1705.8	1622.5	1548.3	1477.1	1425.5
22.5°	2361.8	2211.8	2157.3	2073.9	1913.4	1789.1	1681.6	1580.1	1493.7	1427.1	1374.0
25°	2351.2	2198.2	2122.4	2055.8	1922.4	1771.0	1633.1	1533.1	1448.3	1371.0	1308.9
27.5°	2346.6	2158.8	2087.6	2020.9	1870.9	1717.9	1604.3	1490.7	1393.7	1325.6	1261.9
30°	2340.6	2116.4	2030.0	1952.7	1814.9	1677.0	1540.7	1442.2	1349.8	1263.5	1199.8
32.5°	2301.2	2058.8	1970.9	1889.1	1740.7	1602.8	1495.2	1390.7	1290.7	1210.4	1152.9
35°	2289.1	2005.8	1890.6	1802.8	1657.3	1534.6	1421.0	1334.7	1240.7	1160.4	1092.3
37.5°	2254.2	1951.2	1827.0	1714.9	1563.4	1446.8	1363.4	1277.1	1186.2	1099.8	1045.3
40°	2193.6	1887.6	1746.7	1631.6	1475.5	1357.4	1280.1	1216.5	1127.1	1049.8	983.2
42.5°	2104.2	1822.5	1671.0	1549.8	1377.1	1266.5	1202.9	1142.3	1066.5	986.2	931.7
45°	2001.2	1736.1	1595.2	1460.4	1284.7	1177.1	1110.4	1074.1	1004.4	936.2	872.6
47.5°	1860.3	1646.7	1507.4	1368.0	1189.2	1084.7	1031.7	995.3	946.8	872.6	821.1
50°	1683.1	1531.6	1399.8	1275.6	1095.3	995.3	942.3	915.0	874.1	821.1	771.1
52.5°	1486.1	1398.3	1289.2	1174.1	999.9	905.9	857.5	836.2	805.9	756.0	713.5
55°	1287.7	1249.8	1175.6	1062.0	899.9	822.6	780.2	752.9	730.2	693.8	657.5
57.5°	1110.4	1092.3	1040.8	952.9	816.5	736.3	699.9	681.7	663.5	636.3	599.9
60°	927.1	946.8	893.8	849.9	725.7	656.0	624.2	604.5	595.4	571.1	548.4
62.5°	768.1	786.2	756.0	722.6	634.8	572.6	552.9	534.8	528.7	507.5	484.8
65°	624.2	646.9	624.2	606.0	552.9	501.4	477.2	468.1	462.1	448.4	430.2
67.5°	496.9	519.6	509.0	486.3	469.6	427.2	413.6	404.5	401.5	390.9	375.7
70°	374.2	406.0	409.0	395.4	380.2	360.6	351.5	348.4	340.9	331.8	322.7
72.5°	269.7	306.0	307.5	307.5	298.4	298.4	289.4	284.8	284.8	275.7	265.1
75°	198.5	222.7	225.7	228.8	233.3	237.8	231.8	231.8	230.3	221.2	216.6
77.5°	131.8	153.0	160.6	171.2	177.2	177.2	180.3	183.3	180.3	175.7	172.7
80°	84.8	100.0	109.1	115.1	124.2	128.8	133.3	134.8	131.8	130.3	125.7
82.5°	56.1	60.6	65.1	72.7	83.3	90.9	90.9	89.4	92.4	90.9	89.4
85°	31.8	34.8	36.4	37.9	43.9	51.5	53.0	54.5	57.6	54.5	51.5
87.5°	12.1	13.6	13.6	13.6	16.7	18.2	22.7	28.8	27.3	24.2	24.2
90°	22.3	18.1	16.0	14.4	11.2	7.9	4.7	1.5	4.7	7.9	11.2
92.5°	29.2	26.3	24.8	25.8	27.7	29.6	31.6	33.5	31.6	29.6	27.7
95°	34.5	31.0	29.2	35.8	49.1	62.4	75.7	89.0	75.7	62.4	49.1
97.5°	96.3	112.8	121.1	125.6	134.7	143.8	152.8	161.9	152.8	143.8	134.7
100°	199.8	250.4	275.7	272.5	266.0	259.5	253.0	246.5	253.0	259.5	266.0
102.5°	277.1	333.5	361.7	359.6	355.4	351.2	347.0	342.8	347.0	351.2	355.4
105°	406.9	436.1	450.7	448.9	445.4	441.8	438.3	434.7	438.3	441.8	445.4
107.5°	552.8	547.9	545.5	544.0	541.1	538.2	535.3	532.4	535.3	538.2	541.1
110°	647.1	643.6	641.8	640.5	637.9	635.3	632.7	630.1	632.7	635.3	637.9

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	739.0	735.5	733.7	732.6	730.3	728.0	725.7	723.4	725.7	728.0	730.3
115°	828.5	825.6	824.1	823.1	821.2	819.2	817.3	815.3	817.3	819.2	821.2
117.5°	918.4	916.8	916.0	914.9	912.6	910.3	908.1	905.8	908.1	910.3	912.6
120°	1003.5	1002.5	1002.0	1000.5	997.6	994.7	991.8	988.9	991.8	994.7	997.6
122.5°	1085.6	1084.3	1083.7	1082.6	1080.3	1078.0	1075.8	1073.5	1075.8	1078.0	1080.3
125°	1163.0	1161.7	1161.0	1159.7	1157.1	1154.6	1152.0	1149.4	1152.0	1154.6	1157.1
127.5°	1239.3	1237.7	1236.9	1235.6	1233.0	1230.4	1227.8	1225.2	1227.8	1230.4	1233.0
130°	1308.8	1307.5	1306.9	1305.6	1303.0	1300.4	1297.8	1295.2	1297.8	1300.4	1303.0
132.5°	1375.4	1374.5	1374.0	1372.7	1370.1	1367.5	1364.9	1362.3	1364.9	1367.5	1370.1
135°	1441.5	1440.2	1439.6	1438.6	1436.7	1434.8	1432.8	1430.9	1432.8	1434.8	1436.7
137.5°	1501.9	1501.2	1500.9	1499.6	1497.0	1494.4	1491.8	1489.2	1491.8	1494.4	1497.0
140°	1557.8	1556.8	1556.3	1555.3	1553.4	1551.4	1549.5	1547.5	1549.5	1551.4	1553.4
142.5°	1611.7	1610.8	1610.3	1609.3	1607.4	1605.4	1603.5	1601.5	1603.5	1605.4	1607.4
145°	1662.3	1661.6	1661.3	1660.2	1657.9	1655.6	1653.4	1651.1	1653.4	1655.6	1657.9
147.5°	1707.5	1706.8	1706.5	1705.7	1704.1	1702.4	1700.8	1699.2	1700.8	1702.4	1704.1
150°	1748.4	1747.7	1747.4	1746.9	1745.9	1745.0	1744.0	1743.0	1744.0	1745.0	1745.9
152.5°	1784.3	1784.0	1783.8	1783.6	1783.3	1783.0	1782.7	1782.4	1782.7	1783.0	1783.3
155°	1816.4	1816.1	1815.9	1816.2	1816.9	1817.5	1818.2	1818.8	1818.2	1817.5	1816.9
157.5°	1847.5	1847.8	1848.0	1848.0	1848.0	1848.0	1848.0	1848.0	1848.0	1848.0	1848.0
160°	1872.3	1872.6	1872.8	1873.0	1873.3	1873.6	1874.0	1874.3	1874.0	1873.6	1873.3
162.5°	1894.2	1894.5	1894.7	1895.2	1896.2	1897.1	1898.1	1899.1	1898.1	1897.1	1896.2
165°	1913.1	1913.4	1913.6	1914.1	1915.1	1916.0	1917.0	1918.0	1917.0	1916.0	1915.1
167.5°	1928.2	1928.2	1928.2	1928.9	1930.2	1931.5	1932.8	1934.1	1932.8	1931.5	1930.2
170°	1941.4	1941.4	1941.4	1942.0	1943.3	1944.6	1945.9	1947.2	1945.9	1944.6	1943.3
172.5°	1949.1	1948.8	1948.6	1949.4	1951.0	1952.7	1954.3	1955.9	1954.3	1952.7	1951.0
175°	1956.4	1956.1	1955.9	1956.7	1958.3	1960.0	1961.6	1963.2	1961.6	1960.0	1958.3
177.5°	1959.4	1959.1	1958.9	1959.7	1961.3	1962.9	1964.5	1966.1	1964.5	1962.9	1961.3
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4
2.5°	1746.7	1739.1	1736.1	1728.5	1710.4	1698.2	1684.6	1675.5	1677.0	1669.5	1674.0
5°	1692.2	1690.7	1680.1	1664.9	1639.2	1625.5	1601.3	1589.2	1583.1	1584.6	1575.5
7.5°	1646.7	1633.1	1625.5	1601.3	1577.0	1548.3	1528.6	1518.0	1508.9	1499.8	1493.7
10°	1595.2	1583.1	1571.0	1545.2	1511.9	1484.6	1457.4	1446.8	1433.1	1427.1	1422.5
12.5°	1540.7	1533.1	1518.0	1487.7	1449.8	1424.0	1392.2	1386.2	1368.0	1355.9	1352.8
15°	1490.7	1486.1	1458.9	1424.0	1386.2	1360.4	1333.1	1315.0	1284.7	1290.7	1280.1
17.5°	1437.7	1418.0	1401.3	1354.3	1336.2	1296.8	1265.0	1255.9	1234.7	1221.0	1207.4
20°	1378.6	1366.5	1345.3	1315.0	1271.0	1225.6	1201.3	1186.2	1174.1	1152.9	1146.8
22.5°	1322.5	1307.4	1289.2	1249.8	1211.9	1174.1	1140.7	1127.1	1112.0	1096.8	1087.7
25°	1278.6	1255.9	1236.2	1187.7	1149.8	1118.0	1096.8	1074.1	1052.9	1043.8	1040.8
27.5°	1210.4	1196.8	1177.1	1131.7	1096.8	1062.0	1042.3	1027.1	1004.4	993.8	984.7
30°	1166.5	1139.2	1116.5	1080.1	1045.3	1007.4	989.2	971.1	957.4	943.8	933.2
32.5°	1107.4	1086.2	1068.0	1031.7	996.8	962.0	942.3	915.0	907.4	896.8	884.7
35°	1049.8	1036.2	1016.5	977.1	939.3	915.0	893.8	868.1	859.0	851.4	840.8
37.5°	995.3	975.6	962.0	924.1	890.8	862.0	845.3	824.1	818.1	809.0	801.4
40°	948.3	928.7	915.0	877.1	842.3	812.0	801.4	780.2	771.1	760.5	756.0
42.5°	895.3	878.7	860.5	833.2	796.9	766.6	745.3	733.2	721.1	716.6	707.5
45°	839.3	824.1	810.5	780.2	742.3	721.1	702.9	686.3	677.2	669.6	663.5
47.5°	790.8	777.2	759.0	725.7	695.4	675.7	657.5	640.8	631.7	622.6	615.1
50°	734.7	727.2	707.5	675.7	646.9	624.2	607.5	592.3	586.3	575.7	563.6
52.5°	684.7	671.1	654.4	628.7	602.9	575.7	552.9	543.9	533.3	527.2	516.6
55°	625.7	616.6	598.4	575.7	548.4	525.7	509.0	496.9	483.3	477.2	463.6
57.5°	575.7	559.0	549.9	521.1	495.4	472.7	460.5	448.4	433.3	424.2	418.1
60°	521.1	506.0	492.4	468.1	449.9	425.7	407.5	396.9	386.3	374.2	368.1
62.5°	468.1	456.0	439.3	419.6	396.9	377.2	363.6	348.4	342.4	330.3	325.7
65°	410.5	401.5	387.8	365.1	346.9	330.3	316.6	304.5	298.4	293.9	290.9
67.5°	359.0	346.9	337.8	318.1	298.4	284.8	277.2	269.7	262.1	257.5	253.0
70°	306.0	296.9	287.8	269.7	256.0	243.9	237.8	231.8	227.2	222.7	218.1
72.5°	251.5	246.9	237.8	225.7	215.1	206.0	201.5	193.9	189.4	181.8	178.8
75°	207.5	200.0	195.4	184.8	175.7	168.2	162.1	153.0	146.9	143.9	142.4
77.5°	163.6	160.6	154.5	145.4	140.9	133.3	124.2	121.2	118.2	118.2	116.6
80°	122.7	118.2	113.6	106.0	101.5	95.4	95.4	95.4	93.9	95.4	93.9
82.5°	83.3	80.3	77.3	72.7	71.2	71.2	72.7	72.7	72.7	72.7	72.7
85°	48.5	48.5	48.5	50.0	48.5	48.5	50.0	51.5	50.0	50.0	48.5
87.5°	22.7	22.7	24.2	24.2	25.8	25.8	25.8	25.8	25.8	25.8	27.3
90°	14.4	16.0	18.1	22.3	26.6	30.8	35.0	36.3	37.6	38.9	40.2
92.5°	25.8	24.8	26.3	29.2	32.1	35.0	37.9	40.2	42.4	44.7	47.0
95°	35.8	29.2	31.0	34.5	38.1	41.6	45.2	47.5	49.7	52.0	54.3
97.5°	125.6	121.1	112.8	96.3	79.8	63.2	46.7	49.3	51.9	54.4	57.0
100°	272.5	275.7	250.4	199.8	149.3	98.7	48.1	50.7	53.3	55.9	58.5
102.5°	359.6	361.7	333.5	277.1	220.7	164.3	107.9	97.2	86.5	75.8	65.1
105°	448.9	450.7	436.1	406.9	377.8	348.6	319.4	262.0	204.7	147.3	90.0
107.5°	544.0	545.5	547.9	552.8	557.7	562.5	567.4	517.5	467.6	417.7	367.8
110°	640.5	641.8	643.6	647.1	650.7	654.2	657.8	647.1	636.4	625.7	615.0

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	732.6	733.7	735.5	739.0	742.6	746.1	749.7	752.6	755.5	758.4	761.3
115°	823.1	824.1	825.6	828.5	831.4	834.3	837.2	840.4	843.7	846.9	850.2
117.5°	914.9	916.0	916.8	918.4	920.1	921.7	923.3	925.9	928.5	931.0	933.6
120°	1000.5	1002.0	1002.5	1003.5	1004.4	1005.4	1006.4	1009.0	1011.6	1014.2	1016.8
122.5°	1082.6	1083.7	1084.3	1085.6	1086.9	1088.2	1089.5	1091.1	1092.7	1094.4	1096.0
125°	1159.7	1161.0	1161.7	1163.0	1164.3	1165.6	1166.9	1167.5	1168.2	1168.8	1169.5
127.5°	1235.6	1236.9	1237.7	1239.3	1241.0	1242.6	1244.2	1245.2	1246.1	1247.1	1248.0
130°	1305.6	1306.9	1307.5	1308.8	1310.1	1311.4	1312.7	1314.0	1315.3	1316.6	1317.9
132.5°	1372.7	1374.0	1374.5	1375.4	1376.4	1377.3	1378.3	1379.6	1380.9	1382.2	1383.5
135°	1438.6	1439.6	1440.2	1441.5	1442.8	1444.1	1445.4	1446.4	1447.4	1448.3	1449.3
137.5°	1499.6	1500.9	1501.2	1501.9	1502.5	1503.2	1503.8	1505.4	1507.0	1508.7	1510.3
140°	1555.3	1556.3	1556.8	1557.8	1558.7	1559.7	1560.7	1562.0	1563.3	1564.6	1565.9
142.5°	1609.3	1610.3	1610.8	1611.7	1612.7	1613.6	1614.6	1615.6	1616.6	1617.5	1618.5
145°	1660.2	1661.3	1661.6	1662.3	1662.9	1663.6	1664.2	1664.8	1665.5	1666.1	1666.8
147.5°	1705.7	1706.5	1706.8	1707.5	1708.1	1708.8	1709.4	1710.1	1710.7	1711.4	1712.1
150°	1746.9	1747.4	1747.7	1748.4	1749.0	1749.7	1750.3	1750.9	1751.6	1752.2	1752.9
152.5°	1783.6	1783.8	1784.0	1784.3	1784.6	1785.0	1785.3	1786.6	1787.9	1789.2	1790.5
155°	1816.2	1815.9	1816.1	1816.4	1816.7	1817.1	1817.4	1819.0	1820.6	1822.3	1823.9
157.5°	1848.0	1848.0	1847.8	1847.5	1847.2	1846.8	1846.5	1848.5	1850.4	1852.4	1854.3
160°	1873.0	1872.8	1872.6	1872.3	1872.0	1871.6	1871.3	1873.3	1875.2	1877.2	1879.1
162.5°	1895.2	1894.7	1894.5	1894.2	1893.9	1893.5	1893.2	1895.5	1897.7	1900.0	1902.3
165°	1914.1	1913.6	1913.4	1913.1	1912.8	1912.5	1912.2	1914.8	1917.4	1920.0	1922.6
167.5°	1928.9	1928.2	1928.2	1928.2	1928.2	1928.2	1928.2	1930.8	1933.4	1936.0	1938.6
170°	1942.0	1941.4	1941.4	1941.4	1941.4	1941.4	1941.4	1944.0	1946.6	1949.1	1951.7
172.5°	1949.4	1948.6	1948.8	1949.1	1949.4	1949.8	1950.1	1952.7	1955.3	1957.9	1960.5
175°	1956.7	1955.9	1956.1	1956.4	1956.7	1957.1	1957.4	1959.7	1961.9	1964.2	1966.5
177.5°	1959.7	1958.9	1959.1	1959.4	1959.7	1960.0	1960.3	1962.9	1965.5	1968.1	1970.7
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4
2.5°	1672.5	1674.0	1669.5	1660.4	1658.8	1661.9	1671.0	1667.9	1660.4	1674.0	1661.9
5°	1580.1	1572.5	1569.5	1572.5	1563.4	1558.9	1568.0	1563.4	1568.0	1569.5	1574.0
7.5°	1490.7	1492.2	1483.1	1484.6	1472.5	1475.5	1475.5	1475.5	1480.1	1483.1	1489.2
10°	1413.4	1416.5	1405.9	1407.4	1398.3	1392.2	1396.8	1405.9	1405.9	1405.9	1408.9
12.5°	1351.3	1337.7	1330.1	1328.6	1318.0	1315.0	1324.0	1327.1	1334.7	1334.7	1339.2
15°	1274.1	1271.0	1265.0	1265.0	1239.2	1245.3	1248.3	1258.9	1274.1	1261.9	1265.0
17.5°	1204.4	1196.8	1189.2	1186.2	1183.2	1174.1	1186.2	1184.7	1193.8	1195.3	1199.8
20°	1142.3	1136.2	1121.0	1122.6	1125.6	1112.0	1119.5	1119.5	1128.6	1137.7	1148.3
22.5°	1081.7	1075.6	1068.0	1071.1	1062.0	1058.9	1058.9	1066.5	1077.1	1084.7	1083.2
25°	1034.7	1024.1	1019.5	1015.0	1010.5	1013.5	1008.9	1016.5	1024.1	1028.6	1024.1
27.5°	981.7	977.1	968.0	963.5	955.9	959.0	962.0	968.0	972.6	972.6	977.1
30°	930.2	924.1	921.1	916.5	916.5	910.5	912.0	918.0	922.6	927.1	933.2
32.5°	880.2	875.6	871.1	871.1	868.1	866.5	865.0	874.1	874.1	883.2	883.2
35°	839.3	831.7	831.7	824.1	827.2	825.6	822.6	828.7	830.2	836.2	834.7
37.5°	793.8	793.8	790.8	783.2	777.2	778.7	786.2	786.2	790.8	789.3	793.8
40°	748.4	745.3	745.3	740.8	739.3	737.8	739.3	740.8	748.4	746.9	748.4
42.5°	702.9	704.4	696.9	696.9	696.9	692.3	693.8	695.4	698.4	701.4	706.0
45°	659.0	656.0	654.4	651.4	648.4	649.9	648.4	654.4	652.9	656.0	660.5
47.5°	612.0	607.5	606.0	599.9	599.9	602.9	601.4	606.0	607.5	612.0	609.0
50°	566.6	560.5	556.0	557.5	548.4	551.4	551.4	556.0	560.5	562.0	565.1
52.5°	513.6	512.0	510.5	503.0	501.4	499.9	501.4	503.0	509.0	513.6	515.1
55°	462.1	460.5	451.4	448.4	443.9	443.9	446.9	448.4	459.0	460.5	466.6
57.5°	415.1	410.5	399.9	398.4	398.4	398.4	393.9	399.9	403.0	410.5	410.5
60°	363.6	363.6	354.5	354.5	356.0	354.5	354.5	356.0	356.0	362.1	365.1
62.5°	322.7	321.2	321.2	318.1	316.6	318.1	316.6	316.6	318.1	322.7	327.2
65°	286.3	284.8	283.3	281.8	278.7	278.7	280.3	283.3	283.3	286.3	287.8
67.5°	251.5	251.5	248.4	248.4	246.9	245.4	246.9	245.4	251.5	251.5	253.0
70°	216.6	215.1	210.6	209.1	204.5	206.0	206.0	210.6	212.1	215.1	218.1
72.5°	174.2	174.2	171.2	168.2	169.7	166.6	166.6	168.2	168.2	172.7	174.2
75°	143.9	140.9	139.4	140.9	139.4	142.4	139.4	139.4	142.4	142.4	142.4
77.5°	118.2	118.2	116.6	116.6	118.2	116.6	118.2	118.2	118.2	116.6	118.2
80°	97.0	95.4	95.4	95.4	93.9	93.9	93.9	93.9	93.9	93.9	93.9
82.5°	72.7	72.7	71.2	72.7	72.7	71.2	72.7	71.2	71.2	72.7	72.7
85°	48.5	51.5	48.5	48.5	50.0	50.0	51.5	50.0	51.5	48.5	50.0
87.5°	25.8	27.3	27.3	25.8	25.8	27.3	27.3	27.3	28.8	25.8	27.3
90°	40.8	41.1	41.8	42.5	43.1	43.8	43.1	42.5	41.8	41.1	40.8
92.5°	48.1	48.3	48.6	48.9	49.3	49.6	49.3	48.9	48.6	48.3	48.1
95°	55.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4	55.4
97.5°	58.3	58.5	58.8	59.1	59.5	59.8	59.5	59.1	58.8	58.5	58.3
100°	59.8	60.0	60.3	60.6	61.0	61.3	61.0	60.6	60.3	60.0	59.8
102.5°	59.8	60.1	60.8	61.4	62.1	62.7	62.1	61.4	60.8	60.1	59.8
105°	61.3	61.6	62.3	62.9	63.6	64.2	63.6	62.9	62.3	61.6	61.3
107.5°	342.8	321.6	279.1	236.6	194.2	151.7	194.2	236.6	279.1	321.6	342.8
110°	609.7	586.5	540.2	493.8	447.5	401.1	447.5	493.8	540.2	586.5	609.7

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	762.8	762.5	761.8	761.2	760.5	759.9	760.5	761.2	761.8	762.5	762.8
115°	851.8	852.4	853.7	855.0	856.3	857.6	856.3	855.0	853.7	852.4	851.8
117.5°	934.9	935.1	935.4	935.7	936.1	936.4	936.1	935.7	935.4	935.1	934.9
120°	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1	1018.1
122.5°	1096.8	1097.0	1097.3	1097.6	1098.0	1098.3	1098.0	1097.6	1097.3	1097.0	1096.8
125°	1169.8	1170.1	1170.8	1171.4	1172.1	1172.7	1172.1	1171.4	1170.8	1170.1	1169.8
127.5°	1248.5	1248.2	1247.5	1246.9	1246.2	1245.6	1246.2	1246.9	1247.5	1248.2	1248.5
130°	1318.5	1318.2	1317.5	1316.9	1316.2	1315.6	1316.2	1316.9	1317.5	1318.2	1318.5
132.5°	1384.2	1383.7	1382.7	1381.8	1380.8	1379.8	1380.8	1381.8	1382.7	1383.7	1384.2
135°	1449.8	1449.3	1448.3	1447.4	1446.4	1445.4	1446.4	1447.4	1448.3	1449.3	1449.8
137.5°	1511.1	1510.8	1510.1	1509.5	1508.8	1508.2	1508.8	1509.5	1510.1	1510.8	1511.1
140°	1566.5	1566.2	1565.5	1564.9	1564.2	1563.6	1564.2	1564.9	1565.5	1566.2	1566.5
142.5°	1619.0	1618.5	1617.5	1616.6	1615.6	1614.6	1615.6	1616.6	1617.5	1618.5	1619.0
145°	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1	1667.1
147.5°	1712.4	1711.6	1710.0	1708.3	1706.7	1705.1	1706.7	1708.3	1710.0	1711.6	1712.4
150°	1753.2	1752.7	1751.7	1750.8	1749.8	1748.8	1749.8	1750.8	1751.7	1752.7	1753.2
152.5°	1791.1	1790.3	1788.7	1787.0	1785.4	1783.8	1785.4	1787.0	1788.7	1790.3	1791.1
155°	1824.7	1823.7	1821.8	1819.8	1817.9	1815.9	1817.9	1819.8	1821.8	1823.7	1824.7
157.5°	1855.3	1854.0	1851.4	1848.8	1846.2	1843.6	1846.2	1848.8	1851.4	1854.0	1855.3
160°	1880.1	1879.0	1876.7	1874.4	1872.2	1869.9	1872.2	1874.4	1876.7	1879.0	1880.1
162.5°	1903.4	1902.4	1900.5	1898.6	1896.6	1894.7	1896.6	1898.6	1900.5	1902.4	1903.4
165°	1923.9	1922.8	1920.5	1918.2	1915.9	1913.6	1915.9	1918.2	1920.5	1922.8	1923.9
167.5°	1939.9	1938.6	1936.0	1933.4	1930.8	1928.2	1930.8	1933.4	1936.0	1938.6	1939.9
170°	1953.0	1951.7	1949.1	1946.6	1944.0	1941.4	1944.0	1946.6	1949.1	1951.7	1953.0
172.5°	1961.8	1960.3	1957.4	1954.5	1951.5	1948.6	1951.5	1954.5	1957.4	1960.3	1961.8
175°	1967.6	1966.3	1963.7	1961.1	1958.5	1955.9	1958.5	1961.1	1963.7	1966.3	1967.6
177.5°	1972.0	1970.4	1967.1	1963.9	1960.6	1957.4	1960.6	1963.9	1967.1	1970.4	1972.0
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4	1769.4
2.5°	1674.0	1680.1	1674.0	1661.9	1674.0	1681.6	1689.1	1701.3	1707.3	1707.3	1716.4
5°	1578.6	1590.7	1586.1	1583.1	1595.2	1602.8	1614.9	1630.1	1646.7	1657.3	1669.5
7.5°	1493.7	1501.3	1508.9	1508.9	1521.0	1537.7	1555.8	1574.0	1595.2	1610.4	1619.5
10°	1419.5	1425.5	1430.1	1436.2	1454.3	1472.5	1496.8	1519.5	1537.7	1554.3	1569.5
12.5°	1348.3	1357.4	1368.0	1372.5	1386.2	1408.9	1431.6	1458.9	1487.7	1504.3	1519.5
15°	1280.1	1284.7	1296.8	1310.4	1322.5	1346.8	1375.6	1404.3	1428.6	1454.3	1468.0
17.5°	1210.4	1211.9	1243.8	1236.2	1275.6	1298.3	1313.4	1340.7	1380.1	1401.3	1422.5
20°	1142.3	1157.4	1171.0	1178.6	1199.8	1225.6	1269.5	1290.7	1322.5	1342.2	1360.4
22.5°	1089.2	1112.0	1112.0	1130.1	1140.7	1165.0	1196.8	1237.7	1272.5	1286.2	1311.9
25°	1042.3	1052.9	1071.1	1077.1	1096.8	1118.0	1139.2	1183.2	1221.0	1239.2	1257.4
27.5°	981.7	995.3	1019.5	1019.5	1045.3	1068.0	1093.8	1122.6	1160.4	1186.2	1205.9
30°	934.7	948.3	959.0	975.6	986.2	1007.4	1052.9	1074.1	1107.4	1130.1	1154.4
32.5°	890.8	901.4	910.5	928.7	940.8	965.0	989.2	1027.1	1055.9	1077.1	1102.9
35°	842.3	852.9	865.0	878.7	896.8	919.6	942.3	974.1	1002.9	1022.6	1043.8
37.5°	796.9	804.4	822.6	831.7	846.8	868.1	896.8	930.2	955.9	971.1	992.3
40°	752.9	759.0	772.6	789.3	799.9	816.5	846.8	875.6	907.4	925.6	942.3
42.5°	706.0	713.5	725.7	742.3	759.0	777.2	793.8	827.2	855.9	871.1	889.3
45°	665.1	669.6	678.7	695.4	712.0	725.7	751.4	781.7	809.0	821.1	840.8
47.5°	616.6	621.1	634.8	642.3	660.5	678.7	704.4	734.7	759.0	771.1	789.3
50°	566.6	571.1	580.2	596.9	609.0	628.7	651.4	677.2	707.5	724.1	734.7
52.5°	518.1	527.2	534.8	548.4	563.6	583.2	604.5	628.7	654.4	671.1	683.2
55°	469.6	477.2	486.3	493.9	512.0	530.2	554.5	577.2	599.9	615.1	628.7
57.5°	415.1	425.7	434.8	449.9	463.6	478.7	506.0	524.2	551.4	562.0	574.2
60°	368.1	378.7	386.3	398.4	410.5	430.2	448.4	471.1	493.9	507.5	522.7
62.5°	328.7	333.3	337.8	349.9	362.1	380.2	398.4	421.2	445.4	453.0	465.1
65°	289.4	293.9	301.5	312.1	321.2	331.8	351.5	369.6	392.4	404.5	409.0
67.5°	256.0	260.6	262.1	269.7	277.2	289.4	300.0	318.1	339.3	346.9	356.0
70°	218.1	225.7	227.2	233.3	236.3	243.9	256.0	269.7	286.3	300.0	307.5
72.5°	174.2	184.8	187.9	196.9	201.5	209.1	218.1	228.8	239.4	245.4	251.5
75°	142.4	145.4	146.9	154.5	162.1	172.7	177.2	183.3	192.4	200.0	206.0
77.5°	118.2	119.7	121.2	121.2	122.7	128.8	137.9	145.4	151.5	154.5	159.1
80°	95.4	93.9	93.9	95.4	95.4	95.4	98.5	109.1	112.1	119.7	118.2
82.5°	74.2	71.2	72.7	71.2	71.2	71.2	71.2	72.7	72.7	77.3	80.3
85°	48.5	50.0	48.5	48.5	47.0	48.5	47.0	47.0	45.4	45.4	43.9
87.5°	25.8	27.3	25.8	25.8	24.2	25.8	24.2	24.2	22.7	22.7	19.7
90°	40.2	38.9	37.6	36.3	35.0	30.8	26.6	22.3	18.1	16.0	14.4
92.5°	47.0	44.7	42.4	40.2	37.9	35.0	32.1	29.2	26.3	24.8	25.8
95°	54.3	52.0	49.7	47.5	45.2	41.6	38.1	34.5	31.0	29.2	35.8
97.5°	57.0	54.4	51.9	49.3	46.7	63.2	79.8	96.3	112.8	121.1	125.6
100°	58.5	55.9	53.3	50.7	48.1	98.7	149.3	199.8	250.4	275.7	272.5
102.5°	65.1	75.8	86.5	97.2	107.9	164.3	220.7	277.1	333.5	361.7	359.6
105°	90.0	147.3	204.7	262.0	319.4	348.6	377.8	406.9	436.1	450.7	448.9
107.5°	367.8	417.7	467.6	517.5	567.4	562.5	557.7	552.8	547.9	545.5	544.0
110°	615.0	625.7	636.4	647.1	657.8	654.2	650.7	647.1	643.6	641.8	640.5

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	761.3	758.4	755.5	752.6	749.7	746.1	742.6	739.0	735.5	733.7	732.6
115°	850.2	846.9	843.7	840.4	837.2	834.3	831.4	828.5	825.6	824.1	823.1
117.5°	933.6	931.0	928.5	925.9	923.3	921.7	920.1	918.4	916.8	916.0	914.9
120°	1016.8	1014.2	1011.6	1009.0	1006.4	1005.4	1004.4	1003.5	1002.5	1002.0	1000.5
122.5°	1096.0	1094.4	1092.7	1091.1	1089.5	1088.2	1086.9	1085.6	1084.3	1083.7	1082.6
125°	1169.5	1168.8	1168.2	1167.5	1166.9	1165.6	1164.3	1163.0	1161.7	1161.0	1159.7
127.5°	1248.0	1247.1	1246.1	1245.2	1244.2	1242.6	1241.0	1239.3	1237.7	1236.9	1235.6
130°	1317.9	1316.6	1315.3	1314.0	1312.7	1311.4	1310.1	1308.8	1307.5	1306.9	1305.6
132.5°	1383.5	1382.2	1380.9	1379.6	1378.3	1377.3	1376.4	1375.4	1374.5	1374.0	1372.7
135°	1449.3	1448.3	1447.4	1446.4	1445.4	1444.1	1442.8	1441.5	1440.2	1439.6	1438.6
137.5°	1510.3	1508.7	1507.0	1505.4	1503.8	1503.2	1502.5	1501.9	1501.2	1500.9	1499.6
140°	1565.9	1564.6	1563.3	1562.0	1560.7	1559.7	1558.7	1557.8	1556.8	1556.3	1555.3
142.5°	1618.5	1617.5	1616.6	1615.6	1614.6	1613.6	1612.7	1611.7	1610.8	1610.3	1609.3
145°	1666.8	1666.1	1665.5	1664.8	1664.2	1663.6	1662.9	1662.3	1661.6	1661.3	1660.2
147.5°	1712.1	1711.4	1710.7	1710.1	1709.4	1708.8	1708.1	1707.5	1706.8	1706.5	1705.7
150°	1752.9	1752.2	1751.6	1750.9	1750.3	1749.7	1749.0	1748.4	1747.7	1747.4	1746.9
152.5°	1790.5	1789.2	1787.9	1786.6	1785.3	1785.0	1784.6	1784.3	1784.0	1783.8	1783.6
155°	1823.9	1822.3	1820.6	1819.0	1817.4	1817.1	1816.7	1816.4	1816.1	1815.9	1816.2
157.5°	1854.3	1852.4	1850.4	1848.5	1846.5	1846.8	1847.2	1847.5	1847.8	1848.0	1848.0
160°	1879.1	1877.2	1875.2	1873.3	1871.3	1871.6	1872.0	1872.3	1872.6	1872.8	1873.0
162.5°	1902.3	1900.0	1897.7	1895.5	1893.2	1893.5	1893.9	1894.2	1894.5	1894.7	1895.2
165°	1922.6	1920.0	1917.4	1914.8	1912.2	1912.5	1912.8	1913.1	1913.4	1913.6	1914.1
167.5°	1938.6	1936.0	1933.4	1930.8	1928.2	1928.2	1928.2	1928.2	1928.2	1928.2	1928.9
170°	1951.7	1949.1	1946.6	1944.0	1941.4	1941.4	1941.4	1941.4	1941.4	1941.4	1942.0
172.5°	1960.5	1957.9	1955.3	1952.7	1950.1	1949.8	1949.4	1949.1	1948.8	1948.6	1949.4
175°	1966.5	1964.2	1961.9	1959.7	1957.4	1957.1	1956.7	1956.4	1956.1	1955.9	1956.7
177.5°	1970.7	1968.1	1965.5	1962.9	1960.3	1960.0	1959.7	1959.4	1959.1	1958.9	1959.7
180°	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2	1963.2

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1769.4	1769.4	1769.4	1769.4
2.5°	1724.0	1734.6	1755.8	1774.0
5°	1687.6	1704.3	1736.1	1767.9
7.5°	1643.7	1669.5	1710.4	1754.3
10°	1601.3	1634.6	1684.6	1736.1
12.5°	1558.9	1593.7	1646.7	1713.4
15°	1508.9	1545.2	1608.9	1689.1
17.5°	1464.9	1513.4	1571.0	1651.3
20°	1418.0	1454.3	1528.6	1613.4
22.5°	1358.9	1419.5	1489.2	1578.6
25°	1311.9	1365.0	1434.6	1536.1
27.5°	1254.4	1316.5	1401.3	1490.7
30°	1207.4	1258.9	1337.7	1445.2
32.5°	1152.9	1213.5	1295.3	1401.3
35°	1104.4	1155.9	1233.2	1340.7
37.5°	1046.8	1102.9	1189.2	1284.7
40°	996.8	1051.4	1133.2	1222.5
42.5°	936.2	993.8	1075.6	1151.3
45°	887.7	940.8	1005.9	1075.6
47.5°	828.7	884.7	948.3	996.8
50°	775.6	827.2	877.1	918.0
52.5°	718.1	765.0	810.5	840.8
55°	665.1	701.4	737.8	759.0
57.5°	602.9	637.8	668.1	680.2
60°	548.4	577.2	596.9	610.5
62.5°	490.8	512.0	527.2	534.8
65°	434.8	449.9	457.5	465.1
67.5°	377.2	390.9	395.4	404.5
70°	316.6	331.8	334.8	339.3
72.5°	271.2	271.2	277.2	283.3
75°	216.6	219.7	222.7	222.7
77.5°	169.7	169.7	172.7	174.2
80°	124.2	125.7	125.7	124.2
82.5°	84.8	87.9	84.8	83.3
85°	47.0	53.0	50.0	50.0
87.5°	19.7	19.7	22.7	19.7
90°	11.2	7.9	4.7	1.5
92.5°	27.7	29.6	31.6	33.5
95°	49.1	62.4	75.7	89.0
97.5°	134.7	143.8	152.8	161.9
100°	266.0	259.5	253.0	246.5
102.5°	355.4	351.2	347.0	342.8
105°	445.4	441.8	438.3	434.7
107.5°	541.1	538.2	535.3	532.4
110°	637.9	635.3	632.7	630.1

TEST NUMBER: P1031088

CATALOG NUMBER: S123RDIW-B1165D1535UB2750-4F0-XX-W2A-A_5000K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	730.3	728.0	725.7	723.4
115°	821.2	819.2	817.3	815.3
117.5°	912.6	910.3	908.1	905.8
120°	997.6	994.7	991.8	988.9
122.5°	1080.3	1078.0	1075.8	1073.5
125°	1157.1	1154.6	1152.0	1149.4
127.5°	1233.0	1230.4	1227.8	1225.2
130°	1303.0	1300.4	1297.8	1295.2
132.5°	1370.1	1367.5	1364.9	1362.3
135°	1436.7	1434.8	1432.8	1430.9
137.5°	1497.0	1494.4	1491.8	1489.2
140°	1553.4	1551.4	1549.5	1547.5
142.5°	1607.4	1605.4	1603.5	1601.5
145°	1657.9	1655.6	1653.4	1651.1
147.5°	1704.1	1702.4	1700.8	1699.2
150°	1745.9	1745.0	1744.0	1743.0
152.5°	1783.3	1783.0	1782.7	1782.4
155°	1816.9	1817.5	1818.2	1818.8
157.5°	1848.0	1848.0	1848.0	1848.0
160°	1873.3	1873.6	1874.0	1874.3
162.5°	1896.2	1897.1	1898.1	1899.1
165°	1915.1	1916.0	1917.0	1918.0
167.5°	1930.2	1931.5	1932.8	1934.1
170°	1943.3	1944.6	1945.9	1947.2
172.5°	1951.0	1952.7	1954.3	1955.9
175°	1958.3	1960.0	1961.6	1963.2
177.5°	1961.3	1962.9	1964.5	1966.1
180°	1963.2	1963.2	1963.2	1963.2

(END OF REPORT)