

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031564

Luminaire Tested: S123DIW-B340D1030UB35-4F0-XX-W2A-A

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031564
REPORT IS A COMBINATION OF REPORTS P991218 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B340D1030UB35-4F0-XX-W2A-A
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5620.0 lumens
Efficiency: N/A
Efficacy: 126.3 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.37 / 1.5
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 44.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

Luminous Intensity Polar Plot



TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	33	33	33
1	92	88	85	81	82	79	76	73	61	59	57	45	44	42	30	29	28
2	84	77	71	67	75	69	64	60	54	50	47	39	37	36	26	25	24
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	23	22	21
4	70	60	53	47	62	54	47	42	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	36	37	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	19	17	15	14
7	55	43	35	30	49	39	32	27	30	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	29	24	28	23	20	21	18	15	14	12	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	13	11	10
10	44	32	25	21	39	29	23	19	23	19	16	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	5061	5061	5061	5061
5°	5064	5831	5079	4352
10°	5032	7056	5037	3800
15°	4962	8368	5002	3421
20°	4903	9634	4913	3148
25°	4813	9878	4824	3005
30°	4750	8161	4750	2912
35°	4671	5458	4641	2829
40°	4577	3940	4521	2703
45°	4458	3121	4331	2547
50°	4171	2650	4023	2392
55°	3856	2329	3698	2220
60°	3535	2028	3347	2040
65°	3184	1736	3029	1799
70°	2818	1441	2630	1516
75°	2408	1086	2252	1171
80°	1906	726	1754	768
85°	1316	332	1047	304

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 35°

Vertical Angle: 45°

Luminance: 8162 cd/sqm

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.2	0.8
10°-20°	148.5	2.6
20°-30°	249.9	4.4
30°-40°	282.4	5.0
40°-50°	252.9	4.5
50°-60°	204.2	3.6
60°-70°	142.3	2.5
70°-80°	74.7	1.3
80°-90°	20.7	0.4
90°-100°	48.6	0.9
100°-110°	234.8	4.2
110°-120°	575.4	10.2
120°-130°	730.4	13.0
130°-140°	780.3	13.9
140°-150°	729.6	13.0
150°-160°	588.5	10.5
160°-170°	379.8	6.8
170°-180°	130.9	2.3
0°-30°	444.6	7.9
0°-40°	727.0	12.9
0°-60°	1184.1	21.1
0°-90°	1421.7	25.3
90°-120°	858.7	15.3
90°-150°	3099.0	55.1
90°-180°	4198.0	74.7
0°-180°	5620.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	470	470	470	470	470	
5°	470	558	471	417	470	45
15°	448	831	452	340	448	127
25°	410	987	411	300	410	189
35°	362	532	359	276	362	226
45°	300	287	292	234	300	230
55°	213	195	204	186	213	191
65°	132	127	125	131	132	131
75°	63	65	59	70	63	68
85°	14	15	11	14	14	16
90°	1	31	1	31	1	4
95°	62	39	62	39	62	75
105°	305	45	305	45	305	323
115°	572	602	572	602	572	565
125°	806	823	806	823	806	720
135°	1004	1014	1004	1014	1004	773
145°	1158	1169	1158	1169	1158	725
155°	1276	1274	1276	1274	1276	588
165°	1345	1342	1345	1342	1345	380
175°	1377	1372	1377	1372	1377	131
180°	1377	1377	1377	1377	1377	

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	471.5	475.2	477.0	479.7	482.5	486.6	487.9	490.2	489.3	491.1	492.0
5°	469.7	476.1	481.5	488.4	494.8	499.3	503.9	511.2	516.6	517.5	521.6
7.5°	466.5	475.6	485.2	494.8	507.1	514.3	522.5	532.6	540.8	554.0	559.0
10°	462.4	475.2	488.8	502.0	518.9	530.3	540.3	557.2	574.0	587.7	600.4
12.5°	456.0	472.0	489.7	509.3	531.2	544.4	558.1	580.4	605.9	626.9	640.5
15°	448.3	468.3	491.1	512.1	536.2	560.8	575.4	600.4	636.9	656.5	691.6
17.5°	441.9	462.4	485.2	518.0	550.8	575.4	585.9	631.9	656.9	689.7	729.4
20°	431.9	457.9	487.0	519.8	562.2	577.2	598.6	645.1	676.1	718.9	767.6
22.5°	421.4	449.2	484.3	518.4	565.8	581.8	610.9	647.8	697.0	739.4	793.2
25°	410.0	440.1	475.6	516.2	562.6	585.9	613.2	658.8	712.1	765.4	815.0
27.5°	398.6	431.4	468.3	508.9	554.0	581.3	608.6	656.0	724.4	782.2	845.5
30°	387.7	420.5	457.4	498.9	546.2	572.7	598.6	657.9	733.9	799.1	862.9
32.5°	375.8	409.6	448.3	482.9	530.7	559.0	588.1	657.9	739.9	809.1	867.4
35°	361.7	396.4	429.6	464.2	511.6	543.0	575.8	653.3	745.3	812.3	848.3
37.5°	348.1	378.6	407.3	441.0	490.7	524.4	562.2	647.8	742.6	798.6	808.6
40°	332.6	363.1	386.3	417.8	470.2	509.3	547.6	640.5	730.7	766.3	737.1
42.5°	317.5	341.7	361.7	392.3	449.2	487.5	528.9	627.3	707.5	714.8	649.2
45°	300.2	317.5	335.3	369.9	426.4	465.6	511.6	608.2	670.2	649.2	566.3
47.5°	277.9	293.4	313.0	344.9	402.3	442.8	486.6	583.6	615.9	572.2	481.5
50°	256.5	269.7	287.9	318.9	376.8	416.4	462.9	544.9	560.8	492.0	415.0
52.5°	235.1	245.1	262.9	293.8	351.7	390.0	432.3	505.2	496.1	422.3	354.0
55°	212.8	221.4	238.3	268.8	322.5	359.0	399.5	456.5	432.8	362.6	308.0
57.5°	190.9	200.0	217.3	242.8	293.4	328.9	361.3	405.9	370.4	314.3	266.1
60°	171.3	179.0	192.3	217.3	263.3	292.0	321.6	352.2	322.5	268.3	231.4
62.5°	150.8	158.1	170.4	193.2	232.8	258.3	282.0	307.1	274.3	234.6	201.8
65°	131.7	137.6	149.0	169.9	202.3	223.2	242.4	259.7	233.3	196.8	172.2
67.5°	114.3	119.4	128.9	147.6	174.9	190.0	205.5	220.0	197.7	168.6	147.6
70°	95.7	99.8	108.4	122.1	144.0	159.5	170.8	181.8	161.7	138.5	124.4
72.5°	79.3	83.4	88.8	103.0	118.0	127.6	139.9	145.8	134.4	115.3	101.1
75°	63.3	66.5	71.5	80.6	94.8	101.1	108.9	113.4	103.0	90.2	81.5
77.5°	49.7	51.0	54.7	61.0	70.6	77.9	83.8	86.6	79.3	71.1	63.8
80°	35.1	36.9	39.6	45.1	52.4	54.7	58.3	61.5	56.9	49.7	45.1
82.5°	23.2	25.5	26.9	29.2	33.7	36.4	37.4	40.1	36.0	33.3	31.4
85°	13.7	14.6	15.0	16.4	18.7	20.0	21.4	21.9	21.0	20.5	18.7
87.5°	6.8	6.8	6.8	7.7	8.2	9.1	9.6	9.6	9.6	9.1	8.7
90°	1.0	3.3	5.6	7.9	10.2	11.3	12.8	15.7	18.7	21.6	24.6
92.5°	23.5	22.1	20.8	19.4	18.1	17.4	18.4	20.5	22.5	24.6	26.6
95°	62.4	53.1	43.8	34.5	25.2	20.5	21.7	24.2	26.7	29.2	31.7
97.5°	113.6	107.2	100.8	94.5	88.1	84.9	79.1	67.5	55.9	44.3	32.7
100°	172.9	177.5	182.0	186.6	191.1	193.4	175.7	140.2	104.7	69.3	33.8
102.5°	240.4	243.4	246.3	249.3	252.2	253.7	233.9	194.4	154.8	115.3	75.7
105°	304.9	307.4	309.9	312.4	314.9	316.1	305.9	285.4	265.0	244.5	224.1
107.5°	373.4	375.4	377.5	379.5	381.6	382.6	384.3	387.7	391.2	394.6	398.0
110°	442.0	443.8	445.6	447.5	449.3	450.2	451.4	453.9	456.4	458.9	461.4

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	507.5	509.1	510.7	512.2	513.8	514.6	515.9	518.4	520.9	523.4	525.9
115°	571.9	573.3	574.7	576.0	577.4	578.1	579.1	581.2	583.2	585.3	587.3
117.5°	635.4	637.0	638.6	640.1	641.7	642.5	643.1	644.2	645.3	646.5	647.6
120°	693.7	695.7	697.8	699.8	701.9	702.9	703.2	703.9	704.6	705.3	706.0
122.5°	753.0	754.6	756.2	757.8	759.4	760.2	760.7	761.6	762.5	763.4	764.3
125°	806.2	808.0	809.8	811.7	813.5	814.4	814.9	815.8	816.7	817.6	818.5
127.5°	859.4	861.2	863.0	864.9	866.7	867.6	868.2	869.3	870.4	871.6	872.7
130°	908.5	910.3	912.1	914.0	915.8	916.7	917.2	918.1	919.0	919.9	920.8
132.5°	955.6	957.4	959.2	961.1	962.9	963.8	964.1	964.8	965.5	966.1	966.8
135°	1003.7	1005.1	1006.4	1007.8	1009.1	1009.8	1010.3	1011.2	1012.1	1013.0	1013.9
137.5°	1044.6	1046.4	1048.2	1050.1	1051.9	1052.8	1053.0	1053.5	1053.9	1054.4	1054.8
140°	1085.5	1086.9	1088.3	1089.6	1091.0	1091.7	1092.0	1092.7	1093.4	1094.0	1094.7
142.5°	1123.4	1124.8	1126.1	1127.5	1128.8	1129.5	1129.8	1130.5	1131.2	1131.9	1132.6
145°	1158.2	1159.8	1161.4	1162.9	1164.5	1165.3	1165.5	1166.0	1166.5	1166.9	1167.4
147.5°	1191.9	1193.0	1194.2	1195.3	1196.4	1197.0	1197.2	1197.7	1198.2	1198.6	1199.1
150°	1222.6	1223.3	1224.0	1224.7	1225.4	1225.7	1225.9	1226.4	1226.8	1227.3	1227.7
152.5°	1250.2	1250.4	1250.7	1250.9	1251.2	1251.3	1251.4	1251.6	1251.9	1252.1	1252.3
155°	1275.8	1275.4	1274.9	1274.5	1274.0	1273.8	1273.9	1274.1	1274.4	1274.6	1274.8
157.5°	1296.3	1296.3	1296.3	1296.3	1296.3	1296.3	1296.2	1296.0	1295.7	1295.5	1295.3
160°	1314.7	1314.5	1314.3	1314.0	1313.8	1313.7	1313.6	1313.4	1313.1	1312.9	1312.7
162.5°	1332.1	1331.4	1330.7	1330.0	1329.3	1329.0	1328.9	1328.7	1328.4	1328.2	1328.0
165°	1345.4	1344.7	1344.0	1343.3	1342.6	1342.3	1342.2	1342.0	1341.7	1341.5	1341.3
167.5°	1356.7	1355.8	1354.9	1354.0	1353.1	1352.6	1352.6	1352.6	1352.6	1352.6	1352.6
170°	1365.9	1365.0	1364.1	1363.2	1362.3	1361.8	1361.8	1361.8	1361.8	1361.8	1361.8
172.5°	1372.0	1370.9	1369.7	1368.6	1367.5	1366.9	1367.0	1367.2	1367.5	1367.7	1367.9
175°	1377.1	1376.0	1374.8	1373.7	1372.6	1372.0	1372.1	1372.3	1372.6	1372.8	1373.0
177.5°	1379.2	1378.0	1376.9	1375.7	1374.6	1374.0	1374.1	1374.4	1374.6	1374.9	1375.1
180°	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	495.2	496.1	499.3	501.6	506.1	505.7	505.7	505.2	503.9	506.1	507.5
5°	529.8	537.6	538.5	548.5	549.0	553.1	555.8	553.5	559.0	558.5	554.4
7.5°	572.7	583.1	588.1	597.7	608.6	605.9	616.4	618.2	617.3	621.9	625.0
10°	619.6	637.8	650.6	668.3	672.9	675.6	682.5	688.4	700.2	691.1	697.0
12.5°	673.3	686.6	703.4	731.7	745.8	754.9	758.1	762.2	770.4	765.4	765.8
15°	718.4	736.2	764.9	800.0	804.1	815.5	812.7	837.3	849.2	831.4	841.4
17.5°	765.4	789.1	823.2	853.7	871.1	878.8	886.1	909.8	908.9	906.1	908.4
20°	795.4	834.2	876.5	917.1	922.1	928.0	947.6	957.6	955.8	963.5	968.6
22.5°	837.8	878.8	923.9	950.8	962.2	969.0	984.5	990.9	993.6	995.4	992.2
25°	873.3	917.1	950.3	974.0	980.9	984.5	989.5	991.3	990.0	986.8	989.5
27.5°	897.5	932.6	955.3	966.3	962.6	956.7	947.1	940.8	926.6	919.8	928.0
30°	907.5	923.0	929.8	911.6	893.4	878.8	860.6	826.9	800.4	808.2	797.7
32.5°	891.6	881.5	848.7	801.8	787.7	764.0	712.5	672.9	674.3	653.3	662.0
35°	844.6	799.1	737.1	666.1	647.4	634.6	578.1	569.5	551.2	531.7	537.1
37.5°	761.7	695.2	620.0	567.6	539.9	512.1	480.2	461.0	450.1	441.9	448.3
40°	660.6	579.5	517.5	470.6	446.9	429.2	407.3	388.2	375.8	374.5	376.8
42.5°	561.3	492.9	436.0	391.3	383.6	362.6	348.5	333.5	329.8	323.9	327.1
45°	475.2	419.6	372.7	336.2	327.1	321.6	304.3	294.8	290.7	287.0	292.5
47.5°	412.8	354.4	320.3	298.4	289.3	280.2	270.6	264.2	261.0	261.5	261.0
50°	352.6	309.8	279.7	262.9	257.4	251.0	243.3	239.2	237.8	233.7	236.9
52.5°	303.4	272.4	251.5	235.5	231.4	226.9	220.5	218.2	215.0	214.1	214.1
55°	263.8	239.6	222.8	212.3	207.3	203.6	200.0	197.3	195.0	195.0	195.0
57.5°	232.8	211.8	199.5	190.4	188.6	185.0	180.9	180.9	177.7	177.2	178.6
60°	206.4	187.7	178.1	170.4	167.7	166.7	162.6	162.6	161.7	159.5	161.3
62.5°	179.5	165.8	157.6	151.7	149.0	149.0	145.8	143.5	143.5	144.0	143.1
65°	154.9	144.9	137.6	133.0	131.7	129.8	129.4	127.6	126.2	126.6	126.2
67.5°	133.0	125.3	120.3	116.6	114.3	113.4	112.1	112.1	111.2	111.6	109.3
70°	113.4	105.7	101.6	97.9	97.0	97.0	95.2	95.7	94.8	96.1	95.2
72.5°	93.4	87.5	84.3	82.9	82.0	81.5	80.6	79.7	79.3	80.2	79.7
75°	75.6	70.6	68.3	67.4	66.5	66.5	66.1	65.6	65.1	65.1	65.1
77.5°	58.8	55.6	52.8	53.8	52.4	52.8	51.5	51.5	51.9	51.5	51.5
80°	43.3	41.0	41.0	40.1	38.3	39.2	39.2	37.8	37.4	38.3	36.9
82.5°	28.7	28.2	27.3	26.9	26.0	26.4	26.0	25.5	25.1	26.0	25.1
85°	16.9	16.9	16.4	15.5	16.4	15.9	15.5	15.5	15.0	15.0	15.0
87.5°	8.7	7.7	7.7	7.3	7.7	6.8	7.3	6.8	6.4	6.8	6.4
90°	25.5	26.4	27.3	28.2	28.6	28.8	29.3	29.8	30.2	30.7	30.2
92.5°	28.2	29.8	31.4	33.0	33.8	33.9	34.1	34.4	34.6	34.8	34.6
95°	33.3	34.9	36.5	38.1	38.9	38.9	38.9	38.9	38.9	38.9	38.9
97.5°	34.5	36.3	38.2	40.0	40.9	41.0	41.2	41.5	41.7	41.9	41.7
100°	35.6	37.4	39.2	41.0	41.9	42.0	42.3	42.5	42.8	43.0	42.8
102.5°	68.2	60.7	53.2	45.7	41.9	42.1	42.6	43.1	43.5	44.0	43.5
105°	183.9	143.6	103.4	63.1	43.0	43.2	43.7	44.1	44.6	45.0	44.6
107.5°	363.0	328.0	292.9	257.9	240.4	225.5	195.7	166.0	136.2	106.4	136.2
110°	453.9	446.4	438.9	431.4	427.7	411.4	378.9	346.4	313.9	281.4	313.9

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	527.9	530.0	532.0	534.1	535.1	534.9	534.4	533.9	533.5	533.0	533.5
115°	589.6	591.8	594.1	596.4	597.5	598.0	598.9	599.8	600.7	601.6	600.7
117.5°	649.4	651.2	653.1	654.9	655.8	655.9	656.1	656.4	656.6	656.8	656.6
120°	707.8	709.6	711.4	713.2	714.1	714.1	714.1	714.1	714.1	714.1	714.1
122.5°	765.4	766.6	767.7	768.8	769.4	769.5	769.7	770.0	770.2	770.4	770.2
125°	818.9	819.4	819.8	820.3	820.5	820.7	821.2	821.7	822.1	822.6	822.1
127.5°	873.4	874.1	874.8	875.5	875.8	875.6	875.1	874.6	874.2	873.7	874.2
130°	921.7	922.6	923.5	924.4	924.9	924.7	924.2	923.8	923.3	922.9	923.3
132.5°	967.7	968.6	969.5	970.4	970.9	970.6	969.9	969.2	968.6	967.9	968.6
135°	1014.6	1015.3	1016.0	1016.7	1017.0	1016.7	1016.0	1015.3	1014.6	1013.9	1014.6
137.5°	1055.9	1057.1	1058.2	1059.3	1059.9	1059.7	1059.2	1058.8	1058.3	1057.9	1058.3
140°	1095.6	1096.5	1097.4	1098.3	1098.8	1098.6	1098.1	1097.7	1097.2	1096.8	1097.2
142.5°	1133.3	1134.0	1134.7	1135.4	1135.7	1135.4	1134.7	1134.0	1133.3	1132.6	1133.3
145°	1167.8	1168.3	1168.7	1169.2	1169.4	1169.4	1169.4	1169.4	1169.4	1169.4	1169.4
147.5°	1199.5	1200.0	1200.4	1200.9	1201.1	1200.5	1199.4	1198.3	1197.1	1196.0	1197.1
150°	1228.2	1228.6	1229.1	1229.6	1229.8	1229.5	1228.8	1228.1	1227.4	1226.7	1227.4
152.5°	1253.2	1254.1	1255.0	1255.9	1256.4	1255.8	1254.7	1253.6	1252.4	1251.3	1252.4
155°	1275.9	1277.1	1278.2	1279.3	1279.9	1279.2	1277.9	1276.5	1275.2	1273.8	1275.2
157.5°	1296.7	1298.0	1299.4	1300.7	1301.4	1300.5	1298.7	1296.8	1295.0	1293.2	1295.0
160°	1314.1	1315.4	1316.8	1318.1	1318.8	1318.0	1316.4	1314.8	1313.2	1311.6	1313.2
162.5°	1329.6	1331.2	1332.8	1334.4	1335.2	1334.5	1333.1	1331.8	1330.4	1329.0	1330.4
165°	1343.1	1344.9	1346.8	1348.6	1349.5	1348.7	1347.1	1345.5	1343.9	1342.3	1343.9
167.5°	1354.4	1356.2	1358.0	1359.8	1360.7	1359.8	1358.0	1356.2	1354.4	1352.6	1354.4
170°	1363.6	1365.4	1367.3	1369.1	1370.0	1369.1	1367.3	1365.4	1363.6	1361.8	1363.6
172.5°	1369.7	1371.5	1373.4	1375.2	1376.1	1375.1	1373.0	1371.0	1368.9	1366.9	1368.9
175°	1374.6	1376.2	1377.8	1379.4	1380.2	1379.3	1377.5	1375.6	1373.8	1372.0	1373.8
177.5°	1376.9	1378.7	1380.6	1382.4	1383.3	1382.2	1379.9	1377.6	1375.3	1373.0	1375.3
180°	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	503.9	505.2	501.6	500.7	500.7	502.5	501.1	488.8	491.1	488.4	487.5
5°	559.4	556.7	553.1	551.2	549.0	542.6	542.1	528.0	525.3	516.2	512.1
7.5°	620.5	618.2	607.3	605.9	605.0	599.1	584.0	569.0	558.1	547.6	537.6
10°	690.2	683.4	678.4	668.3	663.3	655.1	635.5	621.4	602.7	586.8	565.8
12.5°	774.0	766.3	749.4	742.1	735.8	713.0	693.4	677.4	641.0	630.1	604.1
15°	835.5	819.1	817.3	801.4	800.4	775.4	738.0	720.7	692.5	652.4	625.5
17.5°	902.0	887.5	876.1	856.9	854.2	830.5	803.2	760.8	729.8	691.6	657.4
20°	950.8	943.0	923.5	915.7	899.8	879.7	851.5	799.1	761.3	723.0	681.1
22.5°	989.5	981.8	966.3	955.8	946.7	920.7	887.0	842.4	790.4	740.3	697.0
25°	989.1	986.8	980.4	975.4	968.6	949.4	921.2	878.3	820.5	765.4	705.2
27.5°	933.0	939.4	950.3	955.8	954.4	951.7	935.8	899.8	847.8	782.2	714.8
30°	816.4	839.6	860.1	887.5	895.7	915.7	924.8	904.3	862.9	801.8	727.1
32.5°	677.0	710.7	755.3	770.4	796.3	835.1	878.3	886.1	860.1	813.2	734.8
35°	555.3	583.1	617.8	641.5	664.7	727.6	782.2	829.6	838.3	807.3	733.0
37.5°	459.7	479.3	509.8	529.8	551.2	605.0	681.5	743.0	786.3	787.2	728.0
40°	390.4	399.1	425.5	440.1	460.6	507.1	575.4	655.6	718.9	748.1	714.8
42.5°	330.7	342.1	364.0	374.9	388.2	428.7	473.8	549.9	628.2	690.7	690.2
45°	295.2	303.4	313.4	322.5	337.6	361.7	413.2	470.2	545.3	615.9	643.7
47.5°	263.8	271.5	281.5	284.3	294.3	317.1	348.5	398.2	468.3	538.5	590.9
50°	237.4	243.7	250.6	255.6	260.1	278.8	302.5	344.4	400.5	468.3	533.5
52.5°	216.9	221.4	227.3	230.1	234.2	247.8	266.1	297.0	343.0	405.0	468.3
55°	197.7	200.9	204.6	209.1	210.9	221.0	235.1	261.5	295.7	351.2	411.4
57.5°	180.0	181.3	183.6	186.3	188.6	197.3	209.6	227.3	257.4	300.2	357.2
60°	159.9	163.6	164.9	167.7	169.0	175.9	185.4	200.5	223.7	260.6	303.4
62.5°	143.1	145.3	147.6	149.0	152.2	154.4	162.2	175.9	195.0	222.3	261.0
65°	128.0	128.9	130.3	131.7	132.6	135.3	142.6	151.7	166.3	190.4	220.5
67.5°	110.7	111.6	113.4	113.9	114.8	118.4	122.5	130.3	142.6	160.8	185.4
70°	93.8	95.2	96.1	97.0	98.4	99.8	104.3	110.7	120.3	133.0	152.2
72.5°	79.3	80.6	80.6	81.5	81.1	82.9	87.5	92.0	98.4	108.9	125.7
75°	64.7	64.7	65.6	66.1	66.5	68.3	70.2	73.8	78.8	87.0	97.5
77.5°	51.0	50.6	51.5	51.5	51.5	52.8	54.7	56.5	59.7	65.6	73.8
80°	37.4	37.4	38.3	38.7	37.8	38.3	39.2	41.0	43.3	47.4	51.9
82.5°	24.6	26.4	26.0	26.4	26.0	26.9	27.3	27.8	28.7	30.5	33.7
85°	15.0	15.0	15.0	15.5	15.0	15.5	15.5	15.5	15.9	16.9	18.2
87.5°	6.4	6.4	6.4	6.8	6.4	6.4	6.8	6.4	6.8	6.8	7.3
90°	29.8	29.3	28.8	28.6	28.2	27.3	26.4	25.5	24.6	21.6	18.7
92.5°	34.4	34.1	33.9	33.8	33.0	31.4	29.8	28.2	26.6	24.6	22.5
95°	38.9	38.9	38.9	38.9	38.1	36.5	34.9	33.3	31.7	29.2	26.7
97.5°	41.5	41.2	41.0	40.9	40.0	38.2	36.3	34.5	32.7	44.3	55.9
100°	42.5	42.3	42.0	41.9	41.0	39.2	37.4	35.6	33.8	69.3	104.7
102.5°	43.1	42.6	42.1	41.9	45.7	53.2	60.7	68.2	75.7	115.3	154.8
105°	44.1	43.7	43.2	43.0	63.1	103.4	143.6	183.9	224.1	244.5	265.0
107.5°	166.0	195.7	225.5	240.4	257.9	292.9	328.0	363.0	398.0	394.6	391.2
110°	346.4	378.9	411.4	427.7	431.4	438.9	446.4	453.9	461.4	458.9	456.4

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	533.9	534.4	534.9	535.1	534.1	532.0	530.0	527.9	525.9	523.4	520.9
115°	599.8	598.9	598.0	597.5	596.4	594.1	591.8	589.6	587.3	585.3	583.2
117.5°	656.4	656.1	655.9	655.8	654.9	653.1	651.2	649.4	647.6	646.5	645.3
120°	714.1	714.1	714.1	714.1	713.2	711.4	709.6	707.8	706.0	705.3	704.6
122.5°	770.0	769.7	769.5	769.4	768.8	767.7	766.6	765.4	764.3	763.4	762.5
125°	821.7	821.2	820.7	820.5	820.3	819.8	819.4	818.9	818.5	817.6	816.7
127.5°	874.6	875.1	875.6	875.8	875.5	874.8	874.1	873.4	872.7	871.6	870.4
130°	923.8	924.2	924.7	924.9	924.4	923.5	922.6	921.7	920.8	919.9	919.0
132.5°	969.2	969.9	970.6	970.9	970.4	969.5	968.6	967.7	966.8	966.1	965.5
135°	1015.3	1016.0	1016.7	1017.0	1016.7	1016.0	1015.3	1014.6	1013.9	1013.0	1012.1
137.5°	1058.8	1059.2	1059.7	1059.9	1059.3	1058.2	1057.1	1055.9	1054.8	1054.4	1053.9
140°	1097.7	1098.1	1098.6	1098.8	1098.3	1097.4	1096.5	1095.6	1094.7	1094.0	1093.4
142.5°	1134.0	1134.7	1135.4	1135.7	1135.4	1134.7	1134.0	1133.3	1132.6	1131.9	1131.2
145°	1169.4	1169.4	1169.4	1169.4	1169.2	1168.7	1168.3	1167.8	1167.4	1166.9	1166.5
147.5°	1198.3	1199.4	1200.5	1201.1	1200.9	1200.4	1200.0	1199.5	1199.1	1198.6	1198.2
150°	1228.1	1228.8	1229.5	1229.8	1229.6	1229.1	1228.6	1228.2	1227.7	1227.3	1226.8
152.5°	1253.6	1254.7	1255.8	1256.4	1255.9	1255.0	1254.1	1253.2	1252.3	1252.1	1251.9
155°	1276.5	1277.9	1279.2	1279.9	1279.3	1278.2	1277.1	1275.9	1274.8	1274.6	1274.4
157.5°	1296.8	1298.7	1300.5	1301.4	1300.7	1299.4	1298.0	1296.7	1295.3	1295.5	1295.7
160°	1314.8	1316.4	1318.0	1318.8	1318.1	1316.8	1315.4	1314.1	1312.7	1312.9	1313.1
162.5°	1331.8	1333.1	1334.5	1335.2	1334.4	1332.8	1331.2	1329.6	1328.0	1328.2	1328.4
165°	1345.5	1347.1	1348.7	1349.5	1348.6	1346.8	1344.9	1343.1	1341.3	1341.5	1341.7
167.5°	1356.2	1358.0	1359.8	1360.7	1359.8	1358.0	1356.2	1354.4	1352.6	1352.6	1352.6
170°	1365.4	1367.3	1369.1	1370.0	1369.1	1367.3	1365.4	1363.6	1361.8	1361.8	1361.8
172.5°	1371.0	1373.0	1375.1	1376.1	1375.2	1373.4	1371.5	1369.7	1367.9	1367.7	1367.5
175°	1375.6	1377.5	1379.3	1380.2	1379.4	1377.8	1376.2	1374.6	1373.0	1372.8	1372.6
177.5°	1377.6	1379.9	1382.2	1383.3	1382.4	1380.6	1378.7	1376.9	1375.1	1374.9	1374.6
180°	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	482.9	481.5	481.5	480.6	477.9	472.9	472.4	473.3	470.6	467.9	463.8
5°	506.6	497.9	495.2	492.5	487.0	477.9	474.3	471.1	466.1	460.1	453.8
7.5°	526.6	514.3	510.7	505.7	494.8	482.0	473.8	467.0	460.1	451.9	444.2
10°	551.7	533.9	525.3	518.0	503.0	485.2	472.9	462.9	451.9	441.9	431.9
12.5°	579.9	551.2	548.5	530.7	513.4	487.0	472.0	457.4	442.8	430.5	420.0
15°	603.6	572.2	560.8	549.0	515.7	482.9	468.3	451.9	435.1	421.9	406.4
17.5°	618.7	592.7	568.6	552.6	518.0	488.8	460.6	441.9	424.1	405.9	393.2
20°	636.9	599.1	578.1	556.7	522.5	484.3	456.0	432.8	410.9	394.5	379.0
22.5°	655.1	604.1	586.8	563.5	523.5	479.7	447.8	424.6	399.5	383.1	366.3
25°	653.3	611.4	582.7	563.1	514.3	475.6	438.3	410.9	387.7	366.7	349.9
27.5°	654.7	603.2	574.0	551.2	508.0	469.7	428.2	399.5	375.4	353.5	335.8
30°	655.1	590.9	565.4	538.0	496.1	455.6	416.9	387.7	362.2	338.5	322.5
32.5°	653.8	580.9	549.0	524.4	477.4	441.9	403.6	372.7	346.7	324.8	309.8
35°	650.6	569.0	532.1	501.1	458.3	422.3	391.3	359.4	331.7	311.6	294.3
37.5°	641.9	556.3	514.3	483.8	436.0	399.5	372.2	345.8	318.9	295.2	280.6
40°	635.5	538.9	496.6	463.3	411.8	376.3	353.5	328.5	302.0	280.6	266.5
42.5°	620.9	522.5	478.4	438.7	388.2	351.7	330.3	310.2	287.5	266.5	253.8
45°	597.3	504.8	456.0	415.9	362.2	327.6	308.0	291.6	271.5	251.5	238.7
47.5°	564.0	479.3	432.3	392.3	336.7	301.6	282.0	269.7	253.8	236.9	226.0
50°	528.0	451.5	408.2	368.6	312.1	277.9	258.8	247.4	236.9	221.4	210.9
52.5°	481.1	421.9	380.4	342.6	285.6	252.8	236.0	227.8	216.9	205.9	196.8
55°	435.5	383.6	349.4	313.4	259.7	229.2	212.8	204.1	197.7	188.6	181.3
57.5°	382.7	348.1	316.6	283.8	235.5	207.7	192.3	181.8	177.7	173.6	166.7
60°	333.9	307.5	282.0	254.7	210.5	185.4	170.4	162.2	158.1	155.4	150.8
62.5°	289.3	268.8	246.9	225.1	185.0	162.2	150.8	142.6	139.0	138.5	134.4
65°	246.5	231.9	214.1	192.7	161.3	141.2	130.3	125.3	121.2	121.2	118.0
67.5°	203.6	193.6	179.5	164.5	139.9	121.2	111.2	106.6	104.3	104.3	102.0
70°	169.5	162.6	149.9	136.7	115.3	101.1	93.4	89.3	87.9	88.4	86.6
72.5°	137.6	130.3	119.8	110.2	94.3	83.8	78.4	73.8	71.5	72.0	71.5
75°	106.6	103.0	93.8	86.6	73.8	66.5	61.5	59.2	57.4	57.9	56.9
77.5°	80.2	74.7	69.7	64.7	56.9	51.0	46.9	44.6	43.3	43.3	43.3
80°	54.7	53.8	49.7	46.9	40.5	36.0	32.8	32.3	31.0	31.0	31.0
82.5°	35.5	33.3	31.0	29.2	25.5	22.8	21.4	20.5	20.0	19.6	20.5
85°	19.6	18.2	17.3	15.5	14.1	12.8	11.4	10.9	10.5	10.9	10.5
87.5°	7.7	6.4	6.4	5.9	5.5	5.0	5.0	4.1	4.1	3.6	3.6
90°	15.7	12.8	11.3	10.2	7.9	5.6	3.3	1.0	3.3	5.6	7.9
92.5°	20.5	18.4	17.4	18.1	19.4	20.8	22.1	23.5	22.1	20.8	19.4
95°	24.2	21.7	20.5	25.2	34.5	43.8	53.1	62.4	53.1	43.8	34.5
97.5°	67.5	79.1	84.9	88.1	94.5	100.8	107.2	113.6	107.2	100.8	94.5
100°	140.2	175.7	193.4	191.1	186.6	182.0	177.5	172.9	177.5	182.0	186.6
102.5°	194.4	233.9	253.7	252.2	249.3	246.3	243.4	240.4	243.4	246.3	249.3
105°	285.4	305.9	316.1	314.9	312.4	309.9	307.4	304.9	307.4	309.9	312.4
107.5°	387.7	384.3	382.6	381.6	379.5	377.5	375.4	373.4	375.4	377.5	379.5
110°	453.9	451.4	450.2	449.3	447.5	445.6	443.8	442.0	443.8	445.6	447.5

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	518.4	515.9	514.6	513.8	512.2	510.7	509.1	507.5	509.1	510.7	512.2
115°	581.2	579.1	578.1	577.4	576.0	574.7	573.3	571.9	573.3	574.7	576.0
117.5°	644.2	643.1	642.5	641.7	640.1	638.6	637.0	635.4	637.0	638.6	640.1
120°	703.9	703.2	702.9	701.9	699.8	697.8	695.7	693.7	695.7	697.8	699.8
122.5°	761.6	760.7	760.2	759.4	757.8	756.2	754.6	753.0	754.6	756.2	757.8
125°	815.8	814.9	814.4	813.5	811.7	809.8	808.0	806.2	808.0	809.8	811.7
127.5°	869.3	868.2	867.6	866.7	864.9	863.0	861.2	859.4	861.2	863.0	864.9
130°	918.1	917.2	916.7	915.8	914.0	912.1	910.3	908.5	910.3	912.1	914.0
132.5°	964.8	964.1	963.8	962.9	961.1	959.2	957.4	955.6	957.4	959.2	961.1
135°	1011.2	1010.3	1009.8	1009.1	1007.8	1006.4	1005.1	1003.7	1005.1	1006.4	1007.8
137.5°	1053.5	1053.0	1052.8	1051.9	1050.1	1048.2	1046.4	1044.6	1046.4	1048.2	1050.1
140°	1092.7	1092.0	1091.7	1091.0	1089.6	1088.3	1086.9	1085.5	1086.9	1088.3	1089.6
142.5°	1130.5	1129.8	1129.5	1128.8	1127.5	1126.1	1124.8	1123.4	1124.8	1126.1	1127.5
145°	1166.0	1165.5	1165.3	1164.5	1162.9	1161.4	1159.8	1158.2	1159.8	1161.4	1162.9
147.5°	1197.7	1197.2	1197.0	1196.4	1195.3	1194.2	1193.0	1191.9	1193.0	1194.2	1195.3
150°	1226.4	1225.9	1225.7	1225.4	1224.7	1224.0	1223.3	1222.6	1223.3	1224.0	1224.7
152.5°	1251.6	1251.4	1251.3	1251.2	1250.9	1250.7	1250.4	1250.2	1250.4	1250.7	1250.9
155°	1274.1	1273.9	1273.8	1274.0	1274.5	1274.9	1275.4	1275.8	1275.4	1274.9	1274.5
157.5°	1296.0	1296.2	1296.3	1296.3	1296.3	1296.3	1296.3	1296.3	1296.3	1296.3	1296.3
160°	1313.4	1313.6	1313.7	1313.8	1314.0	1314.3	1314.5	1314.7	1314.5	1314.3	1314.0
162.5°	1328.7	1328.9	1329.0	1329.3	1330.0	1330.7	1331.4	1332.1	1331.4	1330.7	1330.0
165°	1342.0	1342.2	1342.3	1342.6	1343.3	1344.0	1344.7	1345.4	1344.7	1344.0	1343.3
167.5°	1352.6	1352.6	1352.6	1353.1	1354.0	1354.9	1355.8	1356.7	1355.8	1354.9	1354.0
170°	1361.8	1361.8	1361.8	1362.3	1363.2	1364.1	1365.0	1365.9	1365.0	1364.1	1363.2
172.5°	1367.2	1367.0	1366.9	1367.5	1368.6	1369.7	1370.9	1372.0	1370.9	1369.7	1368.6
175°	1372.3	1372.1	1372.0	1372.6	1373.7	1374.8	1376.0	1377.1	1376.0	1374.8	1373.7
177.5°	1374.4	1374.1	1374.0	1374.6	1375.7	1376.9	1378.0	1379.2	1378.0	1376.9	1375.7
180°	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	462.9	462.4	463.3	460.6	456.0	453.8	447.4	446.0	445.6	446.0	446.5
5°	450.1	449.7	448.3	443.7	438.3	434.2	426.4	426.0	423.2	420.5	421.9
7.5°	437.8	436.0	433.3	427.3	420.0	415.5	409.1	404.6	400.9	398.6	396.8
10°	425.5	422.8	420.0	412.3	403.2	396.4	388.6	385.0	380.9	379.0	377.2
12.5°	409.6	406.8	401.8	392.7	387.2	378.6	370.8	367.2	364.9	361.3	359.0
15°	396.8	391.3	388.6	379.0	367.6	366.7	352.6	351.7	347.1	347.1	343.5
17.5°	382.2	378.1	373.1	363.5	355.3	347.1	339.9	337.1	333.0	332.1	330.3
20°	368.1	362.6	360.8	351.2	342.6	332.6	324.8	322.1	320.3	318.4	319.8
22.5°	353.5	349.0	344.4	335.8	329.4	319.4	314.8	312.1	309.3	308.4	308.9
25°	339.4	335.3	330.7	322.1	315.3	307.1	303.0	301.6	300.2	300.2	299.8
27.5°	325.7	321.6	317.5	309.8	303.0	297.0	293.8	292.5	291.1	292.0	292.9
30°	311.6	308.0	304.3	297.5	292.0	286.6	284.7	283.8	283.4	285.6	285.6
32.5°	298.9	295.7	292.9	286.6	281.1	276.5	275.2	275.6	276.1	277.4	278.4
35°	285.6	283.4	280.6	275.2	270.6	266.5	267.0	267.0	267.9	270.2	272.0
37.5°	273.8	270.6	268.3	263.8	260.1	256.5	257.9	259.2	260.1	262.9	263.8
40°	259.7	258.3	256.5	251.9	248.7	248.3	248.7	249.7	251.5	252.8	254.2
42.5°	248.3	246.5	244.2	240.5	237.8	238.3	238.7	239.6	240.5	242.8	244.2
45°	235.5	234.2	232.3	229.2	226.9	227.3	227.8	227.8	228.7	231.4	232.3
47.5°	221.4	221.9	219.6	216.4	215.0	215.0	215.0	215.9	218.2	219.1	219.6
50°	207.7	206.8	206.4	203.2	202.3	201.8	202.3	202.7	205.9	205.5	206.8
52.5°	193.2	193.2	192.7	190.9	189.5	189.5	188.6	190.9	191.8	192.7	194.1
55°	179.0	177.7	177.2	176.3	174.5	174.0	174.9	177.7	178.6	179.5	180.9
57.5°	163.6	163.6	162.6	161.3	161.3	161.3	161.3	163.1	164.5	165.4	168.1
60°	149.4	147.6	146.2	146.2	146.2	145.8	148.5	148.5	151.3	151.7	152.6
62.5°	132.6	131.7	130.8	131.2	130.8	131.7	132.6	134.4	134.9	136.2	137.6
65°	116.6	116.6	115.7	118.4	116.6	116.6	118.9	118.9	119.8	121.2	123.0
67.5°	101.1	101.6	100.7	100.7	101.6	102.0	102.5	104.3	104.8	106.6	108.9
70°	85.2	86.1	86.6	85.6	86.6	87.5	88.4	88.8	90.7	91.6	92.9
72.5°	71.1	72.0	70.6	71.1	71.5	72.4	72.9	73.8	74.7	77.4	78.4
75°	56.9	56.5	56.0	57.9	56.9	58.8	59.2	59.2	60.1	62.4	63.3
77.5°	43.7	43.7	44.2	43.3	44.6	44.2	44.6	46.0	47.4	47.4	51.0
80°	30.5	31.4	31.4	31.4	31.9	32.3	31.4	33.7	34.2	34.2	35.5
82.5°	19.6	20.0	19.6	20.5	20.5	21.4	21.0	21.4	22.3	23.2	23.7
85°	10.5	10.5	11.4	11.4	10.9	11.4	10.9	11.4	12.3	12.3	12.8
87.5°	3.6	3.6	3.6	3.6	4.1	3.6	4.1	4.1	3.6	3.6	5.0
90°	10.2	11.3	12.8	15.7	18.7	21.6	24.6	25.5	26.4	27.3	28.2
92.5°	18.1	17.4	18.4	20.5	22.5	24.6	26.6	28.2	29.8	31.4	33.0
95°	25.2	20.5	21.7	24.2	26.7	29.2	31.7	33.3	34.9	36.5	38.1
97.5°	88.1	84.9	79.1	67.5	55.9	44.3	32.7	34.5	36.3	38.2	40.0
100°	191.1	193.4	175.7	140.2	104.7	69.3	33.8	35.6	37.4	39.2	41.0
102.5°	252.2	253.7	233.9	194.4	154.8	115.3	75.7	68.2	60.7	53.2	45.7
105°	314.9	316.1	305.9	285.4	265.0	244.5	224.1	183.9	143.6	103.4	63.1
107.5°	381.6	382.6	384.3	387.7	391.2	394.6	398.0	363.0	328.0	292.9	257.9
110°	449.3	450.2	451.4	453.9	456.4	458.9	461.4	453.9	446.4	438.9	431.4

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	513.8	514.6	515.9	518.4	520.9	523.4	525.9	527.9	530.0	532.0	534.1
115°	577.4	578.1	579.1	581.2	583.2	585.3	587.3	589.6	591.8	594.1	596.4
117.5°	641.7	642.5	643.1	644.2	645.3	646.5	647.6	649.4	651.2	653.1	654.9
120°	701.9	702.9	703.2	703.9	704.6	705.3	706.0	707.8	709.6	711.4	713.2
122.5°	759.4	760.2	760.7	761.6	762.5	763.4	764.3	765.4	766.6	767.7	768.8
125°	813.5	814.4	814.9	815.8	816.7	817.6	818.5	818.9	819.4	819.8	820.3
127.5°	866.7	867.6	868.2	869.3	870.4	871.6	872.7	873.4	874.1	874.8	875.5
130°	915.8	916.7	917.2	918.1	919.0	919.9	920.8	921.7	922.6	923.5	924.4
132.5°	962.9	963.8	964.1	964.8	965.5	966.1	966.8	967.7	968.6	969.5	970.4
135°	1009.1	1009.8	1010.3	1011.2	1012.1	1013.0	1013.9	1014.6	1015.3	1016.0	1016.7
137.5°	1051.9	1052.8	1053.0	1053.5	1053.9	1054.4	1054.8	1055.9	1057.1	1058.2	1059.3
140°	1091.0	1091.7	1092.0	1092.7	1093.4	1094.0	1094.7	1095.6	1096.5	1097.4	1098.3
142.5°	1128.8	1129.5	1129.8	1130.5	1131.2	1131.9	1132.6	1133.3	1134.0	1134.7	1135.4
145°	1164.5	1165.3	1165.5	1166.0	1166.5	1166.9	1167.4	1167.8	1168.3	1168.7	1169.2
147.5°	1196.4	1197.0	1197.2	1197.7	1198.2	1198.6	1199.1	1199.5	1200.0	1200.4	1200.9
150°	1225.4	1225.7	1225.9	1226.4	1226.8	1227.3	1227.7	1228.2	1228.6	1229.1	1229.6
152.5°	1251.2	1251.3	1251.4	1251.6	1251.9	1252.1	1252.3	1253.2	1254.1	1255.0	1255.9
155°	1274.0	1273.8	1273.9	1274.1	1274.4	1274.6	1274.8	1275.9	1277.1	1278.2	1279.3
157.5°	1296.3	1296.3	1296.2	1296.0	1295.7	1295.5	1295.3	1296.7	1298.0	1299.4	1300.7
160°	1313.8	1313.7	1313.6	1313.4	1313.1	1312.9	1312.7	1314.1	1315.4	1316.8	1318.1
162.5°	1329.3	1329.0	1328.9	1328.7	1328.4	1328.2	1328.0	1329.6	1331.2	1332.8	1334.4
165°	1342.6	1342.3	1342.2	1342.0	1341.7	1341.5	1341.3	1343.1	1344.9	1346.8	1348.6
167.5°	1353.1	1352.6	1352.6	1352.6	1352.6	1352.6	1352.6	1354.4	1356.2	1358.0	1359.8
170°	1362.3	1361.8	1361.8	1361.8	1361.8	1361.8	1361.8	1363.6	1365.4	1367.3	1369.1
172.5°	1367.5	1366.9	1367.0	1367.2	1367.5	1367.7	1367.9	1369.7	1371.5	1373.4	1375.2
175°	1372.6	1372.0	1372.1	1372.3	1372.6	1372.8	1373.0	1374.6	1376.2	1377.8	1379.4
177.5°	1374.6	1374.0	1374.1	1374.4	1374.6	1374.9	1375.1	1376.9	1378.7	1380.6	1382.4
180°	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.0	446.5	444.6	443.3	446.9	444.6	444.6	445.1	444.2	445.6	445.1
5°	421.0	421.4	418.2	419.1	417.3	416.9	416.4	419.1	418.7	418.2	419.1
7.5°	396.4	396.4	395.0	394.1	394.1	392.7	394.5	394.1	395.0	395.0	396.4
10°	375.8	376.8	374.5	372.2	371.7	372.2	372.2	372.7	373.1	376.3	375.8
12.5°	359.0	357.6	357.2	355.8	353.5	352.6	351.7	356.7	355.3	355.3	355.3
15°	340.3	343.5	343.0	338.9	338.0	339.9	338.9	338.9	343.5	343.0	342.6
17.5°	330.3	329.4	328.5	326.2	326.6	326.2	326.6	326.6	329.4	329.4	329.4
20°	318.9	317.1	317.1	316.2	316.2	314.8	316.6	317.1	318.9	318.9	319.4
22.5°	308.9	307.5	307.5	307.1	308.0	306.1	308.0	308.4	308.4	309.8	309.8
25°	300.2	299.3	299.3	300.2	300.2	300.2	300.2	302.0	300.7	301.1	300.7
27.5°	292.5	292.9	293.4	293.8	293.4	293.8	294.3	295.2	295.7	295.2	294.3
30°	285.2	286.6	287.0	287.0	287.9	288.4	288.8	288.8	289.3	287.9	288.8
32.5°	279.7	279.7	280.6	281.1	282.0	282.5	282.5	283.4	282.9	281.5	282.0
35°	272.0	272.0	273.8	274.7	276.1	275.6	276.1	276.1	276.5	275.6	274.3
37.5°	264.2	265.1	265.1	267.0	267.4	267.9	267.4	268.3	267.9	267.0	266.5
40°	255.1	254.7	255.1	256.5	256.9	256.9	256.9	257.9	257.9	257.9	257.4
42.5°	243.7	245.1	244.6	246.0	245.6	245.6	246.5	247.4	247.8	246.5	246.9
45°	232.8	232.8	233.7	233.7	234.2	234.2	236.0	235.1	236.0	235.1	235.5
47.5°	221.0	221.4	221.4	221.9	222.8	223.7	222.8	223.2	223.2	223.7	222.8
50°	207.7	207.7	208.7	210.0	211.8	210.9	210.5	212.3	210.9	210.9	210.0
52.5°	194.1	195.4	195.9	197.3	198.6	199.1	199.5	198.6	199.1	197.7	198.2
55°	180.9	181.3	183.1	184.5	185.9	185.9	185.4	185.9	186.3	184.5	184.5
57.5°	167.7	169.0	170.8	170.8	172.7	172.7	172.2	172.2	172.7	171.3	170.8
60°	153.5	154.9	157.2	157.2	159.9	160.4	159.5	158.5	158.5	157.2	157.6
62.5°	138.5	139.9	141.2	143.5	145.3	144.4	146.2	144.4	144.9	142.1	142.1
65°	125.3	125.7	128.0	130.3	130.3	131.2	130.3	130.8	129.4	129.4	127.6
67.5°	109.8	109.8	112.1	114.3	116.6	116.6	116.6	115.3	115.3	113.9	113.9
70°	96.1	95.7	97.9	99.3	100.7	101.1	100.2	99.8	98.9	97.5	97.0
72.5°	79.3	80.2	82.5	83.4	85.6	85.2	87.5	84.7	84.7	82.5	82.0
75°	64.2	65.1	67.4	68.8	70.2	70.2	71.5	70.2	68.3	67.4	67.0
77.5°	51.0	50.6	52.4	54.7	55.1	54.7	55.6	55.1	53.3	53.3	52.4
80°	36.4	37.8	39.6	39.2	41.0	40.5	40.5	39.6	39.6	38.3	39.2
82.5°	24.1	25.5	26.0	25.5	26.0	26.9	27.3	26.9	26.9	26.0	26.4
85°	12.8	12.8	13.7	14.1	13.7	13.7	14.1	15.5	14.6	13.7	14.6
87.5°	4.1	3.6	3.6	4.1	3.6	3.6	4.1	4.1	4.6	4.6	4.6
90°	28.6	28.8	29.3	29.8	30.2	30.7	30.2	29.8	29.3	28.8	28.6
92.5°	33.8	33.9	34.1	34.4	34.6	34.8	34.6	34.4	34.1	33.9	33.8
95°	38.9	38.9	38.9	38.9	38.9	38.9	38.9	38.9	38.9	38.9	38.9
97.5°	40.9	41.0	41.2	41.5	41.7	41.9	41.7	41.5	41.2	41.0	40.9
100°	41.9	42.0	42.3	42.5	42.8	43.0	42.8	42.5	42.3	42.0	41.9
102.5°	41.9	42.1	42.6	43.1	43.5	44.0	43.5	43.1	42.6	42.1	41.9
105°	43.0	43.2	43.7	44.1	44.6	45.0	44.6	44.1	43.7	43.2	43.0
107.5°	240.4	225.5	195.7	166.0	136.2	106.4	136.2	166.0	195.7	225.5	240.4
110°	427.7	411.4	378.9	346.4	313.9	281.4	313.9	346.4	378.9	411.4	427.7

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	535.1	534.9	534.4	533.9	533.5	533.0	533.5	533.9	534.4	534.9	535.1
115°	597.5	598.0	598.9	599.8	600.7	601.6	600.7	599.8	598.9	598.0	597.5
117.5°	655.8	655.9	656.1	656.4	656.6	656.8	656.6	656.4	656.1	655.9	655.8
120°	714.1	714.1	714.1	714.1	714.1	714.1	714.1	714.1	714.1	714.1	714.1
122.5°	769.4	769.5	769.7	770.0	770.2	770.4	770.2	770.0	769.7	769.5	769.4
125°	820.5	820.7	821.2	821.7	822.1	822.6	822.1	821.7	821.2	820.7	820.5
127.5°	875.8	875.6	875.1	874.6	874.2	873.7	874.2	874.6	875.1	875.6	875.8
130°	924.9	924.7	924.2	923.8	923.3	922.9	923.3	923.8	924.2	924.7	924.9
132.5°	970.9	970.6	969.9	969.2	968.6	967.9	968.6	969.2	969.9	970.6	970.9
135°	1017.0	1016.7	1016.0	1015.3	1014.6	1013.9	1014.6	1015.3	1016.0	1016.7	1017.0
137.5°	1059.9	1059.7	1059.2	1058.8	1058.3	1057.9	1058.3	1058.8	1059.2	1059.7	1059.9
140°	1098.8	1098.6	1098.1	1097.7	1097.2	1096.8	1097.2	1097.7	1098.1	1098.6	1098.8
142.5°	1135.7	1135.4	1134.7	1134.0	1133.3	1132.6	1133.3	1134.0	1134.7	1135.4	1135.7
145°	1169.4	1169.4	1169.4	1169.4	1169.4	1169.4	1169.4	1169.4	1169.4	1169.4	1169.4
147.5°	1201.1	1200.5	1199.4	1198.3	1197.1	1196.0	1197.1	1198.3	1199.4	1200.5	1201.1
150°	1229.8	1229.5	1228.8	1228.1	1227.4	1226.7	1227.4	1228.1	1228.8	1229.5	1229.8
152.5°	1256.4	1255.8	1254.7	1253.6	1252.4	1251.3	1252.4	1253.6	1254.7	1255.8	1256.4
155°	1279.9	1279.2	1277.9	1276.5	1275.2	1273.8	1275.2	1276.5	1277.9	1279.2	1279.9
157.5°	1301.4	1300.5	1298.7	1296.8	1295.0	1293.2	1295.0	1296.8	1298.7	1300.5	1301.4
160°	1318.8	1318.0	1316.4	1314.8	1313.2	1311.6	1313.2	1314.8	1316.4	1318.0	1318.8
162.5°	1335.2	1334.5	1333.1	1331.8	1330.4	1329.0	1330.4	1331.8	1333.1	1334.5	1335.2
165°	1349.5	1348.7	1347.1	1345.5	1343.9	1342.3	1343.9	1345.5	1347.1	1348.7	1349.5
167.5°	1360.7	1359.8	1358.0	1356.2	1354.4	1352.6	1354.4	1356.2	1358.0	1359.8	1360.7
170°	1370.0	1369.1	1367.3	1365.4	1363.6	1361.8	1363.6	1365.4	1367.3	1369.1	1370.0
172.5°	1376.1	1375.1	1373.0	1371.0	1368.9	1366.9	1368.9	1371.0	1373.0	1375.1	1376.1
175°	1380.2	1379.3	1377.5	1375.6	1373.8	1372.0	1373.8	1375.6	1377.5	1379.3	1380.2
177.5°	1383.3	1382.2	1379.9	1377.6	1375.3	1373.0	1375.3	1377.6	1379.9	1382.2	1383.3
180°	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2	470.2
2.5°	446.5	447.4	447.8	446.0	444.6	446.9	450.1	452.4	454.2	456.5	457.9
5°	420.0	423.2	423.2	424.1	425.5	427.8	433.7	437.8	441.5	444.2	446.5
7.5°	397.7	400.0	401.4	403.6	405.9	409.1	415.9	421.9	427.3	430.5	434.2
10°	377.7	379.5	381.8	383.1	387.2	391.8	400.5	405.5	411.8	416.9	421.4
12.5°	358.5	364.9	366.3	365.8	369.5	374.5	383.1	390.9	397.7	402.7	407.7
15°	344.9	347.1	349.9	349.4	357.2	358.5	365.8	374.9	384.1	387.2	391.8
17.5°	329.8	333.5	336.2	337.6	339.9	344.9	351.7	358.5	370.4	370.8	382.7
20°	318.0	321.6	323.5	325.3	326.6	332.6	338.5	346.2	355.8	360.8	367.2
22.5°	310.2	312.1	313.4	314.8	316.6	319.8	327.1	335.8	342.1	347.6	351.7
25°	301.1	303.0	304.8	305.7	307.1	308.9	314.3	321.2	330.3	333.9	338.0
27.5°	294.8	294.8	295.7	295.7	297.5	299.3	303.4	309.8	317.1	321.6	327.1
30°	287.9	287.5	287.9	287.5	287.0	289.7	293.4	298.9	303.9	309.3	313.0
32.5°	281.1	280.6	280.6	281.1	279.3	280.6	282.5	287.5	292.9	295.7	299.8
35°	273.8	272.9	272.9	272.9	272.0	271.1	272.9	277.4	281.1	284.7	287.9
37.5°	266.5	265.1	265.1	264.2	263.3	262.0	262.0	265.6	270.6	272.0	276.1
40°	256.5	256.5	255.6	255.1	254.2	253.3	251.9	255.1	259.7	261.0	264.2
42.5°	246.5	245.1	244.6	244.6	244.6	243.3	242.4	244.6	247.4	249.7	251.5
45°	235.1	234.2	234.6	234.2	233.3	232.8	232.3	233.3	236.4	237.4	239.6
47.5°	222.8	222.3	222.3	221.9	221.4	221.9	220.0	222.3	223.2	224.1	226.0
50°	210.0	209.6	209.1	208.7	208.7	209.1	208.7	208.7	210.5	211.4	213.2
52.5°	197.3	195.9	195.9	195.4	195.4	194.5	195.4	195.9	196.8	197.7	198.6
55°	183.6	183.6	182.2	182.2	181.3	181.3	181.8	181.3	183.1	184.1	184.1
57.5°	170.4	168.6	169.0	168.1	167.2	166.7	166.7	167.7	168.6	168.6	169.5
60°	156.3	154.4	154.0	152.2	153.1	151.7	152.2	152.2	154.0	153.1	154.0
62.5°	142.1	139.9	138.5	137.6	137.6	138.0	137.1	136.7	137.6	138.5	140.3
65°	127.1	125.7	124.4	123.0	123.0	122.5	123.5	122.1	121.6	122.1	123.0
67.5°	111.6	110.2	108.9	107.5	108.0	106.6	105.7	107.1	106.1	106.6	107.5
70°	96.6	95.7	92.9	92.0	91.6	92.0	91.6	90.7	92.0	91.6	92.0
72.5°	81.5	80.6	79.3	77.0	77.0	76.5	76.1	76.1	75.6	75.6	75.6
75°	67.0	65.1	63.8	63.3	62.4	62.0	61.5	60.6	61.0	61.5	60.6
77.5°	51.9	49.7	49.2	49.2	47.8	47.8	48.3	47.8	47.4	47.4	47.4
80°	38.3	36.4	36.4	35.5	34.6	34.6	34.6	34.6	34.2	33.7	34.2
82.5°	24.6	24.1	23.7	23.7	24.6	22.8	23.7	23.2	22.8	22.8	22.3
85°	13.7	14.1	13.7	14.1	13.2	13.7	13.7	13.7	13.2	13.7	12.8
87.5°	5.0	5.0	5.0	5.5	5.5	5.5	5.5	5.5	5.9	5.5	5.5
90°	28.2	27.3	26.4	25.5	24.6	21.6	18.7	15.7	12.8	11.3	10.2
92.5°	33.0	31.4	29.8	28.2	26.6	24.6	22.5	20.5	18.4	17.4	18.1
95°	38.1	36.5	34.9	33.3	31.7	29.2	26.7	24.2	21.7	20.5	25.2
97.5°	40.0	38.2	36.3	34.5	32.7	44.3	55.9	67.5	79.1	84.9	88.1
100°	41.0	39.2	37.4	35.6	33.8	69.3	104.7	140.2	175.7	193.4	191.1
102.5°	45.7	53.2	60.7	68.2	75.7	115.3	154.8	194.4	233.9	253.7	252.2
105°	63.1	103.4	143.6	183.9	224.1	244.5	265.0	285.4	305.9	316.1	314.9
107.5°	257.9	292.9	328.0	363.0	398.0	394.6	391.2	387.7	384.3	382.6	381.6
110°	431.4	438.9	446.4	453.9	461.4	458.9	456.4	453.9	451.4	450.2	449.3

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	534.1	532.0	530.0	527.9	525.9	523.4	520.9	518.4	515.9	514.6	513.8
115°	596.4	594.1	591.8	589.6	587.3	585.3	583.2	581.2	579.1	578.1	577.4
117.5°	654.9	653.1	651.2	649.4	647.6	646.5	645.3	644.2	643.1	642.5	641.7
120°	713.2	711.4	709.6	707.8	706.0	705.3	704.6	703.9	703.2	702.9	701.9
122.5°	768.8	767.7	766.6	765.4	764.3	763.4	762.5	761.6	760.7	760.2	759.4
125°	820.3	819.8	819.4	818.9	818.5	817.6	816.7	815.8	814.9	814.4	813.5
127.5°	875.5	874.8	874.1	873.4	872.7	871.6	870.4	869.3	868.2	867.6	866.7
130°	924.4	923.5	922.6	921.7	920.8	919.9	919.0	918.1	917.2	916.7	915.8
132.5°	970.4	969.5	968.6	967.7	966.8	966.1	965.5	964.8	964.1	963.8	962.9
135°	1016.7	1016.0	1015.3	1014.6	1013.9	1013.0	1012.1	1011.2	1010.3	1009.8	1009.1
137.5°	1059.3	1058.2	1057.1	1055.9	1054.8	1054.4	1053.9	1053.5	1053.0	1052.8	1051.9
140°	1098.3	1097.4	1096.5	1095.6	1094.7	1094.0	1093.4	1092.7	1092.0	1091.7	1091.0
142.5°	1135.4	1134.7	1134.0	1133.3	1132.6	1131.9	1131.2	1130.5	1129.8	1129.5	1128.8
145°	1169.2	1168.7	1168.3	1167.8	1167.4	1166.9	1166.5	1166.0	1165.5	1165.3	1164.5
147.5°	1200.9	1200.4	1200.0	1199.5	1199.1	1198.6	1198.2	1197.7	1197.2	1197.0	1196.4
150°	1229.6	1229.1	1228.6	1228.2	1227.7	1227.3	1226.8	1226.4	1225.9	1225.7	1225.4
152.5°	1255.9	1255.0	1254.1	1253.2	1252.3	1252.1	1251.9	1251.6	1251.4	1251.3	1251.2
155°	1279.3	1278.2	1277.1	1275.9	1274.8	1274.6	1274.4	1274.1	1273.9	1273.8	1274.0
157.5°	1300.7	1299.4	1298.0	1296.7	1295.3	1295.5	1295.7	1296.0	1296.2	1296.3	1296.3
160°	1318.1	1316.8	1315.4	1314.1	1312.7	1312.9	1313.1	1313.4	1313.6	1313.7	1313.8
162.5°	1334.4	1332.8	1331.2	1329.6	1328.0	1328.2	1328.4	1328.7	1328.9	1329.0	1329.3
165°	1348.6	1346.8	1344.9	1343.1	1341.3	1341.5	1341.7	1342.0	1342.2	1342.3	1342.6
167.5°	1359.8	1358.0	1356.2	1354.4	1352.6	1352.6	1352.6	1352.6	1352.6	1352.6	1353.1
170°	1369.1	1367.3	1365.4	1363.6	1361.8	1361.8	1361.8	1361.8	1361.8	1361.8	1362.3
172.5°	1375.2	1373.4	1371.5	1369.7	1367.9	1367.7	1367.5	1367.2	1367.0	1366.9	1367.5
175°	1379.4	1377.8	1376.2	1374.6	1373.0	1372.8	1372.6	1372.3	1372.1	1372.0	1372.6
177.5°	1382.4	1380.6	1378.7	1376.9	1375.1	1374.9	1374.6	1374.4	1374.1	1374.0	1374.6
180°	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1	1377.1

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	470.2	470.2	470.2	470.2
2.5°	460.1	461.5	466.1	471.5
5°	451.0	454.7	461.0	469.7
7.5°	441.0	446.5	455.6	466.5
10°	429.6	437.4	448.7	462.4
12.5°	417.3	427.3	441.9	456.0
15°	409.6	419.6	432.8	448.3
17.5°	394.5	406.4	420.0	441.9
20°	379.0	392.3	410.0	431.9
22.5°	367.2	381.3	398.2	421.4
25°	353.1	367.6	385.9	410.0
27.5°	338.0	352.6	373.1	398.6
30°	326.6	340.8	360.4	387.7
32.5°	313.0	326.6	347.1	375.8
35°	297.5	313.0	332.6	361.7
37.5°	285.6	299.8	320.3	348.1
40°	272.9	285.2	305.2	332.6
42.5°	259.2	272.9	290.2	317.5
45°	246.5	256.5	274.3	300.2
47.5°	232.8	244.2	257.9	277.9
50°	218.2	227.8	242.8	256.5
52.5°	204.1	211.8	224.6	235.1
55°	189.1	196.8	206.4	212.8
57.5°	174.9	180.4	186.8	190.9
60°	157.6	163.1	167.2	171.3
62.5°	142.1	146.2	148.5	150.8
65°	126.2	128.5	129.8	131.7
67.5°	108.9	111.2	111.6	114.3
70°	92.9	93.4	94.3	95.7
72.5°	77.9	78.8	78.4	79.3
75°	62.4	63.3	62.4	63.3
77.5°	47.4	48.3	48.3	49.7
80°	34.2	34.6	35.1	35.1
82.5°	22.3	23.7	22.8	23.2
85°	12.8	13.2	13.2	13.7
87.5°	5.9	6.4	5.9	6.8
90°	7.9	5.6	3.3	1.0
92.5°	19.4	20.8	22.1	23.5
95°	34.5	43.8	53.1	62.4
97.5°	94.5	100.8	107.2	113.6
100°	186.6	182.0	177.5	172.9
102.5°	249.3	246.3	243.4	240.4
105°	312.4	309.9	307.4	304.9
107.5°	379.5	377.5	375.4	373.4
110°	447.5	445.6	443.8	442.0

TEST NUMBER: P1031564

CATALOG NUMBER: S123DIW-B340D1030UB35-4F0-XX-W2A-A

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	512.2	510.7	509.1	507.5
115°	576.0	574.7	573.3	571.9
117.5°	640.1	638.6	637.0	635.4
120°	699.8	697.8	695.7	693.7
122.5°	757.8	756.2	754.6	753.0
125°	811.7	809.8	808.0	806.2
127.5°	864.9	863.0	861.2	859.4
130°	914.0	912.1	910.3	908.5
132.5°	961.1	959.2	957.4	955.6
135°	1007.8	1006.4	1005.1	1003.7
137.5°	1050.1	1048.2	1046.4	1044.6
140°	1089.6	1088.3	1086.9	1085.5
142.5°	1127.5	1126.1	1124.8	1123.4
145°	1162.9	1161.4	1159.8	1158.2
147.5°	1195.3	1194.2	1193.0	1191.9
150°	1224.7	1224.0	1223.3	1222.6
152.5°	1250.9	1250.7	1250.4	1250.2
155°	1274.5	1274.9	1275.4	1275.8
157.5°	1296.3	1296.3	1296.3	1296.3
160°	1314.0	1314.3	1314.5	1314.7
162.5°	1330.0	1330.7	1331.4	1332.1
165°	1343.3	1344.0	1344.7	1345.4
167.5°	1354.0	1354.9	1355.8	1356.7
170°	1363.2	1364.1	1365.0	1365.9
172.5°	1368.6	1369.7	1370.9	1372.0
175°	1373.7	1374.8	1376.0	1377.1
177.5°	1375.7	1376.9	1378.0	1379.2
180°	1377.1	1377.1	1377.1	1377.1

(END OF REPORT)