

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031133

Luminaire Tested: S123RDIW-B340D1320UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031133
REPORT IS A COMBINATION OF REPORTS P994222 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D1320UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6294.0 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 55.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031133

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031133

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	100	100	100	100	88	88	88	88	66	66	66		46	46	46		28
1	91	87	83	80	80	77	74	71	58	56	54		41	40	39		25
2	83	76	70	65	73	67	63	59	51	48	45		36	34	32		22
3	76	67	60	55	67	59	54	49	45	41	38		32	29	27		20
4	69	59	52	46	61	52	46	41	40	36	32		28	26	24		18
5	63	52	45	39	56	47	40	35	36	31	28		25	23	20		16
6	58	47	39	34	51	42	35	31	32	27	24		23	20	18		14
7	54	42	35	29	47	38	31	27	29	24	21		21	18	16		13
8	50	38	31	26	44	34	28	23	26	22	19		19	16	14		12
9	46	35	28	23	41	31	25	21	24	20	16		17	14	12		11
10	43	32	25	20	38	28	22	18	22	18	15		16	13	11		10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5789	5789	5789
5°	5798	5584	5569
10°	5752	5374	5268
15°	5678	5114	4939
20°	5580	4832	4571
25°	5479	4539	4222
30°	5349	4227	3810
35°	5216	3921	3434
40°	5091	3588	3019
45°	4929	3262	2647
50°	4752	2915	2260
55°	4568	2543	1906
60°	4393	2162	1548
65°	4165	1770	1208
70°	3878	1338	864
75°	3469	906	684
80°	2959	630	480
85°	2219	340	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4929 cd/sqm

TEST NUMBER: P1031133

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	0.8
10°-20°	140.6	2.2
20°-30°	202.5	3.2
30°-40°	228.0	3.6
40°-50°	218.1	3.5
50°-60°	178.6	2.8
60°-70°	120.4	1.9
70°-80°	60.4	1.0
80°-90°	19.1	0.3
90°-100°	58.7	0.9
100°-110°	283.9	4.5
110°-120°	695.6	11.1
120°-130°	883.1	14.0
130°-140°	943.4	15.0
140°-150°	882.1	14.0
150°-160°	711.5	11.3
160°-170°	459.2	7.3
170°-180°	158.2	2.5
0°-30°	393.7	6.3
0°-40°	621.7	9.9
0°-60°	1018.4	16.2
0°-90°	1218.3	19.4
90°-120°	1038.2	16.5
90°-150°	3746.7	59.5
90°-180°	5076.0	80.6
0°-180°	6294.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	538	538	538	538	538	
5°	538	536	530	534	533	51
15°	513	508	496	494	491	145
25°	467	456	436	427	422	215
35°	404	388	361	342	334	253
45°	332	312	279	254	243	256
55°	252	231	194	168	160	226
65°	172	148	114	93	88	171
75°	91	70	46	42	41	97
85°	23	14	12	11	11	25
90°	1	14	30	35	37	6
95°	76	25	38	47	47	90
105°	369	382	271	52	54	391
115°	692	699	710	722	727	683
125°	975	985	990	992	994	871
135°	1213	1221	1226	1230	1226	934
145°	1400	1409	1411	1414	1414	877
155°	1542	1540	1541	1547	1540	711
165°	1627	1623	1622	1632	1623	460
175°	1665	1659	1660	1669	1659	158
180°	1665	1665	1665	1665	1665	

TEST NUMBER: P1031133

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	537.8	537.8	537.8	537.8	537.8
2.5°	540.0	538.2	533.0	537.8	536.9
5°	537.8	535.6	530.4	534.3	533.4
7.5°	533.9	531.7	525.2	527.8	526.5
10°	528.6	525.6	517.7	518.2	516.0
12.5°	521.2	517.7	507.7	507.3	504.7
15°	512.9	508.1	495.9	493.8	490.7
17.5°	502.9	497.7	482.4	478.1	473.7
20°	491.6	484.6	468.0	462.3	457.1
22.5°	478.9	470.6	452.8	445.3	440.5
25°	466.7	455.8	435.7	426.6	421.8
27.5°	451.9	440.1	418.3	406.1	398.7
30°	436.6	423.5	399.1	384.3	377.3
32.5°	421.3	406.1	379.9	363.3	355.9
35°	403.9	388.2	361.2	342.4	334.5
37.5°	386.5	369.4	341.1	320.2	310.6
40°	369.9	350.7	319.7	297.0	287.0
42.5°	351.1	331.9	299.7	274.4	265.6
45°	331.9	312.3	278.7	253.9	243.4
47.5°	313.2	291.4	258.2	231.2	222.0
50°	292.2	271.7	236.4	209.4	199.3
52.5°	273.5	250.8	215.9	187.6	178.8
55°	252.1	230.7	193.7	168.4	159.6
57.5°	232.9	209.8	172.3	148.3	140.9
60°	212.9	188.9	152.7	129.1	121.7
62.5°	192.8	168.8	132.6	110.8	102.9
65°	172.3	148.3	114.3	92.9	88.1
67.5°	151.8	127.4	94.2	78.1	72.8
70°	131.7	108.2	77.6	62.4	57.6
72.5°	111.7	88.5	61.5	49.7	48.4
75°	91.2	70.2	46.2	41.9	41.0
77.5°	72.4	53.2	36.2	33.6	32.7
80°	54.5	36.6	27.5	26.2	25.3
82.5°	37.5	22.7	19.6	18.3	18.3
85°	23.1	13.5	12.2	11.3	11.3
87.5°	10.5	5.7	5.7	5.2	4.8
90°	1.2	13.6	29.7	34.6	37.1
92.5°	28.4	21.0	32.2	40.8	42.1
95°	75.5	24.7	38.3	47.0	47.0
97.5°	137.3	102.7	39.6	49.5	50.7
100°	209.0	233.8	40.8	50.7	52.0
102.5°	290.7	306.8	91.5	50.7	53.2
105°	368.6	382.2	270.9	52.0	54.4
107.5°	451.5	462.6	481.2	290.7	128.6
110°	534.4	544.3	557.9	517.0	340.2

TEST NUMBER: P1031133

CATALOG NUMBER: S123RDIW-B340D1320UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	613.5	622.2	635.8	646.9	644.4
115°	691.5	698.9	710.0	722.4	727.3
117.5°	768.1	776.8	783.0	792.9	794.1
120°	838.6	849.8	853.5	863.4	863.4
122.5°	910.4	919.1	924.0	930.2	931.4
125°	974.7	984.6	989.6	992.0	994.5
127.5°	1039.0	1048.9	1055.1	1058.8	1056.4
130°	1098.4	1108.3	1113.3	1118.2	1115.7
132.5°	1155.3	1165.2	1168.9	1173.9	1170.2
135°	1213.4	1220.9	1225.8	1229.5	1225.8
137.5°	1262.9	1272.8	1275.3	1281.5	1279.0
140°	1312.4	1319.8	1323.5	1328.5	1326.0
142.5°	1358.2	1365.6	1369.3	1373.0	1369.3
145°	1400.2	1408.9	1411.4	1413.8	1413.8
147.5°	1441.0	1447.2	1449.7	1452.2	1446.0
150°	1478.1	1481.9	1484.3	1486.8	1483.1
152.5°	1511.5	1512.8	1514.0	1519.0	1512.8
155°	1542.5	1540.0	1541.2	1547.4	1540.0
157.5°	1567.2	1567.2	1566.0	1573.4	1563.5
160°	1589.5	1588.2	1587.0	1594.4	1585.8
162.5°	1610.5	1606.8	1605.6	1614.2	1606.8
165°	1626.6	1622.9	1621.6	1631.5	1622.9
167.5°	1640.2	1635.2	1635.2	1645.1	1635.2
170°	1651.3	1646.4	1646.4	1656.3	1646.4
172.5°	1658.7	1652.6	1653.8	1663.7	1652.6
175°	1664.9	1658.7	1660.0	1668.6	1658.7
177.5°	1667.4	1661.2	1662.5	1672.3	1660.0
180°	1664.9	1664.9	1664.9	1664.9	1664.9

(END OF REPORT)