

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031626

Luminaire Tested: S123DIW-B340D1535UB35-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031626
REPORT IS A COMBINATION OF REPORTS P991357 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123DIW-B340D1535UB35-4F0-XX-W2A-F1
Description: Define 3 Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6803.0 lumens
Efficiency: N/A
Efficacy: 104.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.18 / 1.3
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 65.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031626

CATALOG NUMBER: S123DIW-B340D1535UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1031626

CATALOG NUMBER: S123DIW-B340D1535UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	88	88	88	88	67	67	67	47	47	47	29	29	29
1	91	87	83	80	80	77	74	71	58	56	55	41	40	39	25	25	24
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20
3	76	67	60	54	66	59	53	49	45	41	38	32	29	27	20	18	17
4	69	59	51	46	61	52	46	41	40	35	32	28	26	23	18	16	15
5	63	52	44	39	56	46	40	35	35	31	27	25	22	20	16	14	13
6	58	47	39	33	51	41	35	30	32	27	24	23	20	17	14	13	11
7	53	42	34	29	47	37	31	26	29	24	21	21	18	15	13	11	10
8	49	38	30	25	44	34	27	23	26	21	18	19	16	14	12	10	9
9	46	34	27	22	41	31	25	20	24	19	16	17	14	12	11	9	8
10	43	31	24	20	38	28	22	18	22	17	14	16	13	11	10	8	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5704	5704	5704
5°	5717	5506	5499
10°	5667	5321	5265
15°	5588	5127	5012
20°	5497	4911	4761
25°	5380	4684	4492
30°	5253	4449	4210
35°	5119	4209	3928
40°	4978	3957	3653
45°	4824	3712	3364
50°	4667	3438	3074
55°	4466	3153	2780
60°	4259	2839	2468
65°	4064	2498	2143
70°	3784	2120	1762
75°	3378	1680	1368
80°	2921	1180	967
85°	2276	635	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4824 cd/sqm

TEST NUMBER: P1031626

CATALOG NUMBER: S123DIW-B340D1535UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.0	0.7
10°-20°	141.0	2.1
20°-30°	208.3	3.1
30°-40°	243.3	3.6
40°-50°	244.6	3.6
50°-60°	214.8	3.2
60°-70°	160.0	2.4
70°-80°	91.1	1.3
80°-90°	30.0	0.4
90°-100°	125.9	1.9
100°-110°	381.1	5.6
110°-120°	648.8	9.5
120°-130°	853.5	12.5
130°-140°	959.4	14.1
140°-150°	943.2	13.9
150°-160°	794.1	11.7
160°-170°	528.7	7.8
170°-180°	185.1	2.7
0°-30°	399.3	5.9
0°-40°	642.6	9.4
0°-60°	1102.0	16.2
0°-90°	1383.1	20.3
90°-120°	1155.8	17.0
90°-150°	3912.0	57.5
90°-180°	5420.0	79.7
0°-180°	6803.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	530	530	530	530	530	
5°	530	528	523	528	527	50
15°	505	503	497	501	498	142
25°	458	456	450	450	449	211
35°	396	394	388	385	383	248
45°	325	323	317	312	309	251
55°	246	246	240	235	233	221
65°	168	166	161	158	156	166
75°	89	87	86	83	82	95
85°	24	23	23	22	22	25
90°	2	17	37	43	46	8
95°	91	101	114	120	120	100
105°	346	349	363	363	366	370
115°	653	658	655	656	655	646
125°	956	960	957	951	945	852
135°	1240	1249	1248	1242	1238	955
145°	1504	1507	1512	1510	1504	940
155°	1722	1722	1724	1730	1719	793
165°	1876	1872	1872	1881	1870	529
175°	1951	1945	1945	1954	1944	185
180°	1956	1956	1956	1956	1956	

TEST NUMBER: P1031626

CATALOG NUMBER: S123DIW-B340D1535UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	529.9	529.9	529.9	529.9	529.9
2.5°	532.1	530.3	525.3	529.9	529.4
5°	530.3	528.0	523.0	527.6	526.7
7.5°	526.2	523.9	518.9	523.0	522.6
10°	520.8	518.5	512.6	516.7	515.7
12.5°	513.5	511.6	506.2	508.9	508.5
15°	504.8	503.0	497.1	500.7	498.0
17.5°	495.2	493.0	487.0	489.8	488.9
20°	484.3	481.6	475.6	477.5	476.1
22.5°	472.0	469.3	463.3	464.7	462.9
25°	458.3	455.6	449.7	450.1	448.8
27.5°	444.2	441.5	435.1	435.6	434.2
30°	428.7	426.4	420.1	420.1	416.9
32.5°	413.2	410.0	405.5	402.3	400.9
35°	396.4	393.6	387.7	385.0	382.7
37.5°	379.5	375.9	369.9	366.8	365.4
40°	361.7	359.0	352.6	349.0	347.2
42.5°	344.0	340.8	334.4	330.8	328.9
45°	324.8	323.0	317.1	311.6	309.4
47.5°	306.2	303.4	298.0	292.5	290.7
50°	287.0	284.8	278.8	273.8	271.1
52.5°	267.0	265.6	259.2	255.1	252.4
55°	246.5	246.0	240.1	235.1	232.8
57.5°	227.3	225.5	221.0	216.4	213.7
60°	206.4	205.9	200.5	196.4	194.1
62.5°	187.7	186.3	180.9	176.8	175.4
65°	168.1	165.8	161.3	157.6	156.3
67.5°	147.2	145.3	141.7	138.5	136.7
70°	128.5	125.7	123.0	119.8	117.5
72.5°	108.9	107.1	103.9	101.1	100.2
75°	88.8	87.0	85.7	83.4	82.0
77.5°	71.1	70.2	68.3	66.5	66.5
80°	53.8	52.4	51.5	51.0	51.0
82.5°	36.9	36.9	36.9	36.0	35.5
85°	23.7	22.8	22.8	21.9	21.9
87.5°	11.8	10.5	10.0	9.6	9.6
90°	1.5	16.9	36.9	43.0	46.1
92.5°	46.1	55.3	64.5	69.1	66.1
95°	90.7	101.4	113.7	119.9	119.9
97.5°	149.0	156.7	165.9	173.6	172.1
100°	209.0	218.2	225.9	230.5	233.6
102.5°	278.1	282.7	293.5	298.1	296.6
105°	345.7	348.8	362.6	362.6	365.7
107.5°	425.6	427.2	433.3	437.9	436.4
110°	499.4	502.5	505.5	511.7	508.6

TEST NUMBER: P1031626

CATALOG NUMBER: S123DIW-B340D1535UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	576.2	577.7	577.7	585.4	585.4
115°	653.0	657.7	654.6	656.1	654.6
117.5°	731.4	732.9	729.9	729.9	725.3
120°	803.6	812.8	805.2	803.6	800.6
122.5°	878.9	885.1	882.0	877.4	872.8
125°	955.7	960.4	957.3	951.1	945.0
127.5°	1026.4	1035.6	1032.6	1023.4	1017.2
130°	1097.1	1109.4	1104.8	1098.6	1087.9
132.5°	1167.8	1180.1	1177.0	1169.3	1161.6
135°	1240.0	1249.2	1247.7	1241.5	1238.5
137.5°	1306.1	1313.8	1318.4	1310.7	1306.1
140°	1375.2	1382.9	1384.4	1382.9	1372.2
142.5°	1438.2	1445.9	1449.0	1447.4	1439.8
145°	1504.3	1507.4	1512.0	1510.4	1504.3
147.5°	1561.2	1567.3	1571.9	1571.9	1562.7
150°	1621.1	1624.2	1627.2	1627.2	1618.0
152.5°	1670.3	1674.9	1676.4	1679.5	1671.8
155°	1722.5	1722.5	1724.0	1730.2	1719.4
157.5°	1767.1	1765.5	1767.1	1773.2	1764.0
160°	1808.5	1805.5	1805.5	1813.2	1807.0
162.5°	1845.4	1840.8	1842.3	1850.0	1839.3
165°	1876.2	1871.5	1871.5	1880.8	1870.0
167.5°	1902.3	1896.1	1897.7	1906.9	1897.7
170°	1923.8	1917.6	1917.6	1928.4	1917.6
172.5°	1940.7	1934.5	1934.5	1943.8	1933.0
175°	1951.4	1945.3	1945.3	1954.5	1943.8
177.5°	1957.6	1951.4	1951.4	1960.7	1949.9
180°	1956.1	1956.1	1956.1	1956.1	1956.1

(END OF REPORT)