

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031149

Luminaire Tested: S123RDIW-B340D460UB2750-4F0-XX-W2A-F1_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031149
REPORT IS A COMBINATION OF REPORTS P994304 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D460UB2750-4F0-XX-W2A-F1_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2770.0 lumens
Efficiency: N/A
Efficacy: 105.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031149

CATALOG NUMBER: S123RDIW-B340D460UB2750-4F0-XX-W2A-F1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031149

CATALOG NUMBER: S123RDIW-B340D460UB2750-4F0-XX-W2A-F1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	85	88	85	82	79	70	68	66	57	56	54	45	44	43
2	88	81	75	70	81	74	69	65	62	58	55	51	48	46	40	38	37
3	81	72	64	59	74	66	60	55	55	50	47	45	42	39	36	34	32
4	74	63	56	50	67	58	52	47	49	44	40	40	37	34	32	30	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	29	26	24
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	26	24	21
7	58	46	38	33	53	42	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	21	18	15
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5789	5789	5789
5°	5798	5584	5569
10°	5752	5374	5268
15°	5678	5114	4939
20°	5580	4832	4571
25°	5479	4539	4222
30°	5349	4227	3810
35°	5216	3921	3434
40°	5091	3588	3019
45°	4929	3262	2647
50°	4752	2915	2260
55°	4568	2543	1906
60°	4393	2162	1548
65°	4165	1770	1208
70°	3878	1338	864
75°	3469	906	684
80°	2959	630	480
85°	2219	340	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4929 cd/sqm

TEST NUMBER: P1031149

CATALOG NUMBER: S123RDIW-B340D460UB2750-4F0-XX-W2A-F1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	1.8
10°-20°	140.6	5.1
20°-30°	202.5	7.3
30°-40°	228.0	8.2
40°-50°	218.1	7.9
50°-60°	178.6	6.4
60°-70°	120.4	4.3
70°-80°	60.4	2.2
80°-90°	17.0	0.6
90°-100°	36.1	1.3
100°-110°	109.3	3.9
110°-120°	186.0	6.7
120°-130°	244.7	8.8
130°-140°	275.0	9.9
140°-150°	270.4	9.8
150°-160°	227.7	8.2
160°-170°	151.6	5.5
170°-180°	53.1	1.9
0°-30°	393.7	14.2
0°-40°	621.7	22.4
0°-60°	1018.4	36.8
0°-90°	1216.2	43.9
90°-120°	331.4	12.0
90°-150°	1121.5	40.5
90°-180°	1554.0	56.1
0°-180°	2770.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	538	538	538	538	538	
5°	538	536	530	534	533	51
15°	513	508	496	494	491	145
25°	467	456	436	427	422	215
35°	404	388	361	342	334	253
45°	332	312	279	254	243	256
55°	252	231	194	168	160	226
65°	172	148	114	93	88	171
75°	91	70	46	42	41	97
85°	23	14	12	11	11	25
90°	0	5	11	12	13	3
95°	26	29	33	34	34	29
105°	99	100	104	104	105	106
115°	187	188	188	188	188	185
125°	274	275	274	273	271	244
135°	356	358	358	356	355	274
145°	431	432	434	433	431	269
155°	494	494	494	496	493	227
165°	538	536	536	539	536	152
175°	560	558	558	560	557	53
180°	561	561	561	561	561	

TEST NUMBER: P1031149

CATALOG NUMBER: S123RDIW-B340D460UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	537.8	537.8	537.8	537.8	537.8
2.5°	540.0	538.2	533.0	537.8	536.9
5°	537.8	535.6	530.4	534.3	533.4
7.5°	533.9	531.7	525.2	527.8	526.5
10°	528.6	525.6	517.7	518.2	516.0
12.5°	521.2	517.7	507.7	507.3	504.7
15°	512.9	508.1	495.9	493.8	490.7
17.5°	502.9	497.7	482.4	478.1	473.7
20°	491.6	484.6	468.0	462.3	457.1
22.5°	478.9	470.6	452.8	445.3	440.5
25°	466.7	455.8	435.7	426.6	421.8
27.5°	451.9	440.1	418.3	406.1	398.7
30°	436.6	423.5	399.1	384.3	377.3
32.5°	421.3	406.1	379.9	363.3	355.9
35°	403.9	388.2	361.2	342.4	334.5
37.5°	386.5	369.4	341.1	320.2	310.6
40°	369.9	350.7	319.7	297.0	287.0
42.5°	351.1	331.9	299.7	274.4	265.6
45°	331.9	312.3	278.7	253.9	243.4
47.5°	313.2	291.4	258.2	231.2	222.0
50°	292.2	271.7	236.4	209.4	199.3
52.5°	273.5	250.8	215.9	187.6	178.8
55°	252.1	230.7	193.7	168.4	159.6
57.5°	232.9	209.8	172.3	148.3	140.9
60°	212.9	188.9	152.7	129.1	121.7
62.5°	192.8	168.8	132.6	110.8	102.9
65°	172.3	148.3	114.3	92.9	88.1
67.5°	151.8	127.4	94.2	78.1	72.8
70°	131.7	108.2	77.6	62.4	57.6
72.5°	111.7	88.5	61.5	49.7	48.4
75°	91.2	70.2	46.2	41.9	41.0
77.5°	72.4	53.2	36.2	33.6	32.7
80°	54.5	36.6	27.5	26.2	25.3
82.5°	37.5	22.7	19.6	18.3	18.3
85°	23.1	13.5	12.2	11.3	11.3
87.5°	10.5	5.7	5.7	5.2	4.8
90°	0.4	4.8	10.6	12.3	13.2
92.5°	13.2	15.9	18.5	19.8	18.9
95°	26.0	29.1	32.6	34.4	34.4
97.5°	42.7	44.9	47.6	49.8	49.3
100°	59.9	62.6	64.8	66.1	67.0
102.5°	79.7	81.1	84.1	85.5	85.0
105°	99.1	100.0	104.0	104.0	104.8
107.5°	122.0	122.5	124.2	125.5	125.1
110°	143.2	144.0	144.9	146.7	145.8

TEST NUMBER: P1031149

CATALOG NUMBER: S123RDIW-B340D460UB2750-4F0-XX-W2A-F1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	165.2	165.6	165.6	167.8	167.8
115°	187.2	188.5	187.7	188.1	187.7
117.5°	209.7	210.1	209.2	209.2	207.9
120°	230.4	233.0	230.8	230.4	229.5
122.5°	252.0	253.7	252.9	251.5	250.2
125°	274.0	275.3	274.4	272.7	270.9
127.5°	294.3	296.9	296.0	293.4	291.6
130°	314.5	318.1	316.7	315.0	311.9
132.5°	334.8	338.3	337.4	335.2	333.0
135°	355.5	358.1	357.7	355.9	355.1
137.5°	374.4	376.6	378.0	375.8	374.4
140°	394.3	396.5	396.9	396.5	393.4
142.5°	412.3	414.5	415.4	415.0	412.8
145°	431.3	432.1	433.5	433.0	431.3
147.5°	447.6	449.3	450.6	450.6	448.0
150°	464.7	465.6	466.5	466.5	463.9
152.5°	478.8	480.2	480.6	481.5	479.3
155°	493.8	493.8	494.3	496.0	492.9
157.5°	506.6	506.2	506.6	508.4	505.7
160°	518.5	517.6	517.6	519.8	518.0
162.5°	529.1	527.7	528.2	530.4	527.3
165°	537.9	536.5	536.5	539.2	536.1
167.5°	545.4	543.6	544.0	546.7	544.0
170°	551.5	549.8	549.8	552.8	549.8
172.5°	556.4	554.6	554.6	557.3	554.2
175°	559.5	557.7	557.7	560.3	557.3
177.5°	561.2	559.5	559.5	562.1	559.0
180°	560.8	560.8	560.8	560.8	560.8

(END OF REPORT)