

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031153

Luminaire Tested: S123RDIW-B340D460UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031153
REPORT IS A COMBINATION OF REPORTS P994310 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D460UB2750-4F0-XX-W2A-F_5000K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3008.0 lumens
Efficiency: N/A
Efficacy: 114.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 26.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031153

CATALOG NUMBER: S123RDIW-B340D460UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1031153

CATALOG NUMBER: S123RDIW-B340D460UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47			40
1	96	92	88	85	87	84	81	78	69	67	65	55	53	52	42	41	40			35
2	88	80	74	70	80	73	68	64	61	57	54	49	46	44	37	36	34			29
3	80	71	64	58	73	65	59	54	54	49	45	43	40	37	33	31	30			25
4	73	63	55	49	66	58	51	46	48	43	39	39	35	32	30	28	26			22
5	67	56	48	42	61	51	45	39	43	38	34	35	31	28	27	25	23			19
6	62	50	42	37	56	46	39	34	39	33	29	31	28	25	25	22	20			17
7	57	45	38	32	52	42	35	30	35	30	26	29	25	22	23	20	18			15
8	53	41	34	28	48	38	31	27	32	27	23	26	22	19	21	18	16			14
9	49	38	30	25	45	35	28	24	29	24	21	24	20	18	19	16	14			12
10	46	34	27	23	42	32	26	21	27	22	19	22	19	16	18	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5789	5789	5789
5°	5798	5584	5569
10°	5752	5374	5268
15°	5678	5114	4939
20°	5580	4832	4571
25°	5479	4539	4222
30°	5349	4227	3810
35°	5216	3921	3434
40°	5091	3588	3019
45°	4929	3262	2647
50°	4752	2915	2260
55°	4568	2543	1906
60°	4393	2162	1548
65°	4165	1770	1208
70°	3878	1338	864
75°	3469	906	684
80°	2959	630	480
85°	2219	340	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4929 cd/sqm

TEST NUMBER: P1031153

CATALOG NUMBER: S123RDIW-B340D460UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	1.7
10°-20°	140.6	4.7
20°-30°	202.5	6.7
30°-40°	228.0	7.6
40°-50°	218.1	7.3
50°-60°	178.6	5.9
60°-70°	120.4	4.0
70°-80°	60.4	2.0
80°-90°	17.0	0.6
90°-100°	20.7	0.7
100°-110°	100.2	3.3
110°-120°	245.6	8.2
120°-130°	311.7	10.4
130°-140°	333.0	11.1
140°-150°	311.4	10.4
150°-160°	251.2	8.4
160°-170°	162.1	5.4
170°-180°	55.9	1.9
0°-30°	393.7	13.1
0°-40°	621.7	20.7
0°-60°	1018.4	33.9
0°-90°	1216.2	40.4
90°-120°	366.5	12.2
90°-150°	1322.6	44.0
90°-180°	1792.0	59.6
0°-180°	3008.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	538	538	538	538	538	
5°	538	536	530	534	533	51
15°	513	508	496	494	491	145
25°	467	456	436	427	422	215
35°	404	388	361	342	334	253
45°	332	312	279	254	243	256
55°	252	231	194	168	160	226
65°	172	148	114	93	88	171
75°	91	70	46	42	41	97
85°	23	14	12	11	11	25
90°	0	5	10	12	13	3
95°	27	9	14	17	17	32
105°	130	135	96	18	19	138
115°	244	247	251	255	257	241
125°	344	348	349	350	351	307
135°	428	431	433	434	433	330
145°	494	497	498	499	499	309
155°	544	544	544	546	544	251
165°	574	573	572	576	573	162
175°	588	586	586	589	586	56
180°	588	588	588	588	588	

TEST NUMBER: P1031153

CATALOG NUMBER: S123RDIW-B340D460UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	537.8	537.8	537.8	537.8	537.8
2.5°	540.0	538.2	533.0	537.8	536.9
5°	537.8	535.6	530.4	534.3	533.4
7.5°	533.9	531.7	525.2	527.8	526.5
10°	528.6	525.6	517.7	518.2	516.0
12.5°	521.2	517.7	507.7	507.3	504.7
15°	512.9	508.1	495.9	493.8	490.7
17.5°	502.9	497.7	482.4	478.1	473.7
20°	491.6	484.6	468.0	462.3	457.1
22.5°	478.9	470.6	452.8	445.3	440.5
25°	466.7	455.8	435.7	426.6	421.8
27.5°	451.9	440.1	418.3	406.1	398.7
30°	436.6	423.5	399.1	384.3	377.3
32.5°	421.3	406.1	379.9	363.3	355.9
35°	403.9	388.2	361.2	342.4	334.5
37.5°	386.5	369.4	341.1	320.2	310.6
40°	369.9	350.7	319.7	297.0	287.0
42.5°	351.1	331.9	299.7	274.4	265.6
45°	331.9	312.3	278.7	253.9	243.4
47.5°	313.2	291.4	258.2	231.2	222.0
50°	292.2	271.7	236.4	209.4	199.3
52.5°	273.5	250.8	215.9	187.6	178.8
55°	252.1	230.7	193.7	168.4	159.6
57.5°	232.9	209.8	172.3	148.3	140.9
60°	212.9	188.9	152.7	129.1	121.7
62.5°	192.8	168.8	132.6	110.8	102.9
65°	172.3	148.3	114.3	92.9	88.1
67.5°	151.8	127.4	94.2	78.1	72.8
70°	131.7	108.2	77.6	62.4	57.6
72.5°	111.7	88.5	61.5	49.7	48.4
75°	91.2	70.2	46.2	41.9	41.0
77.5°	72.4	53.2	36.2	33.6	32.7
80°	54.5	36.6	27.5	26.2	25.3
82.5°	37.5	22.7	19.6	18.3	18.3
85°	23.1	13.5	12.2	11.3	11.3
87.5°	10.5	5.7	5.7	5.2	4.8
90°	0.4	4.8	10.5	12.2	13.1
92.5°	10.0	7.4	11.4	14.4	14.8
95°	26.6	8.7	13.5	16.6	16.6
97.5°	48.5	36.2	14.0	17.5	17.9
100°	73.8	82.5	14.4	17.9	18.3
102.5°	102.6	108.3	32.3	17.9	18.8
105°	130.1	134.9	95.6	18.3	19.2
107.5°	159.4	163.3	169.9	102.6	45.4
110°	188.6	192.1	196.9	182.5	120.1

TEST NUMBER: P1031153

CATALOG NUMBER: S123RDIW-B340D460UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	216.6	219.6	224.4	228.4	227.5
115°	244.1	246.7	250.6	255.0	256.8
117.5°	271.2	274.2	276.4	279.9	280.3
120°	296.1	300.0	301.3	304.8	304.8
122.5°	321.4	324.4	326.2	328.4	328.8
125°	344.1	347.6	349.3	350.2	351.1
127.5°	366.8	370.3	372.5	373.8	372.9
130°	387.8	391.3	393.0	394.7	393.9
132.5°	407.8	411.3	412.7	414.4	413.1
135°	428.4	431.0	432.7	434.0	432.7
137.5°	445.8	449.3	450.2	452.4	451.5
140°	463.3	465.9	467.2	469.0	468.1
142.5°	479.5	482.1	483.4	484.7	483.4
145°	494.3	497.4	498.2	499.1	499.1
147.5°	508.7	510.9	511.8	512.6	510.5
150°	521.8	523.1	524.0	524.9	523.6
152.5°	533.6	534.0	534.5	536.2	534.0
155°	544.5	543.7	544.1	546.3	543.7
157.5°	553.3	553.3	552.8	555.4	551.9
160°	561.1	560.7	560.2	562.9	559.8
162.5°	568.5	567.2	566.8	569.9	567.2
165°	574.2	572.9	572.5	576.0	572.9
167.5°	579.0	577.3	577.3	580.8	577.3
170°	583.0	581.2	581.2	584.7	581.2
172.5°	585.6	583.4	583.8	587.3	583.4
175°	587.8	585.6	586.0	589.1	585.6
177.5°	588.6	586.4	586.9	590.4	586.0
180°	587.8	587.8	587.8	587.8	587.8

(END OF REPORT)