

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031162

Luminaire Tested: S123RDIW-B340D755UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031162
REPORT IS A COMBINATION OF REPORTS P994352 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B340D755UB2750-4F0-XX-W2A-F_3500K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4356.0 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 36.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031162

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1031162

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	37	37	37
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	32
2	85	78	72	67	76	70	65	61	55	52	49	42	40	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	41	37	34	32	26	24	23
4	71	61	53	48	63	55	48	43	44	39	35	33	30	28	23	21	20
5	65	54	46	41	58	49	42	37	39	34	30	30	26	24	21	19	17
6	60	48	41	35	54	44	37	32	35	30	27	27	23	21	19	17	15
7	55	44	36	31	50	40	33	28	32	27	23	24	21	18	18	15	14
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	16	14	12
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	15	13	11
10	44	33	26	21	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6046	6046	6046
5°	6056	5833	5817
10°	6008	5613	5502
15°	5930	5342	5158
20°	5828	5047	4774
25°	5723	4741	4409
30°	5587	4415	3979
35°	5449	4095	3587
40°	5316	3747	3154
45°	5149	3407	2764
50°	4963	3044	2361
55°	4771	2656	1991
60°	4587	2257	1616
65°	4349	1849	1261
70°	4052	1398	901
75°	3621	947	714
80°	3089	658	501
85°	2315	356	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5149 cd/sqm

TEST NUMBER: P1031162

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.8	1.2
10°-20°	146.9	3.4
20°-30°	211.5	4.9
30°-40°	238.2	5.5
40°-50°	227.8	5.2
50°-60°	186.5	4.3
60°-70°	125.7	2.9
70°-80°	63.1	1.4
80°-90°	18.5	0.4
90°-100°	35.7	0.8
100°-110°	172.5	4.0
110°-120°	422.8	9.7
120°-130°	536.7	12.3
130°-140°	573.4	13.2
140°-150°	536.2	12.3
150°-160°	432.5	9.9
160°-170°	279.1	6.4
170°-180°	96.2	2.2
0°-30°	411.2	9.4
0°-40°	649.4	14.9
0°-60°	1063.7	24.4
0°-90°	1271.0	29.2
90°-120°	631.0	14.5
90°-150°	2277.3	52.3
90°-180°	3085.0	70.8
0°-180°	4356.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	562	562	562	562	562	
5°	562	559	554	558	557	53
15°	536	531	518	516	512	151
25°	488	476	455	446	440	224
35°	422	406	377	358	349	264
45°	347	326	291	265	254	268
55°	263	241	202	176	167	236
65°	180	155	119	97	92	178
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	8	18	21	23	4
95°	46	15	23	29	29	55
105°	224	232	165	32	33	238
115°	420	425	432	439	442	415
125°	592	598	601	603	604	529
135°	738	742	745	747	745	568
145°	851	856	858	859	859	533
155°	938	936	937	940	936	432
165°	989	986	986	992	986	279
175°	1012	1008	1009	1014	1008	96
180°	1012	1012	1012	1012	1012	

TEST NUMBER: P1031162

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	561.7	561.7	561.7	561.7	561.7
2.5°	564.0	562.2	556.7	561.7	560.8
5°	561.7	559.4	554.0	558.1	557.2
7.5°	557.6	555.3	548.5	551.2	549.9
10°	552.1	549.0	540.8	541.2	538.9
12.5°	544.4	540.8	530.3	529.8	527.1
15°	535.7	530.7	518.0	515.7	512.5
17.5°	525.3	519.8	503.9	499.3	494.7
20°	513.4	506.1	488.8	482.9	477.4
22.5°	500.2	491.6	472.9	465.1	460.1
25°	487.5	476.1	455.1	445.5	440.5
27.5°	472.0	459.7	436.9	424.1	416.4
30°	456.0	442.4	416.8	401.4	394.1
32.5°	440.1	424.1	396.8	379.5	371.7
35°	421.9	405.5	377.2	357.6	349.4
37.5°	403.6	385.9	356.3	334.4	324.4
40°	386.3	366.3	333.9	310.2	299.8
42.5°	366.7	346.7	313.0	286.5	277.4
45°	346.7	326.2	291.1	265.1	254.2
47.5°	327.1	304.3	269.7	241.4	231.9
50°	305.2	283.8	246.9	218.7	208.2
52.5°	285.6	261.9	225.5	195.9	186.8
55°	263.3	241.0	202.3	175.8	166.7
57.5°	243.3	219.1	179.9	154.9	147.1
60°	222.3	197.3	159.4	134.8	127.1
62.5°	201.4	176.3	138.5	115.7	107.5
65°	179.9	154.9	119.4	97.0	92.0
67.5°	158.5	133.0	98.4	81.5	76.1
70°	137.6	113.0	81.1	65.1	60.1
72.5°	116.6	92.5	64.2	51.9	50.6
75°	95.2	73.3	48.3	43.7	42.8
77.5°	75.6	55.6	37.8	35.1	34.2
80°	56.9	38.3	28.7	27.3	26.4
82.5°	39.2	23.7	20.5	19.1	19.1
85°	24.1	14.1	12.8	11.8	11.8
87.5°	10.9	5.9	5.9	5.5	5.0
90°	0.8	8.3	18.0	21.1	22.6
92.5°	17.3	12.8	19.5	24.8	25.6
95°	45.9	15.0	23.3	28.6	28.6
97.5°	83.5	62.4	24.1	30.1	30.8
100°	127.1	142.1	24.8	30.8	31.6
102.5°	176.7	186.4	55.6	30.8	32.3
105°	224.0	232.3	164.6	31.6	33.1
107.5°	274.4	281.2	292.5	176.7	78.2
110°	324.8	330.8	339.1	314.3	206.7

TEST NUMBER: P1031162

CATALOG NUMBER: S123RDIW-B340D755UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.9	378.2	386.4	393.2	391.7
115°	420.3	424.8	431.5	439.1	442.1
117.5°	466.9	472.1	475.9	481.9	482.7
120°	509.7	516.5	518.7	524.8	524.8
122.5°	553.3	558.6	561.6	565.4	566.1
125°	592.4	598.4	601.4	603.0	604.5
127.5°	631.5	637.5	641.3	643.6	642.0
130°	667.6	673.6	676.6	679.6	678.1
132.5°	702.2	708.2	710.5	713.5	711.2
135°	737.5	742.0	745.0	747.3	745.0
137.5°	767.6	773.6	775.1	778.9	777.4
140°	797.7	802.2	804.4	807.4	805.9
142.5°	825.5	830.0	832.3	834.5	832.3
145°	851.1	856.3	857.8	859.3	859.3
147.5°	875.9	879.6	881.1	882.6	878.9
150°	898.4	900.7	902.2	903.7	901.4
152.5°	918.7	919.5	920.2	923.2	919.5
155°	937.5	936.0	936.8	940.5	936.0
157.5°	952.5	952.5	951.8	956.3	950.3
160°	966.1	965.3	964.6	969.1	963.8
162.5°	978.9	976.6	975.9	981.1	976.6
165°	988.6	986.4	985.6	991.6	986.4
167.5°	996.9	993.9	993.9	999.9	993.9
170°	1003.7	1000.7	1000.7	1006.7	1000.7
172.5°	1008.2	1004.4	1005.2	1011.2	1004.4
175°	1011.9	1008.2	1008.9	1014.2	1008.2
177.5°	1013.4	1009.7	1010.4	1016.4	1008.9
180°	1011.9	1011.9	1011.9	1011.9	1011.9

(END OF REPORT)