

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1031190

Luminaire Tested: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_2700K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1031190
REPORT IS A COMBINATION OF REPORTS P994482 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_2700K
Description: Define 3 Regressed Direct/Indirect Wall Mount with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8282.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 76.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1031190

CATALOG NUMBER: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1031190

CATALOG NUMBER: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	70	70	70	51	51	51	34	34	34
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	29	29
2	84	77	71	67	75	69	64	60	54	50	48	40	38	36	27	25	24
3	77	68	61	56	68	61	55	50	47	43	40	35	33	30	24	22	21
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18
5	64	53	46	40	57	48	41	37	38	33	29	28	25	23	19	17	16
6	59	48	40	35	53	43	36	32	34	29	26	25	22	20	17	15	14
7	55	43	36	30	49	39	32	28	31	26	22	23	20	17	16	14	12
8	51	39	32	27	45	35	29	24	28	23	20	21	18	15	15	13	11
9	47	35	28	24	42	32	26	22	25	21	18	19	16	14	13	11	10
10	44	32	26	21	39	29	23	19	23	19	16	18	15	12	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10038	10038	10038
5°	10055	9684	9658
10°	9977	9319	9136
15°	9846	8869	8564
20°	9677	8380	7926
25°	9501	7871	7321
30°	9277	7330	6607
35°	9045	6799	5956
40°	8827	6221	5236
45°	8548	5657	4590
50°	8241	5055	3920
55°	7922	4409	3306
60°	7616	3748	2683
65°	7223	3070	2095
70°	6726	2320	1496
75°	6014	1572	1186
80°	5130	1093	833
85°	3852	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8548 cd/sqm

TEST NUMBER: P1031190

CATALOG NUMBER: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.1
10°-20°	243.9	2.9
20°-30°	351.2	4.2
30°-40°	395.5	4.8
40°-50°	378.3	4.6
50°-60°	309.7	3.7
60°-70°	208.8	2.5
70°-80°	104.7	1.3
80°-90°	31.4	0.4
90°-100°	71.4	0.9
100°-110°	345.1	4.2
110°-120°	845.7	10.2
120°-130°	1073.6	13.0
130°-140°	1146.9	13.8
140°-150°	1072.5	12.9
150°-160°	865.1	10.4
160°-170°	558.3	6.7
170°-180°	192.4	2.3
0°-30°	682.7	8.2
0°-40°	1078.2	13.0
0°-60°	1766.1	21.3
0°-90°	2111.0	25.5
90°-120°	1262.2	15.2
90°-150°	4555.2	55.0
90°-180°	6171.0	74.5
0°-180°	8282.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	933	933	933	933	933	
5°	933	929	920	927	925	88
15°	890	881	860	856	851	251
25°	809	790	756	740	731	372
35°	700	673	626	594	580	438
45°	576	542	483	440	422	444
55°	437	400	336	292	277	392
65°	299	257	198	161	153	296
75°	158	122	80	73	71	168
85°	40	23	21	20	20	44
90°	2	16	36	42	45	8
95°	92	30	47	57	57	110
105°	448	465	329	63	66	475
115°	841	850	863	878	884	830
125°	1185	1197	1203	1206	1209	1059
135°	1475	1484	1490	1495	1490	1136
145°	1702	1713	1716	1719	1719	1066
155°	1875	1872	1874	1881	1872	864
165°	1978	1973	1972	1984	1973	559
175°	2024	2017	2018	2029	2017	193
180°	2024	2024	2024	2024	2024	

TEST NUMBER: P1031190

CATALOG NUMBER: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	932.6	932.6	932.6	932.6	932.6
2.5°	936.4	933.4	924.3	932.6	931.1
5°	932.6	928.9	919.8	926.6	925.1
7.5°	925.8	922.1	910.7	915.2	913.0
10°	916.8	911.5	897.8	898.6	894.8
12.5°	903.9	897.8	880.4	879.7	875.2
15°	889.5	881.2	860.0	856.2	850.9
17.5°	872.1	863.1	836.6	829.0	821.4
20°	852.5	840.4	811.6	801.8	792.7
22.5°	830.5	816.2	785.1	772.3	764.0
25°	809.3	790.4	755.6	739.8	731.4
27.5°	783.6	763.2	725.4	704.2	691.3
30°	757.2	734.5	692.1	666.4	654.3
32.5°	730.7	704.2	658.8	630.1	617.2
35°	700.4	673.2	626.3	593.8	580.2
37.5°	670.2	640.7	591.5	555.2	538.6
40°	641.4	608.1	554.4	515.1	497.7
42.5°	608.9	575.6	519.6	475.8	460.6
45°	575.6	541.6	483.3	440.2	422.1
47.5°	543.1	505.3	447.8	400.9	385.0
50°	506.8	471.2	410.0	363.1	345.7
52.5°	474.3	434.9	374.4	325.3	310.1
55°	437.2	400.1	335.8	292.0	276.8
57.5°	403.9	363.8	298.8	257.2	244.3
60°	369.1	327.5	264.7	223.9	211.0
62.5°	334.3	292.7	229.9	192.1	178.5
65°	298.8	257.2	198.2	161.1	152.8
67.5°	263.2	220.9	163.4	135.4	126.3
70°	228.4	187.6	134.6	108.2	99.8
72.5°	193.6	153.5	106.7	86.2	84.0
75°	158.1	121.8	80.2	72.6	71.1
77.5°	125.6	92.3	62.8	58.2	56.7
80°	94.5	63.5	47.7	45.4	43.9
82.5°	65.1	39.3	34.0	31.8	31.8
85°	40.1	23.4	21.2	19.7	19.7
87.5°	18.2	9.8	9.8	9.1	8.3
90°	1.5	16.5	36.1	42.1	45.1
92.5°	34.6	25.6	39.1	49.6	51.1
95°	91.7	30.1	46.6	57.1	57.1
97.5°	166.9	124.8	48.1	60.2	61.7
100°	254.2	284.2	49.6	61.7	63.2
102.5°	353.4	373.0	111.3	61.7	64.7
105°	448.2	464.7	329.3	63.2	66.2
107.5°	548.9	562.4	585.0	353.4	156.4
110°	649.7	661.7	678.2	628.6	413.6

TEST NUMBER: P1031190

CATALOG NUMBER: S123RDIW-B560D1535UB2750-4F0-XX-W2A-F_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	745.9	756.4	773.0	786.5	783.5
115°	840.7	849.7	863.2	878.3	884.3
117.5°	933.9	944.4	951.9	964.0	965.5
120°	1019.6	1033.2	1037.7	1049.7	1049.7
122.5°	1106.8	1117.4	1123.4	1130.9	1132.4
125°	1185.0	1197.1	1203.1	1206.1	1209.1
127.5°	1263.2	1275.3	1282.8	1287.3	1284.3
130°	1335.4	1347.5	1353.5	1359.5	1356.5
132.5°	1404.6	1416.6	1421.2	1427.2	1422.7
135°	1475.3	1484.3	1490.3	1494.8	1490.3
137.5°	1535.4	1547.5	1550.5	1558.0	1555.0
140°	1595.6	1604.6	1609.1	1615.2	1612.1
142.5°	1651.2	1660.3	1664.8	1669.3	1664.8
145°	1702.4	1712.9	1715.9	1718.9	1718.9
147.5°	1752.0	1759.5	1762.5	1765.5	1758.0
150°	1797.1	1801.6	1804.6	1807.6	1803.1
152.5°	1837.7	1839.2	1840.7	1846.7	1839.2
155°	1875.3	1872.3	1873.8	1881.3	1872.3
157.5°	1905.4	1905.4	1903.9	1912.9	1900.9
160°	1932.5	1931.0	1929.5	1938.5	1928.0
162.5°	1958.0	1953.5	1952.0	1962.5	1953.5
165°	1977.6	1973.1	1971.6	1983.6	1973.1
167.5°	1994.1	1988.1	1988.1	2000.1	1988.1
170°	2007.7	2001.6	2001.6	2013.7	2001.6
172.5°	2016.7	2009.2	2010.7	2022.7	2009.2
175°	2024.2	2016.7	2018.2	2028.7	2016.7
177.5°	2027.2	2019.7	2021.2	2033.2	2018.2
180°	2024.2	2024.2	2024.2	2024.2	2024.2

(END OF REPORT)